

# Tantalum Surface Mount Capacitors

MIL-PRF (CWR Series)



One world. One KEMET.

Electronic Components  
**KEMET**  
CHARGED.®

| Table of Contents                              | Page |
|------------------------------------------------|------|
| Why Choose KEMET .....                         | 3    |
| T409 Series CWR09 Style MIL-PRF-55365/4 .....  | 5    |
| T419 Series CWR19 Style MIL-PRF-55365/11 ..... | 15   |
| T429 Series CWR29 Style MIL-PRF-55365/11 ..... | 26   |
| T492 Series CWR11 Style MIL-PRF-55365/8 .....  | 38   |
| Packaging Information .....                    | 48   |
| KEMET Corporation Sales Offices .....          | 53   |
| Other KEMET Resources .....                    | 54   |



## One world. One source. One KEMET.

When you partner with KEMET, our entire global organization provides you with the coordinated service you need. No bouncing from supplier to supplier. No endless phone calls and web browsing. We're your single, integrated source for electronic component solutions worldwide.

## Less hassles. More solutions.

Our commitment to product quality and on-time delivery has helped customers succeed for over 90 years. There's a reason KEMET components can be found in defense and aerospace equipment. Our reputation is built on a history of consistency, reliability and service.

## The "Easy-to-Buy-From" company.

KEMET offers a level of responsiveness that far surpasses any other supplier. Our passion for customer service is evident throughout our global sales organization, which offers localized support bolstered by our worldwide logistics capabilities. Whether you need rush samples, technical assistance, in-person consultation, accelerated custom design, design collaboration or prototype services, we have a solution.



## Made for you.

When you need custom products delivered on a tight schedule, you can trust KEMET. Get direct design consultation from global experts, who help you get the job done on time and within budget.

## Working for a better world.

KEMET is dedicated to economically, environmentally and socially sustainable development. We've adopted the Electronic Industry Code of Conduct (EICC) to address all aspects of corporate responsibility. Our manufacturing facilities have won numerous environmental excellence awards and recognitions, and our supply chain is certified. We believe doing the right thing is in everyone's interest.

## About KEMET.

KEMET Corporation is a leading global supplier of electronic components. We offer our customers the broadest selection of capacitor technologies in the industry across multiple dielectrics, along with an expanding range of electromechanical devices, and electromagnetic compatibility solutions. Our vision is to be the preferred supplier of electronic component solutions for customers demanding the highest standards of quality, delivery and service.

## Overview

The KEMET T409 Series is approved to MIL-PRF-55365/4 (CWR09) with Weibull failure rates of B level (0.1% failures per 1,000 hours), C level (0.01% failures per 1,000 hours), D level (0.001% failures per 1,000 hours), or T level (0.01% failures per 1,000 hours), Option C surge current, DPA, Radiographic

inspection, 100% visual inspection, DCL and ESR measurements within +3 standard deviations, and Group C inspection). This CWR09 product is a precision-molded device with compliant terminations and indelible laser marking. Tape and reeling per EIA 481-1 is standard.

## Benefits

- Established reliability options
- Taped and reeled per EIA 481-1
- Symmetrical, compliant terminations
- Laser-marked case
- 100% surge current test available on all case sizes
- Qualified to MIL-PRF-55365/4, Style CWR09
- Termination options B, C, H, K
- Weibull failure options B, C, D, and T
- Exponential failure rates M, P, R, S
- Voltage rating of 4 – 50 VDC
- Operating temperature range of -55°C to +125°C

## Applications

Typical applications include decoupling and filtering in Military and aerospace applications requiring CWR09 devices.



## Environmental Compliance

RoHS Compliant (6/6) according to Directive 2002/95/EC when ordered with 100% Sn Solder.



RoHS Compliant

## SPICE

For a detailed analysis of specific part numbers, please visit [www.kemet.com](http://www.kemet.com) for a free download of KEMET's SPICE software. The KEMET SPICE program is freeware intended to aid design engineers in analyzing the performance of these capacitors over frequency, temperature, ripple, and DC bias conditions.

## KEMET Ordering Information

| T               | 409                            | A                         | 225                                                                                    | K                                                 | 004                                                                                                          | A                                                                                                                                                                                                                                                           | H                                                                                                               | 4252                                                                                                                                       | 7280                                                                     |
|-----------------|--------------------------------|---------------------------|----------------------------------------------------------------------------------------|---------------------------------------------------|--------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------|
| Capacitor Class | Series                         | Case Size                 | Capacitance Code (pF)                                                                  | Capacitance Tolerance                             | Voltage                                                                                                      | Failure Rate/Design                                                                                                                                                                                                                                         | Lead Material                                                                                                   | Surge                                                                                                                                      | Packaging (C-Spec)                                                       |
| T = Tantalum    | CWR 09 Established Reliability | A, B, C, D, E, F, G, H, X | First two digits represent significant figures. Third digit specifies number of zeros. | J = $\pm 5\%$<br>K = $\pm 10\%$<br>M = $\pm 20\%$ | 004 = 4 V<br>006 = 6.3 V<br>010 = 10 V<br>015 = 15 V<br>020 = 20 V<br>025 = 25 V<br>035 = 35 V<br>050 = 50 V | Weibull<br>A = non-ER<br>B = (0.1%/1,000 hours)<br>C = (0.01%/1,000 hours)<br>D = (0.001%/1,000 hours)<br>T = (0.01%/1,000 hours)<br>Exponential<br>M = (1.0%/1,000 hours)<br>P = (0.1%/1,000 hours)<br>R = (0.01%/1,000 hours)<br>S = (0.001%/1,000 hours) | C = Hot Solder Dipped<br>H = Standard Solder Coated (SnPb 5% Pb minimum)<br>B = Gold Plated<br>K = Solder Fused | 4250 = 25°C after Weibull<br>4251 = -55°C and 85°C after Weibull<br>4252 = -55°C and 85°C before Weibull<br>TLVL = Weibull Grade Level "T" | Blank = 7" Reel<br>7280 = 13" Reel<br>7610 = Bag<br>7005 = Moisture bags |

## Defense MIL-PRF-55365/4 Ordering Information

| CWR09               | J                                                                                          | H                                                                                 | 105                                                                                    | K                                                 | C                                                                                                                                                                                                                                                                    | A                                                                                          |
|---------------------|--------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|---------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Capacitor Style     | Voltage                                                                                    | Termination Finish                                                                | Capacitance Code (pF)                                                                  | Capacitance Tolerance                             | Reliability Level                                                                                                                                                                                                                                                    | Surge Current Option                                                                       |
| Per MIL-PRF-55365/4 | C = 4 V<br>D = 6 V<br>F = 10 V<br>H = 15 V<br>J = 20 V<br>K = 25 V<br>M = 35 V<br>N = 50 V | B = Gold Plated<br>C = Hot solder dipped<br>H = Solder Plated<br>K = Solder fused | First two digits represent significant figures. Third digit specifies number of zeros. | J = $\pm 5\%$<br>K = $\pm 10\%$<br>M = $\pm 20\%$ | Weibull<br>A = non-ER<br>B = (0.1%/1,000 hours)<br>C = (0.01%/1,000 hours)<br>D = (0.001%/1,000 hours)<br>T = T Level* (0.01%/1,000 hours)<br>Exponential<br>M = (1.0%/1,000 hours)<br>P = (0.1%/1,000 hours)<br>R = (0.01%/1,000 hours)<br>S = (0.001%/1,000 hours) | A = +25°C after Weibull<br>B = -55°C +85°C after Weibull<br>C = -55°C +85°C before Weibull |

\* When T Level is ordered, no Surge Current Option is needed

## Performance Characteristics

| Item                    | Performance Characteristics                                |
|-------------------------|------------------------------------------------------------|
| Operating Temperature   | -55°C to 125°C                                             |
| Rated Capacitance Range | 0.1 – 100 $\mu$ F @ 120 Hz/25°C                            |
| Capacitance Tolerance   | J Tolerance (5%), K Tolerance (10%), M Tolerance (20%)     |
| Rated Voltage Range     | 4 – 50 V                                                   |
| DF (120 Hz)             | Refer to Part Number Electrical Specification Table        |
| ESR (100 kHz)           | Refer to Part Number Electrical Specification Table        |
| Leakage Current         | $\leq 0.01$ CV ( $\mu$ A) at rated voltage after 5 minutes |

## Qualification

| Test                                               | Condition                                                                                                              |       | Characteristics |                              |          |          |
|----------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|-------|-----------------|------------------------------|----------|----------|
| Endurance                                          | 85°C @ rated voltage, 2,000 hours<br>125°C @ 2/3 rated voltage, 2,000 hours                                            |       | Δ C/C           | Within ±10% of initial value |          |          |
|                                                    |                                                                                                                        |       | DF              | Within initial limits        |          |          |
|                                                    |                                                                                                                        |       | DCL             | Within 1.25 x initial limit  |          |          |
|                                                    |                                                                                                                        |       | ESR             | Within initial limits        |          |          |
| Storage Life                                       | 125°C @ 0 volts, 2,000 hours                                                                                           |       | Δ C/C           | Within ±10% of initial value |          |          |
|                                                    |                                                                                                                        |       | DF              | Within initial limits        |          |          |
|                                                    |                                                                                                                        |       | DCL             | Within 1.25 x initial limit  |          |          |
|                                                    |                                                                                                                        |       | ESR             | Within initial limits        |          |          |
| Thermal Shock                                      | MIL–STD–202, Method 107, Condition B, mounted,<br>-55°C to 125°C, 1,000 cycles                                         |       | Δ C/C           | Within ±5% of initial value  |          |          |
|                                                    |                                                                                                                        |       | DF              | Within initial limits        |          |          |
|                                                    |                                                                                                                        |       | DCL             | Within 1.25 x initial limit  |          |          |
|                                                    |                                                                                                                        |       | ESR             | Within initial limits        |          |          |
| Temperature Stability                              | Extreme temperature exposure at a succession of continuous steps at +25°C, -55°C, +25°C, +85°C, +125°C, +25°C          | Δ C/C | +25°C           | -55°C                        | +85°C    | +125°C   |
|                                                    |                                                                                                                        | IL*   | ±10%            | ±10%                         | ±10%     | ±20%     |
|                                                    |                                                                                                                        | DF    | IL              | IL                           | 1.5 x IL | 1.5 x IL |
|                                                    |                                                                                                                        | DCL   | IL              | n/a                          | 10 x IL  | 12 x IL  |
| Surge Voltage                                      | 25°C and 85°C, 1.32 x rated voltage 1,000 cycles<br>(125°C, 1.2 x rated voltage)                                       |       | Δ C/C           | Within ±5% of initial value  |          |          |
|                                                    |                                                                                                                        |       | DF              | Within initial limits        |          |          |
|                                                    |                                                                                                                        |       | DCL             | Within initial limits        |          |          |
|                                                    |                                                                                                                        |       | ESR             | Within initial limits        |          |          |
| Mechanical Shock/Vibration                         | MIL–STD–202, Method 213, Condition I, 100 G peak<br>MIL–STD–202, Method 204, Condition D, 10 Hz to 2,000 Hz, 20 G peak |       | Δ C/C           | Within ±10% of initial value |          |          |
|                                                    |                                                                                                                        |       | DF              | Within initial limits        |          |          |
|                                                    |                                                                                                                        |       | DCL             | Within initial limits        |          |          |
| Additional qualification tests per MIL–PRF–55365/4 | Please contact KEMET for more information.                                                                             |       |                 |                              |          |          |

\*IL = Initial limit

## Certification


MIL-PRF-55365/4

## Electrical Characteristics

### ESR vs. Frequency



### Capacitance vs. Frequency



## Dimensions – Millimeters (Inches)

Metric will govern



| Case Size | Component        |                  |                  |                                   |                                              |                        |
|-----------|------------------|------------------|------------------|-----------------------------------|----------------------------------------------|------------------------|
| KEMET     | L* ±0.38 (0.015) | W* ±0.38 (0.015) | H* ±0.38 (0.015) | P +0.25 (0.010),<br>-0.13 (0.005) | W <sub>2</sub>                               | H <sub>2</sub> Minimum |
| A         | 2.54 (0.100)     | 1.27 (0.050)     | 1.27 (0.050)     | 0.76 (0.030)                      | 1.27 ±0.13<br>(0.050 ±0.005)                 | 0.76 (0.030)           |
| B         | 3.81 (0.150)     | 1.27 (0.050)     | 1.27 (0.050)     | 0.76 (0.030)                      | 1.27 ±0.13<br>(0.050 ±0.005)                 | 0.76 (0.030)           |
| C         | 5.08 (0.200)     | 1.27 (0.050)     | 1.27 (0.050)     | 0.76 (0.030)                      | 1.27 ±0.13<br>(0.050 ±0.005)                 | 0.76 (0.030)           |
| D         | 3.81 (0.150)     | 2.54 (0.100)     | 1.27 (0.050)     | 0.76 (0.030)                      | 2.41 +0.13, -0.25<br>(0.095 +0.005, -0.010)  | 0.76 (0.030)           |
| E         | 5.08 (0.200)     | 2.54 (0.100)     | 1.27 (0.050)     | 0.76 (0.030)                      | 2.41 +0.13, -0.25<br>(0.095 +0.005, -0.010)  | 0.76 (0.030)           |
| F         | 5.59 (0.220)     | 3.43 (0.135)     | 1.78 (0.070)     | 0.76 (0.030)                      | 3.30 ±0.13<br>(0.130 ±0.005)                 | 1.02 (0.040)           |
| G         | 6.73 (0.265)     | 2.79 (0.110)     | 2.79 (0.110)     | 1.27 (0.050)                      | 2.67 ±0.13<br>(0.105 ±0.005)                 | 1.52 (0.060)           |
| H         | 7.24 (0.285)     | 3.81 (0.150)     | 2.79 (0.110)     | 1.27 (0.050)                      | 3.68 +0.013, -0.51<br>(0.145 +0.005, -0.020) | 1.52 (0.060)           |

Note: When solder coated terminations are required, add an additional 0.38 mm (0.015 inch) to the above tolerances for "L", "W", "H", "P", "W<sub>2</sub>" and "H<sub>2</sub>"

Table 1 – Ratings &amp; Part Number Reference

| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/4 Part Number  | DC Leakage                         | DF                             | ESR                             | Moisture Sensitivity          |
|---------------|-----------|-------------------------|------------------------------|------------------------------|------------------------------------|--------------------------------|---------------------------------|-------------------------------|
| V             | µF        | KEMET/EIA               | (See below for part options) | (See below for part options) | µA @ +20°C<br>Maximum/5<br>Minutes | % @ +20°C<br>120 Hz<br>Maximum | Ω @ +20°C<br>100 kHz<br>Maximum | Reflow Temperature<br>≤ 260°C |
| 4             | 2.2       | A/1005                  | T409A225(1)004(2)(3)(4)      | CWR09C(3)225(1)(2)(5)        | 1                                  | 6.0                            | 8.0                             | 1                             |
| 4             | 4.7       | B/1505                  | T409B475(1)004(2)(3)(4)      | CWR09C(3)475(1)(2)(5)        | 1.0                                | 6.0                            | 8.0                             | 1                             |
| 4             | 6.8       | C/2005                  | T409C685(1)004(2)(3)(4)      | CWR09C(3)685(1)(2)(5)        | 1.0                                | 6.0                            | 5.5                             | 1                             |
| 4             | 10        | D/1510                  | T409D106(1)004(2)(3)(4)      | CWR09C(3)106(1)(2)(5)        | 1.0                                | 8.0                            | 4.0                             | 1                             |
| 4             | 15        | E/2010                  | T409E156(1)004(2)(3)(4)      | CWR09C(3)156(1)(2)(5)        | 1.0                                | 8.0                            | 3.5                             | 1                             |
| 4             | 33        | F/2214                  | T409F336(1)004(2)(3)(4)      | CWR09C(3)336(1)(2)(5)        | 2.0                                | 8.0                            | 2.2                             | 1                             |
| 4             | 68        | G/2711                  | T409G686(1)004(2)(3)(4)      | CWR09C(3)686(1)(2)(5)        | 3.0                                | 10.0                           | 1.1                             | 1                             |
| 4             | 100       | H/2915                  | T409H107(1)004(2)(3)(4)      | CWR09C(3)107(1)(2)(5)        | 4.0                                | 10.0                           | 0.9                             | 1                             |
| 6             | 1.5       | A/1005                  | T409A155(1)006(2)(3)(4)      | CWR09D(3)155(1)(2)(5)        | 1.0                                | 6.0                            | 8.0                             | 1                             |
| 6             | 3.3       | B/1505                  | T409B335(1)006(2)(3)(4)      | CWR09D(3)335(1)(2)(5)        | 1.0                                | 6.0                            | 8.0                             | 1                             |
| 6             | 4.7       | C/2005                  | T409C475(1)006(2)(3)(4)      | CWR09D(3)475(1)(2)(5)        | 1.0                                | 6.0                            | 5.5                             | 1                             |
| 6             | 6.8       | D/1510                  | T409D685(1)006(2)(3)(4)      | CWR09D(3)685(1)(2)(5)        | 1.0                                | 6.0                            | 4.5                             | 1                             |
| 6             | 10        | E/2010                  | T409E106(1)006(2)(3)(4)      | CWR09D(3)106(1)(2)(5)        | 1.0                                | 8.0                            | 3.5                             | 1                             |
| 6             | 22        | F/2214                  | T409F226(1)006(2)(3)(4)      | CWR09D(3)226(1)(2)(5)        | 2.0                                | 8.0                            | 2.2                             | 1                             |
| 6             | 47        | G/2711                  | T409G476(1)006(2)(3)(4)      | CWR09D(3)476(1)(2)(5)        | 3.0                                | 10.0                           | 1.1                             | 1                             |
| 6             | 68        | H/2915                  | T409H686(1)006(2)(3)(4)      | CWR09D(3)686(1)(2)(5)        | 4.0                                | 10.0                           | 0.9                             | 1                             |
| 10            | 1         | A/1005                  | T409A105(1)010(2)(3)(4)      | CWR09F(3)105(1)(2)(5)        | 1.0                                | 6.0                            | 10.0                            | 1                             |
| 10            | 2.2       | B/1505                  | T409B225(1)010(2)(3)(4)      | CWR09F(3)225(1)(2)(5)        | 1.0                                | 6.0                            | 8.0                             | 1                             |
| 10            | 3.3       | C/2005                  | T409C335(1)010(2)(3)(4)      | CWR09F(3)335(1)(2)(5)        | 1.0                                | 6.0                            | 5.5                             | 1                             |
| 10            | 4.7       | D/1510                  | T409D475(1)010(2)(3)(4)      | CWR09F(3)475(1)(2)(5)        | 1.0                                | 6.0                            | 4.5                             | 1                             |
| 10            | 6.8       | E/2010                  | T409E685(1)010(2)(3)(4)      | CWR09F(3)685(1)(2)(5)        | 1.0                                | 6.0                            | 3.5                             | 1                             |
| 10            | 15        | F/2214                  | T409F156(1)010(2)(3)(4)      | CWR09F(3)156(1)(2)(5)        | 2.0                                | 8.0                            | 2.5                             | 1                             |
| 10            | 33        | G/2711                  | T409G336(1)010(2)(3)(4)      | CWR09F(3)336(1)(2)(5)        | 3.0                                | 10.0                           | 1.1                             | 1                             |
| 10            | 47        | H/2915                  | T409H476(1)010(2)(3)(4)      | CWR09F(3)476(1)(2)(5)        | 5.0                                | 10.0                           | 0.9                             | 1                             |
| 15            | 0.68      | A/1005                  | T409A684(1)015(2)(3)(4)      | CWR09H(3)684(1)(2)(5)        | 1.0                                | 6.0                            | 12.0                            | 1                             |
| 15            | 1.5       | B/1505                  | T409B155(1)015(2)(3)(4)      | CWR09H(3)155(1)(2)(5)        | 1.0                                | 6.0                            | 8.0                             | 1                             |
| 15            | 2.2       | C/2005                  | T409C225(1)015(2)(3)(4)      | CWR09H(3)225(1)(2)(5)        | 1.0                                | 6.0                            | 5.5                             | 1                             |
| 15            | 3.3       | D/1510                  | T409D335(1)015(2)(3)(4)      | CWR09H(3)335(1)(2)(5)        | 1.0                                | 6.0                            | 5.0                             | 1                             |
| 15            | 4.7       | E/2010                  | T409E475(1)015(2)(3)(4)      | CWR09H(3)475(1)(2)(5)        | 1.0                                | 6.0                            | 4.0                             | 1                             |
| 15            | 10        | F/2214                  | T409F106(1)015(2)(3)(4)      | CWR09H(3)106(1)(2)(5)        | 2.0                                | 6.0                            | 2.5                             | 1                             |
| 15            | 22        | G/2711                  | T409G226(1)015(2)(3)(4)      | CWR09H(3)226(1)(2)(5)        | 4.0                                | 6.0                            | 1.1                             | 1                             |
| 15            | 33        | H/2915                  | T409H336(1)015(2)(3)(4)      | CWR09H(3)336(1)(2)(5)        | 5.0                                | 8.0                            | 0.9                             | 1                             |
| 20            | 0.47      | A/1005                  | T409A474(1)020(2)(3)(4)      | CWR09J(3)474(1)(2)(5)        | 1.0                                | 8.0                            | 14.0                            | 1                             |
| 20            | 0.68      | B/1505                  | T409B684(1)020(2)(3)(4)      | CWR09J(3)684(1)(2)(5)        | 1.0                                | 6.0                            | 10.0                            | 1                             |
| 20            | 1         | B/1505                  | T409B105(1)020(2)(3)(4)      | CWR09J(3)105(1)(2)(5)        | 1.0                                | 6.0                            | 12.0                            | 1                             |
| 20            | 1.5       | C/2005                  | T409C155(1)020(2)(3)(4)      | CWR09J(3)155(1)(2)(5)        | 1.0                                | 6.0                            | 6.0                             | 1                             |
| 20            | 2.2       | D/1510                  | T409D225(1)020(2)(3)(4)      | CWR09J(3)225(1)(2)(5)        | 1.0                                | 6.0                            | 5.0                             | 1                             |
| 20            | 3.3       | E/2010                  | T409E335(1)020(2)(3)(4)      | CWR09J(3)335(1)(2)(5)        | 1.0                                | 6.0                            | 4.0                             | 1                             |
| 20            | 6.8       | F/2214                  | T409F685(1)020(2)(3)(4)      | CWR09J(3)685(1)(2)(5)        | 2.0                                | 6.0                            | 2.4                             | 1                             |
| 20            | 15        | G/2711                  | T409G156(1)020(2)(3)(4)      | CWR09J(3)156(1)(2)(5)        | 3.0                                | 6.0                            | 1.1                             | 1                             |
| 20            | 22        | H/2915                  | T409H226(1)020(2)(3)(4)      | CWR09J(3)226(1)(2)(5)        | 4.0                                | 6.0                            | 0.9                             | 1                             |
| 25            | 0.33      | A/1005                  | T409A334(1)025(2)(3)(4)      | CWR09K(3)334(1)(2)(5)        | 1.0                                | 6.0                            | 15.0                            | 1                             |
| 25            | 0.68      | B/1505                  | T409B684(1)025(2)(3)(4)      | CWR09K(3)684(1)(2)(5)        | 1.0                                | 6.0                            | 7.5                             | 1                             |
| 25            | 1         | C/2005                  | T409C105(1)025(2)(3)(4)      | CWR09K(3)105(1)(2)(5)        | 1.0                                | 6.0                            | 6.5                             | 1                             |
| 25            | 1.5       | D/1510                  | T409D155(1)025(2)(3)(4)      | CWR09K(3)155(1)(2)(5)        | 1.0                                | 6.0                            | 6.5                             | 1                             |
| 25            | 2.2       | E/2010                  | T409E225(1)025(2)(3)(4)      | CWR09K(3)225(1)(2)(5)        | 1.0                                | 6.0                            | 3.5                             | 1                             |
| 25            | 4.7       | F/2214                  | T409F475(1)025(2)(3)(4)      | CWR09K(3)475(1)(2)(5)        | 2.0                                | 6.0                            | 2.5                             | 1                             |
| 25            | 6.8       | G/2711                  | T409G685(1)025(2)(3)(4)      | CWR09K(3)685(1)(2)(5)        | 2.0                                | 6.0                            | 1.2                             | 1                             |
| V             | µF        | KEMET/EIA               | (See below for part options) | (See below for part options) | µA @ +20°C<br>Maximum/5<br>Minutes | % @ +20°C<br>120 Hz<br>Maximum | Ω @ +20°C<br>100 kHz<br>Maximum | Reflow Temperature<br>≤ 260°C |
| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/4 Part Number  | DC Leakage                         | DF                             | ESR                             | Moisture Sensitivity          |

(1) To complete KEMET/CWR part number, insert M for ±20%, K for ±10%, or J for ±5%. Designates capacitance tolerance.

(2) To complete KEMET/CWR part number, insert B (0.1%/1,000 Hours), C (0.01%/1,000 Hours), D (0.001%/1,000 Hours) or A = N/A. Designates reliability level.

(3) To complete KEMET/CWR part number, insert B = Gold Plated, C = Hot solder dipped, H = Solder plated or K = Solder Fused. Designates termination finish.

(4) To complete KEMET part number, insert 4250 = +25°C after Weibull, 4251 = -55°C +85°C after Weibull, or 4252 = -55°C +85°C before Weibull. Designates surge current option.

(5) To complete CWR part number, insert A = +25°C after Weibull, B = -55°C +85°C after Weibull, or C = -55°C +85°C before Weibull. Designates surge current option. Refer to Ordering Information for additional detail.

**Table 1 – Ratings & Part Number Reference cont'd**

| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/4 Part Number  | DC Leakage                         | DF                             | ESR                             | Moisture Sensitivity          |
|---------------|-----------|-------------------------|------------------------------|------------------------------|------------------------------------|--------------------------------|---------------------------------|-------------------------------|
| V             | μF        | KEMET/EIA               | (See below for part options) | (See below for part options) | μA @ +20°C<br>Maximum/5<br>Minutes | % @ +20°C<br>120 Hz<br>Maximum | Ω @ +20°C<br>100 kHz<br>Maximum | Reflow Temperature<br>≤ 260°C |
| 25            | 10        | G/2711                  | T409G106(1)025(2)(3)(4)      | CWR09K(3)106(1)(2)(5)        | 3.0                                | 6.0                            | 1.4                             | 1                             |
| 25            | 15        | H/2915                  | T409H156(1)025(2)(3)(4)      | CWR09K(3)156(1)(2)(5)        | 4.0                                | 6.0                            | 1.0                             | 1                             |
| 35            | 0.22      | A/1005                  | T409A224(1)035(2)(3)(4)      | CWR09M(3)224(1)(2)(5)        | 1.0                                | 6.0                            | 18.0                            | 1                             |
| 35            | 0.47      | B/1505                  | T409B474(1)035(2)(3)(4)      | CWR09M(3)474(1)(2)(5)        | 1.0                                | 6.0                            | 10.0                            | 1                             |
| 35            | 0.68      | C/2005                  | T409C684(1)035(2)(3)(4)      | CWR09M(3)684(1)(2)(5)        | 1.0                                | 6.0                            | 8.0                             | 1                             |
| 35            | 1         | D/1510                  | T409D105(1)035(2)(3)(4)      | CWR09M(3)105(1)(2)(5)        | 1.0                                | 6.0                            | 6.5                             | 1                             |
| 35            | 1.5       | E/2010                  | T409E155(1)035(2)(3)(4)      | CWR09M(3)155(1)(2)(5)        | 1.0                                | 6.0                            | 4.5                             | 1                             |
| 35            | 3.3       | F/2214                  | T409F335(1)035(2)(3)(4)      | CWR09M(3)335(1)(2)(5)        | 1.0                                | 6.0                            | 2.5                             | 1                             |
| 35            | 4.7       | G/2711                  | T409G475(1)035(2)(3)(4)      | CWR09M(3)475(1)(2)(5)        | 2.0                                | 6.0                            | 1.5                             | 1                             |
| 35            | 6.8       | H/2915                  | T409H685(1)035(2)(3)(4)      | CWR09M(3)685(1)(2)(5)        | 3.0                                | 6.0                            | 1.3                             | 1                             |
| 50            | 0.1       | A/1005                  | T409A104(1)050(2)(3)(4)      | CWR09N(3)104(1)(2)(5)        | 1.0                                | 6.0                            | 22.0                            | 1                             |
| 50            | 0.15      | A/1005                  | T409A154(1)050(2)(3)(4)      | CWR09N(3)154(1)(2)(5)        | 1.0                                | 6.0                            | 17.0                            | 1                             |
| 50            | 0.22      | B/1505                  | T409B224(1)050(2)(3)(4)      | CWR09N(3)224(1)(2)(5)        | 1.0                                | 6.0                            | 14.0                            | 1                             |
| 50            | 0.33      | B/1505                  | T409B334(1)050(2)(3)(4)      | CWR09N(3)334(1)(2)(5)        | 1.0                                | 6.0                            | 12.0                            | 1                             |
| 50            | 0.47      | C/2005                  | T409C474(1)050(2)(3)(4)      | CWR09N(3)474(1)(2)(5)        | 1.0                                | 6.0                            | 8.0                             | 1                             |
| 50            | 0.68      | D/1510                  | T409D684(1)050(2)(3)(4)      | CWR09N(3)684(1)(2)(5)        | 1.0                                | 6.0                            | 7.0                             | 1                             |
| 50            | 1         | E/2010                  | T409E105(1)050(2)(3)(4)      | CWR09N(3)105(1)(2)(5)        | 1.0                                | 6.0                            | 6.0                             | 1                             |
| 50            | 1.5       | F/2214                  | T409F155(1)050(2)(3)(4)      | CWR09N(3)155(1)(2)(5)        | 1.0                                | 6.0                            | 4.0                             | 1                             |
| 50            | 2.2       | F/2214                  | T409F225(1)050(2)(3)(4)      | CWR09N(3)225(1)(2)(5)        | 2.0                                | 6.0                            | 2.5                             | 1                             |
| 50            | 3.3       | G/2711                  | T409G335(1)050(2)(3)(4)      | CWR09N(3)335(1)(2)(5)        | 2.0                                | 6.0                            | 2.0                             | 1                             |
| 50            | 4.7       | H/2915                  | T409H475(1)050(2)(3)(4)      | CWR09N(3)475(1)(2)(5)        | 3.0                                | 6.0                            | 1.5                             | 1                             |
| V             | μF        | KEMET/EIA               | (See below for part options) | (See below for part options) | μA @ +20°C<br>Maximum/5<br>Minutes | % @ +20°C<br>120 Hz<br>Maximum | Ω @ +20°C<br>100 kHz<br>Maximum | Reflow Temperature<br>≤ 260°C |
| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/4 Part Number  | DC Leakage                         | DF                             | ESR                             | Moisture Sensitivity          |

(1) To complete KEMET/CWR part number, insert M for ±20%, K for ±10%, or J for ±5%. Designates capacitance tolerance.

(2) To complete KEMET/CWR part number, insert failure rate letter per the Ordering Information found on page 2. Designates Reliability Level.

(3) To complete KEMET/CWR part number, insert B = Gold Plated, C = Hot solder dipped, H = Solder plated or K = Solder Fused. Designates termination finish.

(4) To complete KEMET part number, insert 4250 = +25°C after Weibull, 4251 = -55°C +85°C after Weibull, or 4252 = -55°C +85°C before Weibull. Designates surge current option.

(5) To complete CWR part number, insert A = +25°C after Weibull, B = -55°C +85°C after Weibull, or C = -55°C +85°C before Weibull. Designates surge current option. Refer to Ordering Information for additional detail.

## Recommended Voltage Derating Guidelines

|                                                 | -55°C to 85°C | 85°C to 125°C |
|-------------------------------------------------|---------------|---------------|
| % Change in Working DC Voltage with Temperature | $V_R$         | 67% of $V_R$  |
| Recommended Maximum Application Voltage         | 50% of $V_R$  | 33% of $V_R$  |



## Ripple Current/Ripple Voltage

Permissible AC ripple voltage and current are related to equivalent series resistance (ESR) and the power dissipation capabilities of the device. Permissible AC ripple voltage which may be applied is limited by two criteria:

1. The positive peak AC voltage plus the DC bias voltage, if any, must not exceed the DC voltage rating of the capacitor.
2. The negative peak AC voltage in combination with bias voltage, if any, must not exceed the allowable limits specified for reverse voltage. See the Reverse Voltage section for allowable limits.

The maximum power dissipation by case size can be determined using the table at right. The maximum power dissipation rating stated in the table must be reduced with increasing environmental operating temperatures. Refer to the table below for temperature compensation requirements.

| KEMET Case Code | EIA Case Code | Maximum Power Dissipation (P max) mWatts @ 25°C w/+20°C Rise |
|-----------------|---------------|--------------------------------------------------------------|
| A               | 1005          | 50                                                           |
| B               | 1505          | 70                                                           |
| C               | 2005          | 75                                                           |
| D               | 1510          | 80                                                           |
| E               | 2010          | 90                                                           |
| F               | 2214          | 100                                                          |
| G               | 2711          | 125                                                          |
| H               | 2915          | 150                                                          |

The maximum power dissipation rating must be reduced with increasing environmental operating temperatures. Refer to the Temperature Compensation Multiplier table for details.

| Temperature Compensation Multipliers for Maximum Power Dissipation |          |           |
|--------------------------------------------------------------------|----------|-----------|
| T ≤ 25°C                                                           | T ≤ 85°C | T ≤ 125°C |
| 1.00                                                               | 0.90     | 0.40      |

T = Environmental Temperature

Using the P max of the device, the maximum allowable rms ripple current or voltage may be determined.

$$I(max) = \sqrt{P_{max}/R}$$

$$E(max) = Z \sqrt{P_{max}/R}$$

I = rms ripple current (amperes)

E = rms ripple voltage (volts)

P max = maximum power dissipation (watts)

R = ESR at specified frequency (ohms)

Z = Impedance at specified frequency (ohms)

## Reverse Voltage

Solid tantalum capacitors are polar devices and may be permanently damaged or destroyed if connected with the wrong polarity. The positive terminal is identified on the capacitor body by a stripe plus in some cases a beveled edge. A small degree of transient reverse voltage is permissible for short periods per the table. The capacitors should not be operated continuously in reverse mode, even within these limits.

| Temperature | Permissible Transient Reverse Voltage |
|-------------|---------------------------------------|
| 25°C        | 15% of Rated Voltage                  |
| 85°C        | 5% of Rated Voltage                   |
| 125°C       | 1% of Rated Voltage                   |

**Table 2 – Land Dimensions/Courtyard**

| KEMET          | Metric Size Code | Density Level A:<br>Maximum (Most) Land Protrusion (mm) |      |      |       |      | Density Level B:<br>Median (Nominal) Land Protrusion (mm) |      |      |      |      | Density Level C:<br>Minimum (Least) Land Protrusion (mm) |      |      |      |      |
|----------------|------------------|---------------------------------------------------------|------|------|-------|------|-----------------------------------------------------------|------|------|------|------|----------------------------------------------------------|------|------|------|------|
|                |                  | L                                                       | W    | S    | V1    | V2   | L                                                         | W    | S    | V1   | V2   | L                                                        | W    | S    | V1   | V2   |
| A <sup>1</sup> | 1005             | 2.19                                                    | 1.44 | 0.15 | 5.54  | 2.66 | 1.89                                                      | 1.32 | 0.15 | 4.44 | 2.16 | 1.52                                                     | 1.22 | 0.29 | 3.58 | 1.90 |
| B              | 1505             | 2.30                                                    | 1.44 | 1.20 | 6.80  | 2.66 | 1.90                                                      | 1.32 | 1.40 | 5.70 | 2.16 | 1.52                                                     | 1.22 | 1.56 | 4.84 | 1.90 |
| C              | 2005             | 2.30                                                    | 1.44 | 2.47 | 8.08  | 2.66 | 1.90                                                      | 1.32 | 2.67 | 6.98 | 2.16 | 1.52                                                     | 1.22 | 2.83 | 6.12 | 1.90 |
| D              | 1510             | 2.30                                                    | 2.58 | 1.20 | 6.80  | 3.92 | 1.90                                                      | 2.46 | 1.40 | 5.70 | 3.42 | 1.52                                                     | 2.36 | 1.56 | 4.84 | 3.16 |
| E              | 2010             | 2.30                                                    | 2.58 | 2.47 | 8.08  | 3.92 | 1.90                                                      | 2.46 | 2.67 | 6.98 | 3.42 | 1.52                                                     | 2.36 | 2.83 | 6.12 | 3.16 |
| F              | 2214             | 2.30                                                    | 3.47 | 2.98 | 8.58  | 4.82 | 1.90                                                      | 3.35 | 3.18 | 7.48 | 4.32 | 1.52                                                     | 3.25 | 3.34 | 6.62 | 4.06 |
| G              | 2711             | 2.81                                                    | 2.84 | 3.10 | 9.72  | 4.18 | 2.41                                                      | 2.72 | 3.30 | 8.62 | 3.68 | 2.03                                                     | 2.62 | 3.46 | 7.76 | 3.42 |
| H              | 2915             | 2.81                                                    | 3.84 | 3.61 | 10.24 | 5.20 | 2.41                                                      | 3.72 | 3.81 | 9.14 | 4.70 | 2.03                                                     | 3.62 | 3.97 | 8.28 | 4.44 |
| X              | 2824             | 2.73                                                    | 3.22 | 3.46 | 9.92  | 6.80 | 2.33                                                      | 3.10 | 3.66 | 8.82 | 6.30 | 1.95                                                     | 3.00 | 3.82 | 7.96 | 6.04 |

**Density Level A:** For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes.

**Density Level B:** For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes.

**Density Level C:** For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC standard 7351 (IPC-7351).

<sup>1</sup> Land pattern geometry is too small for silkscreen outline.



## Soldering Process

KEMET's families of surface mount capacitors are compatible with wave (single or dual), convection, IR, or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/J-STD-020D standard for moisture sensitivity testing. The devices can safely withstand a maximum of three reflow passes at these conditions.

Note that although the X/7343–43 case size can withstand wave soldering, the tall profile (4.3 mm maximum) dictates care in wave process development.

Hand soldering should be performed with care due to the difficulty in process control. If performed, care should be taken to avoid contact of the soldering iron to the molded case. The iron should be used to heat the solder pad, applying solder between the pad and the termination, until reflow occurs. Once reflow occurs, the iron should be removed immediately. "Wiping" the edges of a chip and heating the top surface is not recommended.

During typical reflow operations, a slight darkening of the gold-colored epoxy may be observed. This slight darkening is normal and not harmful to the product. Marking permanency is not affected by this change.

| Profile Feature                                       | SnPb Assembly       | Pb-Free Assembly    |
|-------------------------------------------------------|---------------------|---------------------|
| <b>Preheat/Soak</b>                                   |                     |                     |
| Temperature Minimum ( $T_{smin}$ )                    | 100°C               | 150°C               |
| Temperature Maximum ( $T_{smax}$ )                    | 150°C               | 200°C               |
| Time ( $t_s$ ) from $T_{smin}$ to $T_{smax}$          | 60 – 120 seconds    | 60 – 120 seconds    |
| Ramp-up Rate ( $T_L$ to $T_P$ )                       | 3°C/seconds maximum | 3°C/seconds maximum |
| Liquidous Temperature ( $T_L$ )                       | 183°C               | 217°C               |
| Time Above Liquidous ( $t_L$ )                        | 60 – 150 seconds    | 60 – 150 seconds    |
| Peak Temperature ( $T_P$ )                            | 220°C*<br>235°C**   | 250°C*<br>260°C**   |
| Time within 5°C of Maximum Peak Temperature ( $t_p$ ) | 20 seconds maximum  | 30 seconds maximum  |
| Ramp-down Rate ( $T_P$ to $T_L$ )                     | 6°C/seconds maximum | 6°C/seconds maximum |
| Time 25°C to Peak Temperature                         | 6 minutes maximum   | 8 minutes maximum   |


Note: All temperatures refer to the center of the package, measured on the package body surface that is facing up during assembly reflow.

\*Case Size D, E, P, Y, and X

\*\*Case Size A, B, C, H, I, K, M, R, S, T, U, V, W, and Z



## Construction



## Capacitor Marking



\* 230 = 30<sup>th</sup> week of 2012

| Date Code *                                                  |                                                                                    |
|--------------------------------------------------------------|------------------------------------------------------------------------------------|
| 1 <sup>st</sup> digit = Last number of Year                  | 9 = 2009<br>0 = 2010<br>1 = 2011<br>2 = 2012<br>3 = 2013<br>4 = 2014               |
| 2 <sup>nd</sup> and 3 <sup>rd</sup> digit = Week of the Year | 01 = 1 <sup>st</sup> week of the Year to<br>52 = 52 <sup>nd</sup> week of the Year |

## Storage

Tantalum chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature—reels may soften or warp and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 60% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts and atmospheres should be free of chlorine and sulphur bearing compounds. For optimized solderability chip stock should be used promptly, preferably within three years of receipt.

## Overview

The KEMET T419 Series is approved to MIL-PRF-55365/11 (CWR19) with Weibull failure rates of B level (0.1% failures per 1,000 hours), C level (0.01% failures per 1,000 hours), D level (0.001% failures per 1,000 hours), or T level (0.01% failures per 1,000 hours), Option C surge current, DPA, Radiographic

inspection, 100% visual inspection, DCL and ESR measurements within +3 standard deviations, and Group C inspection). This CWR19 product is a precision-molded device with compliant terminations and indelible laser marking. Tape and reeling per EIA 481-1 is standard.

## Benefits

- Established reliability options
- Taped and reeled per EIA 481-1
- Symmetrical, compliant terminations
- Laser-marked case
- 100% surge current test available on all case sizes
- Qualified to MIL-PRF-55365/11, Style CWR19
- Termination options B, C, H, K
- Weibull failure options B, C, D, and T
- Exponential failure rates M, P, R, S
- Voltage rating of 4 – 35 VDC
- Operating temperature range of -55°C to +125°C

## Applications

Typical applications include decoupling and filtering in Military and aerospace applications requiring CWR19 devices.



## Environmental Compliance

RoHS Compliant (6/6) according to Directive 2002/95/EC when ordered with 100% Sn Solder.



RoHS Compliant

## SPICE

For a detailed analysis of specific part numbers, please visit [www.kemet.com](http://www.kemet.com) for a free download of KEMET's SPICE software. The KEMET SPICE program is freeware intended to aid design engineers in analyzing the performance of these capacitors over frequency, temperature, ripple, and DC bias conditions.

## KEMET Ordering Information

| T               | 419                           | A                         | 225                                                                                    | K                                                 | 004                                                                                            | A                                                                                                                                                                                                                                                           | H                                                                                                               | 4251                                                                                                                                                           | 7280                                                                     |
|-----------------|-------------------------------|---------------------------|----------------------------------------------------------------------------------------|---------------------------------------------------|------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------|
| Capacitor Class | Series                        | Case Size                 | Capacitance Code (pF)                                                                  | Capacitance Tolerance                             | Voltage                                                                                        | Failure Rate/Design                                                                                                                                                                                                                                         | Lead Material                                                                                                   | Surge                                                                                                                                                          | Packaging (C-Spec)                                                       |
| T = Tantalum    | CWR19 Established Reliability | A, B, C, D, E, F, G, H, X | First two digits represent significant figures. Third digit specifies number of zeros. | J = $\pm 5\%$<br>K = $\pm 10\%$<br>M = $\pm 20\%$ | 004 = 4 V<br>006 = 6.3 V<br>010 = 10 V<br>015 = 15 V<br>020 = 20 V<br>025 = 25 V<br>035 = 35 V | Weibull<br>A = non-ER<br>B = (0.1%/1,000 hours)<br>C = (0.01%/1,000 hours)<br>D = (0.001%/1,000 hours)<br>T = (0.01%/1,000 hours)<br>Exponential<br>M = (1.0%/1,000 hours)<br>P = (0.1%/1,000 hours)<br>R = (0.01%/1,000 hours)<br>S = (0.001%/1,000 hours) | C = Hot Solder Dipped<br>H = Standard Solder Coated (SnPb 5% Pb minimum)<br>B = Gold Plated<br>K = Solder Fused | Blank = No Surge<br>4250 = 25°C after Weibull<br>4251 = -55°C and 85°C after Weibull<br>4252 = -55°C and 85°C before Weibull<br>TLVL = Weibull Grade Level "T" | Blank = 7" Reel<br>7280 = 13" Reel<br>7610 = Bag<br>7005 = Moisture bags |

## Defense MIL-PRF-55365/11 Ordering Information

| CWR19                | K                                                                              | H                                                                                 | 225                                                                                    | K                                                 | C                                                                                                                                                                                                                                                                    | D                         | A                                                                                                      |
|----------------------|--------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|---------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|--------------------------------------------------------------------------------------------------------|
| Capacitor Style      | Voltage                                                                        | Termination Finish                                                                | Capacitance Code (pF)                                                                  | Capacitance Tolerance                             | Reliability Level                                                                                                                                                                                                                                                    | Case Code                 | Surge Current Option                                                                                   |
| Per MIL-PRF-55365/11 | C = 4 V<br>D = 6 V<br>F = 10 V<br>H = 15 V<br>J = 20 V<br>K = 25 V<br>M = 35 V | B = Gold Plated<br>C = Hot solder dipped<br>H = Solder Plated<br>K = Solder fused | First two digits represent significant figures. Third digit specifies number of zeros. | J = $\pm 5\%$<br>K = $\pm 10\%$<br>M = $\pm 20\%$ | Weibull<br>A = non-ER<br>B = (0.1%/1,000 hours)<br>C = (0.01%/1,000 hours)<br>D = (0.001%/1,000 hours)<br>T = T Level* (0.01%/1,000 hours)<br>Exponential<br>M = (1.0%/1,000 hours)<br>P = (0.1%/1,000 hours)<br>R = (0.01%/1,000 hours)<br>S = (0.001%/1,000 hours) | A, B, C, D, E, F, G, H, X | A = +25°C after Weibull<br>B = -55°C +85°C after Weibull<br>C = -55°C +85°C before Weibull<br>Z = None |

\* When T Level is ordered, no Surge Current Option is needed

## Performance Characteristics

| Item                    | Performance Characteristics                                |
|-------------------------|------------------------------------------------------------|
| Operating Temperature   | -55°C to 125°C                                             |
| Rated Capacitance Range | 0.33 – 330 $\mu$ F @ 120 Hz/25°C                           |
| Capacitance Tolerance   | J Tolerance (5%), K Tolerance (10%), M Tolerance (20%)     |
| Rated Voltage Range     | 4 – 35 V                                                   |
| DF (120 Hz)             | Refer to Part Number Electrical Specification Table        |
| ESR (100 kHz)           | Refer to Part Number Electrical Specification Table        |
| Leakage Current         | $\leq 0.01$ CV ( $\mu$ A) at rated voltage after 5 minutes |

## Qualification

| Test                                                   | Condition                                                                                                                 |       | Characteristics |                              |          |          |
|--------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|-------|-----------------|------------------------------|----------|----------|
| Endurance                                              | 85°C @ rated voltage, 2,000 hours<br>125°C @ 2/3 rated voltage, 2,000 hours                                               |       | Δ C/C           | Within ±10% of initial value |          |          |
|                                                        |                                                                                                                           |       | DF              | Within initial limits        |          |          |
|                                                        |                                                                                                                           |       | DCL             | Within 1.25 x initial limit  |          |          |
|                                                        |                                                                                                                           |       | ESR             | Within initial limits        |          |          |
| Storage Life                                           | 125°C @ 0 volts, 2,000 hours                                                                                              |       | Δ C/C           | Within ±10% of initial value |          |          |
|                                                        |                                                                                                                           |       | DF              | Within initial limits        |          |          |
|                                                        |                                                                                                                           |       | DCL             | Within 1.25 x initial limit  |          |          |
|                                                        |                                                                                                                           |       | ESR             | Within initial limits        |          |          |
| Thermal Shock                                          | MIL–STD–202, Method 107, Condition B, mounted,<br>-55°C to 125°C, 1,000 cycles                                            |       | Δ C/C           | Within ±5% of initial value  |          |          |
|                                                        |                                                                                                                           |       | DF              | Within initial limits        |          |          |
|                                                        |                                                                                                                           |       | DCL             | Within 1.25 x initial limit  |          |          |
|                                                        |                                                                                                                           |       | ESR             | Within initial limits        |          |          |
| Temperature Stability                                  | Extreme temperature exposure at a<br>succession of continuous steps at +25°C,<br>-55°C, +25°C, +85°C, +125°C, +25°C       | Δ C/C | +25°C           | -55°C                        | +85°C    | +125°C   |
|                                                        |                                                                                                                           | IL*   | ±10%            | ±10%                         | ±20%     |          |
|                                                        |                                                                                                                           | DF    | IL              | IL                           | 1.5 x IL | 1.5 x IL |
|                                                        |                                                                                                                           | DCL   | IL              | n/a                          | 10 x IL  | 12 x IL  |
| Surge Voltage                                          | 25°C and 85°C, 1.32 x rated voltage 1,000 cycles<br>(125°C, 1.2 x rated voltage)                                          |       | Δ C/C           | Within ±5% of initial value  |          |          |
|                                                        |                                                                                                                           |       | DF              | Within initial limits        |          |          |
|                                                        |                                                                                                                           |       | DCL             | Within initial limits        |          |          |
|                                                        |                                                                                                                           |       | ESR             | Within initial limits        |          |          |
| Mechanical Shock/Vibration                             | MIL–STD–202, Method 213, Condition I, 100 G Peak<br>MIL–STD–202, Method 204, Condition D, 10 Hz to 2,000 Hz,<br>20 G peak |       | Δ C/C           | Within ±10% of initial value |          |          |
|                                                        |                                                                                                                           |       | DF              | Within initial limits        |          |          |
|                                                        |                                                                                                                           |       | DCL             | Within initial limits        |          |          |
| Additional qualification tests<br>per MIL–PRF–55365/11 | Please contact KEMET for more information.                                                                                |       |                 |                              |          |          |


\*IL = Initial limit

## Certification


MIL-PRF-55365/11

## Electrical Characteristics

ESR vs. Frequency



Capacitance vs. Frequency



## Dimensions – Millimeters (Inches)

Metric will govern



| Case Size | Component        |                  |                  |                                   |                                              |                        |
|-----------|------------------|------------------|------------------|-----------------------------------|----------------------------------------------|------------------------|
| KEMET     | L* ±0.38 (0.015) | W* ±0.38 (0.015) | H* ±0.38 (0.015) | P +0.25 (0.010),<br>-0.13 (0.005) | W <sub>2</sub>                               | H <sub>2</sub> Minimum |
| A         | 2.54 (0.100)     | 1.27 (0.050)     | 1.27 (0.050)     | 0.76 (0.030)                      | 1.27 ±0.13<br>(0.050 ±0.005)                 | 0.76 (0.030)           |
| B         | 3.81 (0.150)     | 1.27 (0.050)     | 1.27 (0.050)     | 0.76 (0.030)                      | 1.27 ±0.13<br>(0.050 ±0.005)                 | 0.76 (0.030)           |
| C         | 5.08 (0.200)     | 1.27 (0.050)     | 1.27 (0.050)     | 0.76 (0.030)                      | 1.27 ±0.13<br>(0.050 ±0.005)                 | 0.76 (0.030)           |
| D         | 3.81 (0.150)     | 2.54 (0.100)     | 1.27 (0.050)     | 0.76 (0.030)                      | 2.41 +0.13, -0.25<br>(0.095 +0.005, -0.010)  | 0.76 (0.030)           |
| E         | 5.08 (0.200)     | 2.54 (0.100)     | 1.27 (0.050)     | 0.76 (0.030)                      | 2.41 +0.13, -0.25<br>(0.095 +0.005, -0.010)  | 0.76 (0.030)           |
| F         | 5.59 (0.220)     | 3.43 (0.135)     | 1.78 (0.070)     | 0.76 (0.030)                      | 3.30 ±0.13<br>(0.130 ±0.005)                 | 1.02 (0.040)           |
| G         | 6.73 (0.265)     | 2.79 (0.110)     | 2.79 (0.110)     | 1.27 (0.050)                      | 2.67 ±0.13<br>(0.105 ±0.005)                 | 1.52 (0.060)           |
| H         | 7.24 (0.285)     | 3.81 (0.150)     | 2.79 (0.110)     | 1.27 (0.050)                      | 3.68 +0.013, -0.51<br>(0.145 +0.005, -0.020) | 1.52 (0.060)           |
| X         | 6.93 (0.273)     | 5.41 (0.213)     | 2.74 (0.108)     | 1.19 (0.047)                      | 3.05 ±0.13<br>(0.120 ±0.005)                 | 1.22 (0.048)           |

Note: When solder coated terminations are required, add an additional 0.38 mm (0.015 inch) to the above tolerances for "L", "W", "H", "P", "W<sub>2</sub>" and "H<sub>2</sub>"

Table 1 – Ratings &amp; Part Number Reference

| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11 Part Number | DC Leakage           | DF                  | ESR                  | Moisture Sensitivity       |
|---------------|-----------|-------------------------|------------------------------|------------------------------|----------------------|---------------------|----------------------|----------------------------|
| VDC           | µF        | KEMET/EIA               | (See below for part options) | (See below for part options) | µA @ +20°C Max/5 Min | % @ 20°C 120 Hz Max | Ω @ +20°C 100kHz Max | Reflow Temperature ≤ 260°C |
| 4             | 3.3       | A/1005                  | T419A335(1)004(2)(3)(4)      | CWR19C(3)335(1)(2)A(5)       | 1.0                  | 6.0                 | 12.0                 | 1                          |
| 4             | 4.7       | A/1005                  | T419A475(1)004(2)(3)(4)      | CWR19C(3)475(1)(2)A(5)       | 1.0                  | 6.0                 | 12.0                 | 1                          |
| 4             | 6.8       | A/1005                  | T419A685(1)004(2)(3)(4)      | CWR19C(3)685(1)(2)A(5)       | 1.0                  | 6.0                 | 12.0                 | 1                          |
| 4             | 10        | B/1505                  | T419B106(1)004(2)(3)(4)      | CWR19C(3)106(1)(2)B(5)       | 1.0                  | 8.0                 | 8.0                  | 1                          |
| 4             | 15        | B/1505                  | T419B156(1)004(2)(3)(4)      | CWR19C(3)156(1)(2)B(5)       | 1.0                  | 8.0                 | 8.0                  | 1                          |
| 4             | 22        | B/1505                  | T419B226(1)004(2)(3)(4)      | CWR19C(3)226(1)(2)B(5)       | 1.0                  | 8.0                 | 8.0                  | 1                          |
| 4             | 22        | D/1510                  | T419D226(1)004(2)(3)(4)      | CWR19C(3)226(1)(2)D(5)       | 1.0                  | 8.0                 | 4.0                  | 1                          |
| 4             | 33        | D/1510                  | T419D336(1)004(2)(3)(4)      | CWR19C(3)336(1)(2)D(5)       | 2.0                  | 8.0                 | 4.0                  | 1                          |
| 4             | 33        | E/2010                  | T419E336(1)004(2)(3)(4)      | CWR19C(3)336(1)(2)E(5)       | 2.0                  | 8.0                 | 3.0                  | 1                          |
| 4             | 47        | E/2010                  | T419E476(1)004(2)(3)(4)      | CWR19C(3)476(1)(2)E(5)       | 2.0                  | 8.0                 | 3.0                  | 1                          |
| 4             | 68        | E/2010                  | T419E686(1)004(2)(3)(4)      | CWR19C(3)686(1)(2)E(5)       | 3.0                  | 8.0                 | 3.0                  | 1                          |
| 4             | 100       | F/2214                  | T419F107(1)004(2)(3)(4)      | CWR19C(3)107(1)(2)F(5)       | 4.0                  | 10.0                | 2.0                  | 1                          |
| 4             | 150       | G/2711                  | T419G157(1)004(2)(3)(4)      | CWR19C(3)157(1)(2)G(5)       | 6.0                  | 10.0                | 1.0                  | 1                          |
| 4             | 220       | H/2915                  | T419H227(1)004(2)(3)(4)      | CWR19C(3)227(1)(2)H(5)       | 8.0                  | 10.0                | 1.0                  | 1                          |
| 4             | 330       | H/2915                  | T419H337(1)004(2)(3)(4)      | CWR19C(3)337(1)(2)H(5)       | 10.0                 | 10.0                | 0.9                  | 1                          |
| 6             | 3.3       | A/1005                  | T419A335(1)006(2)(3)(4)      | CWR19D(3)335(1)(2)A(5)       | 1.0                  | 6.0                 | 12.0                 | 1                          |
| 6             | 4.7       | A/1005                  | T419A475(1)006(2)(3)(4)      | CWR19D(3)475(1)(2)A(5)       | 1.0                  | 6.0                 | 12.0                 | 1                          |
| 6             | 6.8       | B/1505                  | T419B685(1)006(2)(3)(4)      | CWR19D(3)685(1)(2)B(5)       | 1.0                  | 6.0                 | 8.0                  | 1                          |
| 6             | 10        | B/1505                  | T419B106(1)006(2)(3)(4)      | CWR19D(3)106(1)(2)B(5)       | 1.0                  | 6.0                 | 8.0                  | 1                          |
| 6             | 15        | B/1505                  | T419B156(1)006(2)(3)(4)      | CWR19D(3)156(1)(2)B(5)       | 1.0                  | 8.0                 | 8.0                  | 1                          |
| 6             | 15        | D/1510                  | T419D156(1)006(2)(3)(4)      | CWR19D(3)156(1)(2)D(5)       | 1.0                  | 8.0                 | 5.0                  | 1                          |
| 6             | 15        | E/2010                  | T419E156(1)006(2)(3)(4)      | CWR19D(3)156(1)(2)E(5)       | 1.0                  | 8.0                 | 3.0                  | 1                          |
| 6             | 22        | D/1510                  | T419D226(1)006(2)(3)(4)      | CWR19D(3)226(1)(2)D(5)       | 1.0                  | 6.0                 | 5.0                  | 1                          |
| 6             | 22        | E/2010                  | T419E226(1)006(2)(3)(4)      | CWR19D(3)226(1)(2)E(5)       | 2.0                  | 8.0                 | 3.5                  | 1                          |
| 6             | 33        | E/2010                  | T419E336(1)006(2)(3)(4)      | CWR19D(3)336(1)(2)E(5)       | 2.0                  | 6.0                 | 3.5                  | 1                          |
| 6             | 47        | F/2214                  | T419F476(1)006(2)(3)(4)      | CWR19D(3)476(1)(2)F(5)       | 2.8                  | 8.0                 | 3.5                  | 1                          |
| 6             | 68        | F/2214                  | T419F686(1)006(2)(3)(4)      | CWR19D(3)686(1)(2)F(5)       | 4.0                  | 10.0                | 1.5                  | 1                          |
| 6             | 68        | G/2711                  | T419G686(1)006(2)(3)(4)      | CWR19D(3)686(1)(2)G(5)       | 4.0                  | 10.0                | 1.0                  | 1                          |
| 6             | 100       | G/2711                  | T419G107(1)006(2)(3)(4)      | CWR19D(3)107(1)(2)G(5)       | 6.0                  | 10.0                | 1.1                  | 1                          |
| 6             | 150       | G/2711                  | T419G157(1)006(2)(3)(4)      | CWR19D(3)157(1)(2)G(5)       | 10.0                 | 10.0                | 1.1                  | 1                          |
| 6             | 220       | H/2915                  | T419H227(1)006(2)(3)(4)      | CWR19D(3)227(1)(2)H(5)       | 10.0                 | 10.0                | 0.9                  | 1                          |
| 6             | 330       | H/2915                  | T419H337(1)006(2)(3)(4)      | CWR19D(3)337(1)(2)H(5)       | 20.0                 | 10.0                | 0.9                  | 1                          |
| 10            | 2.2       | A/1005                  | T419A225(1)010(2)(3)(4)      | CWR19F(3)225(1)(2)A(5)       | 1.0                  | 6.0                 | 12.0                 | 1                          |
| 10            | 3.3       | A/1005                  | T419A335(1)010(2)(3)(4)      | CWR19F(3)335(1)(2)A(5)       | 1.0                  | 6.0                 | 12.0                 | 1                          |
| 10            | 4.7       | B/1505                  | T419B475(1)010(2)(3)(4)      | CWR19F(3)475(1)(2)B(5)       | 1.0                  | 6.0                 | 8.0                  | 1                          |
| 10            | 4.7       | C/2005                  | T419C475(1)010(2)(3)(4)      | CWR19F(3)475(1)(2)C(5)       | 1.0                  | 6.0                 | 5.5                  | 1                          |
| 10            | 6.8       | B/1505                  | T419B685(1)010(2)(3)(4)      | CWR19F(3)685(1)(2)B(5)       | 1.0                  | 6.0                 | 8.0                  | 1                          |
| 10            | 6.8       | C/2005                  | T419C685(1)010(2)(3)(4)      | CWR19F(3)685(1)(2)C(5)       | 1.0                  | 6.0                 | 5.5                  | 1                          |
| 10            | 6.8       | D/1510                  | T419D685(1)010(2)(3)(4)      | CWR19F(3)685(1)(2)D(5)       | 1.0                  | 6.0                 | 5.0                  | 1                          |
| 10            | 10        | B/1505                  | T419B106(1)010(2)(3)(4)      | CWR19F(3)106(1)(2)B(5)       | 1.0                  | 8.0                 | 8.0                  | 1                          |
| 10            | 10        | C/2005                  | T419C106(1)010(2)(3)(4)      | CWR19F(3)106(1)(2)C(5)       | 1.0                  | 6.0                 | 5.5                  | 1                          |
| 10            | 10        | D/1510                  | T419D106(1)010(2)(3)(4)      | CWR19F(3)106(1)(2)D(5)       | 1.0                  | 6.0                 | 4.0                  | 1                          |
| 10            | 10        | E/2010                  | T419E106(1)010(2)(3)(4)      | CWR19F(3)106(1)(2)E(5)       | 1.0                  | 6.0                 | 3.5                  | 1                          |
| 10            | 15        | D/1510                  | T419D156(1)010(2)(3)(4)      | CWR19F(3)156(1)(2)D(5)       | 2.0                  | 6.0                 | 5.0                  | 1                          |
| 10            | 15        | E/2010                  | T419E156(1)010(2)(3)(4)      | CWR19F(3)156(1)(2)E(5)       | 2.0                  | 8.0                 | 3.0                  | 1                          |
| 10            | 22        | E/2010                  | T419E226(1)010(2)(3)(4)      | CWR19F(3)226(1)(2)E(5)       | 3.0                  | 8.0                 | 2.0                  | 1                          |
| 10            | 33        | F/2214                  | T419F336(1)010(2)(3)(4)      | CWR19F(3)336(1)(2)F(5)       | 3.0                  | 8.0                 | 1.5                  | 1                          |
| 10            | 47        | F/2214                  | T419F476(1)010(2)(3)(4)      | CWR19F(3)476(1)(2)F(5)       | 4.0                  | 10.0                | 1.5                  | 1                          |
| 10            | 47        | G/2711                  | T419G476(1)010(2)(3)(4)      | CWR19F(3)476(1)(2)G(5)       | 4.0                  | 10.0                | 1.0                  | 1                          |
| VDC           | µF        | KEMET/EIA               | (See below for part options) | (See below for part options) | µA @ +20°C Max/5 Min | % @ 20°C 120 Hz Max | Ω @ +20°C 100kHz Max | Reflow Temperature ≤ 260°C |
| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11 Part Number | DC Leakage           | DF                  | ESR                  | Moisture Sensitivity       |

(1) To complete KEMET/CWR part number, insert M for ±20%, K for ±10%, or J for ±5%. Designates Capacitance tolerance.

(2) To complete KEMET/CWR part number, insert B (0.1%/1,000 Hours), C (0.01%/1,000 Hours), D (0.001%/1,000 Hours) or A = N/A. Designates Reliability Level.

(3) To complete KEMET/CWR part number, insert B = Gold Plated, C = Hot solder dipped, H = Solder plated or K = Solder Fused. Designates Termination Finish.

(4) To complete KEMET part number, insert 4250 = +25°C after Weibull, 4251 = -55°C +85°C after Weibull, or 4252 = -55°C +85°C before Weibull. Designates Surge current option.

(5) To complete CWR part number, insert A = +25°C after Weibull, B = -55°C +85°C after Weibull, C = -55°C +85°C before Weibull or Z = None. Designates Surge current option.

Refer to Ordering Information for additional detail.

**Table 1 – Ratings & Part Number Reference cont'd**

| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11 Part Number | DC Leakage              | DF                     | ESR                     | Moisture Sensitivity          |
|---------------|-----------|-------------------------|------------------------------|------------------------------|-------------------------|------------------------|-------------------------|-------------------------------|
| VDC           | μF        | KEMET/EIA               | (See below for part options) | (See below for part options) | μA @ +20°C<br>Max/5 Min | % @ 20°C 120<br>Hz Max | Ω @ +20°C<br>100kHz Max | Reflow Temperature<br>≤ 260°C |
| 10            | 68        | G/2711                  | T419G686(1)010(2)(3)(4)      | CWR19F(3)686(1)(2)G(5)       | 6.0                     | 10.0                   | 1.1                     | 1                             |
| 10            | 100       | G/2711                  | T419G107(1)010(2)(3)(4)      | CWR19F(3)107(1)(2)G(5)       | 10.0                    | 10.0                   | 1.1                     | 1                             |
| 10            | 100       | H/2915                  | T419H107(1)010(2)(3)(4)      | CWR19F(3)107(1)(2)H(5)       | 10.0                    | 10.0                   | 0.9                     | 1                             |
| 10            | 150       | H/2915                  | T419H157(1)010(2)(3)(4)      | CWR19F(3)157(1)(2)H(5)       | 15.0                    | 10.0                   | 0.9                     | 1                             |
| 10            | 150       | X/2824                  | T419X157(1)010(2)(3)(4)      | CWR19F(3)157(1)(2)X(5)       | 15.0                    | 10.0                   | 0.9                     | 1                             |
| 10            | 220       | H/2915                  | T419H227(1)010(2)(3)(4)      | CWR19F(3)227(1)(2)H(5)       | 20.0                    | 10.0                   | 0.9                     | 1                             |
| 15            | 1         | A/1005                  | T419A105(1)015(2)(3)(4)      | CWR19H(3)105(1)(2)A(5)       | 1.0                     | 6.0                    | 15.0                    | 1                             |
| 15            | 1.5       | A/1005                  | T419A155(1)015(2)(3)(4)      | CWR19H(3)155(1)(2)A(5)       | 1.0                     | 6.0                    | 15.0                    | 1                             |
| 15            | 2.2       | A/1005                  | T419A225(1)015(2)(3)(4)      | CWR19H(3)225(1)(2)A(5)       | 1.0                     | 6.0                    | 15.0                    | 1                             |
| 15            | 3.3       | B/1505                  | T419B335(1)015(2)(3)(4)      | CWR19H(3)335(1)(2)B(5)       | 1.0                     | 6.0                    | 9.0                     | 1                             |
| 15            | 4.7       | B/1505                  | T419B475(1)015(2)(3)(4)      | CWR19H(3)475(1)(2)B(5)       | 1.0                     | 6.0                    | 5.0                     | 1                             |
| 15            | 4.7       | C/2005                  | T419C475(1)015(2)(3)(4)      | CWR19H(3)475(1)(2)C(5)       | 1.0                     | 6.0                    | 5.5                     | 1                             |
| 15            | 4.7       | D/1510                  | T419D475(1)015(2)(3)(4)      | CWR19H(3)475(1)(2)D(5)       | 1.0                     | 6.0                    | 6.0                     | 1                             |
| 15            | 6.8       | D/1510                  | T419D685(1)015(2)(3)(4)      | CWR19H(3)685(1)(2)D(5)       | 1.0                     | 6.0                    | 6.0                     | 1                             |
| 15            | 6.8       | E/2010                  | T419E685(1)015(2)(3)(4)      | CWR19H(3)685(1)(2)E(5)       | 1.0                     | 8.0                    | 3.0                     | 1                             |
| 15            | 10        | D/1510                  | T419D106(1)015(2)(3)(4)      | CWR19H(3)106(1)(2)D(5)       | 2.0                     | 6.0                    | 6.0                     | 1                             |
| 15            | 10        | E/2010                  | T419E106(1)015(2)(3)(4)      | CWR19H(3)106(1)(2)E(5)       | 2.0                     | 6.0                    | 4.0                     | 1                             |
| 15            | 15        | E/2010                  | T419E156(1)015(2)(3)(4)      | CWR19H(3)156(1)(2)E(5)       | 2.0                     | 6.0                    | 4.0                     | 1                             |
| 15            | 15        | F/2214                  | T419F156(1)015(2)(3)(4)      | CWR19H(3)156(1)(2)F(5)       | 2.0                     | 8.0                    | 3.0                     | 1                             |
| 15            | 22        | F/2214                  | T419F226(1)015(2)(3)(4)      | CWR19H(3)226(1)(2)F(5)       | 3.0                     | 8.0                    | 3.0                     | 1                             |
| 15            | 33        | F/2214                  | T419F336(1)015(2)(3)(4)      | CWR19H(3)336(1)(2)F(5)       | 5.0                     | 6.0                    | 3.0                     | 1                             |
| 15            | 33        | G/2711                  | T419G336(1)015(2)(3)(4)      | CWR19H(3)336(1)(2)G(5)       | 6.0                     | 8.0                    | 1.1                     | 1                             |
| 15            | 47        | G/2711                  | T419G476(1)015(2)(3)(4)      | CWR19H(3)476(1)(2)G(5)       | 10.0                    | 8.0                    | 1.1                     | 1                             |
| 15            | 47        | H/2915                  | T419H476(1)015(2)(3)(4)      | CWR19H(3)476(1)(2)H(5)       | 10.0                    | 8.0                    | 0.9                     | 1                             |
| 15            | 68        | G/2711                  | T419G686(1)015(2)(3)(4)      | CWR19H(3)686(1)(2)G(5)       | 10.0                    | 8.0                    | 1.1                     | 1                             |
| 15            | 68        | H/2915                  | T419H686(1)015(2)(3)(4)      | CWR19H(3)686(1)(2)H(5)       | 10.0                    | 8.0                    | 0.9                     | 1                             |
| 15            | 100       | H/2915                  | T419H107(1)015(2)(3)(4)      | CWR19H(3)107(1)(2)H(5)       | 15.0                    | 10.0                   | 0.9                     | 1                             |
| 20            | 0.68      | A/1005                  | T419A684(1)020(2)(3)(4)      | CWR19J(3)684(1)(2)A(5)       | 1.0                     | 6.0                    | 15.0                    | 1                             |
| 20            | 1         | A/1005                  | T419A105(1)020(2)(3)(4)      | CWR19J(3)105(1)(2)A(5)       | 1.0                     | 6.0                    | 15.0                    | 1                             |
| 20            | 1.5       | B/1505                  | T419B155(1)020(2)(3)(4)      | CWR19J(3)155(1)(2)B(5)       | 1.0                     | 6.0                    | 9.0                     | 1                             |
| 20            | 2.2       | B/1505                  | T419B225(1)020(2)(3)(4)      | CWR19J(3)225(1)(2)B(5)       | 1.0                     | 6.0                    | 9.0                     | 1                             |
| 20            | 3.3       | D/1510                  | T419D335(1)020(2)(3)(4)      | CWR19J(3)335(1)(2)D(5)       | 1.0                     | 6.0                    | 6.0                     | 1                             |
| 20            | 4.7       | E/2010                  | T419E475(1)020(2)(3)(4)      | CWR19J(3)475(1)(2)E(5)       | 1.0                     | 6.0                    | 6.0                     | 1                             |
| 20            | 6.8       | E/2010                  | T419E685(1)020(2)(3)(4)      | CWR19J(3)685(1)(2)E(5)       | 2.0                     | 6.0                    | 5.0                     | 1                             |
| 20            | 10        | E/2010                  | T419E106(1)020(2)(3)(4)      | CWR19J(3)106(1)(2)E(5)       | 2.0                     | 6.0                    | 5.0                     | 1                             |
| 20            | 10        | F/2214                  | T419F106(1)020(2)(3)(4)      | CWR19J(3)106(1)(2)F(5)       | 2.0                     | 6.0                    | 3.0                     | 1                             |
| 20            | 15        | F/2214                  | T419F156(1)020(2)(3)(4)      | CWR19J(3)156(1)(2)F(5)       | 3.0                     | 6.0                    | 3.0                     | 1                             |
| 20            | 22        | G/2711                  | T419G226(1)020(2)(3)(4)      | CWR19J(3)226(1)(2)G(5)       | 4.0                     | 6.0                    | 2.5                     | 1                             |
| 20            | 33        | H/2915                  | T419H336(1)020(2)(3)(4)      | CWR19J(3)336(1)(2)H(5)       | 6.0                     | 8.0                    | 0.9                     | 1                             |
| 20            | 47        | H/2915                  | T419H476(1)020(2)(3)(4)      | CWR19J(3)476(1)(2)H(5)       | 10.0                    | 8.0                    | 0.9                     | 1                             |
| 20            | 47        | X/2824                  | T419X476(1)020(2)(3)(4)      | CWR19J(3)476(1)(2)X(5)       | 10.0                    | 8.0                    | 0.9                     | 1                             |
| 25            | 0.47      | A/1005                  | T419A474(1)025(2)(3)(4)      | CWR19K(3)474(1)(2)A(5)       | 1.0                     | 6.0                    | 15.0                    | 1                             |
| 25            | 1         | B/1505                  | T419B105(1)025(2)(3)(4)      | CWR19K(3)105(1)(2)B(5)       | 1.0                     | 6.0                    | 10.0                    | 1                             |
| 25            | 2.2       | D/1510                  | T419D225(1)025(2)(3)(4)      | CWR19K(3)225(1)(2)D(5)       | 1.0                     | 6.0                    | 6.0                     | 1                             |
| 25            | 3.3       | E/2010                  | T419E335(1)025(2)(3)(4)      | CWR19K(3)335(1)(2)E(5)       | 1.0                     | 6.0                    | 4.0                     | 1                             |
| 25            | 6.8       | F/2214                  | T419F685(1)025(2)(3)(4)      | CWR19K(3)685(1)(2)F(5)       | 2.0                     | 6.0                    | 3.0                     | 1                             |
| 25            | 15        | G/2711                  | T419G156(1)025(2)(3)(4)      | CWR19K(3)156(1)(2)G(5)       | 4.0                     | 6.0                    | 1.4                     | 1                             |
| 25            | 22        | G/2711                  | T419G226(1)025(2)(3)(4)      | CWR19K(3)226(1)(2)G(5)       | 6.0                     | 6.0                    | 1.4                     | 1                             |
| 25            | 22        | H/2915                  | T419H226(1)025(2)(3)(4)      | CWR19K(3)226(1)(2)H(5)       | 6.0                     | 6.0                    | 0.9                     | 1                             |
| VDC           | μF        | KEMET/EIA               | (See below for part options) | (See below for part options) | μA @ +20°C<br>Max/5 Min | % @ 20°C 120<br>Hz Max | Ω @ +20°C<br>100kHz Max | Reflow Temperature<br>≤ 260°C |
| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11 Part Number | DC Leakage              | DF                     | ESR                     | Moisture Sensitivity          |

(1) To complete KEMET/CWR part number, insert M for ±20%, K for ±10%, or J for ±5%. Designates Capacitance tolerance.

(2) To complete KEMET/CWR part number, insert B (0.1%/1,000 Hours), C (0.01%/1,000 Hours), D (0.001%/1,000 Hours) or A = N/A. Designates Reliability Level.

(3) To complete KEMET/CWR part number, insert B = Gold Plated, C = Hot solder dipped, H = Solder plated or K = Solder Fused. Designates Termination Finish.

(4) To complete KEMET part number, insert 4250 = +25°C after Weibull, 4251 = -55°C +85°C after Weibull, or 4252 = -55°C +85°C before Weibull. Designates Surge current option.

(5) To complete CWR part number, insert A = +25°C after Weibull, B = -55°C +85°C after Weibull, C = -55°C +85°C before Weibull or Z = None. Designates Surge current option.

Refer to Ordering Information for additional detail.

**Table 1 – Ratings & Part Number Reference cont'd**

| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11<br>Part Number | DC Leakage              | DF                     | ESR                      | Moisture Sensitivity          |
|---------------|-----------|-------------------------|------------------------------|---------------------------------|-------------------------|------------------------|--------------------------|-------------------------------|
| VDC           | μF        | KEMET/EIA               | (See below for part options) | (See below for part options)    | μA @ +20°C<br>Max/5 Min | % @ 20°C<br>120 Hz Max | Ω @ +20°C<br>100 kHz Max | Reflow Temperature<br>≤ 260°C |
| 25            | 22        | X/2824                  | T419X226(1)025(2)(3)(4)      | CWR19K(3)226(1)(2)X(5)          | 6.0                     | 6.0                    | 0.9                      | 1                             |
| 25            | 33        | H/2915                  | T419H336(1)025(2)(3)(4)      | CWR19K(3)336(1)(2)H(5)          | 10.0                    | 8.0                    | 0.9                      | 1                             |
| 25            | 33        | X/2824                  | T419X336(1)025(2)(3)(4)      | CWR19K(3)336(1)(2)X(5)          | 10.0                    | 8.0                    | 0.9                      | 1                             |
| 35            | 0.33      | A/1005                  | T419A334(1)035(2)(3)(4)      | CWR19M(3)334(1)(2)A(5)          | 1.0                     | 6.0                    | 22.0                     | 1                             |
| 35            | 6.8       | G/2711                  | T419G685(1)035(2)(3)(4)      | CWR19M(3)685(1)(2)G(5)          | 3.0                     | 6.0                    | 1.5                      | 1                             |
| 35            | 10        | H/2915                  | T419H106(1)035(2)(3)(4)      | CWR19M(3)106(1)(2)H(5)          | 4.0                     | 8.0                    | 0.9                      | 1                             |
| 35            | 15        | X/2824                  | T419X156(1)035(2)(3)(4)      | CWR19M(3)156(1)(2)X(5)          | 6.0                     | 6.0                    | 0.9                      | 1                             |
| VDC           | μF        | KEMET/EIA               | (See below for part options) | (See below for part options)    | μA @ +20°C<br>Max/5 Min | % @ 20°C<br>120 Hz Max | Ω @ +20°C<br>100 kHz Max | Reflow Temperature<br>≤ 260°C |
| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11<br>Part Number | DC Leakage              | DF                     | ESR                      | Moisture Sensitivity          |

(1) To complete KEMET/CWR part number, insert M for ±20%, K for ±10%, or J for ±5%. Designates Capacitance tolerance.

(2) To complete KEMET/CWR part number, insert failure rate letter per the Ordering Information found on page 2. Designates Reliability Level.

(3) To complete KEMET/CWR part number, insert B = Gold Plated, C = Hot solder dipped, H = Solder plated or K = Solder Fused. Designates Termination Finish.

(4) To complete KEMET part number, insert 4250 = +25°C after Weibull, 4251 = -55°C +85°C after Weibull, or 4252 = -55°C +85°C before Weibull. Designates Surge current option.

(5) To complete CWR part number, insert A = +25°C after Weibull, B = -55°C +85°C after Weibull, C = -55°C +85°C before Weibull or Z = None. Designates Surge current option.

Refer to Ordering Information for additional detail.

## Recommended Voltage Derating Guidelines

|                                                 | -55°C to 85°C | 85°C to 125°C |
|-------------------------------------------------|---------------|---------------|
| % Change in Working DC Voltage with Temperature | $V_R$         | 67% of $V_R$  |
| Recommended Maximum Application Voltage         | 50% of $V_R$  | 33% of $V_R$  |



## Ripple Current/Ripple Voltage

Permissible AC ripple voltage and current are related to equivalent series resistance (ESR) and the power dissipation capabilities of the device. Permissible AC ripple voltage which may be applied is limited by two criteria:

1. The positive peak AC voltage plus the DC bias voltage, if any, must not exceed the DC voltage rating of the capacitor.
2. The negative peak AC voltage in combination with bias voltage, if any, must not exceed the allowable limits specified for reverse voltage. See the Reverse Voltage section for allowable limits.

The maximum power dissipation by case size can be determined using the table at right. The maximum power dissipation rating stated in the table must be reduced with increasing environmental operating temperatures. Refer to the table below for temperature compensation requirements.

| KEMET Case Code | EIA Case Code | Maximum Power Dissipation (P max) mWatts @ 25°C w/+20°C Rise |
|-----------------|---------------|--------------------------------------------------------------|
| A               | 1005          | 50                                                           |
| B               | 1505          | 70                                                           |
| C               | 2005          | 75                                                           |
| D               | 1510          | 80                                                           |
| E               | 2010          | 90                                                           |
| F               | 2214          | 100                                                          |
| G               | 2711          | 125                                                          |
| H               | 2915          | 150                                                          |

The maximum power dissipation rating must be reduced with increasing environmental operating temperatures. Refer to the Temperature Compensation Multiplier table for details.

| Temperature Compensation Multipliers for Maximum Power Dissipation |          |           |
|--------------------------------------------------------------------|----------|-----------|
| T ≤ 25°C                                                           | T ≤ 85°C | T ≤ 125°C |
| 1.00                                                               | 0.90     | 0.40      |

T = Environmental Temperature

Using the P max of the device, the maximum allowable rms ripple current or voltage may be determined.

$$I(max) = \sqrt{P_{max}/R}$$

$$E(max) = Z \sqrt{P_{max}/R}$$

I = rms ripple current (amperes)

E = rms ripple voltage (volts)

P max = maximum power dissipation (watts)

R = ESR at specified frequency (ohms)

Z = Impedance at specified frequency (ohms)

## Reverse Voltage

Solid tantalum capacitors are polar devices and may be permanently damaged or destroyed if connected with the wrong polarity. The positive terminal is identified on the capacitor body by a stripe plus in some cases a beveled edge. A small degree of transient reverse voltage is permissible for short periods per the table. The capacitors should not be operated continuously in reverse mode, even within these limits.

| Temperature | Permissible Transient Reverse Voltage |
|-------------|---------------------------------------|
| 25°C        | 15% of Rated Voltage                  |
| 85°C        | 5% of Rated Voltage                   |
| 125°C       | 1% of Rated Voltage                   |

**Table 2 – Land Dimensions/Courtyard**


| KEMET          | Metric Size Code | Density Level A:<br>Maximum (Most) Land Protrusion (mm) |      |      |       |      | Density Level B:<br>Median (Nominal) Land Protrusion (mm) |      |      |      |      | Density Level C:<br>Minimum (Least) Land Protrusion (mm) |      |      |      |      |
|----------------|------------------|---------------------------------------------------------|------|------|-------|------|-----------------------------------------------------------|------|------|------|------|----------------------------------------------------------|------|------|------|------|
|                |                  | L                                                       | W    | S    | V1    | V2   | L                                                         | W    | S    | V1   | V2   | L                                                        | W    | S    | V1   | V2   |
| A <sup>1</sup> | 1005             | 2.19                                                    | 1.44 | 0.15 | 5.54  | 2.66 | 1.89                                                      | 1.32 | 0.15 | 4.44 | 2.16 | 1.52                                                     | 1.22 | 0.29 | 3.58 | 1.90 |
| B              | 1505             | 2.30                                                    | 1.44 | 1.20 | 6.80  | 2.66 | 1.90                                                      | 1.32 | 1.40 | 5.70 | 2.16 | 1.52                                                     | 1.22 | 1.56 | 4.84 | 1.90 |
| C              | 2005             | 2.30                                                    | 1.44 | 2.47 | 8.08  | 2.66 | 1.90                                                      | 1.32 | 2.67 | 6.98 | 2.16 | 1.52                                                     | 1.22 | 2.83 | 6.12 | 1.90 |
| D              | 1510             | 2.30                                                    | 2.58 | 1.20 | 6.80  | 3.92 | 1.90                                                      | 2.46 | 1.40 | 5.70 | 3.42 | 1.52                                                     | 2.36 | 1.56 | 4.84 | 3.16 |
| E              | 2010             | 2.30                                                    | 2.58 | 2.47 | 8.08  | 3.92 | 1.90                                                      | 2.46 | 2.67 | 6.98 | 3.42 | 1.52                                                     | 2.36 | 2.83 | 6.12 | 3.16 |
| F              | 2214             | 2.30                                                    | 3.47 | 2.98 | 8.58  | 4.82 | 1.90                                                      | 3.35 | 3.18 | 7.48 | 4.32 | 1.52                                                     | 3.25 | 3.34 | 6.62 | 4.06 |
| G              | 2711             | 2.81                                                    | 2.84 | 3.10 | 9.72  | 4.18 | 2.41                                                      | 2.72 | 3.30 | 8.62 | 3.68 | 2.03                                                     | 2.62 | 3.46 | 7.76 | 3.42 |
| H              | 2915             | 2.81                                                    | 3.84 | 3.61 | 10.24 | 5.20 | 2.41                                                      | 3.72 | 3.81 | 9.14 | 4.70 | 2.03                                                     | 3.62 | 3.97 | 8.28 | 4.44 |
| X              | 2824             | 2.73                                                    | 3.22 | 3.46 | 9.92  | 6.80 | 2.33                                                      | 3.10 | 3.66 | 8.82 | 6.30 | 1.95                                                     | 3.00 | 3.82 | 7.96 | 6.04 |

**Density Level A:** For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes.

**Density Level B:** For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes.

**Density Level C:** For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC standard 7351 (IPC-7351).

<sup>1</sup> Land pattern geometry is too small for silkscreen outline.



## Soldering Process

KEMET's families of surface mount capacitors are compatible with wave (single or dual), convection, IR, or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/J-STD-020D standard for moisture sensitivity testing. The devices can safely withstand a maximum of three reflow passes at these conditions.

Note that although the X/7343-43 case size can withstand wave soldering, the tall profile (4.3 mm maximum) dictates care in wave process development.

Hand soldering should be performed with care due to the difficulty in process control. If performed, care should be taken to avoid contact of the soldering iron to the molded case. The iron should be used to heat the solder pad, applying solder between the pad and the termination, until reflow occurs. Once reflow occurs, the iron should be removed immediately. "Wiping" the edges of a chip and heating the top surface is not recommended.

During typical reflow operations, a slight darkening of the gold-colored epoxy may be observed. This slight darkening is normal and not harmful to the product. Marking permanency is not affected by this change.

| Profile Feature                                       | SnPb Assembly       | Pb-Free Assembly    |
|-------------------------------------------------------|---------------------|---------------------|
| Preheat/Soak                                          |                     |                     |
| Temperature Minimum ( $T_{smin}$ )                    | 100°C               | 150°C               |
| Temperature Maximum ( $T_{smax}$ )                    | 150°C               | 200°C               |
| Time ( $t_s$ ) from $T_{smin}$ to $T_{smax}$          | 60 – 120 seconds    | 60 – 120 seconds    |
| Ramp-up Rate ( $T_L$ to $T_p$ )                       | 3°C/seconds maximum | 3°C/seconds maximum |
| Liquidous Temperature ( $T_L$ )                       | 183°C               | 217°C               |
| Time Above Liquidous ( $t_L$ )                        | 60 – 150 seconds    | 60 – 150 seconds    |
| Peak Temperature ( $T_p$ )                            | 220°C*<br>235°C**   | 250°C*<br>260°C**   |
| Time within 5°C of Maximum Peak Temperature ( $t_p$ ) | 20 seconds maximum  | 30 seconds maximum  |
| Ramp-down Rate ( $T_p$ to $T_L$ )                     | 6°C/seconds maximum | 6°C/seconds maximum |
| Time 25°C to Peak Temperature                         | 6 minutes maximum   | 8 minutes maximum   |

Note: All temperatures refer to the center of the package, measured on the package body surface that is facing up during assembly reflow.

\*Case Size D, E, P, Y, and X


\*\*Case Size A, B, C, H, I, K, M, R, S, T, U, V, W, and Z



## Construction



## Capacitor Marking



| Date Code *                                                  |                                                                                    |
|--------------------------------------------------------------|------------------------------------------------------------------------------------|
| 1 <sup>st</sup> digit = Last number of Year                  | 9 = 2009<br>0 = 2010<br>1 = 2011<br>2 = 2012<br>3 = 2013<br>4 = 2014               |
| 2 <sup>nd</sup> and 3 <sup>rd</sup> digit = Week of the Year | 01 = 1 <sup>st</sup> week of the Year to<br>52 = 52 <sup>nd</sup> week of the Year |

## Storage

Tantalum chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature—reels may soften or warp and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 60% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts and atmospheres should be free of chlorine and sulphur bearing compounds. For optimized solderability chip stock should be used promptly, preferably within three years of receipt.

## Overview

The KEMET T429 Series is approved to MIL-PRF-55365/11 (CWR290) with Weibull failure rates of B level (0.1% failures per 1,000 hours), C level (0.01% failures per 1,000 hours), D level (0.001% failures per 1,000 hours), or T level (0.01% failures per 1,000 hours), Option C surge current, DPA, Radiographic


inspection, 100% visual inspection, DCL and ESR measurements within +3 standard deviations, and Group C inspection). This CWR29 product is a precision-molded device with compliant terminations and indelible laser marking. Tape and reeling per EIA 481-1 is standard.

## Benefits

- Established reliability options
- Taped and reeled per EIA 481-1
- Symmetrical, compliant terminations
- Laser-marked case
- 100% surge current test available on all case sizes
- Qualified to MIL-PRF-55365/11, Style CWR29
- Termination options B, C, H, K
- Weibull failure options B, C, D, and T
- Exponential failure rates M, P, R, S
- Voltage rating of 4 – 50 VDC
- Operating temperature range of -55°C to +125°C

## Applications

Typical applications include decoupling and filtering in military and aerospace applications requiring CWR29 devices.



## Environmental Compliance

RoHS Compliant (6/6) according to Directive 2002/95/EC when ordered with 100% Sn Solder.



RoHS Compliant

## SPICE

For a detailed analysis of specific part numbers, please visit [www.kemet.com](http://www.kemet.com) for a free download of KEMET's SPICE software. The KEMET SPICE program is freeware intended to aid design engineers in analyzing the performance of these capacitors over frequency, temperature, ripple, and DC bias conditions.

## KEMET Ordering Information

| T               | 429                           | A                         | 225                                                                                    | K                               | 004                                                                                                          | A                                                                                                                                                                                                                                                           | H                                                                                                               | 4251                                                                                                                                                           | 7280                                                                     |
|-----------------|-------------------------------|---------------------------|----------------------------------------------------------------------------------------|---------------------------------|--------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------|
| Capacitor Class | Series                        | Case Size                 | Capacitance Code (pF)                                                                  | Capacitance Tolerance           | Voltage                                                                                                      | Failure Rate/Design                                                                                                                                                                                                                                         | Lead Material                                                                                                   | Surge                                                                                                                                                          | Packaging (C-Spec)                                                       |
| T = Tantalum    | CWR29 Established Reliability | A, B, C, D, E, F, G, H, X | First two digits represent significant figures. Third digit specifies number of zeros. | J = ±5%<br>K = ±10%<br>M = ±20% | 004 = 4 V<br>006 = 6.3 V<br>010 = 10 V<br>015 = 15 V<br>020 = 20 V<br>025 = 25 V<br>035 = 35 V<br>050 = 50 V | Weibull<br>A = non-ER<br>B = (0.1%/1,000 hours)<br>C = (0.01%/1,000 hours)<br>D = (0.001%/1,000 hours)<br>T = (0.01%/1,000 hours)<br>Exponential<br>M = (1.0%/1,000 hours)<br>P = (0.1%/1,000 hours)<br>R = (0.01%/1,000 hours)<br>S = (0.001%/1,000 hours) | C = Hot Solder Dipped<br>H = Standard Solder Coated (SnPb 5% Pb minimum)<br>B = Gold Plated<br>K = Solder Fused | Blank = No surge<br>4250 = 25°C after Weibull<br>4251 = -55°C and 85°C after Weibull<br>4252 = -55°C and 85°C before Weibull<br>TLVL = Weibull Grade Level "T" | Blank = 7" Reel<br>7280 = 13" Reel<br>7610 = Bag<br>7005 = Moisture bags |

## Defense MIL-PRF-55365/11 Ordering Information

| CWR29                | K                                                                                          | H                                                                                 | 225                                                                                    | K                               | C                                                                                                                                                                                                                                                                    | D                         | A                                                                                                      |
|----------------------|--------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|---------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|--------------------------------------------------------------------------------------------------------|
| Capacitor Style      | Voltage                                                                                    | Termination Finish                                                                | Capacitance Code (pF)                                                                  | Capacitance Tolerance           | Reliability Level                                                                                                                                                                                                                                                    | Case Code                 | Surge Current Option                                                                                   |
| Per MIL-PRF-55365/11 | C = 4 V<br>D = 6 V<br>F = 10 V<br>H = 15 V<br>J = 20 V<br>K = 25 V<br>M = 35 V<br>N = 50 V | B = Gold Plated<br>C = Hot solder dipped<br>H = Solder Plated<br>K = Solder fused | First two digits represent significant figures. Third digit specifies number of zeros. | J = ±5%<br>K = ±10%<br>M = ±20% | Weibull<br>A = non-ER<br>B = (0.1%/1,000 hours)<br>C = (0.01%/1,000 hours)<br>D = (0.001%/1,000 hours)<br>T = T Level* (0.01%/1,000 hours)<br>Exponential<br>M = (1.0%/1,000 hours)<br>P = (0.1%/1,000 hours)<br>R = (0.01%/1,000 hours)<br>S = (0.001%/1,000 hours) | A, B, C, D, E, F, G, H, X | A = +25°C after Weibull<br>B = -55°C +85°C after Weibull<br>C = -55°C +85°C before Weibull<br>Z = None |

\* When T Level is ordered, no Surge Current Option is needed

## Performance Characteristics

| Item                    | Performance Characteristics                            |
|-------------------------|--------------------------------------------------------|
| Operating Temperature   | -55°C to 125°C                                         |
| Rated Capacitance Range | 0.1 – 330 µF @ 120 Hz/25°C                             |
| Capacitance Tolerance   | J Tolerance (5%), K Tolerance (10%), M Tolerance (20%) |
| Rated Voltage Range     | 4 – 50 V                                               |
| DF (120 Hz)             | Refer to Part Number Electrical Specification Table    |
| ESR (100 kHz)           | Refer to Part Number Electrical Specification Table    |
| Leakage Current         | ≤ 0.01 CV (µA) at rated voltage after 5 minutes        |

## Qualification

| Test                                                | Condition                                                                                                              |       | Characteristics |                              |          |          |
|-----------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|-------|-----------------|------------------------------|----------|----------|
| Endurance                                           | 85°C @ rated voltage, 2,000 hours<br>125°C @ 2/3 rated voltage, 2,000 hours                                            |       | Δ C/C           | Within ±10% of initial value |          |          |
|                                                     |                                                                                                                        |       | DF              | Within initial limits        |          |          |
|                                                     |                                                                                                                        |       | DCL             | Within 1.25 x initial limit  |          |          |
|                                                     |                                                                                                                        |       | ESR             | Within initial limits        |          |          |
| Storage Life                                        | 125°C @ 0 volts, 2,000 hours                                                                                           |       | Δ C/C           | Within ±10% of initial value |          |          |
|                                                     |                                                                                                                        |       | DF              | Within initial limits        |          |          |
|                                                     |                                                                                                                        |       | DCL             | Within 1.25 x initial limit  |          |          |
|                                                     |                                                                                                                        |       | ESR             | Within initial limits        |          |          |
| Thermal Shock                                       | MIL-STD-202, Method 107, Condition B, mounted,<br>-55°C to 125°C, 1,000 cycles                                         |       | Δ C/C           | Within ±5% of initial value  |          |          |
|                                                     |                                                                                                                        |       | DF              | Within initial limits        |          |          |
|                                                     |                                                                                                                        |       | DCL             | Within 1.25 x initial limit  |          |          |
|                                                     |                                                                                                                        |       | ESR             | Within initial limits        |          |          |
| Temperature Stability                               | Extreme temperature exposure at a succession of continuous steps at +25°C, -55°C, +25°C, +85°C, +125°C, +25°C          | Δ C/C | +25°C           | -55°C                        | +85°C    | +125°C   |
|                                                     |                                                                                                                        | IL*   | ±10%            | ±10%                         | ±10%     | ±20%     |
|                                                     |                                                                                                                        | DF    | IL              | IL                           | 1.5 x IL | 1.5 x IL |
|                                                     |                                                                                                                        | DCL   | IL              | n/a                          | 10 x IL  | 12 x IL  |
| Surge Voltage                                       | 25°C and 85°C, 1.32 x rated voltage 1,000 cycles<br>(125°C, 1.2 x rated voltage)                                       |       | Δ C/C           | Within ±5% of initial value  |          |          |
|                                                     |                                                                                                                        |       | DF              | Within initial limits        |          |          |
|                                                     |                                                                                                                        |       | DCL             | Within initial limits        |          |          |
|                                                     |                                                                                                                        |       | ESR             | Within initial limits        |          |          |
| Mechanical Shock/Vibration                          | MIL-STD-202, Method 213, Condition I, 100 G Peak<br>MIL-STD-202, Method 204, Condition D, 10 Hz to 2,000 Hz, 20 G peak |       | Δ C/C           | Within ±10% of initial value |          |          |
|                                                     |                                                                                                                        |       | DF              | Within initial limits        |          |          |
|                                                     |                                                                                                                        |       | DCL             | Within initial limits        |          |          |
| Additional qualification tests per MIL-PRF-55365/11 | Please contact KEMET for more information.                                                                             |       |                 |                              |          |          |


\*IL = Initial limit

## Certification


MIL-PRF-55365/11

## Electrical Characteristics

ESR vs. Frequency



Capacitance vs. Frequency



## Dimensions – Millimeters (Inches)

Metric will govern



| Case Size | Component              |                        |                        |                                       |                                                     |               |
|-----------|------------------------|------------------------|------------------------|---------------------------------------|-----------------------------------------------------|---------------|
| KEMET     | $L^* \pm 0.38$ (0.015) | $W^* \pm 0.38$ (0.015) | $H^* \pm 0.38$ (0.015) | $P +0.25$ (0.010),<br>$-0.13$ (0.005) | $W_2$                                               | $H_2$ Minimum |
| A         | 2.54 (0.100)           | 1.27 (0.050)           | 1.27 (0.050)           | 0.76 (0.030)                          | $1.27 \pm 0.13$<br>(0.050 $\pm$ 0.005)              | 0.76 (0.030)  |
| B         | 3.81 (0.150)           | 1.27 (0.050)           | 1.27 (0.050)           | 0.76 (0.030)                          | $1.27 \pm 0.13$<br>(0.050 $\pm$ 0.005)              | 0.76 (0.030)  |
| C         | 5.08 (0.200)           | 1.27 (0.050)           | 1.27 (0.050)           | 0.76 (0.030)                          | $1.27 \pm 0.13$<br>(0.050 $\pm$ 0.005)              | 0.76 (0.030)  |
| D         | 3.81 (0.150)           | 2.54 (0.100)           | 1.27 (0.050)           | 0.76 (0.030)                          | $2.41 +0.13, -0.25$<br>(0.095 $\pm$ 0.005, -0.010)  | 0.76 (0.030)  |
| E         | 5.08 (0.200)           | 2.54 (0.100)           | 1.27 (0.050)           | 0.76 (0.030)                          | $2.41 +0.13, -0.25$<br>(0.095 $\pm$ 0.005, -0.010)  | 0.76 (0.030)  |
| F         | 5.59 (0.220)           | 3.43 (0.135)           | 1.78 (0.070)           | 0.76 (0.030)                          | $3.30 \pm 0.13$<br>(0.130 $\pm$ 0.005)              | 1.02 (0.040)  |
| G         | 6.73 (0.265)           | 2.79 (0.110)           | 2.79 (0.110)           | 1.27 (0.050)                          | $2.67 \pm 0.13$<br>(0.105 $\pm$ 0.005)              | 1.52 (0.060)  |
| H         | 7.24 (0.285)           | 3.81 (0.150)           | 2.79 (0.110)           | 1.27 (0.050)                          | $3.68 +0.013, -0.51$<br>(0.145 $\pm$ 0.005, -0.020) | 1.52 (0.060)  |
| X         | 6.93 (0.273)           | 5.41 (0.213)           | 2.74 (0.108)           | 1.19 (0.047)                          | $3.05 \pm 0.13$<br>(0.120 $\pm$ 0.005)              | 1.22 (0.048)  |

Note: When solder coated terminations are required, add an additional 0.38 mm (0.015 inch) to the above tolerances for "L", "W", "H", "P", "W<sub>2</sub>" and "H<sub>2</sub>"

Table 1 – Ratings &amp; Part Number Reference

| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11 Part Number | DC Leakage           | DF                   | ESR                   | Moisture Sensitivity       |
|---------------|-----------|-------------------------|------------------------------|------------------------------|----------------------|----------------------|-----------------------|----------------------------|
| VDC           | µF        | KEMET/EIA               | (See below for part options) | (See below for part options) | µA @ +20°C Max/5 Min | % @ +20°C 120 Hz Max | Ω @ +20°C 100 kHz Max | Reflow Temperature ≤ 260°C |
| 4             | 2.2       | A/1005                  | T429A225(1)004(2)(3)(4)      | CWR29C(3)225(1)(2)A(5)       | 1.0                  | 6.0                  | 4.0                   | 1                          |
| 4             | 3.3       | A/1005                  | T429A335(1)004(2)(3)(4)      | CWR29C(3)335(1)(2)A(5)       | 1.0                  | 6.0                  | 6.0                   | 1                          |
| 4             | 4.7       | A/1005                  | T429A475(1)004(2)(3)(4)      | CWR29C(3)475(1)(2)A(5)       | 1.0                  | 6.0                  | 6.0                   | 1                          |
| 4             | 4.7       | B/1505                  | T429B475(1)004(2)(3)(4)      | CWR29C(3)475(1)(2)B(5)       | 1.0                  | 6.0                  | 3.2                   | 1                          |
| 4             | 6.8       | A/1005                  | T429A685(1)004(2)(3)(4)      | CWR29C(3)685(1)(2)A(5)       | 1.0                  | 6.0                  | 6.0                   | 1                          |
| 4             | 6.8       | C/2005                  | T429C685(1)004(2)(3)(4)      | CWR29C(3)685(1)(2)C(5)       | 1.0                  | 6.0                  | 2.2                   | 1                          |
| 4             | 10        | B/1505                  | T429B106(1)004(2)(3)(4)      | CWR29C(3)106(1)(2)B(5)       | 1.0                  | 8.0                  | 3.2                   | 1                          |
| 4             | 10        | D/1510                  | T429D106(1)004(2)(3)(4)      | CWR29C(3)106(1)(2)D(5)       | 1.0                  | 8.0                  | 1.3                   | 1                          |
| 4             | 15        | B/1505                  | T429B156(1)004(2)(3)(4)      | CWR29C(3)156(1)(2)B(5)       | 1.0                  | 8.0                  | 3.2                   | 1                          |
| 4             | 15        | E/2010                  | T429E156(1)004(2)(3)(4)      | CWR29C(3)156(1)(2)E(5)       | 1.0                  | 8.0                  | 1.0                   | 1                          |
| 4             | 22        | B/1505                  | T429B226(1)004(2)(3)(4)      | CWR29C(3)226(1)(2)B(5)       | 1.0                  | 8.0                  | 3.2                   | 1                          |
| 4             | 22        | D/1510                  | T429D226(1)004(2)(3)(4)      | CWR29C(3)226(1)(2)D(5)       | 1.0                  | 8.0                  | 1.3                   | 1                          |
| 4             | 33        | D/1510                  | T429D336(1)004(2)(3)(4)      | CWR29C(3)336(1)(2)D(5)       | 2.0                  | 8.0                  | 1.3                   | 1                          |
| 4             | 33        | E/2010                  | T429E336(1)004(2)(3)(4)      | CWR29C(3)336(1)(2)E(5)       | 2.0                  | 8.0                  | 0.9                   | 1                          |
| 4             | 33        | F/2214                  | T429F336(1)004(2)(3)(4)      | CWR29C(3)336(1)(2)F(5)       | 2.0                  | 8.0                  | 0.6                   | 1                          |
| 4             | 47        | E/2010                  | T429E476(1)004(2)(3)(4)      | CWR29C(3)476(1)(2)E(5)       | 2.0                  | 8.0                  | 0.9                   | 1                          |
| 4             | 68        | E/2010                  | T429E686(1)004(2)(3)(4)      | CWR29C(3)686(1)(2)E(5)       | 3.0                  | 8.0                  | 0.9                   | 1                          |
| 4             | 68        | G/2711                  | T429G686(1)004(2)(3)(4)      | CWR29C(3)686(1)(2)G(5)       | 3.0                  | 10.0                 | 0.275                 | 1                          |
| 4             | 100       | F/2214                  | T429F107(1)004(2)(3)(4)      | CWR29C(3)107(1)(2)F(5)       | 4.0                  | 10.0                 | 0.55                  | 1                          |
| 4             | 100       | H/2915                  | T429H107(1)004(2)(3)(4)      | CWR29C(3)107(1)(2)H(5)       | 4.0                  | 10.0                 | 0.18                  | 1                          |
| 4             | 150       | G/2711                  | T429G157(1)004(2)(3)(4)      | CWR29C(3)157(1)(2)G(5)       | 6.0                  | 10.0                 | 0.25                  | 1                          |
| 4             | 220       | H/2915                  | T429H227(1)004(2)(3)(4)      | CWR29C(3)227(1)(2)H(5)       | 8.0                  | 10.0                 | 0.20                  | 1                          |
| 4             | 330       | H/2915                  | T429H337(1)004(2)(3)(4)      | CWR29C(3)337(1)(2)H(5)       | 10.0                 | 10.0                 | 0.18                  | 1                          |
| 6             | 1.5       | A/1005                  | T429A155(1)006(2)(3)(4)      | CWR29D(3)155(1)(2)A(5)       | 1.0                  | 6.0                  | 4.0                   | 1                          |
| 6             | 3.3       | A/1005                  | T429A335(1)006(2)(3)(4)      | CWR29D(3)335(1)(2)A(5)       | 1.0                  | 6.0                  | 6.0                   | 1                          |
| 6             | 3.3       | B/1505                  | T429B335(1)006(2)(3)(4)      | CWR29D(3)335(1)(2)B(5)       | 1.0                  | 6.0                  | 3.2                   | 1                          |
| 6             | 4.7       | A/1005                  | T429A475(1)006(2)(3)(4)      | CWR29D(3)475(1)(2)A(5)       | 1.0                  | 6.0                  | 6.0                   | 1                          |
| 6             | 4.7       | C/2005                  | T429C475(1)006(2)(3)(4)      | CWR29D(3)475(1)(2)C(5)       | 1.0                  | 6.0                  | 2.2                   | 1                          |
| 6             | 6.8       | B/1505                  | T429B685(1)006(2)(3)(4)      | CWR29D(3)685(1)(2)B(5)       | 1.0                  | 6.0                  | 3.2                   | 1                          |
| 6             | 6.8       | D/1510                  | T429D685(1)006(2)(3)(4)      | CWR29D(3)685(1)(2)D(5)       | 1.0                  | 6.0                  | 1.5                   | 1                          |
| 6             | 10        | B/1505                  | T429B106(1)006(2)(3)(4)      | CWR29D(3)106(1)(2)B(5)       | 1.0                  | 6.0                  | 3.2                   | 1                          |
| 6             | 10        | E/2010                  | T429E106(1)006(2)(3)(4)      | CWR29D(3)106(1)(2)E(5)       | 1.0                  | 8.0                  | 1.0                   | 1                          |
| 6             | 15        | B/1505                  | T429B156(1)006(2)(3)(4)      | CWR29D(3)156(1)(2)B(5)       | 1.0                  | 8.0                  | 3.2                   | 1                          |
| 6             | 15        | D/1510                  | T429D156(1)006(2)(3)(4)      | CWR29D(3)156(1)(2)D(5)       | 1.0                  | 8.0                  | 1.7                   | 1                          |
| 6             | 15        | E/2010                  | T429E156(1)006(2)(3)(4)      | CWR29D(3)156(1)(2)E(5)       | 1.0                  | 8.0                  | 0.9                   | 1                          |
| 6             | 22        | D/1510                  | T429D226(1)006(2)(3)(4)      | CWR29D(3)226(1)(2)D(5)       | 1.0                  | 6.0                  | 1.7                   | 1                          |
| 6             | 22        | E/2010                  | T429E226(1)006(2)(3)(4)      | CWR29D(3)226(1)(2)E(5)       | 2.0                  | 8.0                  | 1.0                   | 1                          |
| 6             | 22        | F/2214                  | T429F226(1)006(2)(3)(4)      | CWR29D(3)226(1)(2)F(5)       | 2.0                  | 8.0                  | 0.6                   | 1                          |
| 6             | 33        | E/2010                  | T429E336(1)006(2)(3)(4)      | CWR29D(3)336(1)(2)E(5)       | 2.0                  | 6.0                  | 1.0                   | 1                          |
| 6             | 47        | F/2214                  | T429F476(1)006(2)(3)(4)      | CWR29D(3)476(1)(2)F(5)       | 3.0                  | 8.0                  | 1.0                   | 1                          |
| 6             | 47        | G/2711                  | T429G476(1)006(2)(3)(4)      | CWR29D(3)476(1)(2)G(5)       | 3.0                  | 10.0                 | 0.275                 | 1                          |
| 6             | 68        | F/2214                  | T429F686(1)006(2)(3)(4)      | CWR29D(3)686(1)(2)F(5)       | 4.0                  | 10.0                 | 0.4                   | 1                          |
| 6             | 68        | G/2711                  | T429G686(1)006(2)(3)(4)      | CWR29D(3)686(1)(2)G(5)       | 4.0                  | 10.0                 | 0.25                  | 1                          |
| 6             | 68        | H/2915                  | T429H686(1)006(2)(3)(4)      | CWR29D(3)686(1)(2)H(5)       | 4.0                  | 10.0                 | 0.18                  | 1                          |
| 6             | 100       | G/2711                  | T429G107(1)006(2)(3)(4)      | CWR29D(3)107(1)(2)G(5)       | 6.0                  | 10.0                 | 0.275                 | 1                          |
| 6             | 150       | G/2711                  | T429G157(1)006(2)(3)(4)      | CWR29D(3)157(1)(2)G(5)       | 10.0                 | 10.0                 | 0.275                 | 1                          |
| 6             | 220       | H/2915                  | T429H227(1)006(2)(3)(4)      | CWR29D(3)227(1)(2)H(5)       | 10.0                 | 10.0                 | 0.18                  | 1                          |
| 6             | 330       | H/2915                  | T429H337(1)006(2)(3)(4)      | CWR29D(3)337(1)(2)H(5)       | 20.0                 | 10.0                 | 0.18                  | 1                          |
| VDC           | µF        | KEMET/EIA               | (See below for part options) | (See below for part options) | µA @ +20°C Max/5 Min | % @ +20°C 120 Hz Max | Ω @ +20°C 100 kHz Max | Reflow Temperature ≤ 260°C |
| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11 Part Number | DC Leakage           | DF                   | ESR                   | Moisture Sensitivity       |

(1) To complete KEMET/CWR part number, insert M for ±20%, K for ±10%, or J for ±5%. Designates Capacitance tolerance.

(2) To complete KEMET/CWR part number, insert failure rate letter per the Ordering Information found on page 2. Designates Reliability Level.

(3) To complete KEMET/CWR part number, insert B = Gold Plated, C = Hot solder dipped, H = Solder plated or K = Solder Fused. Designates Termination Finish.

(4) To complete KEMET part number, insert 4250 = +25°C after Weibull, 4251 = -55°C +85°C after Weibull, or 4252 = -55°C +85°C before Weibull. Designates Surge current option.

(5) To complete CWR part number, insert A = +25°C after Weibull, B = -55°C +85°C after Weibull, C = -55°C +85°C before Weibull or Z = None. Designates Surge current option.

Refer to Ordering Information for additional detail.

Table 1 – Ratings &amp; Part Number Reference cont'd

| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11 Part Number | DC Leakage           | DF                   | ESR                   | Moisture Sensitivity       |
|---------------|-----------|-------------------------|------------------------------|------------------------------|----------------------|----------------------|-----------------------|----------------------------|
| VDC           | µF        | KEMET/EIA               | (See below for part options) | (See below for part options) | µA @ +20°C Max/5 Min | % @ +20°C 120 Hz Max | Ω @ +20°C 100 kHz Max | Reflow Temperature ≤ 260°C |
| 10            | 1         | A/1005                  | T429A105(1)010(2)(3)(4)      | CWR29F(3)105(1)(2)A(5)       | 1.0                  | 6.0                  | 5.0                   | 1                          |
| 10            | 2.2       | A/1005                  | T429A225(1)010(2)(3)(4)      | CWR29F(3)225(1)(2)A(5)       | 1.0                  | 6.0                  | 6.0                   | 1                          |
| 10            | 2.2       | B/1505                  | T429B225(1)010(2)(3)(4)      | CWR29F(3)225(1)(2)B(5)       | 1.0                  | 6.0                  | 3.2                   | 1                          |
| 10            | 3.3       | A/1005                  | T429A335(1)010(2)(3)(4)      | CWR29F(3)335(1)(2)A(5)       | 1.0                  | 6.0                  | 6.0                   | 1                          |
| 10            | 3.3       | C/2005                  | T429C335(1)010(2)(3)(4)      | CWR29F(3)335(1)(2)C(5)       | 1.0                  | 6.0                  | 2.2                   | 1                          |
| 10            | 4.7       | B/1505                  | T429B475(1)010(2)(3)(4)      | CWR29F(3)475(1)(2)B(5)       | 1.0                  | 6.0                  | 3.2                   | 1                          |
| 10            | 4.7       | C/2005                  | T429C475(1)010(2)(3)(4)      | CWR29F(3)475(1)(2)C(5)       | 1.0                  | 6.0                  | 2.2                   | 1                          |
| 10            | 4.7       | D/1510                  | T429D475(1)010(2)(3)(4)      | CWR29F(3)475(1)(2)D(5)       | 1.0                  | 6.0                  | 1.5                   | 1                          |
| 10            | 6.8       | B/1505                  | T429B685(1)010(2)(3)(4)      | CWR29F(3)685(1)(2)B(5)       | 1.0                  | 6.0                  | 3.2                   | 1                          |
| 10            | 6.8       | C/2005                  | T429C685(1)010(2)(3)(4)      | CWR29F(3)685(1)(2)C(5)       | 1.0                  | 6.0                  | 2.2                   | 1                          |
| 10            | 6.8       | D/1510                  | T429D685(1)010(2)(3)(4)      | CWR29F(3)685(1)(2)D(5)       | 1.0                  | 6.0                  | 1.7                   | 1                          |
| 10            | 6.8       | E/2010                  | T429E685(1)010(2)(3)(4)      | CWR29F(3)685(1)(2)E(5)       | 1.0                  | 6.0                  | 1.0                   | 1                          |
| 10            | 10        | B/1505                  | T429B106(1)010(2)(3)(4)      | CWR29F(3)106(1)(2)B(5)       | 1.0                  | 8.0                  | 3.2                   | 1                          |
| 10            | 10        | C/2005                  | T429C106(1)010(2)(3)(4)      | CWR29F(3)106(1)(2)C(5)       | 1.0                  | 6.0                  | 2.2                   | 1                          |
| 10            | 10        | D/1510                  | T429D106(1)010(2)(3)(4)      | CWR29F(3)106(1)(2)D(5)       | 1.0                  | 6.0                  | 1.3                   | 1                          |
| 10            | 10        | E/2010                  | T429E106(1)010(2)(3)(4)      | CWR29F(3)106(1)(2)E(5)       | 1.0                  | 6.0                  | 1.0                   | 1                          |
| 10            | 15        | D/1510                  | T429D156(1)010(2)(3)(4)      | CWR29F(3)156(1)(2)D(5)       | 2.0                  | 6.0                  | 1.7                   | 1                          |
| 10            | 15        | E/2010                  | T429E156(1)010(2)(3)(4)      | CWR29F(3)156(1)(2)E(5)       | 2.0                  | 8.0                  | 0.9                   | 1                          |
| 10            | 15        | F/2214                  | T429F156(1)010(2)(3)(4)      | CWR29F(3)156(1)(2)F(5)       | 2.0                  | 8.0                  | 0.7                   | 1                          |
| 10            | 22        | E/2010                  | T429E226(1)010(2)(3)(4)      | CWR29F(3)226(1)(2)E(5)       | 3.0                  | 8.0                  | 0.6                   | 1                          |
| 10            | 33        | F/2214                  | T429F336(1)010(2)(3)(4)      | CWR29F(3)336(1)(2)F(5)       | 3.0                  | 8.0                  | 0.4                   | 1                          |
| 10            | 33        | G/2711                  | T429G336(1)010(2)(3)(4)      | CWR29F(3)336(1)(2)G(5)       | 3.0                  | 10.0                 | 0.275                 | 1                          |
| 10            | 47        | F/2214                  | T429F476(1)010(2)(3)(4)      | CWR29F(3)476(1)(2)F(5)       | 4.0                  | 10.0                 | 0.4                   | 1                          |
| 10            | 47        | G/2711                  | T429G476(1)010(2)(3)(4)      | CWR29F(3)476(1)(2)G(5)       | 4.0                  | 10.0                 | 0.25                  | 1                          |
| 10            | 47        | H/2915                  | T429H476(1)010(2)(3)(4)      | CWR29F(3)476(1)(2)H(5)       | 5.0                  | 10.0                 | 0.18                  | 1                          |
| 10            | 68        | G/2711                  | T429G686(1)010(2)(3)(4)      | CWR29F(3)686(1)(2)G(5)       | 6.0                  | 10.0                 | 0.275                 | 1                          |
| 10            | 100       | G/2711                  | T429G107(1)010(2)(3)(4)      | CWR29F(3)107(1)(2)G(5)       | 10.0                 | 10.0                 | 0.275                 | 1                          |
| 10            | 100       | H/2915                  | T429H107(1)010(2)(3)(4)      | CWR29F(3)107(1)(2)H(5)       | 10.0                 | 10.0                 | 0.18                  | 1                          |
| 10            | 150       | H/2915                  | T429H157(1)010(2)(3)(4)      | CWR29F(3)157(1)(2)H(5)       | 15.0                 | 10.0                 | 0.18                  | 1                          |
| 10            | 150       | X/2824                  | T429X157(1)010(2)(3)(4)      | CWR29F(3)157(1)(2)X(5)       | 15.0                 | 10.0                 | 0.065                 | 1                          |
| 10            | 220       | H/2915                  | T429H227(1)010(2)(3)(4)      | CWR29F(3)227(1)(2)H(5)       | 20.0                 | 10.0                 | 0.18                  | 1                          |
| 15            | 0.68      | A/1005                  | T429A684(1)015(2)(3)(4)      | CWR29H(3)684(1)(2)A(5)       | 1.0                  | 6.0                  | 6.0                   | 1                          |
| 15            | 1         | A/1005                  | T429A105(1)015(2)(3)(4)      | CWR29H(3)105(1)(2)A(5)       | 1.0                  | 6.0                  | 7.5                   | 1                          |
| 15            | 1.5       | A/1005                  | T429A155(1)015(2)(3)(4)      | CWR29H(3)155(1)(2)A(5)       | 1.0                  | 6.0                  | 7.5                   | 1                          |
| 15            | 1.5       | B/1505                  | T429B155(1)015(2)(3)(4)      | CWR29H(3)155(1)(2)B(5)       | 1.0                  | 6.0                  | 3.2                   | 1                          |
| 15            | 2.2       | A/1005                  | T429A225(1)015(2)(3)(4)      | CWR29H(3)225(1)(2)A(5)       | 1.0                  | 6.0                  | 7.5                   | 1                          |
| 15            | 2.2       | C/2005                  | T429C225(1)015(2)(3)(4)      | CWR29H(3)225(1)(2)C(5)       | 1.0                  | 6.0                  | 2.2                   | 1                          |
| 15            | 3.3       | B/1505                  | T429B335(1)015(2)(3)(4)      | CWR29H(3)335(1)(2)B(5)       | 1.0                  | 6.0                  | 3.6                   | 1                          |
| 15            | 3.3       | D/1510                  | T429D335(1)015(2)(3)(4)      | CWR29H(3)335(1)(2)D(5)       | 1.0                  | 6.0                  | 1.7                   | 1                          |
| 15            | 4.7       | B/1505                  | T429B475(1)015(2)(3)(4)      | CWR29H(3)475(1)(2)B(5)       | 1.0                  | 6.0                  | 2.0                   | 1                          |
| 15            | 4.7       | C/2005                  | T429C475(1)015(2)(3)(4)      | CWR29H(3)475(1)(2)C(5)       | 1.0                  | 6.0                  | 2.2                   | 1                          |
| 15            | 4.7       | D/1510                  | T429D475(1)015(2)(3)(4)      | CWR29H(3)475(1)(2)D(5)       | 1.0                  | 6.0                  | 2.0                   | 1                          |
| 15            | 4.7       | E/2010                  | T429E475(1)015(2)(3)(4)      | CWR29H(3)475(1)(2)E(5)       | 1.0                  | 6.0                  | 1.2                   | 1                          |
| 15            | 6.8       | D/1510                  | T429D685(1)015(2)(3)(4)      | CWR29H(3)685(1)(2)D(5)       | 1.0                  | 6.0                  | 2.0                   | 1                          |
| 15            | 6.8       | E/2010                  | T429E685(1)015(2)(3)(4)      | CWR29H(3)685(1)(2)E(5)       | 1.0                  | 8.0                  | 0.9                   | 1                          |
| 15            | 10        | D/1510                  | T429D106(1)015(2)(3)(4)      | CWR29H(3)106(1)(2)D(5)       | 2.0                  | 6.0                  | 2.0                   | 1                          |
| 15            | 10        | E/2010                  | T429E106(1)015(2)(3)(4)      | CWR29H(3)106(1)(2)E(5)       | 2.0                  | 6.0                  | 1.2                   | 1                          |
| 15            | 10        | F/2214                  | T429F106(1)015(2)(3)(4)      | CWR29H(3)106(1)(2)F(5)       | 2.0                  | 6.0                  | 0.667                 | 1                          |
| VDC           | µF        | KEMET/EIA               | (See below for part options) | (See below for part options) | µA @ +20°C Max/5 Min | % @ +20°C 120 Hz Max | Ω @ +20°C 100 kHz Max | Reflow Temperature ≤ 260°C |
| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11 Part Number | DC Leakage           | DF                   | ESR                   | Moisture Sensitivity       |

(1) To complete KEMET/CWR part number, insert M for ±20%, K for ±10%, or J for ±5%. Designates Capacitance tolerance.

(2) To complete KEMET/CWR part number, insert failure rate letter per the Ordering Information found on page 2. Designates Reliability Level.

(3) To complete KEMET/CWR part number, insert B = Gold Plated, C = Hot solder dipped, H = Solder plated or K = Solder Fused. Designates Termination Finish.

(4) To complete KEMET part number, insert 4250 = +25°C after Weibull, 4251 = -55°C +85°C after Weibull, or 4252 = -55°C +85°C before Weibull. Designates Surge current option.

(5) To complete CWR part number, insert A = +25°C after Weibull, B = -55°C +85°C after Weibull, C = -55°C +85°C before Weibull or Z = None. Designates Surge current option.

Refer to Ordering Information for additional detail.

Table 1 – Ratings &amp; Part Number Reference cont'd

| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11 Part Number | DC Leakage              | DF                      | ESR                      | Moisture Sensitivity          |
|---------------|-----------|-------------------------|------------------------------|------------------------------|-------------------------|-------------------------|--------------------------|-------------------------------|
| VDC           | µF        | KEMET/EIA               | (See below for part options) | (See below for part options) | µA @ +20°C<br>Max/5 Min | % @ +20°C 120<br>Hz Max | Ω @ +20°C<br>100 kHz Max | Reflow Temperature<br>≤ 260°C |
| 15            | 15        | E/2010                  | T429E156(1)015(2)(3)(4)      | CWR29H(3)156(1)(2)E(5)       | 2.0                     | 6.0                     | 1.2                      | 1                             |
| 15            | 15        | F/2214                  | T429F156(1)015(2)(3)(4)      | CWR29H(3)156(1)(2)F(5)       | 2.0                     | 8.0                     | 0.8                      | 1                             |
| 15            | 22        | F/2214                  | T429F226(1)015(2)(3)(4)      | CWR29H(3)226(1)(2)F(5)       | 3.0                     | 8.0                     | 0.8                      | 1                             |
| 15            | 22        | G/2711                  | T429G226(1)015(2)(3)(4)      | CWR29H(3)226(1)(2)G(5)       | 4.0                     | 6.0                     | 0.3                      | 1                             |
| 15            | 33        | F/2214                  | T429F336(1)015(2)(3)(4)      | CWR29H(3)336(1)(2)F(5)       | 5.0                     | 6.0                     | 0.8                      | 1                             |
| 15            | 33        | G/2711                  | T429G336(1)015(2)(3)(4)      | CWR29H(3)336(1)(2)G(5)       | 6.0                     | 8.0                     | 0.3                      | 1                             |
| 15            | 33        | H/2915                  | T429H336(1)015(2)(3)(4)      | CWR29H(3)336(1)(2)H(5)       | 5.0                     | 8.0                     | 0.2                      | 1                             |
| 15            | 47        | G/2711                  | T429G476(1)015(2)(3)(4)      | CWR29H(3)476(1)(2)G(5)       | 10.0                    | 8.0                     | 0.3                      | 1                             |
| 15            | 47        | H/2915                  | T429H476(1)015(2)(3)(4)      | CWR29H(3)476(1)(2)H(5)       | 10.0                    | 8.0                     | 0.2                      | 1                             |
| 15            | 68        | G/2711                  | T429G686(1)015(2)(3)(4)      | CWR29H(3)686(1)(2)G(5)       | 10.0                    | 8.0                     | 0.3                      | 1                             |
| 15            | 68        | H/2915                  | T429H686(1)015(2)(3)(4)      | CWR29H(3)686(1)(2)H(5)       | 10.0                    | 8.0                     | 0.2                      | 1                             |
| 15            | 100       | H/2915                  | T429H107(1)015(2)(3)(4)      | CWR29H(3)107(1)(2)H(5)       | 15.0                    | 10.0                    | 0.2                      | 1                             |
| 20            | 0.47      | A/1005                  | T429A474(1)020(2)(3)(4)      | CWR29J(3)474(1)(2)A(5)       | 1.0                     | 8.0                     | 7.5                      | 1                             |
| 20            | 0.68      | A/1005                  | T429A684(1)020(2)(3)(4)      | CWR29J(3)684(1)(2)A(5)       | 1.0                     | 6.0                     | 7.5                      | 1                             |
| 20            | 0.68      | B/1505                  | T429B684(1)020(2)(3)(4)      | CWR29J(3)684(1)(2)B(5)       | 1.0                     | 6.0                     | 5.6                      | 1                             |
| 20            | 1         | A/1005                  | T429A105(1)020(2)(3)(4)      | CWR29J(3)105(1)(2)A(5)       | 1.0                     | 6.0                     | 7.5                      | 1                             |
| 20            | 1         | B/1505                  | T429B105(1)020(2)(3)(4)      | CWR29J(3)105(1)(2)B(5)       | 1.0                     | 6.0                     | 4.8                      | 1                             |
| 20            | 1.5       | B/1505                  | T429B155(1)020(2)(3)(4)      | CWR29J(3)155(1)(2)B(5)       | 1.0                     | 6.0                     | 3.6                      | 1                             |
| 20            | 1.5       | C/2005                  | T429C155(1)020(2)(3)(4)      | CWR29J(3)155(1)(2)C(5)       | 1.0                     | 6.0                     | 2.4                      | 1                             |
| 20            | 2.2       | B/1505                  | T429B225(1)020(2)(3)(4)      | CWR29J(3)225(1)(2)B(5)       | 1.0                     | 6.0                     | 3.6                      | 1                             |
| 20            | 2.2       | D/1510                  | T429D225(1)020(2)(3)(4)      | CWR29J(3)225(1)(2)D(5)       | 1.0                     | 6.0                     | 1.7                      | 1                             |
| 20            | 3.3       | D/1510                  | T429D335(1)020(2)(3)(4)      | CWR29J(3)335(1)(2)D(5)       | 1.0                     | 6.0                     | 2.0                      | 1                             |
| 20            | 3.3       | E/2010                  | T429E335(1)020(2)(3)(4)      | CWR29J(3)335(1)(2)E(5)       | 1.0                     | 6.0                     | 1.2                      | 1                             |
| 20            | 4.7       | E/2010                  | T429E475(1)020(2)(3)(4)      | CWR29J(3)475(1)(2)E(5)       | 1.0                     | 6.0                     | 1.7                      | 1                             |
| 20            | 6.8       | E/2010                  | T429E685(1)020(2)(3)(4)      | CWR29J(3)685(1)(2)E(5)       | 2.0                     | 6.0                     | 1.5                      | 1                             |
| 20            | 6.8       | F/2214                  | T429F685(1)020(2)(3)(4)      | CWR29J(3)685(1)(2)F(5)       | 2.0                     | 6.0                     | 0.7                      | 1                             |
| 20            | 10        | E/2010                  | T429E106(1)020(2)(3)(4)      | CWR29J(3)106(1)(2)E(5)       | 2.0                     | 6.0                     | 1.5                      | 1                             |
| 20            | 10        | F/2214                  | T429F106(1)020(2)(3)(4)      | CWR29J(3)106(1)(2)F(5)       | 2.0                     | 6.0                     | 0.8                      | 1                             |
| 20            | 15        | F/2214                  | T429F156(1)020(2)(3)(4)      | CWR29J(3)156(1)(2)F(5)       | 3.0                     | 6.0                     | 0.8                      | 1                             |
| 20            | 15        | G/2711                  | T429G156(1)020(2)(3)(4)      | CWR29J(3)156(1)(2)G(5)       | 3.0                     | 6.0                     | 0.275                    | 1                             |
| 20            | 22        | G/2711                  | T429G226(1)020(2)(3)(4)      | CWR29J(3)226(1)(2)G(5)       | 4.0                     | 6.0                     | 0.625                    | 1                             |
| 20            | 22        | H/2915                  | T429H226(1)020(2)(3)(4)      | CWR29J(3)226(1)(2)H(5)       | 4.0                     | 6.0                     | 0.18                     | 1                             |
| 20            | 33        | H/2915                  | T429H336(1)020(2)(3)(4)      | CWR29J(3)336(1)(2)H(5)       | 6.0                     | 8.0                     | 0.18                     | 1                             |
| 20            | 47        | H/2915                  | T429H476(1)020(2)(3)(4)      | CWR29J(3)476(1)(2)H(5)       | 10.0                    | 8.0                     | 0.18                     | 1                             |
| 20            | 47        | X/2824                  | T429X476(1)020(2)(3)(4)      | CWR29J(3)476(1)(2)X(5)       | 10.0                    | 8.0                     | 0.11                     | 1                             |
| 25            | 0.33      | A/1005                  | T429A334(1)025(2)(3)(4)      | CWR29K(3)334(1)(2)A(5)       | 1.0                     | 6.0                     | 7.5                      | 1                             |
| 25            | 0.47      | A/1005                  | T429A474(1)025(2)(3)(4)      | CWR29K(3)474(1)(2)A(5)       | 1.0                     | 6.0                     | 7.5                      | 1                             |
| 25            | 0.68      | B/1505                  | T429B684(1)025(2)(3)(4)      | CWR29K(3)684(1)(2)B(5)       | 1.0                     | 6.0                     | 4.0                      | 1                             |
| 25            | 1         | B/1505                  | T429B105(1)025(2)(3)(4)      | CWR29K(3)105(1)(2)B(5)       | 1.0                     | 6.0                     | 4.0                      | 1                             |
| 25            | 1         | C/2005                  | T429C105(1)025(2)(3)(4)      | CWR29K(3)105(1)(2)C(5)       | 1.0                     | 6.0                     | 2.6                      | 1                             |
| 25            | 1.5       | D/1510                  | T429D155(1)025(2)(3)(4)      | CWR29K(3)155(1)(2)D(5)       | 1.0                     | 6.0                     | 1.7                      | 1                             |
| 25            | 2.2       | D/1510                  | T429D225(1)025(2)(3)(4)      | CWR29K(3)225(1)(2)D(5)       | 1.0                     | 6.0                     | 2.0                      | 1                             |
| 25            | 2.2       | E/2010                  | T429E225(1)025(2)(3)(4)      | CWR29K(3)225(1)(2)E(5)       | 1.0                     | 6.0                     | 1.0                      | 1                             |
| 25            | 3.3       | E/2010                  | T429E335(1)025(2)(3)(4)      | CWR29K(3)335(1)(2)E(5)       | 1.0                     | 6.0                     | 1.2                      | 1                             |
| 25            | 4.7       | F/2214                  | T429F475(1)025(2)(3)(4)      | CWR29K(3)475(1)(2)F(5)       | 2.0                     | 6.0                     | 0.7                      | 1                             |
| 25            | 6.8       | F/2214                  | T429F685(1)025(2)(3)(4)      | CWR29K(3)685(1)(2)F(5)       | 2.0                     | 6.0                     | 0.8                      | 1                             |
| 25            | 6.8       | G/2711                  | T429G685(1)025(2)(3)(4)      | CWR29K(3)685(1)(2)G(5)       | 2.0                     | 6.0                     | 0.3                      | 1                             |
| 25            | 10        | G/2711                  | T429G106(1)025(2)(3)(4)      | CWR29K(3)106(1)(2)G(5)       | 3.0                     | 6.0                     | 0.35                     | 1                             |
| VDC           | µF        | KEMET/EIA               | (See below for part options) | (See below for part options) | µA @ +20°C<br>Max/5 Min | % @ +20°C 120<br>Hz Max | Ω @ +20°C<br>100 kHz Max | Reflow Temperature<br>≤ 260°C |
| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11 Part Number | DC Leakage              | DF                      | ESR                      | Moisture Sensitivity          |

(1) To complete KEMET/CWR part number, insert M for ±20%, K for ±10%, or J for ±5%. Designates Capacitance tolerance.

(2) To complete KEMET/CWR part number, insert failure rate letter per the Ordering Information found on page 2. Designates Reliability Level.

(3) To complete KEMET/CWR part number, insert B = Gold Plated, C = Hot solder dipped, H = Solder plated or K = Solder Fused. Designates Termination Finish.

(4) To complete KEMET part number, insert 4250 = +25°C after Weibull, 4251 = -55°C +85°C after Weibull, or 4252 = -55°C +85°C before Weibull. Designates Surge current option.

(5) To complete CWR part number, insert A = +25°C after Weibull, B = -55°C +85°C after Weibull, C = -55°C +85°C before Weibull or Z = None. Designates Surge current option.

Refer to Ordering Information for additional detail.

Table 1 – Ratings &amp; Part Number Reference cont'd

| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11 Part Number | DC Leakage           | DF                   | ESR                   | Moisture Sensitivity       |
|---------------|-----------|-------------------------|------------------------------|------------------------------|----------------------|----------------------|-----------------------|----------------------------|
| VDC           | μF        | KEMET/EIA               | (See below for part options) | (See below for part options) | μA @ +20°C Max/5 Min | % @ +20°C 120 Hz Max | Ω @ +20°C 100 kHz Max | Reflow Temperature ≤ 260°C |
| 25            | 15        | G/2711                  | T429G156(1)025(2)(3)(4)      | CWR29K(3)156(1)(2)G(5)       | 4.0                  | 6.0                  | 0.35                  | 1                          |
| 25            | 15        | H/2915                  | T429H156(1)025(2)(3)(4)      | CWR29K(3)156(1)(2)H(5)       | 4.0                  | 6.0                  | 0.2                   | 1                          |
| 25            | 22        | G/2711                  | T429G226(1)025(2)(3)(4)      | CWR29K(3)226(1)(2)G(5)       | 6.0                  | 6.0                  | 0.35                  | 1                          |
| 25            | 22        | H/2915                  | T429H226(1)025(2)(3)(4)      | CWR29K(3)226(1)(2)H(5)       | 6.0                  | 6.0                  | 0.18                  | 1                          |
| 25            | 22        | X/2824                  | T429X226(1)025(2)(3)(4)      | CWR29K(3)226(1)(2)X(5)       | 6.0                  | 6.0                  | 0.16                  | 1                          |
| 25            | 33        | H/2915                  | T429H336(1)025(2)(3)(4)      | CWR29K(3)336(1)(2)H(5)       | 10.0                 | 8.0                  | 0.18                  | 1                          |
| 25            | 33        | X/2824                  | T429X336(1)025(2)(3)(4)      | CWR29K(3)336(1)(2)X(5)       | 10.0                 | 8.0                  | 0.13                  | 1                          |
| 35            | 0.22      | A/1005                  | T429A224(1)035(2)(3)(4)      | CWR29M(3)224(1)(2)A(5)       | 1.0                  | 6.0                  | 12.0                  | 1                          |
| 35            | 0.33      | A/1005                  | T429A334(1)035(2)(3)(4)      | CWR29M(3)334(1)(2)A(5)       | 1.0                  | 6.0                  | 12.0                  | 1                          |
| 35            | 0.47      | B/1505                  | T429B474(1)035(2)(3)(4)      | CWR29M(3)474(1)(2)B(5)       | 1.0                  | 6.0                  | 6.8                   | 1                          |
| 35            | 0.68      | C/2005                  | T429C684(1)035(2)(3)(4)      | CWR29M(3)684(1)(2)C(5)       | 1.0                  | 6.0                  | 4.0                   | 1                          |
| 35            | 1         | D/1510                  | T429D105(1)035(2)(3)(4)      | CWR29M(3)105(1)(2)D(5)       | 1.0                  | 6.0                  | 2.2                   | 1                          |
| 35            | 1.5       | E/2010                  | T429E155(1)035(2)(3)(4)      | CWR29M(3)155(1)(2)E(5)       | 1.0                  | 6.0                  | 1.3                   | 1                          |
| 35            | 3.3       | F/2214                  | T429F335(1)035(2)(3)(4)      | CWR29M(3)335(1)(2)F(5)       | 1.0                  | 6.0                  | 0.7                   | 1                          |
| 35            | 4.7       | G/2711                  | T429G475(1)035(2)(3)(4)      | CWR29M(3)475(1)(2)G(5)       | 2.0                  | 6.0                  | 0.375                 | 1                          |
| 35            | 6.8       | F/2214                  | T429F685(1)035(2)(3)(4)      | CWR29M(3)685(1)(2)F(5)       | 3.0                  | 6.0                  | 0.375                 | 1                          |
| 35            | 6.8       | H/2915                  | T429H685(1)035(2)(3)(4)      | CWR29M(3)685(1)(2)H(5)       | 3.0                  | 6.0                  | 0.5                   | 1                          |
| 35            | 10        | H/2915                  | T429H106(1)035(2)(3)(4)      | CWR29M(3)106(1)(2)H(5)       | 4.0                  | 8.0                  | 0.5                   | 1                          |
| 35            | 15        | X/2824                  | T429X156(1)035(2)(3)(4)      | CWR29M(3)156(1)(2)X(5)       | 6.0                  | 6.0                  | 0.19                  | 1                          |
| 50            | 0.1       | A/1005                  | T429A104(1)050(2)(3)(4)      | CWR29N(3)104(1)(2)A(5)       | 1.0                  | 6.0                  | 12.0                  | 1                          |
| 50            | 0.15      | A/1005                  | T429A154(1)050(2)(3)(4)      | CWR29N(3)154(1)(2)A(5)       | 1.0                  | 6.0                  | 12.0                  | 1                          |
| 50            | 0.22      | B/1505                  | T429B224(1)050(2)(3)(4)      | CWR29N(3)224(1)(2)B(5)       | 1.0                  | 6.0                  | 6.8                   | 1                          |
| 50            | 0.33      | B/1505                  | T429B334(1)050(2)(3)(4)      | CWR29N(3)334(1)(2)B(5)       | 1.0                  | 6.0                  | 4.8                   | 1                          |
| 50            | 0.47      | C/2005                  | T429C474(1)050(2)(3)(4)      | CWR29N(3)474(1)(2)C(5)       | 1.0                  | 6.0                  | 3.2                   | 1                          |
| 50            | 0.68      | D/1510                  | T429D684(1)050(2)(3)(4)      | CWR29N(3)684(1)(2)D(5)       | 1.0                  | 6.0                  | 2.3                   | 1                          |
| 50            | 1         | E/2010                  | T429E105(1)050(2)(3)(4)      | CWR29N(3)105(1)(2)E(5)       | 1.0                  | 6.0                  | 1.7                   | 1                          |
| 50            | 1.5       | F/2214                  | T429F155(1)050(2)(3)(4)      | CWR29N(3)155(1)(2)F(5)       | 1.0                  | 6.0                  | 1.1                   | 1                          |
| 50            | 2.2       | F/2214                  | T429F225(1)050(2)(3)(4)      | CWR29N(3)225(1)(2)F(5)       | 2.0                  | 6.0                  | 0.7                   | 1                          |
| 50            | 3.3       | G/2711                  | T429G335(1)050(2)(3)(4)      | CWR29N(3)335(1)(2)G(5)       | 2.0                  | 6.0                  | 0.5                   | 1                          |
| 50            | 4.7       | H/2915                  | T429H475(1)050(2)(3)(4)      | CWR29N(3)475(1)(2)H(5)       | 3.0                  | 6.0                  | 0.5                   | 1                          |
| VDC           | μF        | KEMET/EIA               | (See below for part options) | (See below for part options) | μA @ +20°C Max/5 Min | % @ +20°C 120 Hz Max | Ω @ +20°C 100 kHz Max | Reflow Temperature ≤ 260°C |
| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL-PRF-55365/11 Part Number | DC Leakage           | DF                   | ESR                   | Moisture Sensitivity       |

(1) To complete KEMET/CWR part number, insert M for ±20%, K for ±10%, or J for ±5%. Designates Capacitance tolerance.

(2) To complete KEMET/CWR part number, insert failure rate letter per the Ordering Information found on page 2. Designates Reliability Level.

(3) To complete KEMET/CWR part number, insert B = Gold Plated, C = Hot solder dipped, H = Solder plated or K = Solder Fused. Designates Termination Finish.

(4) To complete KEMET part number, insert 4250 = +25°C after Weibull, 4251 = -55°C +85°C after Weibull, or 4252 = -55°C +85°C before Weibull. Designates Surge current option.

(5) To complete CWR part number, insert A = +25°C after Weibull, B = -55°C +85°C after Weibull, C = -55°C +85°C before Weibull or Z = None. Designates Surge current option.

Refer to Ordering Information for additional detail.

## Recommended Voltage Derating Guidelines

|                                                 | -55°C to 85°C | 85°C to 125°C |
|-------------------------------------------------|---------------|---------------|
| % Change in Working DC Voltage with Temperature | $V_R$         | 67% of $V_R$  |
| Recommended Maximum Application Voltage         | 50% of $V_R$  | 33% of $V_R$  |



## Ripple Current/Ripple Voltage

Permissible AC ripple voltage and current are related to equivalent series resistance (ESR) and the power dissipation capabilities of the device. Permissible AC ripple voltage which may be applied is limited by two criteria:

1. The positive peak AC voltage plus the DC bias voltage, if any, must not exceed the DC voltage rating of the capacitor.
2. The negative peak AC voltage in combination with bias voltage, if any, must not exceed the allowable limits specified for reverse voltage. See the Reverse Voltage section for allowable limits.

The maximum power dissipation by case size can be determined using the table at right. The maximum power dissipation rating stated in the table must be reduced with increasing environmental operating temperatures. Refer to the table below for temperature compensation requirements.

| KEMET Case Code | EIA Case Code | Maximum Power Dissipation (P max) mWatts @ 25°C w/+20°C Rise |
|-----------------|---------------|--------------------------------------------------------------|
| A               | 1005          | 50                                                           |
| B               | 1505          | 70                                                           |
| C               | 2005          | 75                                                           |
| D               | 1510          | 80                                                           |
| E               | 2010          | 90                                                           |
| F               | 2214          | 100                                                          |
| G               | 2711          | 125                                                          |
| H               | 2915          | 150                                                          |

The maximum power dissipation rating must be reduced with increasing environmental operating temperatures. Refer to the Temperature Compensation Multiplier table for details.

| Temperature Compensation Multipliers for Maximum Power Dissipation |          |           |
|--------------------------------------------------------------------|----------|-----------|
| T ≤ 25°C                                                           | T ≤ 85°C | T ≤ 125°C |
| 1.00                                                               | 0.90     | 0.40      |

T = Environmental Temperature

Using the P max of the device, the maximum allowable rms ripple current or voltage may be determined.

$$I(max) = \sqrt{P_{max}/R}$$

$$E(max) = Z \sqrt{P_{max}/R}$$

I = rms ripple current (amperes)

E = rms ripple voltage (volts)

P max = maximum power dissipation (watts)

R = ESR at specified frequency (ohms)

Z = Impedance at specified frequency (ohms)

## Reverse Voltage

Solid tantalum capacitors are polar devices and may be permanently damaged or destroyed if connected with the wrong polarity. The positive terminal is identified on the capacitor body by a stripe plus in some cases a beveled edge. A small degree of transient reverse voltage is permissible for short periods per the table. The capacitors should not be operated continuously in reverse mode, even within these limits.

| Temperature | Permissible Transient Reverse Voltage |
|-------------|---------------------------------------|
| 25°C        | 15% of Rated Voltage                  |
| 85°C        | 5% of Rated Voltage                   |
| 125°C       | 1% of Rated Voltage                   |

**Table 2 – Land Dimensions/Courtyard**


| KEMET          | Metric Size Code | Density Level A:<br>Maximum (Most) Land Protrusion (mm) |      |      |       |      | Density Level B:<br>Median (Nominal) Land Protrusion (mm) |      |      |      |      | Density Level C:<br>Minimum (Least) Land Protrusion (mm) |      |      |      |      |
|----------------|------------------|---------------------------------------------------------|------|------|-------|------|-----------------------------------------------------------|------|------|------|------|----------------------------------------------------------|------|------|------|------|
|                |                  | L                                                       | W    | S    | V1    | V2   | L                                                         | W    | S    | V1   | V2   | L                                                        | W    | S    | V1   | V2   |
| A <sup>1</sup> | 1005             | 2.19                                                    | 1.44 | 0.15 | 5.54  | 2.66 | 1.89                                                      | 1.32 | 0.15 | 4.44 | 2.16 | 1.52                                                     | 1.22 | 0.29 | 3.58 | 1.90 |
| B              | 1505             | 2.30                                                    | 1.44 | 1.20 | 6.80  | 2.66 | 1.90                                                      | 1.32 | 1.40 | 5.70 | 2.16 | 1.52                                                     | 1.22 | 1.56 | 4.84 | 1.90 |
| C              | 2005             | 2.30                                                    | 1.44 | 2.47 | 8.08  | 2.66 | 1.90                                                      | 1.32 | 2.67 | 6.98 | 2.16 | 1.52                                                     | 1.22 | 2.83 | 6.12 | 1.90 |
| D              | 1510             | 2.30                                                    | 2.58 | 1.20 | 6.80  | 3.92 | 1.90                                                      | 2.46 | 1.40 | 5.70 | 3.42 | 1.52                                                     | 2.36 | 1.56 | 4.84 | 3.16 |
| E              | 2010             | 2.30                                                    | 2.58 | 2.47 | 8.08  | 3.92 | 1.90                                                      | 2.46 | 2.67 | 6.98 | 3.42 | 1.52                                                     | 2.36 | 2.83 | 6.12 | 3.16 |
| F              | 2214             | 2.30                                                    | 3.47 | 2.98 | 8.58  | 4.82 | 1.90                                                      | 3.35 | 3.18 | 7.48 | 4.32 | 1.52                                                     | 3.25 | 3.34 | 6.62 | 4.06 |
| G              | 2711             | 2.81                                                    | 2.84 | 3.10 | 9.72  | 4.18 | 2.41                                                      | 2.72 | 3.30 | 8.62 | 3.68 | 2.03                                                     | 2.62 | 3.46 | 7.76 | 3.42 |
| H              | 2915             | 2.81                                                    | 3.84 | 3.61 | 10.24 | 5.20 | 2.41                                                      | 3.72 | 3.81 | 9.14 | 4.70 | 2.03                                                     | 3.62 | 3.97 | 8.28 | 4.44 |
| X              | 2824             | 2.73                                                    | 3.22 | 3.46 | 9.92  | 6.80 | 2.33                                                      | 3.10 | 3.66 | 8.82 | 6.30 | 1.95                                                     | 3.00 | 3.82 | 7.96 | 6.04 |

**Density Level A:** For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes.

**Density Level B:** For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes.

**Density Level C:** For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC standard 7351 (IPC-7351).

<sup>1</sup> Land pattern geometry is too small for silkscreen outline.



## Soldering Process

KEMET's families of surface mount capacitors are compatible with wave (single or dual), convection, IR, or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/J-STD-020D standard for moisture sensitivity testing. The devices can safely withstand a maximum of three reflow passes at these conditions.

Note that although the X/7343-43 case size can withstand wave soldering, the tall profile (4.3 mm maximum) dictates care in wave process development.

Hand soldering should be performed with care due to the difficulty in process control. If performed, care should be taken to avoid contact of the soldering iron to the molded case. The iron should be used to heat the solder pad, applying solder between the pad and the termination, until reflow occurs. Once reflow occurs, the iron should be removed immediately. "Wiping" the edges of a chip and heating the top surface is not recommended.

During typical reflow operations, a slight darkening of the gold-colored epoxy may be observed. This slight darkening is normal and not harmful to the product. Marking permanency is not affected by this change.

| Profile Feature                                       | SnPb Assembly       | Pb-Free Assembly    |
|-------------------------------------------------------|---------------------|---------------------|
| <b>Preheat/Soak</b>                                   |                     |                     |
| Temperature Minimum ( $T_{smin}$ )                    | 100°C               | 150°C               |
| Temperature Maximum ( $T_{smax}$ )                    | 150°C               | 200°C               |
| Time ( $t_s$ ) from $T_{smin}$ to $T_{smax}$          | 60 – 120 seconds    | 60 – 120 seconds    |
| Ramp-up Rate ( $T_L$ to $T_P$ )                       | 3°C/seconds maximum | 3°C/seconds maximum |
| Liquidous Temperature ( $T_L$ )                       | 183°C               | 217°C               |
| Time Above Liquidous ( $t_L$ )                        | 60 – 150 seconds    | 60 – 150 seconds    |
| Peak Temperature ( $T_P$ )                            | 220°C*<br>235°C**   | 250°C*<br>260°C**   |
| Time within 5°C of Maximum Peak Temperature ( $t_p$ ) | 20 seconds maximum  | 30 seconds maximum  |
| Ramp-down Rate ( $T_P$ to $T_L$ )                     | 6°C/seconds maximum | 6°C/seconds maximum |
| Time 25°C to Peak Temperature                         | 6 minutes maximum   | 8 minutes maximum   |

*Note: All temperatures refer to the center of the package, measured on the package body surface that is facing up during assembly reflow.*

\*Case Size D, E, P, Y, and X

\*\*Case Size A, B, C, H, I, K, M, R, S, T, U, V, W, and Z



## Construction



## Capacitor Marking



\* 230 = 30<sup>th</sup> week of 2012

| Date Code *                                                  |                                                                                 |
|--------------------------------------------------------------|---------------------------------------------------------------------------------|
| 1 <sup>st</sup> digit = Last number of Year                  | 9 = 2009<br>0 = 2010<br>1 = 2011<br>2 = 2012<br>3 = 2013<br>4 = 2014            |
| 2 <sup>nd</sup> and 3 <sup>rd</sup> digit = Week of the Year | 01 = 1 <sup>st</sup> week of the Year<br>52 = 52 <sup>nd</sup> week of the Year |

## Storage

Tantalum chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature— reels may soften or warp and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 60% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts and atmospheres should be free of chlorine and sulphur bearing compounds. For optimized solderability chip stock should be used promptly, preferably within three years of receipt.

## Overview

The KEMET T492 Series is approved to MIL-PRF-55365/8 (CWR11) with Weibull failure rates of B level (0.1% failures per 1,000 hours), C level (0.01% failures per 1,000 hours), D level (0.001% failures per 1,000 hours), or T level (0.01% failures per 1,000 hours), Option C surge current, DPA, Radiographic inspection, 100% visual inspection, DCL and ESR measure-

ments within +3 standard deviations, and Group C inspection). This CWR11 product is a precision-molded device with compliant terminations and indelible laser marking. This is the military version of the global IEC/EIA standard represented by KEMET's T491 Series. Tape and reeling per EIA 481-1 is standard.

## Benefits

- Established reliability options
- Taped and reeled per EIA 481-1
- Symmetrical, compliant terminations
- Laser-marked case
- 100% surge current test available on all case sizes
- Qualified to MIL-PRF-55365/8, Style CWR11
- Termination options B, C, H, K
- Weibull failure options B, C, D, and T
- Exponential failure rates M, P, R, S
- Voltage rating of 4 – 50 VDC
- Operating temperature range of -55°C to +125°C

## Applications

Typical applications include decoupling and filtering in military and aerospace applications requiring CWR11 devices.



## Environmental Compliance

RoHS Compliant (6/6) according to Directive 2002/95/EC when ordered with 100% Sn Solder.



RoHS Compliant

## SPICE

For a detailed analysis of specific part numbers, please visit [www.kemet.com](http://www.kemet.com) for a free download of KEMET's SPICE software. The KEMET SPICE program is freeware intended to aid design engineers in analyzing the performance of these capacitors over frequency, temperature, ripple, and DC bias conditions.

## KEMET Ordering Information

| T               | 492                              | D          | 156                                                                                    | K                                                 | 020                                                                                             | A                                                                                                                                                                                                                                                           | C                                                                                                               | 4251                                                                                                                                       |
|-----------------|----------------------------------|------------|----------------------------------------------------------------------------------------|---------------------------------------------------|-------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Capacitor Class | Series                           | Case Size  | Capacitance Code (pF)                                                                  | Capacitance Tolerance                             | Voltage                                                                                         | Failure Rate/Design                                                                                                                                                                                                                                         | Lead Material                                                                                                   | Surge (C-Spec)                                                                                                                             |
| T = Tantalum    | CWR11<br>Established Reliability | A, B, C, D | First two digits represent significant figures. Third digit specifies number of zeros. | J = $\pm 5\%$<br>K = $\pm 10\%$<br>M = $\pm 20\%$ | 006 = 6.3 V<br>010 = 10 V<br>015 = 15 V<br>020 = 20 V<br>025 = 25 V<br>035 = 35 V<br>050 = 50 V | Weibull<br>A = non-ER<br>B = (0.1%/1,000 hours)<br>C = (0.01%/1,000 hours)<br>D = (0.001%/1,000 hours)<br>T = (0.01%/1,000 hours)<br>Exponential<br>M = (1.0%/1,000 hours)<br>P = (0.1%/1,000 hours)<br>R = (0.01%/1,000 hours)<br>S = (0.001%/1,000 hours) | C = Hot Solder Dipped<br>H = Standard Solder Coated (SnPb 5% Pb minimum)<br>B = Gold Plated<br>K = Solder Fused | 4250 = 25°C after Weibull<br>4251 = -55°C and 85°C after Weibull<br>4252 = -55°C and 85°C before Weibull<br>TLVL = Weibull Grade Level "T" |

## Defense MIL–PRF–55365/8 Ordering Information

| CWR11               | M                                                                                          | H                                                                                 | 105                                                                                    | K                                                 | B                                                                                                                                                                                                                                                                    | A                                                                                                      |
|---------------------|--------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|---------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------|
| Capacitor Style     | Voltage                                                                                    | Termination Finish                                                                | Capacitance Code (pF)                                                                  | Capacitance Tolerance                             | Reliability Level                                                                                                                                                                                                                                                    | Surge Current Option                                                                                   |
| Per MIL–PRF–55365/8 | C = 4 V<br>D = 6 V<br>F = 10 V<br>H = 15 V<br>J = 20 V<br>K = 25 V<br>M = 35 V<br>N = 50 V | B = Gold Plated<br>C = Hot solder dipped<br>H = Solder Plated<br>K = Solder fused | First two digits represent significant figures. Third digit specifies number of zeros. | J = $\pm 5\%$<br>K = $\pm 10\%$<br>M = $\pm 20\%$ | Weibull<br>A = non-ER<br>B = (0.1%/1,000 hours)<br>C = (0.01%/1,000 hours)<br>D = (0.001%/1,000 hours)<br>T = T Level* (0.01%/1,000 hours)<br>Exponential<br>M = (1.0%/1,000 hours)<br>P = (0.1%/1,000 hours)<br>R = (0.01%/1,000 hours)<br>S = (0.001%/1,000 hours) | A = +25°C after Weibull<br>B = -55°C +85°C after Weibull<br>C = -55°C +85°C before Weibull<br>Z = None |

\* When T Level is ordered, no Surge Current Option is needed

## Performance Characteristics

| Item                    | Performance Characteristics                                |
|-------------------------|------------------------------------------------------------|
| Operating Temperature   | -55°C to 125°C                                             |
| Rated Capacitance Range | 0.1 – 100 $\mu$ F @ 120 Hz/25°C                            |
| Capacitance Tolerance   | J Tolerance (5%), K Tolerance (10%), M Tolerance (20%)     |
| Rated Voltage Range     | 4 – 50 V                                                   |
| DF (120 Hz)             | Refer to Part Number Electrical Specification Table        |
| ESR (100 kHz)           | Refer to Part Number Electrical Specification Table        |
| Leakage Current         | $\leq 0.01$ CV ( $\mu$ A) at rated voltage after 5 minutes |

## Qualification

| Test                                                  | Condition                                                                                                                 |       | Characteristics |                              |          |          |
|-------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|-------|-----------------|------------------------------|----------|----------|
| Endurance                                             | 85°C @ rated voltage, 2,000 hours<br>125°C @ 2/3 rated voltage, 2,000 hours                                               |       | Δ C/C           | Within ±10% of initial value |          |          |
|                                                       |                                                                                                                           |       | DF              | Within initial limits        |          |          |
|                                                       |                                                                                                                           |       | DCL             | Within 1.25 x initial limit  |          |          |
|                                                       |                                                                                                                           |       | ESR             | Within initial limits        |          |          |
| Storage Life                                          | 125°C @ 0 volts, 2,000 hours                                                                                              |       | Δ C/C           | Within ±10% of initial value |          |          |
|                                                       |                                                                                                                           |       | DF              | Within initial limits        |          |          |
|                                                       |                                                                                                                           |       | DCL             | Within 1.25 x initial limit  |          |          |
|                                                       |                                                                                                                           |       | ESR             | Within initial limits        |          |          |
| Thermal Shock                                         | MIL–STD–202, Method 107, Condition B, mounted,<br>-55°C to 125°C, 1,000 cycles                                            |       | Δ C/C           | Within ±5% of initial value  |          |          |
|                                                       |                                                                                                                           |       | DF              | Within initial limits        |          |          |
|                                                       |                                                                                                                           |       | DCL             | Within 1.25 x initial limit  |          |          |
|                                                       |                                                                                                                           |       | ESR             | Within initial limits        |          |          |
| Temperature Stability                                 | Extreme temperature exposure at a<br>succession of continuous steps at +25°C,<br>-55°C, +25°C, +85°C, +125°C, +25°C       | Δ C/C | +25°C           | -55°C                        | +85°C    | +125°C   |
|                                                       |                                                                                                                           | DF    | IL*             | ±10%                         | ±10%     | ±20%     |
|                                                       |                                                                                                                           | DCL   | IL              | IL                           | 1.5 x IL | 1.5 x IL |
|                                                       |                                                                                                                           | DCL   | IL              | n/a                          | 10 x IL  | 12 x IL  |
| Surge Voltage                                         | 25°C and 85°C, 1.32 x rated voltage 1,000 cycles<br>(125°C, 1.2 x rated voltage)                                          |       | Δ C/C           | Within ±5% of initial value  |          |          |
|                                                       |                                                                                                                           |       | DF              | Within initial limits        |          |          |
|                                                       |                                                                                                                           |       | DCL             | Within initial limits        |          |          |
|                                                       |                                                                                                                           |       | ESR             | Within initial limits        |          |          |
| Mechanical Shock/Vibration                            | MIL–STD–202, Method 213, Condition I, 100 G peak<br>MIL–STD–202, Method 204, Condition D, 10 Hz to 2,000 Hz,<br>20 G peak |       | Δ C/C           | Within ±10% of initial value |          |          |
|                                                       |                                                                                                                           |       | DF              | Within initial limits        |          |          |
|                                                       |                                                                                                                           |       | DCL             | Within initial limits        |          |          |
| Additional qualification tests<br>per MIL–PRF–55365/8 | Please contact KEMET for more information.                                                                                |       |                 |                              |          |          |

\*IL = Initial Limit

## Certification

MIL–PRF–55365/8

## Electrical Characteristics

ESR vs. Frequency



Capacitance vs. Frequency



## Dimensions – Millimeters (Inches)

Metric will govern



| Case Size | Component                    |                           |                              |                      |                              |                                   |
|-----------|------------------------------|---------------------------|------------------------------|----------------------|------------------------------|-----------------------------------|
| KEMET     | H*                           | H <sub>2</sub><br>Minimum | L                            | P +/- 0.3<br>(0.012) | W                            | W <sub>2</sub> +/- 0.1<br>(0.004) |
| A         | 1.6 ± 0.2<br>(0.063 ± 0.008) | 0.7 (0.028)               | 3.2 ± 0.2<br>(0.126 ± 0.008) | 0.8 (0.031)          | 1.6 ± 0.2<br>(0.063 ± 0.008) | 1.2 (0.047)                       |
| B         | 1.9 ± 0.2<br>(0.075 ± 0.008) | 0.7 (0.028)               | 3.5 ± 0.2<br>(0.138 ± 0.008) | 0.8 (0.031)          | 2.8 ± 0.2<br>(0.110 ± 0.008) | 2.2 (0.087)                       |
| C         | 2.5 ± 0.3<br>(0.098 ± 0.012) | 1.0 (0.039)               | 6.0 ± 0.3<br>(0.236 ± 0.012) | 1.3 (0.051)          | 3.2 ± 0.3<br>(0.126 ± 0.012) | 2.2 (0.087)                       |
| D         | 2.8 ± 0.3<br>(0.110 ± 0.012) | 1.0 (0.039)               | 7.3 ± 0.3<br>(0.287 ± 0.012) | 1.3 (0.051)          | 4.3 ± 0.3<br>(0.169 ± 0.012) | 2.4 (0.094)                       |

Note: When solder coated terminations are required, add an additional 0.38 mm (0.015 inch) to the above tolerances for "L", "W", "H", "P", "W<sub>2</sub>" and "H<sub>2</sub>"

Table 1 – Ratings &amp; Part Number Reference

| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL–PRF–55365/8 Part Number  | DC Leakage           | DF                   | ESR                   | Moisture Sensitivity       |
|---------------|-----------|-------------------------|------------------------------|------------------------------|----------------------|----------------------|-----------------------|----------------------------|
| VDC           | µF        | KEMET/EIA               | (See below for part options) | (See below for part options) | µA @ +20°C Max/5 Min | % @ +20°C 120 Hz Max | Ω @ +20°C 100 kHz Max | Reflow Temperature ≤ 260°C |
| 4             | 2.2       | A/3216-18               | T492A225(1)004(2)(3)(4)      | CWR11C(6)225(1)(2)(5)        | 0.5                  | 6.0                  | 8.0                   | 1                          |
| 4             | 4.7       | A/3216-18               | T492A475(1)004(2)(3)(4)      | CWR11C(6)475(1)(2)(5)        | 0.5                  | 6.0                  | 8.0                   | 1                          |
| 4             | 6.8       | B/3528-21               | T492B685(1)004(2)(3)(4)      | CWR11C(6)685(1)(2)(5)        | 0.5                  | 6.0                  | 5.5                   | 1                          |
| 4             | 10        | B/3528-21               | T492B106(1)004(2)(3)(4)      | CWR11C(6)106(1)(2)(5)        | 0.5                  | 6.0                  | 4.0                   | 1                          |
| 4             | 15        | B/3528-21               | T492B156(1)004(2)(3)(4)      | CWR11C(6)156(1)(2)(5)        | 0.6                  | 6.0                  | 3.5                   | 1                          |
| 4             | 33        | C/6032-28               | T492C336(1)004(2)(3)(4)      | CWR11C(6)336(1)(2)(5)        | 1.3                  | 6.0                  | 2.2                   | 1                          |
| 4             | 68        | D/7343-31               | T492D686(1)004(2)(3)(4)      | CWR11C(6)686(1)(2)(5)        | 2.7                  | 6.0                  | 1.1                   | 1                          |
| 4             | 100       | D/7343-31               | T492D107(1)004(2)(3)(4)      | CWR11C(6)107(1)(2)(5)        | 4.0                  | 8.0                  | 0.9                   | 1                          |
| 6             | 1.5       | A/3216-18               | T492A155(1)006(2)(3)(4)      | CWR11D(6)155(1)(2)(5)        | 0.5                  | 6.0                  | 8.0                   | 1                          |
| 6             | 2.2       | A/3216-18               | T492A225(1)006(2)(3)(4)      | CWR11D(6)225(1)(2)(5)        | 0.5                  | 6.0                  | 8.0                   | 1                          |
| 6             | 3.3       | A/3216-18               | T492A335(1)006(2)(3)(4)      | CWR11D(6)335(1)(2)(5)        | 0.5                  | 6.0                  | 8.0                   | 1                          |
| 6             | 4.7       | B/3528-21               | T492B475(1)006(2)(3)(4)      | CWR11D(6)475(1)(2)(5)        | 0.5                  | 6.0                  | 5.5                   | 1                          |
| 6             | 6.8       | B/3528-21               | T492B685(1)006(2)(3)(4)      | CWR11D(6)685(1)(2)(5)        | 0.5                  | 6.0                  | 4.5                   | 1                          |
| 6             | 10        | B/3528-21               | T492B106(1)006(2)(3)(4)      | CWR11D(6)106(1)(2)(5)        | 0.6                  | 6.0                  | 3.5                   | 1                          |
| 6             | 15        | C/6032-28               | T492C156(1)006(2)(3)(4)      | CWR11D(6)156(1)(2)(5)        | 0.9                  | 6.0                  | 3.0                   | 1                          |
| 6             | 22        | C/6032-28               | T492C226(1)006(2)(3)(4)      | CWR11D(6)226(1)(2)(5)        | 1.3                  | 6.0                  | 2.2                   | 1                          |
| 6             | 47        | D/7343-31               | T492D476(1)006(2)(3)(4)      | CWR11D(6)476(1)(2)(5)        | 2.8                  | 6.0                  | 1.1                   | 1                          |
| 6             | 68        | D/7343-31               | T492D686(1)006(2)(3)(4)      | CWR11D(6)686(1)(2)(5)        | 4.1                  | 6.0                  | 0.9                   | 1                          |
| 10            | 1         | A/3216-18               | T492A105(1)010(2)(3)(4)      | CWR11F(6)105(1)(2)(5)        | 0.5                  | 4.0                  | 10.0                  | 1                          |
| 10            | 1.5       | A/3216-18               | T492A155(1)010(2)(3)(4)      | CWR11F(6)155(1)(2)(5)        | 0.5                  | 6.0                  | 8.0                   | 1                          |
| 10            | 2.2       | A/3216-18               | T492A225(1)010(2)(3)(4)      | CWR11F(6)225(1)(2)(5)        | 0.5                  | 6.0                  | 8.0                   | 1                          |
| 10            | 3.3       | B/3528-21               | T492B335(1)010(2)(3)(4)      | CWR11F(6)335(1)(2)(5)        | 0.5                  | 6.0                  | 5.5                   | 1                          |
| 10            | 4.7       | B/3528-21               | T492B475(1)010(2)(3)(4)      | CWR11F(6)475(1)(2)(5)        | 0.5                  | 6.0                  | 4.5                   | 1                          |
| 10            | 6.8       | B/3528-21               | T492B685(1)010(2)(3)(4)      | CWR11F(6)685(1)(2)(5)        | 0.7                  | 6.0                  | 3.5                   | 1                          |
| 10            | 15        | C/6032-28               | T492C156(1)010(2)(3)(4)      | CWR11F(6)156(1)(2)(5)        | 1.5                  | 6.0                  | 2.5                   | 1                          |
| 10            | 33        | D/7343-31               | T492D336(1)010(2)(3)(4)      | CWR11F(6)336(1)(2)(5)        | 3.3                  | 6.0                  | 1.1                   | 1                          |
| 10            | 47        | D/7343-31               | T492D476(1)010(2)(3)(4)      | CWR11F(6)476(1)(2)(5)        | 4.7                  | 6.0                  | 0.9                   | 1                          |
| 15            | 0.68      | A/3216-18               | T492A684(1)015(2)(3)(4)      | CWR11H(6)684(1)(2)(5)        | 0.5                  | 4.0                  | 12.0                  | 1                          |
| 15            | 1         | A/3216-18               | T492A105(1)015(2)(3)(4)      | CWR11H(6)105(1)(2)(5)        | 0.5                  | 4.0                  | 10.0                  | 1                          |
| 15            | 1.5       | A/3216-18               | T492A155(1)015(2)(3)(4)      | CWR11H(6)155(1)(2)(5)        | 0.5                  | 6.0                  | 8.0                   | 1                          |
| 15            | 2.2       | B/3528-21               | T492B225(1)015(2)(3)(4)      | CWR11H(6)225(1)(2)(5)        | 0.5                  | 6.0                  | 5.5                   | 1                          |
| 15            | 3.3       | B/3528-21               | T492B335(1)015(2)(3)(4)      | CWR11H(6)335(1)(2)(5)        | 0.5                  | 6.0                  | 5.0                   | 1                          |
| 15            | 4.7       | B/3528-21               | T492B475(1)015(2)(3)(4)      | CWR11H(6)475(1)(2)(5)        | 0.7                  | 6.0                  | 4.0                   | 1                          |
| 15            | 10        | C/6032-28               | T492C106(1)015(2)(3)(4)      | CWR11H(6)106(1)(2)(5)        | 1.5                  | 6.0                  | 2.5                   | 1                          |
| 15            | 22        | D/7343-31               | T492D226(1)015(2)(3)(4)      | CWR11H(6)226(1)(2)(5)        | 3.3                  | 6.0                  | 1.1                   | 1                          |
| 15            | 33        | D/7343-31               | T492D336(1)015(2)(3)(4)      | CWR11H(6)336(1)(2)(5)        | 5.0                  | 6.0                  | 0.9                   | 1                          |
| 20            | 0.47      | A/3216-18               | T492A474(1)020(2)(3)(4)      | CWR11J(6)474(1)(2)(5)        | 0.5                  | 4.0                  | 14.0                  | 1                          |
| 20            | 0.68      | A/3216-18               | T492A684(1)020(2)(3)(4)      | CWR11J(6)684(1)(2)(5)        | 0.5                  | 4.0                  | 12.0                  | 1                          |
| 20            | 1         | A/3216-18               | T492A105(1)020(2)(3)(4)      | CWR11J(6)105(1)(2)(5)        | 0.5                  | 4.0                  | 10.0                  | 1                          |
| 20            | 1.5       | B/3528-21               | T492B155(1)020(2)(3)(4)      | CWR11J(6)155(1)(2)(5)        | 0.5                  | 6.0                  | 6.0                   | 1                          |
| 20            | 2.2       | B/3528-21               | T492B225(1)020(2)(3)(4)      | CWR11J(6)225(1)(2)(5)        | 0.5                  | 6.0                  | 5.0                   | 1                          |
| 20            | 3.3       | B/3528-21               | T492B335(1)020(2)(3)(4)      | CWR11J(6)335(1)(2)(5)        | 0.7                  | 6.0                  | 4.0                   | 1                          |
| 20            | 4.7       | C/6032-28               | T492C475(1)020(2)(3)(4)      | CWR11J(6)475(1)(2)(5)        | 0.9                  | 6.0                  | 3.0                   | 1                          |
| 20            | 6.8       | C/6032-28               | T492C685(1)020(2)(3)(4)      | CWR11J(6)685(1)(2)(5)        | 1.4                  | 6.0                  | 2.4                   | 1                          |
| 20            | 15        | D/7343-31               | T492D156(1)020(2)(3)(4)      | CWR11J(6)156(1)(2)(5)        | 3.0                  | 6.0                  | 1.1                   | 1                          |
| 20            | 22        | D/7343-31               | T492D226(1)020(2)(3)(4)      | CWR11J(6)226(1)(2)(5)        | 4.4                  | 6.0                  | 0.9                   | 1                          |
| VDC           | µF        | KEMET/EIA               | (See below for part options) | (See below for part options) | µA @ +20°C Max/5 Min | % @ +20°C 120 Hz Max | Ω @ +20°C 100 kHz Max | Reflow Temperature ≤ 260°C |
| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number            | MIL–PRF–55365/8 Part Number  | DC Leakage           | DF                   | ESR                   | Moisture Sensitivity       |

Other part number options:

(1) To complete KEMET/CWR part number, insert M for ±20%, K for ±10%, or J for ±5%. Designates Capacitance tolerance.

(2) To complete KEMET/CWR part number, insert B (0.1%/1,000 Hours), C (0.01%/1,000 Hours), D (0.001%/1,000 Hours) or A = N/A. Designates Reliability Level.

(3) To complete KEMET part number, insert B = Gold Plated, C = Hot solder dipped, H or S = Solder Plated or K = Solder Fused. Designates Termination Finish.

(4) To complete KEMET part number, insert 4250 = +25°C after Weibull, 4251 = -55°C +85°C after Weibull, or 4252 = -55°C +85°C before Weibull. Designates Surge current option.

(5) To complete CWR part number, insert A = +25°C after Weibull, B = -55°C +85°C after Weibull, C = -55°C +85°C before Weibull or Z = None. Designates Surge current option.

(6) To complete CWR part number, insert B = Gold Plated, C = Hot Solder Dipped, H = Solder Plated or K = Solder Fused. Designates Termination Finish.

Refer to Ordering Information for additional detail.

Table 1 – Ratings &amp; Part Number Reference cont'd

| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number               | MIL–PRF–55365/8<br>Part Number  | DC Leakage              | DF                      | ESR                      | Moisture Sensitivity          |
|---------------|-----------|-------------------------|---------------------------------|---------------------------------|-------------------------|-------------------------|--------------------------|-------------------------------|
| VDC           | μF        | KEMET/EIA               | (See below for<br>part options) | (See below for<br>part options) | μA @ +20°C<br>Max/5 Min | % @ +20°C<br>120 Hz Max | Ω @ +20°C<br>100 kHz Max | Reflow Temperature<br>≤ 260°C |
| 25            | 0.68      | B/3528-21               | T492B684(1)025(2)(3)(4)         | CWR11K(6)684(1)(2)(5)           | 0.5                     | 4.0                     | 7.5                      | 1                             |
| 25            | 1         | B/3528-21               | T492B105(1)025(2)(3)(4)         | CWR11K(6)105(1)(2)(5)           | 0.5                     | 4.0                     | 6.5                      | 1                             |
| 25            | 1.5       | B/3528-21               | T492B155(1)025(2)(3)(4)         | CWR11K(6)155(1)(2)(5)           | 0.5                     | 6.0                     | 6.5                      | 1                             |
| 25            | 2.2       | C/6032-28               | T492C225(1)025(2)(3)(4)         | CWR11K(6)225(1)(2)(5)           | 0.6                     | 6.0                     | 3.5                      | 1                             |
| 25            | 3.3       | C/6032-28               | T492C335(1)025(2)(3)(4)         | CWR11K(6)335(1)(2)(5)           | 0.8                     | 6.0                     | 3.5                      | 1                             |
| 25            | 4.7       | C/6032-28               | T492C475(1)025(2)(3)(4)         | CWR11K(6)475(1)(2)(5)           | 1.2                     | 6.0                     | 2.5                      | 1                             |
| 25            | 6.8       | D/7343-31               | T492D685(1)025(2)(3)(4)         | CWR11K(6)685(1)(2)(5)           | 1.7                     | 6.0                     | 1.4                      | 1                             |
| 25            | 10        | D/7343-31               | T492D106(1)025(2)(3)(4)         | CWR11K(6)106(1)(2)(5)           | 2.5                     | 6.0                     | 1.2                      | 1                             |
| 25            | 15        | D/7343-31               | T492D156(1)025(2)(3)(4)         | CWR11K(6)156(1)(2)(5)           | 3.8                     | 6.0                     | 1.0                      | 1                             |
| 35            | 0.1       | A/3216-18               | T492A104(1)035(2)(3)(4)         | CWR11M(6)104(1)(2)(5)           | 0.5                     | 4.0                     | 24.0                     | 1                             |
| 35            | 0.15      | A/3216-18               | T492A154(1)035(2)(3)(4)         | CWR11M(6)154(1)(2)(5)           | 0.5                     | 4.0                     | 21.0                     | 1                             |
| 35            | 0.22      | A/3216-18               | T492A224(1)035(2)(3)(4)         | CWR11M(6)224(1)(2)(5)           | 0.5                     | 4.0                     | 18.0                     | 1                             |
| 35            | 0.33      | A/3216-18               | T492A334(1)035(2)(3)(4)         | CWR11M(6)334(1)(2)(5)           | 0.5                     | 4.0                     | 15.0                     | 1                             |
| 35            | 0.47      | B/3528-21               | T492B474(1)035(2)(3)(4)         | CWR11M(6)474(1)(2)(5)           | 0.5                     | 4.0                     | 10.0                     | 1                             |
| 35            | 0.68      | B/3528-21               | T492B684(1)035(2)(3)(4)         | CWR11M(6)684(1)(2)(5)           | 0.5                     | 4.0                     | 8.0                      | 1                             |
| 35            | 1         | B/3528-21               | T492B105(1)035(2)(3)(4)         | CWR11M(6)105(1)(2)(5)           | 0.5                     | 4.0                     | 6.5                      | 1                             |
| 35            | 1.5       | C/6032-28               | T492C155(1)035(2)(3)(4)         | CWR11M(6)155(1)(2)(5)           | 0.5                     | 6.0                     | 4.5                      | 1                             |
| 35            | 2.2       | C/6032-28               | T492C225(1)035(2)(3)(4)         | CWR11M(6)225(1)(2)(5)           | 0.8                     | 6.0                     | 3.5                      | 1                             |
| 35            | 3.3       | C/6032-28               | T492C335(1)035(2)(3)(4)         | CWR11M(6)335(1)(2)(5)           | 1.2                     | 6.0                     | 2.5                      | 1                             |
| 35            | 4.7       | D/7343-31               | T492D475(1)035(2)(3)(4)         | CWR11M(6)475(1)(2)(5)           | 1.6                     | 6.0                     | 1.5                      | 1                             |
| 35            | 6.8       | D/7343-31               | T492D685(1)035(2)(3)(4)         | CWR11M(6)685(1)(2)(5)           | 2.4                     | 6.0                     | 1.3                      | 1                             |
| 50            | 0.1       | A/3216-18               | T492A104(1)050(2)(3)(4)         | CWR11N(6)104(1)(2)(5)           | 0.5                     | 6.0                     | 22.0                     | 1                             |
| 50            | 0.15      | B/3528-21               | T492B154(1)050(2)(3)(4)         | CWR11N(6)154(1)(2)(5)           | 0.5                     | 4.0                     | 17.0                     | 1                             |
| 50            | 0.22      | B/3528-21               | T492B224(1)050(2)(3)(4)         | CWR11N(6)224(1)(2)(5)           | 0.5                     | 4.0                     | 14.0                     | 1                             |
| 50            | 0.33      | B/3528-21               | T492B334(1)050(2)(3)(4)         | CWR11N(6)334(1)(2)(5)           | 0.5                     | 4.0                     | 12.0                     | 1                             |
| 50            | 0.47      | C/6032-28               | T492C474(1)050(2)(3)(4)         | CWR11N(6)474(1)(2)(5)           | 0.5                     | 4.0                     | 8.0                      | 1                             |
| 50            | 0.68      | C/6032-28               | T492C684(1)050(2)(3)(4)         | CWR11N(6)684(1)(2)(5)           | 0.5                     | 4.0                     | 7.0                      | 1                             |
| 50            | 1         | C/6032-28               | T492C105(1)050(2)(3)(4)         | CWR11N(6)105(1)(2)(5)           | 0.5                     | 4.0                     | 6.0                      | 1                             |
| 50            | 1.5       | D/7343-31               | T492D155(1)050(2)(3)(4)         | CWR11N(6)155(1)(2)(5)           | 0.8                     | 6.0                     | 4.0                      | 1                             |
| 50            | 2.2       | D/7343-31               | T492D225(1)050(2)(3)(4)         | CWR11N(6)225(1)(2)(5)           | 1.1                     | 6.0                     | 2.5                      | 1                             |
| 50            | 3.3       | D/7343-31               | T492D335(1)050(2)(3)(4)         | CWR11N(6)335(1)(2)(5)           | 1.7                     | 6.0                     | 2.0                      | 1                             |
| 50            | 4.7       | D/7343-31               | T492D475(1)050(2)(3)(4)         | CWR11N(6)475(1)(2)(5)           | 2.4                     | 6.0                     | 1.5                      | 1                             |
| VDC           | μF        | KEMET/EIA               | (See below for<br>part options) | (See below for<br>part options) | μA @ +20°C<br>Max/5 Min | % @ +20°C<br>120 Hz Max | Ω @ +20°C<br>100 kHz Max | Reflow Temperature<br>≤ 260°C |
| Rated Voltage | Rated Cap | Case Code/<br>Case Size | KEMET Part Number               | MIL–PRF–55365/8<br>Part Number  | DC Leakage              | DF                      | ESR                      | Moisture Sensitivity          |

(1) To complete KEMET/CWR part number, insert M for ±20%, K for ±10%, or J for ±5%. Designates Capacitance tolerance.

Other part number options:

(1) To complete KEMET/CWR part number, insert M for ±20%, K for ±10%, or J for ±5%. Designates Capacitance tolerance.

(2) To complete KEMET/CWR part number, insert B (0.1%/1,000 Hours), C (0.01%/1,000 Hours), D (0.001%/1,000 Hours) or A = N/A. Designates Reliability Level.

(3) To complete KEMET part number, insert B = Gold Plated, C = Hot solder dipped, H or S = Solder Plated or K = Solder Fused. Designates Termination Finish.

(4) To complete KEMET part number, insert 4250 = +25°C after Weibull, 4251 = -55°C +85°C after Weibull, or 4252 = -55°C +85°C before Weibull. Designates Surge current option.


(5) To complete CWR part number, insert A = +25°C after Weibull, B = -55°C +85°C after Weibull, C = -55°C +85°C before Weibull or Z = None. Designates Surge current option.

(6) To complete CWR part number, insert B = Gold Plated, C = Hot Solder Dipped, H = Solder Plated or K = Solder Fused. Designates Termination Finish.

Refer to Ordering Information for additional detail.

## Recommended Voltage Derating Guidelines

|                                                 | -55°C to 85°C | 85°C to 125°C |
|-------------------------------------------------|---------------|---------------|
| % Change in Working DC Voltage with Temperature | $V_R$         | 67% of $V_R$  |
| Recommended Maximum Application Voltage         | 50% of $V_R$  | 33% of $V_R$  |



## Ripple Current/Ripple Voltage

Permissible AC ripple voltage and current are related to equivalent series resistance (ESR) and the power dissipation capabilities of the device. Permissible AC ripple voltage which may be applied is limited by two criteria:

1. The positive peak AC voltage plus the DC bias voltage, if any, must not exceed the DC voltage rating of the capacitor.
2. The negative peak AC voltage in combination with bias voltage, if any, must not exceed the allowable limits specified for reverse voltage. See the Reverse Voltage section for allowable limits.

The maximum power dissipation by case size can be determined using the table at right. The maximum power dissipation rating stated in the table must be reduced with increasing environmental operating temperatures. Refer to the table below for temperature compensation requirements.

| Temperature Compensation Multipliers<br>for Maximum Power Dissipation |                           |                            |
|-----------------------------------------------------------------------|---------------------------|----------------------------|
| $T \leq 25^\circ\text{C}$                                             | $T \leq 85^\circ\text{C}$ | $T \leq 125^\circ\text{C}$ |
| 1.00                                                                  | 0.90                      | 0.40                       |

$T$  = Environmental Temperature

Using the P max of the device, the maximum allowable rms ripple current or voltage may be determined.

$$I(\text{max}) = \sqrt{P_{\text{max}}/R}$$

$$E(\text{max}) = Z \sqrt{P_{\text{max}}/R}$$

$I$  = rms ripple current (amperes)

$E$  = rms ripple voltage (volts)

$P_{\text{max}}$  = maximum power dissipation (watts)

$R$  = ESR at specified frequency (ohms)

$Z$  = Impedance at specified frequency (ohms)

| KEMET<br>Case Code | EIA<br>Case Code | Maximum Power<br>Dissipation (P max)<br>mWatts @ 25°C<br>w/+20°C Rise |
|--------------------|------------------|-----------------------------------------------------------------------|
| A                  | 3216–18          | 75                                                                    |
| B                  | 3528–21          | 85                                                                    |
| C                  | 6032–28          | 110                                                                   |
| D                  | 7343–31          | 150                                                                   |
| X                  | 7343–43          | 165                                                                   |
| E                  | 7360–38          | 200                                                                   |
| S                  | 3216–12          | 60                                                                    |
| T                  | 3528–12          | 70                                                                    |
| U                  | 6032–15          | 90                                                                    |
| V                  | 7343–20          | 125                                                                   |
| T510X              | 7343–43          | 270                                                                   |
| T510E              | 7360–38          | 285                                                                   |

The maximum power dissipation rating must be reduced with increasing environmental operating temperatures. Refer to the Temperature Compensation Multiplier table for details.

## Reverse Voltage

Solid tantalum capacitors are polar devices and may be permanently damaged or destroyed if connected with the wrong polarity. The positive terminal is identified on the capacitor body by a stripe plus in some cases a beveled edge. A small degree of transient reverse voltage is permissible for short periods per the table. The capacitors should not be operated continuously in reverse mode, even within these limits.

| Temperature | Permissible Transient Reverse Voltage |
|-------------|---------------------------------------|
| 25°C        | 15% of Rated Voltage                  |
| 85°C        | 5% of Rated Voltage                   |
| 125°C       | 1% of Rated Voltage                   |

**Table 2 – Land Dimensions/Courtyard**

| KEMET          | Metric Size Code | Density Level A:<br>Maximum (Most) Land Protrusion (mm) |      |      |       |      | Density Level B:<br>Median (Nominal) Land Protrusion (mm) |      |      |      |      | Density Level C:<br>Minimum (Least) Land Protrusion (mm) |      |      |      |      |
|----------------|------------------|---------------------------------------------------------|------|------|-------|------|-----------------------------------------------------------|------|------|------|------|----------------------------------------------------------|------|------|------|------|
|                |                  | W                                                       | L    | S    | V1    | V2   | W                                                         | L    | S    | V1   | V2   | W                                                        | L    | S    | V1   | V2   |
| A              | 3216–18          | 1.35                                                    | 2.20 | 0.62 | 6.02  | 2.80 | 1.23                                                      | 1.80 | 0.82 | 4.92 | 2.30 | 1.13                                                     | 1.42 | 0.98 | 4.06 | 2.04 |
| B              | 3528–21          | 2.35                                                    | 2.21 | 0.92 | 6.32  | 4.00 | 2.23                                                      | 1.80 | 1.12 | 5.22 | 3.50 | 2.13                                                     | 1.42 | 1.28 | 4.36 | 3.24 |
| C              | 6032–25          | 2.35                                                    | 2.77 | 2.37 | 8.92  | 4.50 | 2.23                                                      | 2.37 | 2.57 | 7.82 | 4.00 | 2.13                                                     | 1.99 | 2.73 | 6.96 | 3.74 |
| D              | 7343–31          | 2.55                                                    | 2.77 | 3.67 | 10.22 | 5.60 | 2.43                                                      | 2.37 | 3.87 | 9.12 | 5.10 | 2.33                                                     | 1.99 | 4.03 | 8.26 | 4.84 |
| L              | 6032–19          | 2.35                                                    | 2.77 | 2.37 | 8.92  | 4.50 | 2.23                                                      | 2.37 | 2.57 | 7.82 | 4.00 | 2.13                                                     | 1.99 | 2.73 | 6.96 | 3.74 |
| M              | 3528–15          | 2.35                                                    | 2.20 | 0.92 | 6.32  | 4.00 | 2.23                                                      | 1.80 | 1.12 | 5.22 | 3.50 | 2.13                                                     | 1.42 | 1.28 | 4.36 | 3.24 |
| H              | 7360–20          | 4.25                                                    | 2.77 | 3.67 | 10.22 | 7.30 | 4.13                                                      | 2.37 | 3.87 | 9.12 | 6.80 | 4.03                                                     | 1.99 | 4.03 | 8.26 | 6.54 |
| E <sup>1</sup> | 7360–38          | 4.25                                                    | 2.77 | 3.67 | 10.22 | 7.30 | 4.13                                                      | 2.37 | 3.87 | 9.12 | 6.80 | 4.03                                                     | 1.99 | 4.03 | 8.26 | 6.54 |
| Q              | 7343–12          | 2.55                                                    | 2.77 | 3.67 | 10.22 | 5.60 | 2.43                                                      | 2.37 | 3.87 | 9.12 | 5.10 | 2.33                                                     | 1.99 | 4.03 | 8.26 | 4.84 |
| R <sup>2</sup> | 2012–12          | 1.05                                                    | 1.83 | 0.15 | 4.82  | 2.50 | 0.93                                                      | 1.50 | 0.22 | 3.72 | 2.00 | 0.83                                                     | 1.12 | 0.38 | 2.86 | 1.74 |
| S <sup>2</sup> | 3216–12          | 1.35                                                    | 2.20 | 0.62 | 6.02  | 2.80 | 1.23                                                      | 1.80 | 0.82 | 4.92 | 2.30 | 1.13                                                     | 1.42 | 0.98 | 4.06 | 2.04 |
| T              | 3528–12          | 2.35                                                    | 2.20 | 0.92 | 6.32  | 4.00 | 2.23                                                      | 1.80 | 1.12 | 5.22 | 3.50 | 2.13                                                     | 1.42 | 1.28 | 4.36 | 3.24 |
| U              | 6032–15          | 2.35                                                    | 2.77 | 2.37 | 8.92  | 4.50 | 2.23                                                      | 2.37 | 2.57 | 7.82 | 4.00 | 2.13                                                     | 1.99 | 2.73 | 6.96 | 3.74 |
| V              | 7343–20          | 2.55                                                    | 2.77 | 3.67 | 10.22 | 5.60 | 2.43                                                      | 2.37 | 3.87 | 9.12 | 5.10 | 2.33                                                     | 1.99 | 4.03 | 8.26 | 4.84 |
| W              | 7343–15          | 2.55                                                    | 2.77 | 3.67 | 10.22 | 5.60 | 2.43                                                      | 2.37 | 3.87 | 9.12 | 5.10 | 2.33                                                     | 1.99 | 4.03 | 8.26 | 4.84 |
| X <sup>1</sup> | 7343–43          | 2.55                                                    | 2.77 | 3.67 | 10.22 | 5.60 | 2.43                                                      | 2.37 | 3.87 | 9.12 | 5.10 | 2.33                                                     | 1.99 | 4.03 | 8.26 | 4.84 |
| Y <sup>1</sup> | 7343–40          | 2.55                                                    | 2.77 | 3.67 | 10.22 | 5.60 | 2.43                                                      | 2.37 | 3.87 | 9.12 | 5.10 | 2.33                                                     | 1.99 | 4.03 | 8.26 | 4.84 |


**Density Level A:** For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes.

**Density Level B:** For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes.

**Density Level C:** For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC standard 7351 (IPC–7351).

<sup>1</sup> Height of these chips may create problems in wave soldering.

<sup>2</sup> Land pattern geometry is too small for silkscreen outline.



## Soldering Process

KEMET's families of surface mount capacitors are compatible with wave (single or dual), convection, IR or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/J–STD–020D standard for moisture sensitivity testing. The devices can safely withstand a maximum of three reflow passes at these conditions.

Note that although the X/7343–43 case size can withstand wave soldering, the tall profile (4.3 mm maximum) dictates care in wave process development.

Hand soldering should be performed with care due to the difficulty in process control. If performed, care should be taken to avoid contact of the soldering iron to the molded case. The iron should be used to heat the solder pad, applying solder between the pad and the termination, until reflow occurs. Once reflow occurred, the iron should be removed immediately. "Wiping" the edges of a chip and heating the top surface is not recommended.

During typical reflow operations, a slight darkening of the gold-colored epoxy may be observed. This slight darkening is normal and is not harmful to the product. Marking permanency is not affected by this change.

| Profile Feature                                       | SnPb Assembly       | Pb-Free Assembly    |
|-------------------------------------------------------|---------------------|---------------------|
| Preheat/Soak                                          |                     |                     |
| Temperature Minimum ( $T_{smin}$ )                    | 100°C               | 150°C               |
| Temperature Maximum ( $T_{smax}$ )                    | 150°C               | 200°C               |
| Time ( $t_s$ ) from $T_{smin}$ to $T_{smax}$          | 60–120 seconds      | 60–120 seconds      |
| Ramp-up Rate ( $T_L$ to $T_P$ )                       | 3°C/seconds maximum | 3°C/seconds maximum |
| Liquidous Temperature ( $T_L$ )                       | 183°C               | 217°C               |
| Time Above Liquidous ( $t_L$ )                        | 60–150 seconds      | 60–150 seconds      |
| Peak Temperature ( $T_P$ )                            | 220°C*<br>235°C**   | 250°C*<br>260°C**   |
| Time within 5°C of Maximum Peak Temperature ( $t_p$ ) | 20 seconds maximum  | 30 seconds maximum  |
| Ramp-down Rate ( $T_P$ to $T_L$ )                     | 6°C/seconds maximum | 6°C/seconds maximum |
| Time 25°C to Peak Temperature                         | 6 minutes maximum   | 8 minutes maximum   |

*Note: All temperatures refer to the center of the package, measured on the package body surface that is facing up during assembly reflow.*

\*Case Size D, E, P, Y and X


\*\*Case Size A, B, C, H, I, K, M, R, S, T, U, V, W and Z



## Construction



## Capacitor Marking



| Date Code *                                                  |                                                                                    |
|--------------------------------------------------------------|------------------------------------------------------------------------------------|
| 1 <sup>st</sup> digit = Last number of Year                  | 9 = 2009<br>0 = 2010<br>1 = 2011<br>2 = 2012<br>3 = 2013<br>4 = 2014               |
| 2 <sup>nd</sup> and 3 <sup>rd</sup> digit = Week of the Year | 01 = 1 <sup>st</sup> week of the Year to<br>52 = 52 <sup>nd</sup> week of the Year |

## Storage

Tantalum chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature– reels may soften or warp and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 60% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts and atmospheres should be free of chlorine and sulphur bearing compounds. For optimized solderability chip stock should be used promptly, preferably within three years of receipt.


## Tape & Reel Packaging Information

KEMET's molded tantalum and aluminum chip capacitor families are packaged in 8 and 12 mm plastic tape on 7" and 13" reels in accordance with *EIA Standard 481-1: Embossed Carrier Taping of Surface Mount Components for Automatic Handling*. This packaging system is compatible with all tape-fed automatic pick-and-place systems.



**Table 3 – Packaging Quantity**

| KEMET Case Codes |      | Tape Width (mm) | Tape and Reel Dimensions |                       |
|------------------|------|-----------------|--------------------------|-----------------------|
|                  |      |                 | 180 mm (7" diameter)     | 330 mm (13" diameter) |
| A                | 1005 | 8               | 2500                     | 9500                  |
| B                | 1505 | 12              | 2500                     | 9500                  |
| C                | 2005 | 12              | 2500                     | 9500                  |
| D                | 1510 | 12              | 2500                     | 9500                  |
| E                | 2010 | 12              | 2500                     | 9500                  |
| F                | 2214 | 12              | 500                      | 3500                  |
| G                | 2711 | 12              | 500                      | 2500                  |
| H                | 2915 | 12              | 500                      | 2500                  |
| X                | 2824 | 12              | 500                      | 2500                  |

**Figure 1 – Embossed (Plastic) Carrier Tape Dimensions****Table 4 – Embossed (Plastic) Carrier Tape Dimensions**

Metric will govern

| Constant Dimensions — Millimeters (Inches) |                                       |                                  |                              |                             |                             |                        |                                  |                                                  |                        |
|--------------------------------------------|---------------------------------------|----------------------------------|------------------------------|-----------------------------|-----------------------------|------------------------|----------------------------------|--------------------------------------------------|------------------------|
| Tape Size                                  | D <sub>0</sub>                        | D <sub>1</sub> Minimum<br>Note 1 | E <sub>1</sub>               | P <sub>0</sub>              | P <sub>2</sub>              | R Reference<br>Note 2  | S <sub>1</sub> Minimum<br>Note 3 | T Maximum                                        | T <sub>1</sub> Maximum |
| 8 mm                                       | 1.5 +0.10/-0.0<br>(0.059 +0.004/-0.0) | 1.0<br>(0.039)                   | 1.75 ±0.10<br>(0.069 ±0.004) | 4.0 ±0.10<br>(0.157 ±0.004) | 2.0 ±0.05<br>(0.079 ±0.002) | 25.0<br>(0.984)        | 0.600<br>(0.024)                 | 0.600<br>(0.024)                                 | 0.100<br>(0.004)       |
| 12 mm                                      |                                       | 1.5<br>(0.059)                   |                              |                             |                             | 30<br>(1.181)          |                                  |                                                  |                        |
| 16 mm                                      |                                       |                                  |                              |                             |                             |                        |                                  |                                                  |                        |
| Variable Dimensions — Millimeters (Inches) |                                       |                                  |                              |                             |                             |                        |                                  |                                                  |                        |
| Tape Size                                  | Pitch                                 | B <sub>1</sub> Maximum<br>Note 4 | E <sub>2</sub> Minimum       | F                           | P <sub>1</sub>              | T <sub>2</sub> Maximum | W Maximum                        | A <sub>0</sub> , B <sub>0</sub> & K <sub>0</sub> |                        |
| 8 mm                                       | Single (4 mm)                         | 4.35<br>(0.171)                  | 6.25<br>(0.246)              | 3.5 ±0.05<br>(0.138 ±0.002) | 4.0 ±0.10<br>(0.157 ±0.004) | 2.5<br>(0.098)         | 8.3<br>(0.327)                   | Note 5                                           |                        |
| 12 mm                                      | Single (4 mm) &<br>Double (8 mm)      | 8.2<br>(0.323)                   | 10.25<br>(0.404)             | 5.5 ±0.05<br>(0.217 ±0.002) | 8.0 ±0.10<br>(0.315 ±0.004) | 4.6<br>(0.181)         | 12.3<br>(0.484)                  |                                                  |                        |
| 16 mm                                      | Triple (12 mm)                        | 12.1<br>(0.476)                  | 14.25<br>(0.561)             | 5.5 ±0.05<br>(0.217 ±0.002) | 8.0 ±0.10<br>(0.315 ±0.004) | 4.6<br>(0.181)         | 16.3<br>(0.642)                  |                                                  |                        |

1. The embossment hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of embossment location and hole location shall be applied independent of each other.
2. The tape, with or without components, shall pass around R without damage (see Figure 5).
3. If  $S_1 < 1.0$  mm, there may not be enough area for cover tape to be properly applied (see EIA Standard 481–D, paragraph 4.3, section b).
4.  $B_1$  dimension is a reference dimension for tape feeder clearance only.
5. The cavity defined by  $A_0$ ,  $B_0$  and  $K_0$  shall surround the component with sufficient clearance that:
  - (a) the component does not protrude above the top surface of the carrier tape.
  - (b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.
  - (c) rotation of the component is limited to 20° maximum for 8 and 12 mm tapes and 10° maximum for 16 mm tapes (see Figure 2).
  - (d) lateral movement of the component is restricted to 0.5 mm maximum for 8 mm and 12 mm wide tape and to 1.0 mm maximum for 16 mm tape (see Figure 3).
  - (e) see Addendum in EIA Standard 481–D for standards relating to more precise taping requirements.

## Packaging Information Performance Notes



- 1. Cover Tape Break Force:** 1.0 Kg minimum.
- 2. Cover Tape Peel Strength:** The total peel strength of the cover tape from the carrier tape shall be:

| Tape Width   | Peel Strength                    |
|--------------|----------------------------------|
| 8 mm         | 0.1 to 1.0 Newton (10 to 100 gf) |
| 12 and 16 mm | 0.1 to 1.3 Newton (10 to 130 gf) |


The direction of the pull shall be opposite the direction of the carrier tape travel. The pull angle of the carrier tape shall be 165° to 180° from the plane of the carrier tape. During peeling, the carrier and/or cover tape shall be pulled at a velocity of 300 ±10 mm/minute.

- 3. Labeling:** Bar code labeling (standard or custom) shall be on the side of the reel opposite the sprocket holes. Refer to EIA Standards 556 and 624.


## Figure 2 – Maximum Component Rotation




## Figure 3 – Maximum Lateral Movement



## Figure 4 – Bending Radius



**Figure 5 – Reel Dimensions**

Note: Drive spokes optional; if used, dimensions B and D shall apply.

**Table 5 – Reel Dimensions**

Metric will govern

| Constant Dimensions — Millimeters (Inches) |                                                                   |                                       |                                        |                                                      |
|--------------------------------------------|-------------------------------------------------------------------|---------------------------------------|----------------------------------------|------------------------------------------------------|
| Tape Size                                  | A                                                                 | B Minimum                             | C                                      | D Minimum                                            |
| 8 mm                                       | 178 ±0.20<br>(7.008 ±0.008)<br>or<br>330 ±0.20<br>(13.000 ±0.008) | 1.5<br>(0.059)                        | 13.0 +0.5/-0.2<br>(0.521 +0.02/-0.008) | 20.2<br>(0.795)                                      |
| 12 mm                                      |                                                                   |                                       |                                        |                                                      |
| 16 mm                                      |                                                                   |                                       |                                        |                                                      |
| Variable Dimensions — Millimeters (Inches) |                                                                   |                                       |                                        |                                                      |
| Tape Size                                  | N Minimum                                                         | W1                                    | W2 Maximum                             | W3                                                   |
| 8 mm                                       | 50<br>(1.969)                                                     | 8.4 +1.5/-0.0<br>(0.331 +0.059/-0.0)  | 14.4<br>(0.567)                        | Shall accommodate tape width<br>without interference |
| 12 mm                                      |                                                                   | 12.4 +2.0/-0.0<br>(0.488 +0.078/-0.0) | 18.4<br>(0.724)                        |                                                      |
| 16 mm                                      |                                                                   | 16.4 +2.0/-0.0<br>(0.646 +0.078/-0.0) | 22.4<br>(0.882)                        |                                                      |

**Figure 6 – Tape Leader & Trailer Dimensions****Figure 7 – Maximum Camber**

## **KEMET Corporation World Headquarters**

2835 KEMET Way  
Simpsonville, SC 29681

Mailing Address:  
P.O. Box 5928  
Greenville, SC 29606

www.kemet.com  
Tel: 864-963-6300  
Fax: 864-963-6521

**Corporate Offices**  
Fort Lauderdale, FL  
Tel: 954-766-2800

## **North America**

### **Southeast**

Lake Mary, FL  
Tel: 407-855-8886

### **Northeast**

Wilmington, MA  
Tel: 978-658-1663

### **Central**

Novi, MI  
Tel: 248-994-1030

### **West**

Milpitas, CA  
Tel: 408-433-9950

### **Mexico**

Guadalajara, Jalisco  
Tel: 52-33-3123-2141

## **Europe**

### **Southern Europe**

Paris, France  
Tel: 33-1-4646-1006

Sasso Marconi, Italy  
Tel: 39-051-939111

### **Central Europe**

Landsberg, Germany  
Tel: 49-8191-3350800

Kamen, Germany  
Tel: 49-2307-438110

### **Northern Europe**

Bishop's Stortford, United Kingdom  
Tel: 44-1279-460122

Espoo, Finland  
Tel: 358-9-5406-5000

## **Asia**

### **Northeast Asia**

Hong Kong  
Tel: 852-2305-1168

Shenzhen, China  
Tel: 86-755-2518-1306

Beijing, China  
Tel: 86-10-5829-1711

Shanghai, China  
Tel: 86-21-6447-0707

Taipei, Taiwan  
Tel: 886-2-27528585

### **Southeast Asia**

Singapore  
Tel: 65-6586-1900

Penang, Malaysia  
Tel: 60-4-6430200

Bangalore, India  
Tel: 91-806-53-76817

*Note: KEMET reserves the right to modify minor details of internal and external construction at any time in the interest of product improvement. KEMET does not assume any responsibility for infringement that might result from the use of KEMET Capacitors in potential circuit designs. KEMET is a registered trademark of KEMET Electronics Corporation.*

## Other KEMET Resources

| Tools                          |                                                                             |
|--------------------------------|-----------------------------------------------------------------------------|
| Resource                       | Location                                                                    |
| Configure A Part: CapEdge      | <a href="http://capacitoredge.kemet.com">http://capacitoredge.kemet.com</a> |
| SPICE & FIT Software           | <a href="http://www.kemet.com/spice">http://www.kemet.com/spice</a>         |
| Search Our FAQs: KnowledgeEdge | <a href="http://www.kemet.com/keask">http://www.kemet.com/keask</a>         |
| Electrolytic LifeCalculator    | <a href="http://www.kemet.com:8080/elc">http://www.kemet.com:8080/elc</a>   |

| Product Information                                  |                                                                                           |
|------------------------------------------------------|-------------------------------------------------------------------------------------------|
| Resource                                             | Location                                                                                  |
| Products                                             | <a href="http://www.kemet.com/products">http://www.kemet.com/products</a>                 |
| Technical Resources (Including Soldering Techniques) | <a href="http://www.kemet.com/technicalpapers">http://www.kemet.com/technicalpapers</a>   |
| RoHS Statement                                       | <a href="http://www.kemet.com/rohs">http://www.kemet.com/rohs</a>                         |
| Quality Documents                                    | <a href="http://www.kemet.com/qualitydocuments">http://www.kemet.com/qualitydocuments</a> |

| Product Request         |                                                                       |
|-------------------------|-----------------------------------------------------------------------|
| Resource                | Location                                                              |
| Sample Request          | <a href="http://www.kemet.com/sample">http://www.kemet.com/sample</a> |
| Engineering Kit Request | <a href="http://www.kemet.com/kits">http://www.kemet.com/kits</a>     |

| Contact            |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| Resource           | Location                                                                            |
| Website            | <a href="http://www.kemet.com">www.kemet.com</a>                                    |
| Contact Us         | <a href="http://www.kemet.com/contact">http://www.kemet.com/contact</a>             |
| Investor Relations | <a href="http://www.kemet.com/ir">http://www.kemet.com/ir</a>                       |
| Call Us            | 1-877-MyKEMET                                                                       |
| Twitter            | <a href="http://twitter.com/kemetcapacitors">http://twitter.com/kemetcapacitors</a> |

## Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed.

All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.



Product & Process Design

Sales & Marketing

Supplier

Material Management

Quality

Manufacturing

Logistics & Distribution

People: Leadership  
& Development

# KEMET Production System

**Corporate Offices**

KEMET Corporation  
2835 KEMET Way  
Simpsonville, SC 29681  
USA  
Tel: 864.963.6300  
Fax: 864.963.6521

KEMET Electronics GmbH  
Rudolf-Diesel-Straße 21  
86899 Landsberg  
Germany  
Tel: +49 8191 3350 ext. 0  
Fax: 49 8191 335063

KEMET Electronics Marketing (S) Pte Ltd.  
73 Bukit Timah Road  
#05-01 Rex House  
Singapore 229832  
Tel: 65.6586.1900  
Fax: 65.6586.1901

[www.kemet.com](http://www.kemet.com)

One world. One KEMET.

Electronic Components  
**KEMET**  
CHARGED®