







7-#12
PC TAIL DIA. 0.057 ±0.001 REF.




10-#16
PC TAIL DIA. 0.048 ±0.001 REF.



12-#16
PC TAIL DIA. 0.048 ±0.001 REF.



18-#20
PC TAIL DIA. 0.0395 ±0.001 REF.



20-#20
PC TAIL DIA. 0.0395 ±0.001 REF.

WIRE VIEWS

CUSTOMER APPROVAL

CHECKED BY: _____
APPROVED BY: _____
DATE: _____

E		AN	03-14-06	ADDED CUSTOMER PRINT PER DOR 04-E149JC AND ECR 6107			
REV.		INIT.		DATE		DESCRIPTION	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.				ORIG. DRAWN BY:		DATE:	
				AL		04-27-99	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16 ▷ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX				CHECKED BY:		 601 E. WILDWOOD VILLA PARK, IL 60181 TITLE: HOLE PATTERNS MAXI-CON-X CUSTOMER: STANDARD PRODUCT PART NUMBER: HPMXSTD	
				APPROVED BY:			
SCALE		SIZE		SHEET		REV. E	
2:1		B		1 OF 1			
FILE:		HPMXSTDH1		DIRECTORY:		DETAILS	