







NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. CONTACT RATING: 50mA @ 12VDC
4. CONTACT RESISTANCE: 100 m Ω MAX.
5. INSULATION RESISTANCE: 100M Ω MIN @ 500VDC.
6. OPERATING FORCE: 160 $\pm$ 50gf $\varnothing$.80
7. TRAVEL: 0.2 $\pm$ 0.1mm [.031 in]
8. OPERATING TEMPERATURE: -25°C to +70°C 2 PLS
9. OPERATING LIFE: 500,000 CYCLES
10. LED: RED
11. ▲ DENOTES CRITICAL PARAMETERS
12. 2011/65/EU (ROHS) COMPLIANT
13. PARTS TO BE PACKAGED IN TAPE & REEL, 450 PIECES PER REEL



▲ LED SPECS	UNITS	RED
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @20mA	V	2.0 TYP; 2.3 MAX
LUMINOUS INTENSITY @ 20mA	mcd	1000 TYP

C	22949	Show Cathode lead on Pin 6 side of switch	8/7/17	MW
B	20570	Chg T&R qty from 500 to 450	4/25/12	rc
A	20373	New Release	12/12/11	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



E-SWITCH®

TITLE	TL3240F160R
-------	-------------

SCALE
4:1

DATE	12/12/2011
------	------------

DR	rc
----	----

DWG N324000

REV
C