

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

112095-5003

Status:

Active

Overview:

Brad® Harsh-Duty IO Modules

Description:

Brad® HarshIO Digital Module for Ethernet/IP, Classic 60mm, IP67, 8 Ports M12, 16 Inputs, NPN, 5 pole Power

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification

UL

E200650

General

Product Family

Series

Application

Approvals

Current - Maximum Output

Format

I/O Ports

IP Rating

Mechanical Shock

Overview

Product Literature Order No

Product Name

Protocol

Software Downloads

Industrial I/O Modules

112095

Filling and Packaging Machines, Machine Tool Industry, Material Handling Systems

ODVA, UL, cUL, CE

N/A

Classic (60mm)

8x M12

IP67

10G, 11ms, 3 AXIS

Brad® Harsh-Duty IO Modules

987650-5285

HarshIO EtherNet/IP

EtherNet/IP

/molex/mysst/searchBrad.action?itemSoftware=true&itemDocument=true&itemTechNote=true&itemDemo=true&RPP=10&legacy=false&partnumber=DxU

UPC

883906226534

Physical

Bus Input

Bus Output

Housing Width

I/O Connector

I/O Signal Mix

Net Weight

Power Input

Power Output

Temperature Range - Operating

Vibration

4-pole Micro-Change® (M12), D-Coded, Female

4-pole Micro-Change® (M12), D-Coded, Female

60.00mm

5-pole Micro-Change® (M12), A-Coded, Female

16 input

640.000/g

5-pole Mini-Change®, Male

5-pole Mini-Change®, Female

-25°C to +70°C

IEC 60068-2-6

Electrical

EMC

Input Delay

Input Device Supply

Input Type

IEC 61000-6-2

2.5ms


200 mA per port at 25°C

NPN or Dry Contact

Material Info

Old Part Number

TCDEI-8D0N-D1U



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

112095Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION