





D

C

B

A



SECTION Y-Y

- 1 SEE TABLE FOR RIB QTY
- 2. THIS COUPLING SHROUD IS TO BE USED WITH AMPMODU[®] MTE RECEPTACLE ASSEMBLIES WITH GUIDE RIBS. THE NUMBER OF POSITIONS LISTED EQUALS THE TOTAL NUMBER OF POSITIONS WHICH CAN BE CONTAINED WITHIN THE COUPLING SHROUD.
- 3 .133 BETWEEN RIBS REFERENCED BY NOTE 1 ONLY. .153 ON ENDS (AREAS OUTSIDE OF THE RIBS).
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	2.460	2.505	2.685	2	50	1-104500-1
	1.960	2.005	2.085	2	40	1-104500-0
4 OBSOLETE	1.660	1.705	1.885	2	34	-104500-9
	1.560	1.605	1.785	2	32	104500-8
	1.460	1.505	1.685	2	30	-104500-7
OBSOLETE	1.360	1.405	1.585	2	28	-104500-6
4	1.260	1.305	1.485	2	26	-104500-5
	1.160	1.205	1.385	2	24	104500-4
	1.060	1.105	1.285	2	22	104500-3
	.960	1.005	1.185	2	20	104500-2
4 OBSOLETE	.860	.905	1.085	2	18	-104500-1
	C	B	A	NO OF RIBS	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
D. KEITZER
CHK
S. SHUEY
APVD
C. SINISI

01DEC88
07DEC88
14DEC88

TE Connectivity

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0. PLC ± .
1. PLC ± .
2. PLC ± .
3. PLC ± .010
4. PLC ± .
ANGLES ± .

PRODUCT SPEC
108-25034
APPLICATION SPEC
114-25026

MATERIAL
FLAME RETARDANT THERMOPLASTIC
COLOR-BLACK

FINISH
-

WEIGHT
-

SIZE
A1

CAGE CODE
00779

DRAWING NO
104500

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
1

OF
1

REV
L2