

Surface Mount Frequency Multiplier

Output 1.0 to 2.2 GHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C


Pin Connections

INPUT	10
OUTPUT	5
50Ω TERMINATED	3
GROUND	1,2,4,6,7,8,9

Outline Drawing



TOLERANCES
2 PL DECIMALS ±.01
3 PL DECIMALS ±.005
UNLESS OTHERWISE SPECIFIED




SUGGESTED LAYOUT FOR PCB LAND PATTERN

Outline Dimensions (inch)

A	B	C	D	E	F	G
.30	.250	.085	.274	.050	.050	.012
7.62	6.35	2.16	6.96	1.27	1.27	0.30
H	J	K	L	M	wt.	
.057	.004	.085	2.96	.030	grams	
1.45	0.10	2.16	7.52	0.76	0.25	

Demo Board MCL PIN: TB-144
Suggested PCB Layout (PL-045)



NOTE: TRACE WIDTH IS SHOWN FOR ROGERS R04350 WITH DIELECTRIC THICKNESS 0.020" ± 0.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

□ DENOTES PCB COPPER LAYOUT
▨ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK


Features

- low conversion loss, 10.5 dB typ.
- LTCC design
- low profile, 0.085"
- low cost

Applications

- synthesizers
- local oscillators

NEW!
KC2-11



BLUE CELL™

CASE STYLE: DZ885
PRICE:\$5.95 ea. QTY (10-49)





Frequency Multiplier Electrical Specifications

MODEL NO.	MULTIPLICATION FACTOR	FREQUENCY (GHz)		INPUT POWER (dBm)		CONVERSION LOSS (dB)		*HARMONIC OUTPUT (dBc)					
		Input	Output	Min.	Max.	Typ.	Max.	F1 Typ.	F1 Min.	F3 Typ.	F3 Min.	F4 Typ.	F4 Min.
KC2-11	2	0.5 - 1.1	1.0 - 2.2	5	10	10.5	13.5	27	18	34	20	21	12
		0.55 - 0.75	1.1 - 1.5	5	10	10.0	13.5	30	21	34	21	21	12

*Harmonic output below power level of F2

Typical Performance Data

RF=5dBm					RF=10dBm				
Input Frequency (MHz)	Conversion Loss (dB)	Harmonic Output (-dBc)			Conversion Loss (dB)	Harmonic Output (-dBc)			
		F1	F3	F4		F1	F3	F4	
500.00	11.02	32.07	30.29	18.52	10.39	33.22	29.34	16.59	
550.00	10.46	34.11	33.67	22.15	9.65	33.10	30.50	18.18	
600.00	10.48	35.71	36.35	27.92	9.39	32.02	31.53	16.77	
650.00	10.14	37.99	43.65	25.22	9.43	31.11	33.01	16.33	
700.00	10.20	42.23	46.39	22.94	9.62	31.08	35.78	18.30	
750.00	9.91	37.54	48.95	23.42	9.91	30.15	33.90	19.01	
800.00	9.83	29.48	39.88	23.38	10.35	28.56	31.75	17.73	
850.00	9.96	27.93	34.61	21.93	11.04	27.29	27.33	18.07	
900.00	10.27	27.40	35.02	21.75	11.29	25.98	26.91	17.41	
950.00	10.02	26.99	41.50	25.97	10.69	24.88	29.84	25.84	
1000.00	10.21	27.27	41.54	34.18	10.38	26.16	32.38	34.74	
1050.00	11.02	27.61	44.32	43.17	11.15	27.23	35.50	52.58	
1100.00	12.37	29.48	35.70	27.14	12.06	29.84	34.52	31.25	



Mini-Circuits®

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

ISO 9001 CERTIFIED

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

REV. OR
M91754
KC2-11
ED-11593/2
DJ/RS/CP
040414