


PART NUMBER
SSB-LX2350IW



REV.
B

REV.	E.C.N. NUMBER AND REVISION COMMENTS	DATE
A	E.C.N. #10BRDR. & REDRAWN.	6.21.01
B	ECN-Lumex201600058	09.01.16



ELECTRO-OPTICAL CHARACTERISTICS $T_A=25^\circ\text{C}$


PARAMETER	MIN	TYP	MAX	UNITS	TEST COND
PEAK WAVELENGTH		630		nm	
FORWARD VOLTAGE		2.0	2.0	V_f	
REVERSE VOLTAGE			5.0	V_r	$I_r=100\mu\text{A}$
LUMINOUS INTENSITY		45		mcd	$I_f=20\text{MA}$
EMITTED COLOR: RED					
EPOXY LENS FINISH: MILKY WITH DIFFUSED					



LIMITS OF SAFE OPERATION AT 25°C

PARAMETER	MAX	UNITS
FORWARD CURRENT	20	mA
OPERATING, STORAGE TEMP.	-40 TO +85	$^\circ\text{C}$
SOLDERING TEMP.**	MAX. 3SEC.@260	$^\circ\text{C}$

**2mm BELOW PACKAGE BASE



*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= +DECIMAL PRECISION -0.00 MAX= +0.00 -DECIMAL PRECISION

REV.	PART NUMBER
B	SSB-LX2350IW

5mm x 20mm 4 CHIP LIGHT BAR,
630nm HIGH INTENSITY RED CHIPS, MILKY WHITE DIFFUSED.

CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

RELIABILITY NOTE
OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.

LUMEX 425 N. GARY AVE
CAROL STREAM, IL 60188
PHONE: 800-278-5666
FAX: 630-315-2152
WEB: WWW.LUMEX.COM

DRAWN BY: K.Y.	CHECKED BY: G.Y.	APPROVED BY: R.C.	DATE: 09.01.16 PAGE: 1 OF 1 SCALE: N/A
-------------------	---------------------	----------------------	--