


NOTES:

1. MATERIAL: COPPER ALLOY
2. PLATING:
ITEM 1: 30µin HARD GOLD OVER min. 50µin NICKEL
ITEM 2: GOLD FLASH over NICKEL
ITEM 3: NICKEL PLATED
3. CRIMPING: USE CRIMP TOOL 360X10409X
WITH TOOL INSERT 360X20029X
SELECTOR SETTINGS: 3 FOR AWG 16
2 FOR AWG 18
2 FOR AWG 20



STRIPPING DIMENSIONS

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

finish:				tolerance		scale:		
see notes				ISO 2768-m		5:1		
				dim. in mm		material:		
						see notes		
				date		title:		
				name		HIGH POWER CONTACT FEMALE		
				drawn 23.03.98		CRIMP VERSION 10A		
				appd. 23.03.98		D-SUB COMBINATION		
				norm		dwg no:		
				d-old		13K1IE7A		
3 x b	Ä3854	19.01.2011	K.H.					DIN-A4
a	Origin							sh: 1
rev.	description	date	name					part no:

