

SPECIFICATION

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor

- Samsung P/N: **CL05X105KQ5NNNC**
- Description : **CAP, 1 μ F, 6.3V, $\pm$ 10%, X6S, 0402**

A. Samsung Part Number

CL **05** **X** **105** **K** **Q** **5** **N** **N** **N** **C**
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

① Series	Samsung Multi-layer Ceramic Capacitor						
② Size	0402 (inch code)	L: 1.0 ± 0.05	mm	W: 0.5 ± 0.05	mm		
③ Dielectric	X6S	⑧ Inner electrode	Ni				
④ Capacitance	1 μF	Termination	Cu				
⑤ Capacitance tolerance	±10 %	Plating	Sn 100% (Pb Free)				
⑥ Rated Voltage	6.3 V	⑨ Product	Normal				
⑦ Thickness	0.5 ± 0.05 mm	⑩ Special	Reserved for future use				
		⑪ Packaging	Cardboard Type, 7" reel				

B. Samsung Reliability Test and Judgement condition

	Judgement	Test condition
Capacitance	Within specified tolerance	1kHz $\pm$ 10% 1.0 $\pm$ 0.2Vrms
Tan δ (DF)	0.1 max.	
Insulation Resistance	10,000Mohm or 100Mohm $\cdot\mu$ F Whichever is Smaller	Rated Voltage 60~120 sec.
Appearance	No abnormal exterior appearance	Microscope ($\times$ 10)
Withstanding Voltage	No dielectric breakdown or mechanical breakdown	250% of the rated voltage
Temperature Characterisitcs	X6S (From -55 $^{\circ}$ C to 105 $^{\circ}$ C, Capacitance change should be within $\pm$ 22%)	
Adhesive Strength of Termination	No peeling shall be occur on the terminal electrode	500g $\cdot$ F, for 10 $\pm$ 1 sec.
Bending Strength	Capacitance change : within $\pm$ 12.5%	Bending to the limit (1mm) with 1.0mm/sec.
Solderability	More than 75% of terminal surface is to be soldered newly	1) Sn63Pb37 solder 235 $\pm$ 5 $^{\circ}$ C, 5 $\pm$ 0.5sec. 2) SnAg3.0Cu0.5 solder 245 $\pm$ 5 $^{\circ}$ C, 3 $\pm$ 0.3sec. (preheating : 80~120 $^{\circ}$ C for 10~30sec.)
Resistance to Soldering heat	Capacitance change : within $\pm$ 15% Tan δ , IR : initial spec.	Solder pot : 270 $\pm$ 5 $^{\circ}$ C, 10 $\pm$ 1sec.

	Judgement	Test condition
Vibration Test	Capacitance change : within $\pm 10\%$ Tan δ , IR : initial spec.	Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours $\times$ 3 direction (x, y, z)
Moisture Resistance	Capacitance change : within $\pm 12.5\%$ Tan δ : 0.125 max IR : 12.5M $\Omega \cdot \mu F$ or Over	With rated voltage 40 $\pm 2^{\circ}C$, 90~95%RH, 500+12/-0hrs
High Temperature Resistance	Capacitance change : within $\pm 12.5\%$ Tan δ : 0.125 max IR : 25M $\Omega \cdot \mu F$ or Over	With 100% of the rated voltage Max. operating temperature 1000+48/-0hrs
Temperature Cycling	Capacitance change : within $\pm 15\%$ Tan δ , IR : initial spec.	1 cycle condition Min. operating temperature $\rightarrow 25^{\circ}C$ $\rightarrow$ Max. operating temperature $\rightarrow 25^{\circ}C$ 5 cycle test

C. Recommended Soldering method :

Reflow (Reflow Peak Temperature : 260+0/-5 $^{\circ}C$, 10sec. Max)

* For the more detail Specification, Please refer to the Samsung MLCC catalogue.