


ADSL LINE TRANSFORMERS

For Analog Devices AD20msp930 Chipset



- Compatible with ADSL and ADSL over ISDN Central Office Applications
- Excellent THD performance in a small footprint
- Designed to meet UL1950 and EN60950 supplementary insulation requirements for working voltages up to 250 Vrms

Electrical Specifications @ 25°C — Operating Temperature -40°C to 85°C

Part Number	Mounting	Application	Turns Ratio (1-4):(10-7) ($\pm 2\%$)	OCL @ 10 KHz, 0.1 V (1-4) with 2-3 shorted	Leakage Inductance @ 100 KHz, 0.1 V (MAX) (1-4) with 2-3, 8-9, 10-7 shorted	Longitudinal Balance (10 KHz - 1.1 MHz)
B2136	THT	ADSL	1:1.1	1.75 mH	7.5 μ H	50 dB MIN
B2137 ²	SMT	ADSL	1:1.1	1.75 mH	7.5 μ H	50 dB MIN
B2168 ²	SMT	ADSL/ISDN	1:1	100 μ H	4.0 μ H	46 dB MIN
B2188	THT	ADSL/ISDN	1:1	100 μ H	4.0 μ H	46 dB MIN

Additional Specifications


Part Number	THD Typical (Linearity)	DC Resistance (Ω - MAX)		Isolation Voltage (Vrms)	Insertion Loss ¹ (dB @ 300 KHz)
B2136	-80 dB @ 30 KHz	1.5 (1-4) with (2-3) short	1.3 (10-7) with (8-9) short	1500	<0.5
B2137 ²	-80 dB @ 30 KHz	1.5 (1-4) with (2-3) short	1.3 (10-7) with (8-9) short	1500	<0.5
B2168 ²	-80 dB @ 30 KHz	1.0 (1-4) = (2-3)	1.0 (10-8) = (9-7)	1500	<0.5
B2188	-80 dB @ 100 KHz	1.0 (1-4) = (2-3)	1.0 (10-8) = (9-7)	1500	<0.5

¹ Frequency Response: ± 1.0 dB MAX, from 30 KHz to 1.1 MHz.


² Transformers are shipped in trays, unless Tape & Reel packaging is specified by adding the suffix "T" to this part number (B2137T)

Mechanicals

B21XX



B21XX



Weight 6.2 grams
 Tape & Reel 150/reel
 Tray 60/tray (SMT) 65/tray (THT)

Dimensions: $\frac{\text{Inches}}{\text{mm}}$ Unless otherwise specified, all tolerances are $\pm \frac{.010}{.025}$

For More Information :

UNITED STATES (Worldwide)	UNITED KINGDOM (Northern Europe)	FRANCE (Southern Europe)	SINGAPORE (Southern Asia)	TAIWAN, R.O.C. (Northern Asia)	HONG KONG (Great China)	DISTRIBUTOR
12220 World Trade Drive San Diego, CA 92128 U.S.A. http://www.pulseeng.com TEL: 858 674 8100 FAX: 858 674 8262	1 & 2 Huxley Road The Surrey Research Park Guildford, Surrey GU2 5RE United Kingdom TEL: 44 1483 401700 FAX: 44 1483 401701	Zone Industrielle F-39270 Orgelet France TEL: 33 3 84 35 04 04 FAX: 33 3 84 25 46 41	150 Kampong Ampat #07-01/02 KA Centre Singapore 368324 TEL: 65 287 8998 FAX: 65 280 0080	3F-4, No. 81, Sec. 1 HsinTai Wu Road Hsi-Chih, Taipei Hsien Taiwan, R.O.C. Tel: 886 2 2698 0228 FAX: 886 2 2698 0948	19/F, China United Plaza 1008 Tai Nan West Street Cheung Sha Wan, Kowloon Hong Kong, China TEL: 852 2788 6588 FAX: 852 2776 1055	

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.

