





Alcoa Fastening
Systems

DATA SHEET



.09 in. = 2 mm
.22 in. = 6 mm
.72 in. = 18 mm
1.19 in. = 30 mm
1.63 in. = 41 mm



REPLACEMENT PARTS

REF	PART NO.	REQ	DESCRIPTION
1	100820	1	Anvil - Inner
2	103126	1	Anvil - Outer
3	83326	1	Jaws minus O-ring
4	104269	1	Washer - Jaw Follower
5	104267	1	Sleeve
6	501549	1	Ret. Ring (SPIROLOX RRT-100)
7	103116	1	Retainer - Anvil
8	103129	1	Washer - Spring Bearing
9	103130	1	Spring
10	103122	1	Drawbolt
11	103131	1	Adapter - Tool
12	103141	1	Bushing & Release Assem. (inc. 13)
13	103143	1	Release - Jaw
14	500774	7	O-ring (AS 568-008)
15	83311	1	Collet
16	103115	1	Sleeve - Shift
17	103123	1	Ejector
18	103124	1	Spring - Ejector
19	103128	1	Housing - Spring
20	103132	1	Adapter - Drawbolt
21	104270	1	Locknut

SEE OTHER SIDE FOR NOTES AND ASSEMBLY INSTRUCTIONS

99-561

NOSE ASSEMBLY

Alcoa Fastening Systems

Commercial Products

1 Corporate Drive - Kingston, NY 12401

TYPE: Double Action, Blind Rivet

FOR: CKL-P5;100V5, AFS40911-461,460

TOOL: 1365

PRODUCT

REVISION: 12-62

REVISED: 9/19/01

OTHER