

8333 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232 Applications



For more Information
please call

1-800-Belden1

**Description:**

24 AWG stranded (7x32) tinned copper conductors, semi-rigid PVC insulation, multi-paired cable with overall Beldfoil® (100% coverage) + TC braid shield (65% coverage), PVC jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material
3	24	7x32	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material
S-R PVC - Semi-Rigid Polyvinyl Chloride

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	65

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cabling

Overall Nominal Diameter: 6.731 mm

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue & Blue/White
2	White/Orange & Orange/White
3	White/Green & Green/White

Pair Lay Length & Direction:

Lay Length (mm)	Twists/ft. (twist/m)
22.85991	45.934

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +80°C
UL Temperature Rating:	80°C (UL AWM Style 2464)
Bulk Cable Weight:	55.063 Kg/Km
Min. Bend Radius (Install)/Minor Axis:	68.580 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: CMG

8333 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232 Applications

CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2464 (300 V 80°C)
CSA Specification:	AWM I A
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

C(UL) Flame Test:	FT4
-------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
98.43

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
164.05

Nominal Velocity of Propagation:

VP (%)
60

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
78.744

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
21.6546

Max. Operating Voltage - UL:

Voltage
300 V RMS (UL AWM Style 2464)

Max. Recommended Current:

Current
1.6 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8333 060100	30 MT	2.177 KG	CHROME		3 PR #24 PVCR SHLD PVC
8333 0601000	305 MT	19.958 KG	CHROME	C	3 PR #24 PVCR SHLD PVC
8333 060500	152 MT	9.299 KG	CHROME	C	3 PR #24 PVCR SHLD PVC

METRIC MEASUREMENT VERSION

8333 Multi-Conductor - Low Capacitance Computer Cable for EIA RS-232 Applications

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-16-2008

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.