

PIN	STYLE	MATING
01		5.9
02		8
03		9.9
04		11.4
05		9.2
06		10.4
07		5.3
09		17.00
10		8.10
11		8.50
12		3.05
13		14.35
14		4.00

PLATING


1 = 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

4 = 2µm TIN MIN FULL PLATED

5 = 0.25µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

8 = 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

– 1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS



mat'l. code				surface	tolerance	projection	product family			
				ISO 1302	ISO 406	ISO 1101	BERGSTIK			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title			
N	F08-0253	LMU	08.12.10	angles	linear		UNSHR.HEADER			
P	B-18789	LMU	14.09.11				DR SMT			
R	B-18983	LMU	14.10.03			scale N/A	dwg no			
S	B-20276	LMU	15.02.16	dr	D.LE	01.01.24	sheet 2 of -			
T	B-20561	AMA	15.03.26	enr	JM.C	01.01.24	95278			
				chr	JM.C	01.01.24	A3			
				appd	JF.N	01.01.24	type CUSTOMER Drawing			
sheet index	revision sheet									