


Tous droits strictement réservés. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.




Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



PRODUCT NUMBER
SEE TABLE



CONFIDENTIAL

mat'l code				SEE NOTES		tolerances unless otherwise specified		CUSTOMER		ELECTRONICS	
lfr	ecn no.	dr	date	linear				COPY		FCI	www.fciconnect.com
				angles				projection		title PCI STYLE ASSEMBLY w/ MOUNTING BRACKET	
				dr	G. PETERS	2/16/98		MM		product family	METAGIG(tm)
				enr	D. CASEY	2/16/98		scale		size	dwg no
				chr	G. PETERS	2/16/98		3:1		A	74403
				appd	D. CASEY	2/16/98					
sheet index	revision sheet	E	2								

Pro/E

PDM: Rev:E

STATUS: Released


cage code 22526

Printed: Dec 09, 2007



PRODUCT NUMBER

SEE TABLE



RECOMMENDED PCB FOOTPRINT AS
VIEWED FROM COMPONENT SIDE

CONFIDENTIAL

mat'l code				SEE NOTES				tolerances unless otherwise specified				CUSTOMER				 ELECTRONICS www.fciconnect.com			
lfr		ecn no.		dr		date		linear				projection				title PCI STYLE ASSEMBLY w/ MOUNTING BRACKET			
								angles						product family		METAGIG (tm)		code	
								dr		G. PETERS		2/16/98		size		dwg no		213	
								engr		D. CASEY		2/16/98		scale		A		sheet	
								chr		G. PETERS		2/16/98		5:1		74403		3	
								appd		D. CASEY		2/16/98							
sheet index		revision sheet		E		3													

Pro/E

PDM: Rev:E

STATUS: **Released**


Printed: Dec 09, 2007

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



PRODUCT NUMBER
SEE TABLE



RECOMMEDED PCI OPENING

CONFIDENTIAL

mat'l code				SEE NOTES		tolerances unless otherwise specified		CUSTOMER		FCI ELECTRONICS	
litr	ecn no.	dr	date	linear		COPY		projection		title	
										PCI STYLE ASSEMBLY	
										w/ MOUNTING BRACKET	
										product family	
				angles		dr	G.PETERS	2/16/98		METAGIG(tm)	
						engr	D.CASEY	2/16/98		code	
						chr	G.PETERS	2/16/98		213	
						appd	D.CASEY	2/16/98		sheet	
										4	
sheet index	revision	E									
	sheet	4									



1 | 2

3 |


4

PRODUCT NUMBER	DESCRIPTION	NO. of POSI.	PACKAGING
74403-001	PCI ASSY w/15GXT CONTACTS, HSG. COLOR BLK.	1	IN TRAYS
74403-002	PCI ASSY w/30Au CONTACTS, HSG. COLOR, NAT.	1	IN TRAYS
74403-003	PCI ASSY w/15GXT CONTACTS, HSG. COLOR BLK.	1	TAPE & REEL
74403-004	PCI ASSY w/30Au CONTACTS, HSG. COLOR NAT.	1	TAPE & REEL
74403-005	PCI ASSY w/15GXT CONTACTS, HSG. COLOR BLK.	2	IN TRAYS
74403-006	PCI ASSY w/30Au CONTACTS, HSG. COLOR NAT.	2	IN TRAYS
74403-007	PCI ASSY w/15GXT CONTACTS, HSG, COLOR BLK.	3	IN TRAYS
74403-008	PCI ASSY w/30Au CONTACTS, HSG. COLOR NAT.	3	IN TRAYS
74403-009	PCI ASSY w/15GXT CONTACTS, HSG. COLOR BLK.	4	IN TRAYS
74403-010	PCI ASSY w/30Au CONTACTS, HSG. COLOR NAT.	4	IN TRAYS

NOTES:

- UNLESS OTHERWISE SPECIFIED:
ALL DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994.
ALL UNTOLERANCED DIMENSIONS ARE BASIC.
 0.25
- DIMENSIONS SHOWN IN PARANTHESES ARE "REFERENCE DIMENSION"
AS PER ASME Y14.5M, 1994.
- FOR DETAILS OF PCI BRACKET SEE DRAWING 73592.1
- ④ DATUM & DIMENSIONS ESTABLISHED BY CUSTOMER.
- CONNECTOR WILL ACCOMMODATE P.C.B'S. UP TO 3.00 MAX THICKNESS.
- ⑥ MATERIAL: CONTACTS, BeCu
SHIELD, Phos Bronze
HOUSING, UL 94 V-O RATED HIGH TEMP. THERMOPLASTIC
BRACKET, A91 MAGNESIUM OR ZAMAK 3
PLATING: CONTACTS, NOBLE METAL PLATING IN CONTACT AREA
SHIELD, TIN-LEAD
BRACKET, ELECTROLESS TIN-LEAD
- RECOMMENDED PCI BRACKET OR PANEL THICKNESS OF 0.76 ± 0.03 .

CONFIDENTIAL

mat'l code				SEE NOTES		tolerances unless otherwise specified		CUSTOMER		 ELECTRONICS www.fciconnect.com	
lfr	ecn no.	dr	date	linear		projection		COPY		title PCI STYLE ASSEMBLY w/ MOUNTING BRACKET	
				angles				product family METAGIG (tm)		code 213	
				dr	G.PETERS	2/16/98		MM		size 74403	
				enr	D.CASEY	2/16/98		scale 2:1		sheet 5	
				chr	G.PETERS	2/16/98		A		sheet 5	
				appd	D.CASEY	2/16/98					
sheet	revision	E									
index	sheet	5									

1 | 2

Pro/E

3 |

cage code 22526

4

PDM: Rev:E

STATUS: **Released**

Printed: Dec 09, 2007