

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE	DIMENSIONS - in. [mm]				
		A ± .03 [0,8]	W ± .01 [0,3]	C ± .02 [0,5]	M ± .03 [0,8]	H ± .01 [0,3]
P18-6RHT6	#6	.62 [15,75]	.25 [6,35]	.21 [5,33]	.50 [12,70]	.15 [3,81]
P18-8RHT6	#8	.71 [18,03]	.31 [7,87]	.25 [6,35]	.55 [13,97]	.17 [4,32]
P18-10RHT6	#10	.71 [18,03]	.31 [7,87]	.25 [6,35]	.55 [13,97]	.20 [5,08]

UL TOOLS
CT-100A CT-200 CT-600-A (CT-570CH) CT-1570 CT-2500 (CT-2570CH)
PANDUIT APPROVED TOOLS
CT-160 CT-260

NOTES:

1. UL LISTED FOR:

- A. #22-16 AWG SOLID OR STRANDED COPPER WIRE
- B. 650°F [343°C] MAX TEMP RATING
- C. 2000 VOLTS MAX


2. SEE www.panduit.com FOR PACKAGE QUANTITIES

3. MATERIAL:

- A. STAMPING - .03" [0,8] THK COPPER, NICKEL PLATED

4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS

5. WIRE STRIP LENGTH: $9/32'' \begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$ [7,1mm $\begin{smallmatrix} +0,8 \\ -0 \end{smallmatrix}$]



TITLE	
#22-16 BARREL NON-INSULATED RING TONGUE, HIGH TEMPERATURE, 650° F	
CUSTOMER DRAWING	
ITEM REVISION NAME	N41265BA/07
DATASET FILE NAME	N41265BA/07
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	MATERIAL: SEE NOTE 3
.X ± .XX ±	.XXX ± ANGLES ±
THIRD ANGLE PROJECTION	DRAWING NUMBER: A41265
DRAWN BY: DAW	DATE: NONE
CHK: NONE	SCALE: NONE
SHT 1 OF 1	SIZE: A