

For more Information
please call

1-800-Belden1



General Description:

20 AWG solid .032" bare copper conductor, gas-injected foam HDPE insulation, bare copper braid shields (95% coverage), Belflex® jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	20	Solid	BC - Bare Copper	0.8128

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FHDPE - Foam High Density Polyethylene	3.683

Inner Shield

Inner Shield Material:

Type	Inner Shield Material	Coverage (%)
Braid	BC - Bare Copper	95

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (mm)
PE - Polyethylene	5.4864

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Belflex®	PVC Blend - Polyvinyl Chloride Blend

Overall Cable

Overall Nominal Diameter: 9.144 mm

Mechanical Characteristics (Overall)

Operating Temperature Range:	-35°C To +75°C
Non-UL Temperature Rating:	75°C
Bulk Cable Weight:	113.103 Kg/Km
Max. Recommended Pulling Tension:	551.577 N
Min. Bend Radius/Minor Axis:	95.250 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes

CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	59/U

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black for permanent installations. All colors for field deployable use.

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Inductance:

Inductance (µH/m)
0.318257

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
53.1522

Nominal Velocity of Propagation:

VP (%)
83

Nominal Delay:

Delay (ns/m)
4.00282

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
33.1381

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/km)
8.2025

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
5.2496

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1	0.9843
3.6	1.9686
10	2.6248
71.5	7.2182
135	9.843
270	13.7802
360	15.7488
540	19.3579
720	22.6389
750	23.2951
1000	28.8728
1500	39.372
2250	53.8084
3000	66.9324

Max. Operating Voltage - Non-UL:

Voltage
300 V RMS

Minimum Structural Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
5	850	21
851	3000	15

Sweep Test

Sweep Testing:	100% Sweep tested 5 MHz to 3 GHz.
----------------	-----------------------------------

Notes (Overall)

Notes: Permanent indent printing for field identification.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1856A B591000	1,000 FT	83.000 LB	BLACK, MATTE	C	#20 PE/GIFHDPELDPE PVC TRIAX
1856A 0021000	1,000 FT	83.000 LB	RED	C	#20 PE/GIFHDPELDPE PVC TRIAX
1856A 0041000	1,000 FT	83.000 LB	YELLOW	C	#20 PE/GIFHDPELDPE PVC TRIAX
1856A 0051000	1,000 FT	83.000 LB	GREEN, DARK	C	#20 PE/GIFHDPELDPE PVC TRIAX
1856A 0061000	1,000 FT	83.000 LB	BLUE, LIGHT	C	#20 PE/GIFHDPELDPE PVC TRIAX

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 09-19-2012

© 2015 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.