

- Low Supply-Voltage Range: 1.8 V to 3.6 V
- Ultra-Low Power Consumption:  
Active Mode: 262  $\mu$ A at 1 MHz, 2.2 V  
Standby Mode: 1.1  $\mu$ A  
Off Mode (RAM Retention): 0.1  $\mu$ A
- Five Power-Saving Modes
- Wake-Up From Standby Mode in Less Than 6  $\mu$ s
- 16-Bit RISC Architecture, 125-ns Instruction Cycle Time
- 16-Bit Sigma-Delta Analog-to-Digital (A/D) Converter With Internal Reference and Five Differential Analog Inputs
- Dual 12-Bit Digital-to-Analog (D/A) Converter
- Dual Configurable Operational Amplifiers
- 16-Bit Timer\_A With Three Capture/Compare Registers
- 16-Bit Timer\_B With Three Capture/Compare-With-Shadow Registers
- Two Universal Serial Communication Interfaces (USCI)
  - USCI\_A0
    - Enhanced UART Supporting Auto-Baudrate Detection
    - IrDA Encoder and Decoder
    - Synchronous SPI
  - USCI\_B0
    - I<sup>2</sup>C™
    - Synchronous SPI
- Integrated LCD Driver With Contrast Control for Up to 128 Segments
- Brownout Detector
- Basic Timer With Real-Time Clock Feature
- Supply Voltage Supervisor/Monitor With Programmable Level Detection
- On-Chip Comparator
- Serial Onboard Programming, No External Programming Voltage Needed
- Programmable Code Protection by Security Fuse
- Bootstrap Loader
- On-Chip Emulation Module
- MSP430FG47x Family Members Include
  - MSP430FG477: 32KB+256B Flash Memory 2KB RAM
  - MSP430FG478: 48KB+256B Flash Memory 2KB RAM
  - MSP430FG479: 60KB+256B Flash Memory 2KB RAM
- Available in 113-Ball BGA (ZQW) and 80-Pin QFP (PN) Packages (see Available Options)
- For Complete Module Descriptions, See the *MSP430x4xx Family User's Guide*, Literature Number SLAU056

## description

The Texas Instruments MSP430 family of ultralow-power microcontrollers consists of several devices featuring different sets of peripherals targeted for various applications. The architecture, combined with five low-power modes, is optimized to achieve extended battery life in portable measurement applications. The device features a powerful 16-bit RISC CPU, 16-bit registers, and constant generators that contribute to maximum code efficiency. The digitally controlled oscillator (DCO) allows wake-up from low-power modes to active mode in less than 6  $\mu$ s.

The MSP430FG47x is a microcontroller configuration with two 16-bit timers, a basic timer with a real-time clock, a high performance 16-bit sigma-delta A/D converter, dual 12-bit D/A converters, two configurable operational amplifiers, two universal serial communication interface, 48 I/O pins, and a liquid crystal display driver.

Typical applications for this device include analog and digital sensor systems, digital motor control, remote controls, thermostats, digital timers, hand-held meters, etc.



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage. ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications. These devices have limited built-in ESD protection.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

**PRODUCTION DATA** information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 2011, Texas Instruments Incorporated

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

### AVAILABLE OPTIONS<sup>†</sup>

| T <sub>A</sub> | PACKAGED DEVICES <sup>‡</sup>                         |                                                    |
|----------------|-------------------------------------------------------|----------------------------------------------------|
|                | PLASTIC 113-BALL BGA (ZQW)                            | PLASTIC 80-PIN QFP (PN)                            |
| -40°C to 85°C  | MSP430FG477IZQW<br>MSP430FG478IZQW<br>MSP430FG479IZQW | MSP430FG477IPN<br>MSP430FG478IPN<br>MSP430FG479IPN |

<sup>†</sup> For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI web site at [www.ti.com](http://www.ti.com).

<sup>‡</sup> Package drawings, thermal data, and symbolization are available at [www.ti.com/packaging](http://www.ti.com/packaging).

## DEVELOPMENT TOOL SUPPORT


All MSP430 microcontrollers include an Embedded Emulation Module (EEM) allowing advanced debugging and programming through easy to use development tools. Recommended hardware options include the following:

- Debugging and Programming Interface
  - MSP-FET430UIF (USB)
  - MSP-FET430PIF (Parallel Port)
- Debugging and Programming Interface with Target Board
  - MSP-FET430U80 (PN package)
- Production Programmer
  - MSP-GANG430



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

**pin designation, MSP430FG47xIZQW**




Note: For terminal assignments, see the *MSP430xG47x Terminal Functions* table.


MSP430FG47x  
MIXED SIGNAL MICROCONTROLLER

SLAS580D - OCTOBER 2008 - REVISED MARCH 2011

pin designation, MSP430FG47xIPN



**functional block diagram**



# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

### Terminal Functions

| TERMINAL                                    |        |          | I/O | DESCRIPTION                                                                                                                                                                                                                                         |
|---------------------------------------------|--------|----------|-----|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| NAME                                        | NO.    |          |     |                                                                                                                                                                                                                                                     |
|                                             | 80 PIN | 113 PIN  |     |                                                                                                                                                                                                                                                     |
| AV <sub>CC</sub>                            | 52     | F12      |     | Analog supply voltage, positive terminal.                                                                                                                                                                                                           |
| AV <sub>SS</sub>                            | 53     | E12      |     | Analog supply voltage, negative terminal.                                                                                                                                                                                                           |
| DV <sub>CC1</sub>                           | 1      | A1       |     | Digital supply voltage, positive terminal. Supplies all digital parts.                                                                                                                                                                              |
| DV <sub>SS1</sub>                           | 79     | A3       |     | Digital supply voltage, negative terminal. Supplies all digital parts.                                                                                                                                                                              |
| DV <sub>CC2</sub>                           | 80     | A2       |     | Digital supply voltage, positive terminal. Supplies all digital parts.                                                                                                                                                                              |
| DV <sub>SS2</sub>                           | 78     | B2<br>B3 |     | Digital supply voltage, negative terminal. Supplies all digital parts.                                                                                                                                                                              |
| P1.0/TA0/<br>OA0RFB                         | 58     | C11      | I/O | General-purpose digital I/O pin<br>Timer_A, capture: CCI0A input, compare: Out0 output<br>Range switch to OA0 output<br>BSL transmit                                                                                                                |
| P1.1/TA0/MCLK/<br>OA1RFB                    | 57     | C12      | I/O | General-purpose digital I/O pin<br>Timer_A, capture: CCI0B input, compare: Out0 output<br>MCLK signal output<br>Range switch to OA1 output<br>BSL receive                                                                                           |
| P1.2/TA1/A4-/<br>OA0I3 (SW0C)               | 56     | D11      | I/O | General-purpose digital I/O pin<br>Timer_A, capture: CCI1A input, compare: Out1 output<br>SD16 negative analog input A4<br>OA0, analog input I3                                                                                                     |
| P1.3/TBOUTH/<br>SVSOUT/A4+/<br>OA1I3 (SW1C) | 55     | D12      | I/O | General-purpose digital I/O pin/Timer_A, capture: CCI2A input, compare: Out2 output<br>switch all PWM digital output ports to high impedance – Timer_B TB0 to TB2<br>SVS comparator output<br>SD16 positive analog input A4<br>OA1, analog input I3 |
| P1.4/TBCLK/<br>SMCLK/A3-/<br>OA1I0/DAC1     | 54     | E11      | I/O | General-purpose digital I/O pin/<br>Timer_B, clock signal TBCLK input<br>SMCLK signal output<br>SD16 negative analog input A3<br>OA1, analog input I0<br>DAC12.1 output                                                                             |
| P1.5/TACLK/<br>ACLK/A3+                     | 51     | F11      | I/O | General-purpose digital I/O pin<br>Timer_A, clock signal TACLK input<br>ACLK signal output<br>SD16 positive analog input A3                                                                                                                         |
| P1.6/CA0/A2-/<br>OA0I0/DAC0                 | 50     | G12      | I/O | General-purpose digital I/O pin<br>Comparator_A input 0<br>SD16 negative analog input A2<br>OA0, analog input I0<br>DAC12.0 output                                                                                                                  |
| P1.7/CA1/A2+                                | 49     | G11      | I/O | General-purpose digital I/O pin<br>Comparator_A input 1<br>SD16 positive analog input A2                                                                                                                                                            |
| P2.0/TA2/S1                                 | 4      | C2<br>C3 | I/O | General-purpose digital I/O pin<br>Timer_A, capture: CCI2A/B input, compare: Out2 output<br>LCD segment output 1                                                                                                                                    |
| P2.1/TB0/S0                                 | 3      | C1       | I/O | General-purpose digital I/O pin<br>Timer_B, capture: CCI0A/B input, compare: Out0 output<br>LCD segment output 0                                                                                                                                    |



### Terminal Functions (continued)

| TERMINAL                      |        |         | I/O | DESCRIPTION                                                                                                                                              |
|-------------------------------|--------|---------|-----|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| NAME                          | NO.    |         |     |                                                                                                                                                          |
|                               | 80 PIN | 113 PIN |     |                                                                                                                                                          |
| P2.2/TB1                      | 2      | B1      | I/O | General-purpose digital I/O pin<br>Timer_B, capture: CCI1A/B input, compare: Out1 output                                                                 |
| P2.3/TB2                      | 77     | B4      | I/O | General-purpose digital I/O pin<br>Timer_B, capture: CCI2A/B input, compare: Out2 output                                                                 |
| P2.4/UCA0TXD/<br>UCA0SIMO     | 76     | A4      | I/O | General-purpose digital I/O pin<br>USCIA transmit data output in UART mode, slave data in/master out in SPI mode                                         |
| P2.5/UCA0RXD/<br>UCA0SOMI     | 75     | D4      | I/O | General-purpose digital I/O pin<br>USCI A0 receive data input in UART mode, slave data out/master in in SPI mode                                         |
| P2.6/CAOUT/S2                 | 5      | D1      | I/O | General-purpose digital I/O pin<br>Comparator_A output<br>LCD segment output 2                                                                           |
| P2.7/S3                       | 6      | D2      | I/O | General-purpose digital I/O pin<br>LCD segment output 3                                                                                                  |
| P3.0/UCB0STE/<br>UCA0CLK      | 41     | M12     | I/O | General-purpose digital I/O pin<br>USCI B0 slave transmit enable/USCI A0 clock input/output                                                              |
| P3.1/UCB0SIMO/<br>UCB0SDA/S26 | 42     | L12     | I/O | General-purpose digital I/O pin<br>USCI B0 slave in/master out in SPI mode, SDA I <sup>2</sup> C data in I <sup>2</sup> C mode<br>LCD segment output 26  |
| P3.2/UCB0SOMI/<br>UCB0SCL/S27 | 43     | K11     | I/O | General-purpose digital I/O pin<br>USCI B0 slave out/master in in SPI mode, SCL I <sup>2</sup> C clock in I <sup>2</sup> C mode<br>LCD segment output 27 |
| P3.3/UCB0CLK/<br>UCA0STE      | 44     | K12     | I/O | General-purpose digital I/O<br>USCI B0 clock input/output, USCI A0 slave transmit enable                                                                 |
| P3.4/S28                      | 45     | J11     | I/O | General-purpose digital I/O pin<br>LCD segment output 28                                                                                                 |
| P3.5/S29                      | 46     | J12     | I/O | General-purpose digital I/O pin<br>LCD segment output 29                                                                                                 |
| P3.6/S30                      | 47     | H11     | I/O | General-purpose digital I/O pin<br>LCD segment output 30                                                                                                 |
| P3.7/S31                      | 48     | H12     | I/O | General-purpose digital I/O pin<br>LCD segment output 31                                                                                                 |
| P4.0/S11                      | 18     | K2      | I/O | General-purpose digital I/O pin<br>LCD segment output 11                                                                                                 |
| P4.1/S10                      | 17     | K1      | I/O | General-purpose digital I/O pin<br>LCD segment output 10                                                                                                 |
| P4.2/S9                       | 16     | J2      | I/O | General-purpose digital I/O pin<br>LCD segment output 9                                                                                                  |
| P4.3/S8                       | 15     | J1      | I/O | General-purpose digital I/O pin<br>LCD segment output 8                                                                                                  |
| P4.4/S7                       | 14     | H2      | I/O | General-purpose digital I/O pin<br>LCD segment output 7                                                                                                  |
| P4.5/S6                       | 13     | H1      | I/O | General-purpose digital I/O pin<br>LCD segment output 6                                                                                                  |
| P4.6/S5                       | 12     | G2      | I/O | General-purpose digital I/O pin<br>LCD segment output 5                                                                                                  |
| P4.7/S4                       | 11     | G1      | I/O | General-purpose digital I/O pin<br>LCD segment output 4                                                                                                  |

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

### Terminal Functions (continued)

| TERMINAL                    |        |         | I/O | DESCRIPTION                                                                                                                                  |
|-----------------------------|--------|---------|-----|----------------------------------------------------------------------------------------------------------------------------------------------|
| NAME                        | NO.    |         |     |                                                                                                                                              |
|                             | 80 PIN | 113 PIN |     |                                                                                                                                              |
| COM0                        | 33     | L8      | O   | Common output, COM0–3 are used for LCD backplanes                                                                                            |
| P5.0/S20                    | 27     | L5      | I/O | General-purpose digital I/O pin<br>LCD segment output 20                                                                                     |
| P5.1/S21                    | 28     | M5      | I/O | General-purpose digital I/O pin<br>LCD segment output 21                                                                                     |
| P5.2/COM1                   | 34     | M8      | I/O | General-purpose digital I/O pin<br>common output, COM0–3 are used for LCD backplanes                                                         |
| P5.3/COM2                   | 35     | L9      | I/O | General-purpose digital I/O pin<br>common output, COM0–3 are used for LCD backplanes                                                         |
| P5.4/COM3                   | 36     | M9      | I/O | General-purpose digital I/O pin<br>common output, COM0–3 are used for LCD backplanes                                                         |
| LDCAP/R33                   | 37     | J9      | I/O | Capacitor connection for LCD charge pump<br>input port of most positive analog LCD level (V4)                                                |
| P5.5/R23                    | 38     | M10     | I/O | General-purpose digital I/O pin<br>input port of the second most positive analog LCD level (V3)                                              |
| P5.6/LCDREF/<br>R13         | 39     | L10     | I/O | General-purpose digital I/O pin<br>External LCD reference voltage input<br>input port of the third most positive analog LCD level (V3 or V2) |
| P5.7/R03                    | 40     | M11     | I/O | General-purpose digital I/O pin<br>input port of the fourth most positive analog LCD level (V1)                                              |
| P6.0/A0+/OA0O               | 67     | B8      | I/O | General-purpose digital I/O pin<br>SD16 positive analog input A0<br>OA0, output                                                              |
| P6.1/A0–/OA0FB              | 66     | B9      | I/O | General-purpose digital I/O pin<br>SD16 positive negative input A0<br>OA0, analog input feedback                                             |
| P6.2/OA0I1<br>(SW0A)        | 65     | A9      | I/O | General-purpose digital I/O pin<br>OA0, analog input I1                                                                                      |
| P6.3/A1+/OA1O               | 64     | D9      | I/O | General-purpose digital I/O pin<br>SD16 positive analog input A1<br>OA1, output                                                              |
| P6.4/A1–/OA1FB              | 63     | A10     | I/O | General-purpose digital I/O pin<br>SD16 positive negative input A1<br>OA1, analog input feedback                                             |
| P6.5/OA0I2<br>(SW0B)        | 62     | B10     | I/O | General-purpose digital I/O pin<br>OA0, analog input I2                                                                                      |
| P6.6/OA1I1<br>(SW1A)        | 61     | A11     | I/O | General-purpose digital I/O pin<br>OA1, analog input I1                                                                                      |
| P6.7/OA1I2/<br>SVSIN (SW1B) | 59     | B12     | I/O | General-purpose digital I/O pin<br>OA1, analog input I2<br>SVS input                                                                         |
| S12                         | 19     | L1      | O   | LCD segment output 12                                                                                                                        |
| S13                         | 20     | M1      | O   | LCD segment output 13                                                                                                                        |
| S14                         | 21     | M2      | O   | LCD segment output 14                                                                                                                        |
| S15                         | 22     | M3      | O   | LCD segment output 15                                                                                                                        |
| S16                         | 23     | L3      | O   | LCD segment output 16                                                                                                                        |



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265



### Terminal Functions (continued)

| TERMINAL         |        |                                                                                                                          | I/O | DESCRIPTION                                                                                            |
|------------------|--------|--------------------------------------------------------------------------------------------------------------------------|-----|--------------------------------------------------------------------------------------------------------|
| NAME             | NO.    |                                                                                                                          |     |                                                                                                        |
|                  | 80 PIN | 113 PIN                                                                                                                  |     |                                                                                                        |
| S17              | 24     | L4                                                                                                                       | O   | LCD segment output 17                                                                                  |
| S18              | 25     | M4                                                                                                                       | O   | LCD segment output 18                                                                                  |
| S19              | 26     | J4                                                                                                                       | O   | LCD segment output 19                                                                                  |
| S22              | 29     | L6                                                                                                                       | O   | LCD segment output 22                                                                                  |
| S23              | 30     | M6                                                                                                                       | O   | LCD segment output 23                                                                                  |
| S24              | 31     | L7                                                                                                                       | O   | LCD segment output 24                                                                                  |
| S25              | 32     | M7                                                                                                                       | O   | LCD segment output 25                                                                                  |
| GND              | 7      | E2                                                                                                                       |     | Ground. It is used to shield the oscillator. See Note 1.                                               |
| XIN              | 8      | E1                                                                                                                       | I   | Input port for crystal oscillator XT1. Standard or watch crystals can be connected.                    |
| XOUT             | 9      | F1                                                                                                                       | O   | Output port for crystal oscillator XT1. Standard or watch crystals can be connected.                   |
| GND              | 10     | F2                                                                                                                       |     | Ground. It is used to shield the oscillator. See Note NO TAG.                                          |
| V <sub>REF</sub> | 60     | A12                                                                                                                      | O   | Input for an external reference voltage/internal reference voltage output                              |
| RST/NMI          | 74     | B5                                                                                                                       | I   | Reset input, nonmaskable interrupt input port, or bootstrap loader start (in flash devices).           |
| TCK              | 73     | A5                                                                                                                       | I   | Test clock (JTAG). TCK is the clock input port for device programming test and bootstrap loader start. |
| TDI/TCLK         | 71     | A6                                                                                                                       | I   | Test data input or test clock input. The device protection fuse is connected to TDI/TCLK.              |
| TDO/TDI          | 70     | B7                                                                                                                       | I/O | Test data output port. TDO/TDI data output or programming data input terminal.                         |
| TMS              | 72     | B6                                                                                                                       | I   | Test mode select. TMS is used as an input port for device programming and test.                        |
| XT2OUT           | 68     | A8                                                                                                                       | O   | Output terminal of crystal oscillator XT2                                                              |
| XT2IN            | 69     | A7                                                                                                                       | I   | Input port for crystal oscillator XT2                                                                  |
| Reserved         | NA     | B11, D6, D7, D8, E4, E5, E6, E7, E8, E9, F4, F5, F8, F9, G4, G5, G8, G9, H4, H5, H6, H7, H8, H9, J5, J6, J7, J8, L2, L11 |     | BGA package unused balls. Connection to DV <sub>SS</sub> /AV <sub>SS</sub> recommended.                |

NOTE 1: It is recommended to connect GND externally to DV<sub>SS</sub>.

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

### short-form description

#### CPU

The MSP430 CPU has a 16-bit RISC architecture that is highly transparent to the application. All operations, other than program-flow instructions, are performed as register operations in conjunction with seven addressing modes for source operand and four addressing modes for destination operand.

The CPU is integrated with 16 registers that provide reduced instruction execution time. The register-to-register operation execution time is one cycle of the CPU clock.

Four of the registers, R0 to R3, are dedicated as program counter, stack pointer, status register, and constant generator, respectively. The remaining registers are general-purpose registers.

Peripherals are connected to the CPU using data, address, and control buses, and can be handled with all instructions.

#### instruction set

The instruction set consists of 51 instructions with three formats and seven address modes. Each instruction can operate on word and byte data. Table 1 shows examples of the three types of instruction formats, and Table 2 lists the address modes.

|                          |           |
|--------------------------|-----------|
| Program Counter          | PC/R0     |
| Stack Pointer            | SP/R1     |
| Status Register          | SR/CG1/R2 |
| Constant Generator       | CG2/R3    |
| General-Purpose Register | R4        |
| General-Purpose Register | R5        |
| General-Purpose Register | R6        |
| General-Purpose Register | R7        |
| General-Purpose Register | R8        |
| General-Purpose Register | R9        |
| General-Purpose Register | R10       |
| General-Purpose Register | R11       |
| General-Purpose Register | R12       |
| General-Purpose Register | R13       |
| General-Purpose Register | R14       |
| General-Purpose Register | R15       |

**Table 1. Instruction Word Formats**

|                                   |                 |                       |
|-----------------------------------|-----------------|-----------------------|
| Dual operands, source-destination | e.g., ADD R4,R5 | R4 + R5 ---> R5       |
| Single operands, destination only | e.g., CALL R8   | PC -->(TOS), R8--> PC |
| Relative jump, un/conditional     | e.g., JNE       | Jump-on-equal bit = 0 |

**Table 2. Address Mode Descriptions**

| ADDRESS MODE           | S | D | SYNTAX             | EXAMPLE          | OPERATION                     |
|------------------------|---|---|--------------------|------------------|-------------------------------|
| Register               | ● | ● | MOV Rs,Rd          | MOV R10,R11      | R10 → R11                     |
| Indexed                | ● | ● | MOV X(Rn),Y(Rm)    | MOV 2(R5),6(R6)  | M(2+R5) → M(6+R6)             |
| Symbolic (PC relative) | ● | ● | MOV EDE,TONI       |                  | M(EDE) → M(TONI)              |
| Absolute               | ● | ● | MOV & MEM, & TCDAT |                  | M(MEM) → M(TCDAT)             |
| Indirect               | ● |   | MOV @Rn,Y(Rm)      | MOV @R10,Tab(R6) | M(R10) → M(Tab+R6)            |
| Indirect autoincrement | ● |   | MOV @Rn+,Rm        | MOV @R10+,R11    | M(R10) → R11<br>R10 + 2 → R10 |
| Immediate              | ● |   | MOV #X,TONI        | MOV #45,TONI     | #45 → M(TONI)                 |

NOTE: S = source D = destination



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

## **operating modes**

The MSP430 has one active mode and five software selectable low-power modes of operation. An interrupt event can wake up the device from any of the five low-power modes, service the request, and restore back to the low-power mode on return from the interrupt program.

The following six operating modes can be configured by software:

- Active mode (AM)
  - All clocks are active
- Low-power mode 0 (LPM0)
  - CPU is disabled
  - ACLK and SMCLK remain active
  - FLL+ loop control remains active
- Low-power mode 1 (LPM1)
  - CPU is disabled
  - ACLK and SMCLK remain active
  - FLL+ loop control is disabled
- Low-power mode 2 (LPM2)
  - CPU is disabled
  - MCLK, FLL+ loop control, and DCOCLK are disabled
  - DCO's dc generator remains enabled
  - ACLK remains active
- Low-power mode 3 (LPM3)
  - CPU is disabled
  - MCLK, FLL+ loop control, and DCOCLK are disabled
  - DCO's dc generator is disabled
  - ACLK remains active
- Low-power mode 4 (LPM4)
  - CPU is disabled
  - ACLK is disabled
  - MCLK, FLL+ loop control, and DCOCLK are disabled
  - DCO's dc generator is disabled
  - Crystal oscillator is stopped

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

### interrupt vector addresses

The interrupt vectors and the power-up starting address are located in the address range 0xFFFF to 0xFFC0. The vector contains the 16-bit address of the appropriate interrupt-handler instruction sequence.

If the reset vector (located at address 0xFFFFE) contains 0xFFFF (e.g., flash is not programmed) the CPU goes into LPM4 immediately after power-up.

| INTERRUPT SOURCE                                                                       | INTERRUPT FLAG                                                                            | SYSTEM INTERRUPT                                | WORD ADDRESS | PRIORITY    |
|----------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|-------------------------------------------------|--------------|-------------|
| Power-Up<br>External Reset<br>Watchdog<br>Flash Memory<br>PC Out-of-Range (see Note 4) | PORIFG<br>RSTIFG<br>WDTIFG<br>KEYV<br>(see Note 1)                                        | Reset                                           | 0xFFFFE      | 15, highest |
| NMI<br>Oscillator Fault<br>Flash Memory Access Violation                               | NMIIFG (see Notes 1 and 3)<br>OFIFG (see Notes 1 and 3)<br>ACCVIFG (see Notes 1, 2 and 4) | (Non)maskable<br>(Non)maskable<br>(Non)maskable | 0xFFFC       | 14          |
| Timer_B3                                                                               | TBCCR0 CCIFG0 (see Note 2)                                                                | Maskable                                        | 0xFFFA       | 13          |
| Timer_B3                                                                               | TBCCR1 CCIFG1 ... TBCCR3 CCIFG3,<br>TBIFG (see Notes 1 and 2)                             | Maskable                                        | 0xFFF8       | 12          |
| Comparator_A                                                                           | CAIFG                                                                                     | Maskable                                        | 0xFFF6       | 11          |
| Watchdog Timer+                                                                        | WDTIFG                                                                                    | Maskable                                        | 0xFFF4       | 10          |
| USCI_A0/USCI_B0 receive<br>USCI_B0 I2C status                                          | UCA0RXIFG, UCB0RXIFG<br>(see Notes 1 and 5)                                               | Maskable                                        | 0xFFF2       | 9           |
| USCI_A0/USCI_B0 transmit<br>USCI_B0 I2C receive/transmit                               | UCA0TXIFG, UCB0TXIFG<br>(see Note 1 and 6)                                                | Maskable                                        | 0xFFF0       | 8           |
| SD16_A                                                                                 | SD16CCTLx SD16OVIFG, SD16CCTLx SD16IFG<br>(see Notes 1 and 2)                             | Maskable                                        | 0xFFEE       | 7           |
| Timer_A3                                                                               | TACCR0 CCIFG0 (see Note 2)                                                                | Maskable                                        | 0xFFEC       | 6           |
| Timer_A3                                                                               | TACCR1 CCIFG1 and TACCR2 CCIFG2,<br>TAIFG (see Notes 1 and 2)                             | Maskable                                        | 0xFFEA       | 5           |
| I/O Port P1 (Eight Flags)                                                              | P1IFG.0 to P1IFG.7 (see Notes 1 and 2)                                                    | Maskable                                        | 0xFFE8       | 4           |
| DAC12                                                                                  | DAC12_0IFG, DAC12_1IFG                                                                    | Maskable                                        | 0xFFE6       | 3           |
|                                                                                        |                                                                                           | Maskable                                        | 0xFFE4       | 2           |
| I/O Port P2 (Eight Flags)                                                              | P2IFG.0 to P2IFG.7 (see Notes 1 and 2)                                                    | Maskable                                        | 0xFFE2       | 1           |
| Basic Timer1/RTC                                                                       | BTIFG                                                                                     | Maskable                                        | 0xFFE0       | 0, lowest   |

- NOTES: 1. Multiple source flags  
2. Interrupt flags are located in the module.  
3. A reset is generated if the CPU tries to fetch instructions from within the module register memory address range (0h to 01FFh).  
(Non)maskable: the individual interrupt-enable bit can disable an interrupt event, but the general-interrupt enable cannot disable it.  
4. Access and key violations, KEYV and ACCVIFG.  
5. In SPI mode: UCB0RXIFG. In I2C mode: UCALIFG, UCNACKIFG, ICSTTIFG, UCSTPIFG.  
6. In UART/SPI mode: UCB0TXIFG. In I2C mode: UCB0RXIFG, UCB0TXIFG.

## special function registers

Most interrupt and module-enable bits are collected in the lowest address space. Special-function register bits not allocated to a functional purpose are not physically present in the device. This arrangement provides simple software access.

### interrupt enable 1 and 2

| Address | 7 | 6 | 5      | 4     | 3 | 2 | 1    | 0     |
|---------|---|---|--------|-------|---|---|------|-------|
| 00h     |   |   | ACCVIE | NMIIE |   |   | OFIE | WDTIE |
|         |   |   | rw-0   | rw-0  |   |   | rw-0 | rw-0  |

WDTIE      Watchdog timer interrupt enable. Inactive if watchdog mode is selected. Active if watchdog timer is configured in interval timer mode.

OFIE      Oscillator fault enable

NMIIE      (Non)maskable interrupt enable

ACCVIE      Flash access violation interrupt enable

| Address | 7    | 6 | 5 | 4 | 3        | 2        | 1        | 0        |
|---------|------|---|---|---|----------|----------|----------|----------|
| 01h     | BTIE |   |   |   | UCB0TXIE | UCB0RXIE | UCA0TXIE | UCA0RXIE |
|         | rw-0 |   |   |   | rw-0     | rw-0     | rw-0     | rw-0     |

UCA0RXIE      USCI\_A0 receive interrupt enable

UCA0TXIE      USCI\_A0 transmit interrupt enable

UCB0RXIE      USCI\_B0 receive interrupt enable

UCB0TXIE      USCI\_B0 transmit interrupt enable

BTIE      Basic timer interrupt enable

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011


### interrupt flag register 1 and 2

| Address | 7 | 6 | 5 | 4      | 3      | 2      | 1     | 0      |
|---------|---|---|---|--------|--------|--------|-------|--------|
| 02h     |   |   |   | NMIIFG | RSTIFG | PORIFG | OFIFG | WDTIFG |
|         |   |   |   | rw-0   | rw-(0) | rw-(1) | rw-1  | rw-(0) |

- WDTIFG Set on watchdog timer overflow (in watchdog mode) or security key violation. Reset on  $V_{CC}$  power-up or a reset condition at  $\overline{RST}$ /NMI pin in reset mode.
- OFIFG Flag set on oscillator fault.
- RSTIFG External reset interrupt flag. Set on a reset condition at  $\overline{RST}$ /NMI pin in reset mode. Reset on  $V_{CC}$  power-up.
- PORIFG Power-on interrupt flag. Set on  $V_{CC}$  power-up.
- NMIIFG Set via  $\overline{RST}$ /NMI pin.

| Address | 7     | 6 | 5 | 4 | 3          | 2          | 1          | 0          |
|---------|-------|---|---|---|------------|------------|------------|------------|
| 03h     | BTIFG |   |   |   | UCB0 TXIFG | UCB0 RXIFG | UCA0 TXIFG | UCA0 RXIFG |
|         | rw-0  |   |   |   | rw-1       | rw-0       | rw-1       | rw-0       |

- UCA0RXIFG USCI\_A0 receive interrupt flag
- UCA0TXIFG USCI\_A0 transmit interrupt flag
- UCB0RXIFG USCI\_B0 receive interrupt flag
- UCB0TXIFG USCI\_B0 transmit interrupt flag
- BTIFG Basic Timer1 interrupt flag

- Legend**
- rw:** Bit can be read and written.
- rw-0,1:** Bit can be read and written. It is Reset or Set by PUC.
- rw-(0,1):** Bit can be read and written. It is Reset or Set by POR.
-  SFR bit is not present in device

## memory organization

|                        |           | MSP430FG477      | MSP430FG478      | MSP430FG479      |
|------------------------|-----------|------------------|------------------|------------------|
| Memory                 | Size      | 32KB             | 48KB             | 60KB             |
| Main: interrupt vector | Flash     | 0FFFFh to 0FFE0h | 0FFFFh to 0FFE0h | 0FFFFh to 0FFE0h |
| Main: code memory      | Flash     | 0FFFFh to 08000h | 0FFFFh to 04000h | 0FFFFh to 01100h |
| Information memory     | Size      | 256 Byte         | 256 Byte         | 256 Byte         |
|                        | Flash     | 010FFh to 01000h | 010FFh to 01000h | 010FFh to 01000h |
| Boot memory            | Size      | 1KB              | 1KB              | 1KB              |
|                        | ROM       | 0FFFh to 0C00h   | 0FFFh to 0C00h   | 0FFFh to 0C00h   |
| RAM                    | Size      | 2KB              | 2KB              | 2KB              |
|                        |           | 09FFh to 0200h   | 09FFh to 0200h   | 09FFh to 0200h   |
| Peripherals            | 16-bit    | 01FFh to 0100h   | 01FFh to 0100h   | 01FFh to 0100h   |
|                        | 8-bit     | 0FFh to 010h     | 0FFh to 010h     | 0FFh to 010h     |
|                        | 8-bit SFR | 0Fh to 00h       | 0Fh to 00h       | 0Fh to 00h       |

## bootstrap loader (BSL)

The MSP430 BSL enables users to program the flash memory or RAM using a UART serial interface. Access to the MSP430 memory via the BSL is protected by user-defined password. For complete description of the features of the BSL and its implementation, see the application report *Features of the MSP430 Bootstrap Loader*, literature number SLAA089.

| BSL FUNCTION  | PN PACKAGE PINS | ZQW PACKAGE PINS |
|---------------|-----------------|------------------|
| Data Transmit | 58 - P1.0       | C11 - P1.0       |
| Data Receive  | 57 - P1.1       | C12 - P1.1       |

## flash memory (Flash)

The flash memory can be programmed via the JTAG port, the bootstrap loader, or in-system by the CPU. The CPU can perform single-byte and single-word writes to the flash memory. Features of the flash memory include:

- Flash memory has n segments of main memory and four segments of information memory (A to D) of 64 bytes each. Each segment in main memory is 512 bytes in size.
- Segments 0 to n may be erased in one step, or each segment may be individually erased.
- Segments A to D can be erased individually, or as a group with segments 0 to n. Segments A to D are also called *information memory*.
- Segment A might contain calibration data. After reset, segment A is protected against programming or erasing. It can be unlocked, but care should be taken not to erase this segment if this calibration data is required.
- Flash content integrity check with marginal read modes.

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

---

### peripherals

Peripherals are connected to the CPU through data, address, and control buses and can be handled using all instructions. For complete module descriptions, see the *MSP430x4xx Family User's Guide*, literature number SLAU056.

### oscillator and system clock

The clock system in the MSP430FG47x is supported by the FLL+ module, which includes support for a 32768-Hz watch crystal oscillator, an internal digitally-controlled oscillator (DCO), and a 8-MHz high-frequency crystal oscillator (XT1), plus a 8-MHz high-frequency crystal oscillator (XT2). The FLL+ clock module is designed to meet the requirements of both low system cost and low power consumption. The FLL+ features digital frequency locked loop (FLL) hardware that, in conjunction with a digital modulator, stabilizes the DCO frequency to a programmable multiple of the watch crystal frequency. The internal DCO provides a fast turn-on clock source and stabilizes in less than 6  $\mu$ s. The FLL+ module provides the following clock signals:

- Auxiliary clock (ACLK), sourced from a 32768-Hz watch crystal or a high-frequency crystal
- Main clock (MCLK), the system clock used by the CPU
- Sub-Main clock (SMCLK), the sub-system clock used by the peripheral modules
- ACLK/n, the buffered output of ACLK, ACLK/2, ACLK/4, or ACLK/8

### brownout, supply voltage supervisor

The brownout circuit is implemented to provide the proper internal reset signal to the device during power on and power off. The supply voltage supervisor (SVS) circuitry detects if the supply voltage drops below a user selectable level and supports both supply voltage supervision (the device is automatically reset) and supply voltage monitoring (SVM, the device is not automatically reset).

The CPU begins code execution after the brownout circuit releases the device reset. However,  $V_{CC}$  may not have ramped to  $V_{CC(min)}$  at that time. The user must ensure the default FLL+ settings are not changed until  $V_{CC}$  reaches  $V_{CC(min)}$ . If desired, the SVS circuit can be used to determine when  $V_{CC}$  reaches  $V_{CC(min)}$ .

### digital I/O

There are six 8-bit I/O ports implemented, ports P1 through P6.

- All individual I/O bits are independently programmable.
- Any combination of input, output, and interrupt conditions is possible.
- Edge-selectable interrupt input capability for all the eight bits of ports P1 and P2.
- Read/write access to port-control registers is supported by all instructions.





## watchdog timer (WDT+)

The primary function of the WDT+ module is to perform a controlled system restart after a software problem occurs. If the selected time interval expires, a system reset is generated. If the watchdog function is not needed in an application, the module can be configured as an interval timer and can generate interrupts at selected time intervals.

## Basic Timer1 and Real-Time Clock

The Basic Timer1 has two independent 8-bit timers that can be cascaded to form a 16-bit timer/counter. Both timers can be read and written by software. The Basic Timer1 is extended to provide an integrated real-time clock (RTC). An internal calendar compensates for month with less than 31 days and includes leap year correction.

## LCD\_A driver with regulated charge pump

The LCD\_A driver generates the segment and common signals required to drive an LCD display. The LCD\_A controller has dedicated data memory to hold segment drive information. Common and segment signals are generated as defined by the mode. Static, 2-MUX, 3-MUX, and 4-MUX LCDs are supported by this peripheral. The module can provide a LCD voltage independent of the supply voltage via an integrated charge pump. Furthermore, it is possible to control the level of the LCD voltage and, thus, contrast in software.

## Timer\_A3

Timer\_A3 is a 16-bit timer/counter with three capture/compare registers. Timer\_A3 can support multiple capture/compares, PWM outputs, and interval timing. Timer\_A3 also has extensive interrupt capabilities. Interrupts may be generated from the counter on overflow conditions and from each of the capture/compare registers.

| TIMER_A3 SIGNAL CONNECTIONS |     |                     |                   |              |                      |                   |     |
|-----------------------------|-----|---------------------|-------------------|--------------|----------------------|-------------------|-----|
| INPUT PIN NUMBER            |     | DEVICE INPUT SIGNAL | MODULE INPUT NAME | MODULE BLOCK | MODULE OUTPUT SIGNAL | OUTPUT PIN NUMBER |     |
| PN                          | ZQW |                     |                   |              |                      | PN                | ZQW |
| P1.5 – 51                   | F11 | TACLK               | TACLK             | Timer        | NA                   |                   |     |
|                             |     | ACLK                | ACLK              |              |                      |                   |     |
|                             |     | SMCLK               | SMCLK             |              |                      |                   |     |
| P1.5 – 51                   | F11 | TAINCLK             | INCLK             |              |                      |                   |     |
| P1.0 – 58                   | C11 | TA0                 | CCI0A             | CCR0         | TA0                  | P1.0 – 58         | C11 |
| P1.1 – 57                   | C12 | TA0                 | CCI0B             |              |                      | P1.1 – 57         | C12 |
|                             |     | DV <sub>SS</sub>    | GND               |              |                      |                   |     |
|                             |     | DV <sub>CC</sub>    | V <sub>CC</sub>   |              |                      |                   |     |
| P1.2 – 56                   | D11 | TA1                 | CCI1A             | CCR1         | TA1                  | P1.2 – 56         | D11 |
|                             |     | CAOUT (internal)    | CCI1B             |              |                      |                   |     |
|                             |     | DV <sub>SS</sub>    | GND               |              |                      |                   |     |
|                             |     | DV <sub>CC</sub>    | V <sub>CC</sub>   |              |                      |                   |     |
| P2.0 – 4                    | C2  | TA2                 | CCI2A             | CCR2         | TA2                  | P2.0 – 4          | C2  |
|                             |     | ACLK (internal)     | CCI2B             |              |                      |                   |     |
|                             |     | DV <sub>SS</sub>    | GND               |              |                      |                   |     |
|                             |     | DV <sub>CC</sub>    | V <sub>CC</sub>   |              |                      |                   |     |

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

### Timer\_B3

Timer\_B3 is a 16-bit timer/counter with three capture/compare registers. Timer\_B3 can support multiple capture/compares, PWM outputs, and interval timing. Timer\_B3 also has extensive interrupt capabilities. Interrupts may be generated from the counter on overflow conditions and from each of the capture/compare registers.

| TIMER_B3 SIGNAL CONNECTIONS |     |                       |                   |              |                      |                   |     |
|-----------------------------|-----|-----------------------|-------------------|--------------|----------------------|-------------------|-----|
| INPUT PIN NUMBER            |     | DEVICE INPUT SIGNAL   | MODULE INPUT NAME | MODULE BLOCK | MODULE OUTPUT SIGNAL | OUTPUT PIN NUMBER |     |
| PN                          | ZQW |                       |                   |              |                      | PN                | ZQW |
| P1.4 – 54                   | E11 | TBCLK                 | TBCLK             | Timer        | NA                   |                   |     |
|                             |     | ACLK                  | ACLK              |              |                      |                   |     |
|                             |     | SMCLK                 | SMCLK             |              |                      |                   |     |
| P1.4 – 54                   | E11 | TBCLK<br>(See Note 1) | INCLK             |              |                      |                   |     |
| P2.1 – 3                    | C1  | TB0                   | CCI0A             | CCR0         | TB0                  | P2.1 – 3          | C1  |
| P2.1 – 3                    | C1  | TB0                   | CCI0B             |              |                      |                   |     |
|                             |     | V <sub>SS</sub>       | GND               |              |                      |                   |     |
|                             |     | V <sub>CC</sub>       | V <sub>CC</sub>   |              |                      |                   |     |
| P2.2 – 2                    | B1  | TB1                   | CCI1A             | CCR1         | TB1                  | P2.2 – 2          | B1  |
| P2.2 – 2                    | B1  | TB1                   | CCI1B             |              |                      |                   |     |
|                             |     | V <sub>SS</sub>       | GND               |              |                      |                   |     |
|                             |     | V <sub>CC</sub>       | V <sub>CC</sub>   |              |                      |                   |     |
| P2.3 – 77                   | B4  | TB2                   | CCI2A             | CCR2         | TB2                  | P2.3 – 77         | B4  |
|                             |     | ACLK (internal)       | CCI2B             |              |                      |                   |     |
|                             |     | V <sub>SS</sub>       | GND               |              |                      |                   |     |
|                             |     | V <sub>CC</sub>       | V <sub>CC</sub>   |              |                      |                   |     |

NOTE 1: The inversion of TBCLK is done inside the module.

### universal serial communication interfaces (USCIs) (USCI\_A0, USCI\_B0)

The USCI module is used for serial data communication. The USCI module supports synchronous communication protocols such as SPI (3 pin or 4 pin), I2C, and asynchronous communication protocols such as UART, enhanced UART with automatic baudrate detection (LIN), and IrDA.

USCI\_A0 provides support for SPI (3 pin or 4 pin), UART, enhanced UART and IrDA.

USCI\_B0 provides support for SPI (3 pin or 4 pin) and I2C.

### Comparator\_A

The primary function of the comparator\_A module is to support precision slope analog-to-digital conversions, battery-voltage supervision, and monitoring of external analog signals.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

## SD16\_A

The SD16\_A module supports 16-bit analog-to-digital conversions. The module implements a 16-bit sigma-delta core and a reference generator. In addition to external analog inputs, an internal  $V_{CC}$  sense and temperature sensor are also available.

## DAC12

The DAC12 module is a 12-bit R-ladder voltage-output DAC. The DAC12 may be used in 8-bit or 12-bit mode. When multiple DAC12 modules are present, they may be grouped together for synchronous operation.

## OA

The MSP430FG47x has two configurable low-current general-purpose operational amplifiers. Each OA input and output terminal is software-selectable and offer a flexible choice of connections for various applications. The OA op amps primarily support front-end analog signal conditioning prior to analog-to-digital conversion.

| OA0 SIGNAL CONNECTIONS |     |                           |                      |                 |        |                            |                   |     |
|------------------------|-----|---------------------------|----------------------|-----------------|--------|----------------------------|-------------------|-----|
| INPUT PIN NUMBER       |     | DEVICE<br>INPUT<br>SIGNAL | MODULE<br>INPUT NAME | MODULE<br>BLOCK |        | MODULE<br>OUTPUT<br>SIGNAL | OUTPUT PIN NUMBER |     |
| PN                     | ZQW |                           |                      |                 |        |                            | PN                | ZQW |
| P1.6 – 50              | G12 | OA0I0                     | OAxI0                | OA0             | OA0OUT | OA0O                       | P6.0 – 67         | B8  |
| P6.2 – 65              | A9  | OA0I1                     | OAxI1                |                 |        |                            |                   |     |
| P6.5 – 62              | B10 | OA0I2                     | OAxIA                |                 |        |                            |                   |     |
| P1.2 – 56              | D11 | OA0I3                     | OAxIB                |                 |        |                            |                   |     |
| P1.4 – 54              | E11 | OA1I0                     | OAxI0                | OA1             | OA1OUT | OA1O                       | P6.4 – 64         | A10 |
| P6.6 – 61              | A11 | OA1I1                     | OAxI1                |                 |        |                            |                   |     |
| P6.7 – 59              | B12 | OA1I2                     | OAxIA                |                 |        |                            |                   |     |
| P1.3 – 55              | D12 | OA1I3                     | OAxIB                |                 |        |                            |                   |     |

# MSP430FG47x MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

## peripheral file map

| PERIPHERALS WITH WORD ACCESS                                    |                                            |            |       |
|-----------------------------------------------------------------|--------------------------------------------|------------|-------|
| <b>Watchdog</b>                                                 | Watchdog timer control                     | WDTCTL     | 0120h |
| <b>Timer_B3</b>                                                 | Capture/compare register 2                 | TBCCR2     | 0196h |
|                                                                 | Capture/compare register 1                 | TBCCR1     | 0194h |
|                                                                 | Capture/compare register 0                 | TBCCR0     | 0192h |
|                                                                 | Timer_B register                           | TBR        | 0190h |
|                                                                 | Capture/compare control 2                  | TBCCTL2    | 0186h |
|                                                                 | Capture/compare control 1                  | TBCCTL1    | 0184h |
|                                                                 | Capture/compare control 0                  | TBCCTL0    | 0182h |
|                                                                 | Timer_B control                            | TBCTL      | 0180h |
|                                                                 | Timer_B interrupt vector                   | TBIV       | 011Eh |
| <b>Timer_A3</b>                                                 | Capture/compare register 2                 | TACCR2     | 0176h |
|                                                                 | Capture/compare register 1                 | TACCR1     | 0174h |
|                                                                 | Capture/compare register 0                 | TACCR0     | 0172h |
|                                                                 | Timer_A register                           | TAR        | 0170h |
|                                                                 | Capture/compare control 2                  | TACCTL2    | 0166h |
|                                                                 | Capture/compare control 1                  | TACCTL1    | 0164h |
|                                                                 | Capture/compare control 0                  | TACCTL0    | 0162h |
|                                                                 | Timer_A control                            | TACTL      | 0160h |
|                                                                 | Timer_A interrupt vector                   | TAIV       | 012Eh |
| <b>Flash</b>                                                    | Flash control 4                            | FCTL4      | 01BEh |
|                                                                 | Flash control 3                            | FCTL3      | 012Ch |
|                                                                 | Flash control 2                            | FCTL2      | 012Ah |
|                                                                 | Flash control 1                            | FCTL1      | 0128h |
| <b>DAC12</b>                                                    | DAC12_1 data                               | DAC12_1DAT | 01CAh |
|                                                                 | DAC12_1 control                            | DAC12_1CTL | 01C2h |
|                                                                 | DAC12_0 data                               | DAC12_0DAT | 01C8h |
|                                                                 | DAC12_0 control                            | DAC12_0CTL | 01C0h |
| <b>SD16_A</b><br>(see also:<br>Peripherals with<br>Byte Access) | General control                            | SD16CTL    | 0100h |
|                                                                 | Channel 0 control                          | SD16CCTL0  | 0102h |
|                                                                 | Channel 0 conversion memory                | SD16MEM0   | 0112h |
|                                                                 | Interrupt vector word register             | SD16IV     | 0110h |
| <b>OA switches</b>                                              | Switch control register 1                  | SWCTL_1    | 00CEh |
| PERIPHERALS WITH BYTE ACCESS                                    |                                            |            |       |
| <b>OA switches</b>                                              | Switch control register                    | SWCTL      | 00CFh |
|                                                                 | Switch control register 1                  | SWCTL1     | 00CEh |
| <b>OA1</b>                                                      | Operational amplifier 1 control register 1 | OA1CTL1    | 00C3h |
|                                                                 | Operational amplifier 1 control register 0 | OA1CTL0    | 00C2h |
| <b>OA0</b>                                                      | Operational amplifier 0 control register 1 | OA0CTL1    | 00C1h |
|                                                                 | Operational amplifier 0 control register 0 | OA0CTL0    | 00C0h |
| <b>SD16_A</b><br>(see also:<br>Peripherals with<br>Word Access) | Channel 0 input control                    | SD16INCTL0 | 0B0h  |
|                                                                 | Analog enable                              | SD16AE     | 0B7h  |

**peripheral file map (continued)**

|                      |                                                 |            |        |
|----------------------|-------------------------------------------------|------------|--------|
| <b>LCD_A</b>         | LCD voltage control 1                           | LCDAVCTL1  | 0AFh   |
|                      | LCD voltage control 0                           | LCDAVCTL0  | 0AEh   |
|                      | LCD voltage port control 1                      | LCDAPCTL1  | 0ADh   |
|                      | LCD voltage port control 0                      | LCDAPCTL0  | 0ACh   |
|                      | LCD memory 20                                   | LCDM20     | 0A4h   |
|                      | :                                               | :          | :      |
|                      | LCD memory 16                                   | LCDM16     | 0A0h   |
|                      | LCD memory 15                                   | LCDM15     | 09Fh   |
|                      | :                                               | :          | :      |
|                      | LCD memory 1                                    | LCDM1      | 091h   |
|                      | LCD control and mode                            | LCDACTL    | 090h   |
| <b>USCI A0/B0</b>    | USCI A0 auto baud rate control                  | UCA0ABCTL  | 0x005D |
|                      | USCI A0 transmit buffer                         | UCA0TXBUF  | 0x0067 |
|                      | USCI A0 receive buffer                          | UCA0RXBUF  | 0x0066 |
|                      | USCI A0 status                                  | UCA0STAT   | 0x0065 |
|                      | USCI A0 modulation control                      | UCA0MCTL   | 0x0064 |
|                      | USCI A0 baud rate control 1                     | UCA0BR1    | 0x0063 |
|                      | USCI A0 baud rate control 0                     | UCA0BR0    | 0x0062 |
|                      | USCI A0 control 1                               | UCA0CTL1   | 0x0061 |
|                      | USCI A0 control 0                               | UCA0CTL0   | 0x0060 |
|                      | USCI A0 IrDA receive control                    | UCA0IRRCTL | 0x005F |
|                      | USCI A0 IrDA transmit control                   | UCA0IRTCTL | 0x005E |
|                      | USCI B0 transmit buffer                         | UCB0TXBUF  | 0x006F |
|                      | USCI B0 receive buffer                          | UCB0RXBUF  | 0x006E |
|                      | USCI B0 status                                  | UCB0STAT   | 0x006D |
|                      | USCI B0 I2C Interrupt enable                    | UCB0CIE    | 0x006C |
|                      | USCI B0 baud rate control 1                     | UCB0BR1    | 0x006B |
|                      | USCI B0 baud rate control 0                     | UCB0BR0    | 0x006A |
|                      | USCI B0 control 1                               | UCB0CTL1   | 0x0069 |
|                      | USCI B0 control 0                               | UCB0CTL0   | 0x0068 |
|                      | USCI B0 I2C slave address                       | UCB0SA     | 0x011A |
|                      | USCI B0 I2C own address                         | UCB0OA     | 0x0118 |
| <b>Comparator_A</b>  | Comparator_A port disable                       | CAPD       | 05Bh   |
|                      | Comparator_A control2                           | CACTL2     | 05Ah   |
|                      | Comparator_A control1                           | CACTL1     | 059h   |
| <b>Brownout, SVS</b> | SVS control register (reset by brownout signal) | SVSCTL     | 056h   |
| <b>FLL+ Clock</b>    | FLL+ control 1                                  | FLL_CTL1   | 054h   |
|                      | FLL+ control 0                                  | FLL_CTL0   | 053h   |
|                      | System clock frequency control                  | SCFQCTL    | 052h   |
|                      | System clock frequency integrator               | SCFI1      | 051h   |
|                      | System clock frequency integrator               | SCFI0      | 050h   |

# MSP430FG47x MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

## peripheral file map (continued)

| PERIPHERALS WITH BYTE ACCESS  |                                |           |      |
|-------------------------------|--------------------------------|-----------|------|
| <b>RTC<br/>(Basic Timer1)</b> | Real-time clock year high byte | RTCYEARH  | 04Fh |
|                               | Real-time clock year low byte  | RTCYEARL  | 04Eh |
|                               | Real-time clock month          | RTCMON    | 04Dh |
|                               | Real-time clock day of month   | RTCDAY    | 04Ch |
|                               | Basic Timer1 counter           | BTCNT2    | 047h |
|                               | Basic Timer1 counter           | BTCNT1    | 046h |
|                               | Real-time counter 4            | RTCNT4    | 045h |
|                               | (Real-time clock day of week)  | (RTCDOW)  |      |
|                               | Real-time counter 3            | RTCNT3    | 044h |
|                               | (Real-time clock hour)         | (RTCHOUR) |      |
|                               | Real-time counter 2            | RTCNT2    | 043h |
|                               | (Real-time clock minute)       | (RTCMIN)  |      |
|                               | Real-time counter 1            | RTCNT1    | 042h |
|                               | (Real-time clock second)       | (RTCSEC)  |      |
|                               | Real-time clock control        | RTCCTL    | 041h |
|                               | Basic Timer1 control           | BTCTL     | 040h |
| <b>Port P6</b>                | Port P6 selection              | P6SEL     | 037h |
|                               | Port P6 direction              | P6DIR     | 036h |
|                               | Port P6 output                 | P6OUT     | 035h |
|                               | Port P6 input                  | P6IN      | 034h |
| <b>Port P5</b>                | Port P5 selection              | P5SEL     | 033h |
|                               | Port P5 direction              | P5DIR     | 032h |
|                               | Port P5 output                 | P5OUT     | 031h |
|                               | Port P5 input                  | P5IN      | 030h |
| <b>Port P4</b>                | Port P4 selection              | P4SEL     | 01Fh |
|                               | Port P4 direction              | P4DIR     | 01Eh |
|                               | Port P4 output                 | P4OUT     | 01Dh |
|                               | Port P4 input                  | P4IN      | 01Ch |
| <b>Port P3</b>                | Port P3 selection              | P3SEL     | 01Bh |
|                               | Port P3 direction              | P3DIR     | 01Ah |
|                               | Port P3 output                 | P3OUT     | 019h |
|                               | Port P3 input                  | P3IN      | 018h |
| <b>Port P2</b>                | Port P2 selection              | P2SEL     | 02Eh |
|                               | Port P2 interrupt enable       | P2IE      | 02Dh |
|                               | Port P2 interrupt-edge select  | P2IES     | 02Ch |
|                               | Port P2 interrupt flag         | P2IFG     | 02Bh |
|                               | Port P2 direction              | P2DIR     | 02Ah |
|                               | Port P2 output                 | P2OUT     | 029h |
|                               | Port P2 input                  | P2IN      | 028h |

**peripheral file map (continued)**

| <b>PERIPHERALS WITH BYTE ACCESS (CONTINUED)</b> |                               |        |      |
|-------------------------------------------------|-------------------------------|--------|------|
| <b>Port P1</b>                                  | Port P1 selection 2 register  | P1SEL2 | 057h |
|                                                 | Port P1 selection             | P1SEL  | 026h |
|                                                 | Port P1 interrupt enable      | P1IE   | 025h |
|                                                 | Port P1 interrupt-edge select | P1IES  | 024h |
|                                                 | Port P1 interrupt flag        | P1IFG  | 023h |
|                                                 | Port P1 direction             | P1DIR  | 022h |
|                                                 | Port P1 output                | P1OUT  | 021h |
|                                                 | Port P1 input                 | P1IN   | 020h |
| <b>Special functions</b>                        | SFR interrupt flag 2          | IFG2   | 003h |
|                                                 | SFR interrupt flag 1          | IFG1   | 002h |
|                                                 | SFR interrupt enable 2        | IE2    | 001h |
|                                                 | SFR interrupt enable 1        | IE1    | 000h |

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

### absolute maximum ratings over operating free-air temperature (see Note 1)

|                                                                    |                            |
|--------------------------------------------------------------------|----------------------------|
| Voltage applied at $V_{CC}$ to $V_{SS}$                            | -0.3 V to 4.1 V            |
| Voltage applied to any pin (see Note 2)                            | -0.3 V to $V_{CC} + 0.3$ V |
| Diode current at any device terminal                               | $\pm 2$ mA                 |
| Storage temperature, $T_{stg}$ : (unprogrammed device, see Note 3) | -55°C to 150°C             |
| (programmed device, see Note 3)                                    | -40°C to 85°C              |

- NOTES: 1. Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
2. All voltages referenced to  $V_{SS}$ . The JTAG fuse-blow voltage,  $V_{FB}$ , is allowed to exceed the absolute maximum rating. The voltage is applied to the TDI/TCLK pin when blowing the JTAG fuse.
3. Higher temperature may be applied during board soldering process according to the current JEDEC J-STD-020 specification with peak reflow temperatures not higher than classified on the device label on the shipping boxes or reels.

### recommended operating conditions

|                                                                                           |                                 |                   | MIN  | NOM    | MAX  | UNITS |
|-------------------------------------------------------------------------------------------|---------------------------------|-------------------|------|--------|------|-------|
| Supply voltage during program execution, $V_{CC}$ ( $AV_{CC} = DV_{CC} = V_{CC}$ )        |                                 |                   | 1.8  |        | 3.6  | V     |
| Supply voltage during flash memory programming, $V_{CC}$ ( $AV_{CC} = DV_{CC} = V_{CC}$ ) |                                 |                   | 2.2  |        | 3.6  | V     |
| Supply voltage, $V_{SS}$ ( $AV_{SS} = DV_{SS} = V_{SS}$ )                                 |                                 |                   | 0    |        | 0    | V     |
| Operating free-air temperature range, $T_A$                                               |                                 |                   | -40  |        | 85   | °C    |
| LFXT1 crystal frequency, $f_{(LFXT1)}$<br>(see Note 1)                                    | LF selected,<br>$XTS\_FLL = 0$  | Watch crystal     |      | 32.768 |      | kHz   |
|                                                                                           | XT1 selected,<br>$XTS\_FLL = 1$ | Ceramic resonator | 0.45 |        | 6    | MHz   |
|                                                                                           | XT1 selected,<br>$XTS\_FLL = 1$ | Crystal           | 1    |        | 6    | MHz   |
| XT2 crystal frequency, $f_{(XT2)}$                                                        | Ceramic resonator               |                   | 0.45 |        | 8    | MHz   |
|                                                                                           | Crystal                         |                   | 1    |        | 8    |       |
| System frequency, MCLK, ACLK, SMCLK, $f_{(System)}$                                       | $V_{CC} = 1.8$ V                |                   | dc   |        | 4.15 | MHz   |
|                                                                                           | $V_{CC} = 2.5$ V                |                   | dc   |        | 8    |       |

- NOTES: 1. In LF mode, the LFXT1 oscillator requires a watch crystal. In XT1 mode, LFXT1 accepts a ceramic resonator or a crystal.




Figure 1. Frequency vs Supply Voltage, Typical Characteristics



**electrical characteristics over recommended operating free-air temperature (unless otherwise noted)**

**supply current into AV<sub>CC</sub> + DV<sub>CC</sub> excluding external current**

| PARAMETER           |                                                                                                                                                                                                                                                                                         | TEST CONDITIONS                | V <sub>CC</sub> | MIN | TYP | MAX | UNIT |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|-----------------|-----|-----|-----|------|
| I <sub>(AM)</sub>   | Active mode (see Note 1)<br>f <sub>(MCLK)</sub> = f <sub>(SMCLK)</sub> = 1 MHz,<br>f <sub>(ACLK)</sub> = 32,768 Hz<br>XTS = 0, SELM = (0,1)                                                                                                                                             | T <sub>A</sub> = -40°C to 85°C | 2.2 V           |     | 262 | 295 | μA   |
|                     |                                                                                                                                                                                                                                                                                         |                                | 3 V             |     | 420 | 460 |      |
| I <sub>(LPM0)</sub> | Low-power mode (LPM0)<br>(see Note 1)                                                                                                                                                                                                                                                   | T <sub>A</sub> = -40°C to 85°C | 2.2 V           |     | 32  | 62  | μA   |
|                     |                                                                                                                                                                                                                                                                                         |                                | 3 V             |     | 51  | 77  |      |
| I <sub>(LPM2)</sub> | Low-power mode (LPM2),<br>f <sub>(MCLK)</sub> = f <sub>(SMCLK)</sub> = 0 MHz,<br>f <sub>(ACLK)</sub> = 32,768 Hz, SCG0 = 0 (see Note 2)                                                                                                                                                 | T <sub>A</sub> = -40°C to 85°C | 2.2 V           |     | 5   | 9   | μA   |
|                     |                                                                                                                                                                                                                                                                                         |                                | 3 V             |     | 7   | 13  |      |
| I <sub>(LPM3)</sub> | Low-power mode (LPM3)<br>f <sub>(MCLK)</sub> = f <sub>(SMCLK)</sub> = 0 MHz,<br>f <sub>(ACLK)</sub> = 32,768 Hz, SCG0 = 1<br>Basic Timer1 enabled, ACLK selected<br>LCD_A enabled, LCDCPEN = 0:<br>(static mode, f <sub>LCD</sub> = f <sub>(ACLK)</sub> /32)<br>(see Note 2 and Note 3) | T <sub>A</sub> = -40°C         | 2.2 V           |     | 1.0 | 1.8 | μA   |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 25°C          |                 |     | 1.0 | 1.8 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 60°C          |                 |     | 1.1 | 2.0 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 85°C          |                 |     | 2.3 | 4.0 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = -40°C         | 3 V             |     | 1.2 | 2.0 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 25°C          |                 |     | 1.2 | 2.0 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 60°C          |                 |     | 1.4 | 2.2 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 85°C          |                 |     | 2.7 | 4.5 |      |
| I <sub>(LPM3)</sub> | Low-power mode (LPM3)<br>f <sub>(MCLK)</sub> = f <sub>(SMCLK)</sub> = 0 MHz,<br>f <sub>(ACLK)</sub> = 32,768 Hz, SCG0 = 1<br>Basic Timer1 enabled, ACLK selected<br>LCD_A enabled, LCDCPEN = 0:<br>(4-mux mode, f <sub>LCD</sub> = f <sub>(ACLK)</sub> /32)<br>(see Note 2 and Note 3)  | T <sub>A</sub> = -40°C         | 2.2 V           |     | 1.0 | 3.0 | μA   |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 25°C          |                 |     | 1.1 | 3.2 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 85°C          |                 |     | 3.5 | 6.0 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = -40°C         | 3 V             |     | 1.8 | 3.3 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 25°C          |                 |     | 2.0 | 4.0 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 85°C          |                 |     | 4.2 | 7.5 |      |
| I <sub>(LPM4)</sub> | Low-power mode (LPM4)<br>f <sub>(MCLK)</sub> = 0 MHz, f <sub>(SMCLK)</sub> = 0 MHz,<br>f <sub>(ACLK)</sub> = 0 Hz, SCG0 = 1 (see Note 2)                                                                                                                                                | T <sub>A</sub> = -40°C         | 2.2 V           |     | 0.1 | 0.5 | μA   |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 25°C          |                 |     | 0.1 | 0.5 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 60°C          |                 |     | 0.7 | 1.1 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 85°C          |                 |     | 1.7 | 3.0 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = -40°C         | 3 V             |     | 0.1 | 0.8 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 25°C          |                 |     | 0.1 | 0.8 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 60°C          |                 |     | 0.8 | 1.2 |      |
|                     |                                                                                                                                                                                                                                                                                         | T <sub>A</sub> = 85°C          |                 |     | 1.5 | 3.5 |      |

- NOTES: 1. Timer\_A is clocked by f<sub>(DCOCLK)</sub> = 1 MHz. All inputs are tied to 0 V or to V<sub>CC</sub>. Outputs do not source or sink any current.  
2. All inputs are tied to 0 V or to V<sub>CC</sub>. Outputs do not source or sink any current.  
3. The LPM3 currents are characterized with a Micro Crystal CC4V-T1A (9pF) crystal and OSCCAPx = 01h.

#### Current consumption of active mode versus system frequency

$$I_{(AM)} = I_{(AM)} [1 \text{ MHz}] \times f_{(\text{System})} [\text{MHz}]$$

#### Current consumption of active mode versus supply voltage

$$I_{(AM)} = I_{(AM)} [3 \text{ V}] + 200 \mu\text{A/V} \times (V_{\text{CC}} - 2.2 \text{ V})$$

MSP430FG47x  
MIXED SIGNAL MICROCONTROLLER

SLAS580D - OCTOBER 2008 - REVISED MARCH 2011

typical characteristics - LPM4 current




Figure 2.  $I_{LPM4}$  - LPM4 Current vs Temperature

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)**

**Schmitt-trigger inputs - Ports P1, P2, P3, P4, P5, and P6,  $\overline{\text{RST}}$ /NMI, JTAG (TCK, TMS, TDI/TCLK, TDO/TDI)**

| PARAMETER |                                                  | TEST CONDITIONS          | MIN | MAX  | UNIT |
|-----------|--------------------------------------------------|--------------------------|-----|------|------|
| $V_{IT+}$ | Positive-going input threshold voltage           | $V_{CC} = 2.2 \text{ V}$ | 1.1 | 1.55 | V    |
|           |                                                  | $V_{CC} = 3 \text{ V}$   | 1.5 | 1.98 |      |
| $V_{IT-}$ | Negative-going input threshold voltage           | $V_{CC} = 2.2 \text{ V}$ | 0.4 | 0.9  | V    |
|           |                                                  | $V_{CC} = 3 \text{ V}$   | 0.9 | 1.3  |      |
| $V_{hys}$ | Input voltage hysteresis ( $V_{IT+} - V_{IT-}$ ) | $V_{CC} = 2.2 \text{ V}$ | 0.3 | 1.1  | V    |
|           |                                                  | $V_{CC} = 3 \text{ V}$   | 0.5 | 1    |      |

**inputs Px.y, TA<sub>x</sub>**

| PARAMETER            |                                                   | TEST CONDITIONS                                                                        | V <sub>CC</sub> | MIN | MAX | UNIT |
|----------------------|---------------------------------------------------|----------------------------------------------------------------------------------------|-----------------|-----|-----|------|
| t <sub>(int)</sub>   | External interrupt timing                         | Port P1, P2: P1.x to P2.x, external trigger signal for the interrupt flag (see Note 1) | 2.2 V           | 62  |     | ns   |
|                      |                                                   |                                                                                        | 3 V             | 50  |     |      |
| t <sub>(cap)</sub>   | Timer_A capture timing                            | TA0, TA1, TA2                                                                          | 2.2 V           | 62  |     | ns   |
|                      |                                                   |                                                                                        | 3 V             | 50  |     |      |
| f <sub>(TAext)</sub> | Timer_A clock frequency externally applied to pin | TACLK, INCLK: t <sub>(H)</sub> = t <sub>(L)</sub>                                      | 2.2 V           | 8   |     | MHz  |
|                      |                                                   |                                                                                        | 3 V             | 10  |     |      |
| f <sub>(TAint)</sub> | Timer_A, clock frequency                          | SMCLK or ACLK signal selected                                                          | 2.2 V           | 8   |     | MHz  |
|                      |                                                   |                                                                                        | 3 V             | 10  |     |      |

NOTES: 1. The external signal sets the interrupt flag every time the minimum  $t_{(int)}$  parameters are met. It may be set even with trigger signals shorter than  $t_{(int)}$ .

**leakage current - Ports P1, P2, P3, P4, P5, and P6 (see Note 1)**

| PARAMETER       |                 |         | TEST CONDITIONS                                                | MIN | MAX | UNIT |
|-----------------|-----------------|---------|----------------------------------------------------------------|-----|-----|------|
| $I_{lkg}(Px.y)$ | Leakage current | Port Px | $V_{(Px.y)}$ (see Note 2) $V_{CC} = 2.2 \text{ V}/3 \text{ V}$ |     | ±50 | nA   |

NOTES: 1. The leakage current is measured with  $V_{SS}$  or  $V_{CC}$  applied to the corresponding pin(s), unless otherwise noted.  
2. The port pin must be selected as input.

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)**

### outputs – Ports P1, P2, P3, P4, P5, and P6

| PARAMETER                                 | TEST CONDITIONS                                                     | MIN                   | MAX                   | UNIT |
|-------------------------------------------|---------------------------------------------------------------------|-----------------------|-----------------------|------|
| V <sub>OH</sub> High-level output voltage | I <sub>OH(max)</sub> = -1.5 mA, V <sub>CC</sub> = 2.2 V, See Note 1 | V <sub>CC</sub> -0.25 | V <sub>CC</sub>       | V    |
|                                           | I <sub>OH(max)</sub> = -6 mA, V <sub>CC</sub> = 2.2 V, See Note 2   | V <sub>CC</sub> -0.6  | V <sub>CC</sub>       |      |
|                                           | I <sub>OH(max)</sub> = -1.5 mA, V <sub>CC</sub> = 3 V, See Note 1   | V <sub>CC</sub> -0.25 | V <sub>CC</sub>       |      |
|                                           | I <sub>OH(max)</sub> = -6 mA, V <sub>CC</sub> = 3 V, See Note 2     | V <sub>CC</sub> -0.6  | V <sub>CC</sub>       |      |
| V <sub>OL</sub> Low-level output voltage  | I <sub>OL(max)</sub> = 1.5 mA, V <sub>CC</sub> = 2.2 V, See Note 1  | V <sub>SS</sub>       | V <sub>SS</sub> +0.25 | V    |
|                                           | I <sub>OL(max)</sub> = 6 mA, V <sub>CC</sub> = 2.2 V, See Note 2    | V <sub>SS</sub>       | V <sub>SS</sub> +0.6  |      |
|                                           | I <sub>OL(max)</sub> = 1.5 mA, V <sub>CC</sub> = 3 V, See Note 1    | V <sub>SS</sub>       | V <sub>SS</sub> +0.25 |      |
|                                           | I <sub>OL(max)</sub> = 6 mA, V <sub>CC</sub> = 3 V, See Note 2      | V <sub>SS</sub>       | V <sub>SS</sub> +0.6  |      |

NOTES: 1. The maximum total current, I<sub>OH(max)</sub> and I<sub>OL(max)</sub>, for all outputs combined, should not exceed ±12 mA to satisfy the maximum specified voltage drop.  
 2. The maximum total current, I<sub>OH(max)</sub> and I<sub>OL(max)</sub>, for all outputs combined, should not exceed ±48 mA to satisfy the maximum specified voltage drop.

### output frequency

| PARAMETER           |                                   | TEST CONDITIONS                                                            |                                             | MIN            | TYP | MAX                 | UNIT |
|---------------------|-----------------------------------|----------------------------------------------------------------------------|---------------------------------------------|----------------|-----|---------------------|------|
| f <sub>(Px.y)</sub> | (x = 1, 2, 3, 4, 5, 6, 0 ≤ y ≤ 7) | C <sub>L</sub> = 20 pF,<br>I <sub>L</sub> = ±1.5 mA                        | V <sub>CC</sub> = 2.2 V / 3 V               | DC             |     | f <sub>System</sub> | MHz  |
| f <sub>(MCLK)</sub> | P1.1/TA0/MCLK                     | C <sub>L</sub> = 20 pF                                                     |                                             |                |     | f <sub>System</sub> | MHz  |
| t <sub>(Xdc)</sub>  | Duty cycle of output frequency    | P1.1/TA0/MCLK,<br>C <sub>L</sub> = 20 pF,<br>V <sub>CC</sub> = 2.2 V / 3 V | f <sub>(MCLK)</sub> = f <sub>(XT1)</sub>    | 40%            |     | 60%                 |      |
|                     |                                   |                                                                            | f <sub>(MCLK)</sub> = f <sub>(DCOCLK)</sub> | 50% –<br>15 ns | 50% | 50%+<br>15 ns       |      |

electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)

outputs - Ports P1, P2, P3, P4, P5, and P6 (continued)




Figure 3




Figure 4




Figure 5




Figure 6

MSP430FG47x  
MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)

wake-up LPM3

| PARAMETER     |            | TEST CONDITIONS    |                                    | MIN | MAX | UNIT          |
|---------------|------------|--------------------|------------------------------------|-----|-----|---------------|
| $t_{d(LPM3)}$ | Delay time | $f = 1\text{ MHz}$ | $V_{CC} = 2.2\text{ V}/3\text{ V}$ |     | 6   | $\mu\text{s}$ |
|               |            | $f = 2\text{ MHz}$ |                                    |     | 6   |               |
|               |            | $f = 3\text{ MHz}$ |                                    |     | 6   |               |

POR/brownout reset (BOR) (see Note 1)

| PARAMETER         |                          | TEST CONDITIONS                                                                                                                   | MIN | TYP                       | MAX  | UNIT          |
|-------------------|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------|-----|---------------------------|------|---------------|
| $t_{d(BOR)}$      | Brownout<br>(see Note 2) |                                                                                                                                   |     |                           | 2000 | $\mu\text{s}$ |
| $V_{CC(start)}$   |                          | $dV_{CC}/dt \leq 3\text{ V/s}$ (see Figure 7)                                                                                     |     | $0.7 \times V_{(B\_IT-)}$ |      | V             |
| $V_{(B\_IT-)}$    |                          | $dV_{CC}/dt \leq 3\text{ V/s}$ (see Figure 7 through Figure 9)                                                                    |     |                           | 1.71 | V             |
| $V_{hys(B\_IT-)}$ |                          | $dV_{CC}/dt \leq 3\text{ V/s}$ (see Figure 7)                                                                                     |     |                           |      | mV            |
| $t_{(reset)}$     |                          | Pulse length needed at $\overline{\text{RST}}/\text{NMI}$ pin to accepted reset internally,<br>$V_{CC} = 2.2\text{ V}/3\text{ V}$ | 2   |                           |      | $\mu\text{s}$ |

- NOTES: 1. The current consumption of the brownout module is already included in the  $I_{CC}$  current consumption data. The voltage level  $V_{(B\_IT-)} + V_{hys(B\_IT-)}$  is  $\leq 1.8\text{ V}$ .
2. During power up, the CPU begins code execution following a period of  $t_{d(BOR)}$  after  $V_{CC} = V_{(B\_IT-)} + V_{hys(B\_IT-)}$ . The default FLL+ settings must not be changed until  $V_{CC} \geq V_{CC(min)}$ , where  $V_{CC(min)}$  is the minimum supply voltage for the desired operating frequency. See the *MSP430x4xx Family User's Guide* (SLAU056) for more information on the brownout.

typical characteristics




Figure 7. POR/Brownout Reset (BOR) vs Supply Voltage

electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)

typical characteristics (continued)




Figure 8.  $V_{CC(min)}$  Level With a Square Voltage Drop to Generate a POR/Brownout Signal




Figure 9.  $V_{CC(min)}$  Level With a Triangle Voltage Drop to Generate a POR/Brownout Signal

# MSP430FG47x MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted)**

## SVS (supply voltage supervisor/monitor)

| PARAMETER                     | TEST CONDITIONS                                                                              |               | MIN                           | TYP              | MAX                           | UNIT          |
|-------------------------------|----------------------------------------------------------------------------------------------|---------------|-------------------------------|------------------|-------------------------------|---------------|
| $t_{(SVSR)}$                  | $dV_{CC}/dt > 30 \text{ V/ms}$ (see Figure 10)                                               |               | 5                             |                  | 150                           | $\mu\text{s}$ |
|                               | $dV_{CC}/dt \leq 30 \text{ V/ms}$                                                            |               |                               |                  | 2000                          | $\mu\text{s}$ |
| $t_{d(SVSON)}$                | SVSON, switch from VLD = 0 to VLD $\neq$ 0, $V_{CC} = 3 \text{ V}$                           |               |                               | 150              | 300                           | $\mu\text{s}$ |
| $t_{\text{settle}}$           | VLD $\neq$ 0 <sup>†</sup>                                                                    |               |                               |                  | 12                            | $\mu\text{s}$ |
| $V_{(SVSstart)}$              | VLD $\neq$ 0, $V_{CC}/dt \leq 3 \text{ V/s}$ (see Figure 10)                                 |               |                               | 1.55             | 1.7                           | V             |
| $V_{\text{hys}(SVS\_IT-)}$    | $V_{CC}/dt \leq 3 \text{ V/s}$ (see Figure 10)                                               | VLD = 1       | 70                            | 120              | 210                           | mV            |
|                               |                                                                                              | VLD = 2 .. 14 | $V_{(SVS\_IT-)} \times 0.001$ |                  | $V_{(SVS\_IT-)} \times 0.016$ |               |
|                               | $V_{CC}/dt \leq 3 \text{ V/s}$ (see Figure 10), External voltage applied on A7               |               | VLD = 15                      | 4.4              | 20                            | mV            |
| $V_{(SVS\_IT-)}$              | $V_{CC}/dt \leq 3 \text{ V/s}$ (see Figure 10 and Figure 11)                                 | VLD = 1       | 1.8                           | 1.9              | 2.05                          | V             |
|                               |                                                                                              | VLD = 2       | 1.94                          | 2.1              | 2.25                          |               |
|                               |                                                                                              | VLD = 3       | 2.05                          | 2.2              | 2.37                          |               |
|                               |                                                                                              | VLD = 4       | 2.14                          | 2.3              | 2.48                          |               |
|                               |                                                                                              | VLD = 5       | 2.24                          | 2.4              | 2.6                           |               |
|                               |                                                                                              | VLD = 6       | 2.33                          | 2.5              | 2.71                          |               |
|                               |                                                                                              | VLD = 7       | 2.46                          | 2.65             | 2.86                          |               |
|                               |                                                                                              | VLD = 8       | 2.58                          | 2.8              | 3                             |               |
|                               |                                                                                              | VLD = 9       | 2.69                          | 2.9              | 3.13                          |               |
|                               |                                                                                              | VLD = 10      | 2.83                          | 3.05             | 3.29                          |               |
|                               |                                                                                              | VLD = 11      | 2.94                          | 3.2              | 3.42                          |               |
|                               |                                                                                              | VLD = 12      | 3.11                          | 3.35             | 3.61 <sup>†</sup>             |               |
|                               |                                                                                              | VLD = 13      | 3.24                          | 3.5              | 3.76 <sup>†</sup>             |               |
|                               |                                                                                              | VLD = 14      | 3.43                          | 3.7 <sup>†</sup> | 3.99 <sup>†</sup>             |               |
|                               | $V_{CC}/dt \leq 3 \text{ V/s}$ (see Figure 10 and Figure 11), External voltage applied on A7 |               | VLD = 15                      | 1.1              | 1.2                           | 1.3           |
| $I_{CC(SVS)}$<br>(see Note 1) | VLD $\neq$ 0, $V_{CC} = 2.2 \text{ V}/3 \text{ V}$                                           |               |                               | 10               | 15                            | $\mu\text{A}$ |

<sup>†</sup> The recommended operating voltage range is limited to 3.6 V.

<sup>‡</sup>  $t_{\text{settle}}$  is the settling time that the comparator o/p needs to have a stable level after VLD is switched VLD  $\neq$  0 to a different VLD value somewhere between 2 and 15. The overdrive is assumed to be  $> 50 \text{ mV}$ .

NOTE 1: The current consumption of the SVS module is not included in the  $I_{CC}$  current consumption data.



typical characteristics




Figure 10. SVS Reset (SVSR) vs Supply Voltage




Figure 11.  $V_{CC(min)}$ : Square Voltage Drop and Triangle Voltage Drop to Generate an SVS Signal ( $VLD = 1$ )

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER


SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted)**

### DCO

| PARAMETER             | TEST CONDITIONS                                                                                                                                                              | V <sub>CC</sub> | MIN  | TYP  | MAX  | UNIT |
|-----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|------|------|------|------|
| f <sub>(DCOCLK)</sub> | N <sub>(DCO)</sub> = 01E0h, FN <sub>8</sub> = FN <sub>4</sub> = FN <sub>3</sub> = FN <sub>2</sub> = 0, D = 2, DCOPLUS = 0                                                    | 2.2 V/3 V       | 1    |      |      | MHz  |
| f <sub>(DCO2)</sub>   | FN <sub>8</sub> = FN <sub>4</sub> = FN <sub>3</sub> = FN <sub>2</sub> = 0, DCOPLUS = 1                                                                                       | 2.2 V           | 0.3  | 0.65 | 1.25 | MHz  |
|                       |                                                                                                                                                                              | 3 V             | 0.3  | 0.7  | 1.3  |      |
| f <sub>(DCO27)</sub>  | FN <sub>8</sub> = FN <sub>4</sub> = FN <sub>3</sub> = FN <sub>2</sub> = 0, DCOPLUS = 1 (see Note 1)                                                                          | 2.2 V           | 2.5  | 5.6  | 10.5 | MHz  |
|                       |                                                                                                                                                                              | 3 V             | 2.7  | 6.1  | 11.3 |      |
| f <sub>(DCO2)</sub>   | FN <sub>8</sub> = FN <sub>4</sub> = FN <sub>3</sub> = 0, FN <sub>2</sub> = 1, DCOPLUS = 1                                                                                    | 2.2 V           | 0.7  | 1.3  | 2.3  | MHz  |
|                       |                                                                                                                                                                              | 3 V             | 0.8  | 1.5  | 2.5  |      |
| f <sub>(DCO27)</sub>  | FN <sub>8</sub> = FN <sub>4</sub> = FN <sub>3</sub> = 0, FN <sub>2</sub> = 1, DCOPLUS = 1 (see Note 1)                                                                       | 2.2 V           | 5.7  | 10.8 | 18   | MHz  |
|                       |                                                                                                                                                                              | 3 V             | 6.5  | 12.1 | 20   |      |
| f <sub>(DCO2)</sub>   | FN <sub>8</sub> = FN <sub>4</sub> = 0, FN <sub>3</sub> = 1, FN <sub>2</sub> = x, DCOPLUS = 1                                                                                 | 2.2 V           | 1.2  | 2    | 3    | MHz  |
|                       |                                                                                                                                                                              | 3 V             | 1.3  | 2.2  | 3.5  |      |
| f <sub>(DCO27)</sub>  | FN <sub>8</sub> = FN <sub>4</sub> = 0, FN <sub>3</sub> = 1, FN <sub>2</sub> = x, DCOPLUS = 1 (see Note 1)                                                                    | 2.2 V           | 9    | 15.5 | 25   | MHz  |
|                       |                                                                                                                                                                              | 3 V             | 10.3 | 17.9 | 28.5 |      |
| f <sub>(DCO2)</sub>   | FN <sub>8</sub> = 0, FN <sub>4</sub> = 1, FN <sub>3</sub> = FN <sub>2</sub> = x, DCOPLUS = 1                                                                                 | 2.2 V           | 1.8  | 2.8  | 4.2  | MHz  |
|                       |                                                                                                                                                                              | 3 V             | 2.1  | 3.4  | 5.2  |      |
| f <sub>(DCO27)</sub>  | FN <sub>8</sub> = 0, FN <sub>4</sub> = 1, FN <sub>3</sub> = FN <sub>2</sub> = x, DCOPLUS = 1 (see Note 1)                                                                    | 2.2 V           | 13.5 | 21.5 | 33   | MHz  |
|                       |                                                                                                                                                                              | 3 V             | 16   | 26.6 | 41   |      |
| f <sub>(DCO2)</sub>   | FN <sub>8</sub> = 1, FN <sub>4</sub> = FN <sub>3</sub> = FN <sub>2</sub> = x, DCOPLUS = 1                                                                                    | 2.2 V           | 2.8  | 4.2  | 6.2  | MHz  |
|                       |                                                                                                                                                                              | 3 V             | 4.2  | 6.3  | 9.2  |      |
| f <sub>(DCO27)</sub>  | FN <sub>8</sub> = 1, FN <sub>4</sub> = FN <sub>3</sub> = FN <sub>2</sub> = x, DCOPLUS = 1 (see Note 1)                                                                       | 2.2 V           | 21   | 32   | 46   | MHz  |
|                       |                                                                                                                                                                              | 3 V             | 30   | 46   | 70   |      |
| S <sub>n</sub>        | Step size between adjacent DCO taps:<br>S <sub>n</sub> = f <sub>DCO(Tap n+1)</sub> / f <sub>DCO(Tap n)</sub> (see Figure 13 for taps 21 to 27)                               | 1 < TAP ≤ 20    | 1.06 |      | 1.11 |      |
|                       |                                                                                                                                                                              | TAP = 27        | 1.07 |      | 1.17 |      |
| D <sub>t</sub>        | Temperature drift, N <sub>(DCO)</sub> = 01E0h, FN <sub>8</sub> = FN <sub>4</sub> = FN <sub>3</sub> = FN <sub>2</sub> = 0, D = 2, DCOPLUS = 0 (see Note 2)                    | 2.2 V           | –0.2 | –0.3 | –0.4 | %/°C |
|                       |                                                                                                                                                                              | 3 V             | –0.2 | –0.3 | –0.4 |      |
| D <sub>V</sub>        | Drift with V <sub>CC</sub> variation, N <sub>(DCO)</sub> = 01E0h, FN <sub>8</sub> = FN <sub>4</sub> = FN <sub>3</sub> = FN <sub>2</sub> = 0, D = 2, DCOPLUS = 0 (see Note 2) |                 | 0    | 5    | 15   | %/V  |

NOTES: 1. Do not exceed the maximum system frequency.  
2. This parameter is not production tested.



**Figure 12. DCO Frequency vs Supply Voltage  $V_{CC}$  and vs Ambient Temperature**

# MSP430FG47x MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)




Figure 13. DCO Tap Step Size




Figure 14. Five Overlapping DCO Ranges Controlled by FN\_x Bits

electrical characteristics over recommended operating free-air temperature (unless otherwise noted)

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)**

**crystal oscillator, LFXT1, low frequency modes (see Note 4)**

| PARAMETER             | TEST CONDITIONS                                             | V <sub>CC</sub> | MIN    | TYP    | MAX | UNIT |
|-----------------------|-------------------------------------------------------------|-----------------|--------|--------|-----|------|
| f <sub>LFXT1,LF</sub> | LFXT1 oscillator crystal frequency, LF mode 0, 1            | 1.8 V to 3.6 V  | 32,768 |        |     | Hz   |
| OA <sub>LF</sub>      | Oscillation allowance for LF crystals                       |                 | 500    |        |     | kΩ   |
|                       |                                                             |                 | 200    |        |     |      |
| C <sub>L,eff</sub>    | Integrated effective load capacitance, LF mode (see Note 1) |                 | 1      |        |     | pF   |
|                       |                                                             |                 | 5.5    |        |     |      |
|                       |                                                             |                 | 8.5    |        |     |      |
|                       |                                                             |                 | 11     |        |     |      |
| Duty cycle, LF mode   |                                                             | 2.2 V/3 V       | 30     | 50     | 70  | %    |
| f <sub>Fault,LF</sub> | Oscillator fault frequency, LF mode (see Note 3)            | 2.2 V/3 V       | 10     | 10,000 |     | Hz   |

- NOTES: 1. Includes parasitic bond and package capacitance (approximately 2 pF per pin).  
Since the PCB adds additional capacitance it is recommended to verify the correct load by measuring the ACLK frequency. For a correct setup the effective load capacitance should always match the specification of the used crystal.
2. Measured with logic level input frequency but also applies to operation with crystals.
3. Frequencies below the MIN specification set the fault flag, frequencies above the MAX specification do not set the fault flag, and frequencies in between might set the flag.
4. To improve EMI on the LFXT1 oscillator the following guidelines should be observed.
- Keep the trace between the device and the crystal as short as possible.
  - Design a good ground plane around the oscillator pins.
  - Prevent crosstalk from other clock or data lines into oscillator pins XIN and XOUT.
  - Avoid running PCB traces underneath or adjacent to the XIN and XOUT pins.
  - Use assembly materials and praxis to avoid any parasitic load on the oscillator XIN and XOUT pins.
  - If conformal coating is used, ensure that it does not induce capacitive/resistive leakage between the oscillator pins.
  - Do not route the XOUT line to the JTAG header to support the serial programming adapter as shown in other documentation. This signal is no longer required for the serial programming adapter.

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted)**

### crystal oscillator, LFXT1, high frequency modes

| PARAMETER          | TEST CONDITIONS                                             | V <sub>CC</sub>   | MIN            | TYP  | MAX | UNIT |
|--------------------|-------------------------------------------------------------|-------------------|----------------|------|-----|------|
| f <sub>LFXT1</sub> | LFXT1 oscillator crystal frequency                          | Ceramic resonator | 1.8 V to 3.6 V | 0.45 | 8   | MHz  |
| f <sub>LFXT1</sub> | LFXT1 oscillator crystal frequency                          | Crystal resonator | 1.8 V to 3.6 V | 1    | 8   | MHz  |
| C <sub>L,eff</sub> | Integrated effective load capacitance, HF mode (see Note 1) | (see Note 2)      |                | 1    |     | pF   |
| Duty cycle         | Measured at P1.5/ACLK,                                      | 2.2 V/3 V         | 40             | 50   | 60  | %    |

- NOTES: 1. Includes parasitic bond and package capacitance (approximately 2 pF per pin).  
 Since the PCB adds additional capacitance it is recommended to verify the correct load by measuring the ACLK frequency. For a correct setup the effective load capacitance should always match the specification of the used crystal.
2. Requires external capacitors at both terminals. Values are specified by crystal manufacturers.

### crystal oscillator, XT2, high frequency modes

| PARAMETER          | TEST CONDITIONS                                             | V <sub>CC</sub>   | MIN            | TYP  | MAX | UNIT |
|--------------------|-------------------------------------------------------------|-------------------|----------------|------|-----|------|
| f <sub>XT2</sub>   | XT2 oscillator crystal frequency                            | Ceramic resonator | 1.8 V to 3.6 V | 0.45 | 8   | MHz  |
| f <sub>XT2</sub>   | XT2 oscillator crystal frequency                            | Crystal resonator | 1.8 V to 3.6 V | 1    | 8   | MHz  |
| C <sub>L,eff</sub> | Integrated effective load capacitance, HF mode (see Note 1) | (see Note 2)      |                | 1    |     | pF   |
| Duty cycle         | Measured at P1.4/SMCLK,                                     | 2.2 V/3 V         | 40             | 50   | 60  | %    |

- NOTES: 1. Includes parasitic bond and package capacitance (approximately 2 pF per pin).  
 Since the PCB adds additional capacitance it is recommended to verify the correct load by measuring the ACLK frequency. For a correct setup the effective load capacitance should always match the specification of the used crystal.
2. Requires external capacitors at both terminals. Values are specified by crystal manufacturers.

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted)**

**RAM**

| PARAMETER         | TEST CONDITIONS         | MIN | MAX | UNIT |
|-------------------|-------------------------|-----|-----|------|
| V <sub>RAMh</sub> | CPU halted (see Note 1) | 1.6 |     | V    |

NOTE 1: This parameter defines the minimum supply voltage when the data in program memory RAM remain unchanged. No program execution should take place during this supply voltage condition.

**LCD\_A**

| PARAMETER                                                | TEST CONDITIONS                                                                                                                                                        | V <sub>CC</sub> | MIN | TYP             | MAX  | UNIT |
|----------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|-----|-----------------|------|------|
| V <sub>CC(LCD)</sub> Supply Voltage Range                | Charge pump enabled (LCDPEN = 1, VLCDx > 0000)                                                                                                                         |                 | 2.2 |                 | 3.6  | V    |
| C <sub>LCD</sub> Capacitor on LCDCAP (see Note 1)        | Charge pump enabled (LCDPEN = 1, VLCDx > 0000)                                                                                                                         |                 | 4.7 |                 |      | μF   |
| I <sub>CC(LCD)</sub> Average Supply Current (see Note 2) | V <sub>LCD(typ)</sub> = 3 V, LCDPEN = 1, VLCDx = 1000, All segments on, f <sub>LCD</sub> = f <sub>ACLK</sub> /32, No LCD connected (see Note 3), T <sub>A</sub> = 25°C | 2.2 V           |     | 3.8             |      | μA   |
| f <sub>LCD</sub> LCD frequency                           |                                                                                                                                                                        |                 |     |                 | 1.1  | kHz  |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 0000                                                                                                                                                           |                 |     | V <sub>CC</sub> |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 0001                                                                                                                                                           |                 |     | 2.60            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 0010                                                                                                                                                           |                 |     | 2.66            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 0011                                                                                                                                                           |                 |     | 2.72            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 0100                                                                                                                                                           |                 |     | 2.78            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 0101                                                                                                                                                           |                 |     | 2.84            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 0110                                                                                                                                                           |                 |     | 2.90            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 0111                                                                                                                                                           |                 |     | 2.96            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 1000                                                                                                                                                           |                 |     | 3.02            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 1001                                                                                                                                                           |                 |     | 3.08            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 1010                                                                                                                                                           |                 |     | 3.14            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 1011                                                                                                                                                           |                 |     | 3.20            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 1100                                                                                                                                                           |                 |     | 3.26            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 1101                                                                                                                                                           |                 |     | 3.32            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 1110                                                                                                                                                           |                 |     | 3.38            |      | V    |
| V <sub>LCD</sub> LCD voltage                             | VLCDx = 1111                                                                                                                                                           |                 |     | 3.44            | 3.60 | V    |
| R <sub>LCD</sub> LCD Driver Output impedance             | V <sub>LCD</sub> = 3 V, LCDPEN = 1, VLCDx = 1000, I <sub>LOAD</sub> = ±10 μA                                                                                           | 2.2 V           |     |                 | 10   | kΩ   |

NOTES: 1. Enabling the internal charge pump with an external capacitor smaller than the minimum specified might damage the device.  
2. Refer to the supply current specifications I<sub>(LPM3)</sub> for additional current specifications with the LCD\_A module active.  
3. Connecting an actual display will increase the current consumption depending on the size of the LCD.

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)**

### Comparator\_A (see Note 1)

| PARAMETER                                      |                                                                                         | TEST CONDITIONS                                                                                |                               | MIN  | TYP                | MAX  | UNIT |
|------------------------------------------------|-----------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------|-------------------------------|------|--------------------|------|------|
| I <sub>(CC)</sub>                              |                                                                                         | CAON = 1, CARSEL = 0, CAREF = 0                                                                | V <sub>CC</sub> = 2.2 V       | 25   |                    | 40   | μA   |
|                                                |                                                                                         |                                                                                                | V <sub>CC</sub> = 3 V         | 45   |                    | 60   |      |
| I <sub>(Refladder/RefDiode)</sub>              |                                                                                         | CAON = 1, CARSEL = 0, CAREF = 1/2/3,<br>No load at P1.6/CA0 and P1.7/CA1                       | V <sub>CC</sub> = 2.2 V       | 30   |                    | 50   | μA   |
|                                                |                                                                                         |                                                                                                | V <sub>CC</sub> = 3 V         | 45   |                    | 80   |      |
| V <sub>(Ref025)</sub>                          | $\frac{\text{Voltage @ } 0.25\text{ V}_{\text{CC}} \text{ node}}{\text{V}_{\text{CC}}}$ | PCA0 = 1, CARSEL = 1, CAREF = 1,<br>No load at P1.6/CA0 and P1.7/CA1                           | V <sub>CC</sub> = 2.2 V / 3 V | 0.23 | 0.24               | 0.25 |      |
| V <sub>(Ref050)</sub>                          | $\frac{\text{Voltage @ } 0.5\text{ V}_{\text{CC}} \text{ node}}{\text{V}_{\text{CC}}}$  | PCA0 = 1, CARSEL = 1, CAREF = 2,<br>No load at P1.6/CA0 and P1.7/CA1                           | V <sub>CC</sub> = 2.2V / 3 V  | 0.47 | 0.48               | 0.5  |      |
| V <sub>(RefVT)</sub>                           | See Figure 15 and<br>Figure 16                                                          | PCA0 = 1, CARSEL = 1, CAREF = 3,<br>No load at P1.6/CA0 and P1.7/CA1,<br>T <sub>A</sub> = 85°C | V <sub>CC</sub> = 2.2 V       | 390  | 480                | 540  | mV   |
|                                                |                                                                                         |                                                                                                | V <sub>CC</sub> = 3 V         | 400  | 490                | 550  |      |
| V <sub>IC</sub>                                | Common-mode input<br>voltage range                                                      | CAON = 1                                                                                       | V <sub>CC</sub> = 2.2 V / 3 V | 0    | V <sub>CC</sub> -1 |      | V    |
| V <sub>p</sub> -V <sub>S</sub>                 | Offset voltage                                                                          | See Note 2                                                                                     | V <sub>CC</sub> = 2.2 V / 3 V | -30  | 30                 |      | mV   |
| V <sub>hys</sub>                               | Input hysteresis                                                                        | CAON = 1                                                                                       | V <sub>CC</sub> = 2.2 V / 3 V | 0    | 0.7                | 1.4  | mV   |
| t <sub>(response LH and HL)</sub> , see Note 3 |                                                                                         | T <sub>A</sub> = 25°C,<br>Overdrive 10 mV, without filter: CAF = 0                             | V <sub>CC</sub> = 2.2 V       | 80   | 165                | 300  | ns   |
|                                                |                                                                                         |                                                                                                | V <sub>CC</sub> = 3 V         | 70   | 120                | 240  |      |
|                                                |                                                                                         | T <sub>A</sub> = 25°C<br>Overdrive 10 mV, with filter: CAF = 1                                 | V <sub>CC</sub> = 2.2 V       | 1.4  | 1.9                | 2.8  | μs   |
|                                                |                                                                                         |                                                                                                | V <sub>CC</sub> = 3 V         | 0.9  | 1.5                | 2.2  |      |

- NOTES: 1. The leakage current for the Comparator\_A terminals is identical to  $I_{\text{lk}(P_{X.X})}$  specification.
2. The input offset voltage can be cancelled by using the CAEX bit to invert the Comparator\_A inputs on successive measurements. The two successive measurements are then summed together.
3. The response time is measured at P1.6/CA0 with an input voltage step and the Comparator\_A already enabled (CAON = 1). If CAON is set at the same time, a settling time of up to 300ns is added to the response time.



electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)

typical characteristics




Figure 15. V<sub>(RefVT)</sub> vs Temperature




Figure 16. V<sub>(RefVT)</sub> vs Temperature




Figure 17. Block Diagram of Comparator\_A Module




Figure 18. Overdrive Definition

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)**

### SD16\_A, power supply and recommended operating conditions

| PARAMETER                                                            | TEST CONDITIONS                                                                 | V <sub>CC</sub>             | MIN  | TYP  | MAX  | UNIT |
|----------------------------------------------------------------------|---------------------------------------------------------------------------------|-----------------------------|------|------|------|------|
| AV <sub>CC</sub> Analog supply voltage                               | AV <sub>CC</sub> = DV <sub>CC</sub><br>AV <sub>SS</sub> = DV <sub>SS</sub> = 0V |                             | 2.5  |      | 3.6  | V    |
| I <sub>SD16</sub> Analog supply current including internal reference | SD16LP = 0,<br>f <sub>SD16</sub> = 1 MHz,<br>SD16OSR = 256                      | SD16BUFx = 00, GAIN: 1,2    | 3 V  | 750  | 1050 | μA   |
|                                                                      |                                                                                 | SD16BUFx = 00, GAIN: 4,8,16 | 3 V  | 830  | 1150 |      |
|                                                                      |                                                                                 | SD16BUFx = 00, GAIN: 32     | 3 V  | 1150 | 1700 |      |
|                                                                      | SD16LP = 1,<br>f <sub>SD16</sub> = 0.5 MHz,<br>SD16OSR = 256                    | SD16BUFx = 00, GAIN: 1      | 3 V  | 730  | 1030 |      |
|                                                                      |                                                                                 | SD16BUFx = 00, GAIN: 32     | 3 V  | 830  | 1150 |      |
|                                                                      | SD16LP = 0,<br>SD16OSR = 256                                                    | SD16BUFx = 01, GAIN: 1      | 3 V  | 850  |      |      |
|                                                                      |                                                                                 | SD16BUFx = 10, GAIN: 1      | 3 V  | 1000 |      |      |
|                                                                      |                                                                                 | SD16BUFx = 11, GAIN: 1      | 3 V  | 1130 |      |      |
| f <sub>SD16</sub> Analog front-end input clock frequency             | SD16LP = 0 (Low power mode disabled)                                            | 3 V                         | 0.03 | 1    | 1.1  | MHz  |
|                                                                      | SD16LP = 1 (Low power mode enabled)                                             | 3 V                         | 0.03 | 0.5  |      |      |

### SD16\_A, input range

| PARAMETER                                                                               | TEST CONDITIONS                             | V <sub>CC</sub> | MIN                      | TYP  | MAX                      | UNIT |
|-----------------------------------------------------------------------------------------|---------------------------------------------|-----------------|--------------------------|------|--------------------------|------|
| V <sub>I</sub> Absolute input voltage range                                             | SD16BUFx = 00                               |                 | AV <sub>SS</sub> - 0.1V  |      | AV <sub>CC</sub>         | V    |
|                                                                                         | SD16BUFx > 00                               |                 | AV <sub>SS</sub> + 0.2V  |      | AV <sub>CC</sub> - 1.2 V |      |
| V <sub>IC</sub> Common-mode input voltage range                                         | SD16BUFx = 00                               |                 | AV <sub>SS</sub> - 0.1V  |      | AV <sub>CC</sub>         | V    |
|                                                                                         | SD16BUFx > 00                               |                 | AV <sub>SS</sub> + 0.2V  |      | AV <sub>CC</sub> - 1.2 V |      |
| V <sub>ID,FSR</sub> Differential full scale input voltage range                         | Bipolar mode, SD16UNI = 0                   |                 | -V <sub>REF</sub> /2GAIN |      | +V <sub>REF</sub> /2GAIN | mV   |
|                                                                                         | Unipolar mode, SD16UNI = 1                  |                 | 0                        |      | +V <sub>REF</sub> /2GAIN | mV   |
| V <sub>ID</sub> Differential input voltage range for specified performance (see Note 1) | SD16REFON = 1                               | SD16GAINx = 1   |                          | ±500 |                          | mV   |
|                                                                                         |                                             | SD16GAINx = 2   |                          | ±250 |                          |      |
|                                                                                         |                                             | SD16GAINx = 4   |                          | ±125 |                          |      |
|                                                                                         |                                             | SD16GAINx = 8   |                          | ±62  |                          |      |
|                                                                                         |                                             | SD16GAINx = 16  |                          | ±31  |                          |      |
|                                                                                         |                                             | SD16GAINx = 32  |                          | ±15  |                          |      |
| Z <sub>I</sub> Input impedance (one input pin to AV <sub>SS</sub> )                     | f <sub>SD16</sub> = 1 MHz,<br>SD16BUFx = 00 | SD16GAINx = 1   | 3 V                      | 200  |                          | kΩ   |
|                                                                                         |                                             | SD16GAINx = 32  | 3 V                      | 75   |                          |      |
|                                                                                         | f <sub>SD16</sub> = 1 MHz,<br>SD16BUFx = 01 | SD16GAINx = 1   | 3 V                      | >10  |                          | MΩ   |
| Z <sub>ID</sub> Differential input impedance (IN+ to IN-)                               | f <sub>SD16</sub> = 1 MHz,<br>SD16BUFx = 00 | SD16GAINx = 1   | 3 V                      | 300  | 400                      | kΩ   |
|                                                                                         |                                             | SD16GAINx = 32  | 3 V                      | 100  | 150                      |      |
|                                                                                         | f <sub>SD16</sub> = 1 MHz,<br>SD16BUFx > 00 | SD16GAINx = 1   | 3 V                      | >10  |                          | MΩ   |

NOTES: 1. The analog input range depends on the reference voltage applied to V<sub>REF</sub>. If V<sub>REF</sub> is sourced externally, the full-scale range is defined by V<sub>FSR+</sub> = +(V<sub>REF</sub>/2)/GAIN and V<sub>FSR-</sub> = -(V<sub>REF</sub>/2)/GAIN. The analog input range should not exceed 80% of V<sub>FSR+</sub> or V<sub>FSR-</sub>.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)**

**SD16\_A, performance ( $f_{SD16} = 30\text{kHz}$ ,  $SD16REFON = 1$ ,  $SD16BUFx = 01$ )**

| PARAMETER                                        | TEST CONDITIONS                                                               | V <sub>CC</sub> | MIN  | TYP  | MAX  | UNIT   |
|--------------------------------------------------|-------------------------------------------------------------------------------|-----------------|------|------|------|--------|
| SINAD<br>Signal-to-noise + distortion ratio      | SD16GAINx = 1, Signal Amplitude = 500mV<br>SD16OSRx = 256                     | 3 V             |      | 84   |      | dB     |
|                                                  | SD16GAINx = 1, Signal Amplitude = 500mV<br>SD16OSRx = 512                     | 3 V             |      | 84   |      |        |
|                                                  | SD16GAINx = 1, Signal Amplitude = 500mV<br>SD16OSRx = 1024                    | 3 V             |      | 84   |      |        |
| Nominal gain                                     | SD16GAINx = 1, SD16OSRx = 1024                                                | 3 V             | 0.97 | 1.00 | 1.02 |        |
| dG/dT<br>Gain temperature drift                  | SD16GAINx = 1, SD16OSRx = 1024 (see Note 1)                                   | 3 V             |      | 15   |      | ppm/°C |
| dG/dV <sub>CC</sub><br>Gain supply voltage drift | SD16GAINx = 1, SD16OSRx = 1024, V <sub>CC</sub> = 2.5 V to 3.6 V (see Note 2) |                 |      | 0.35 |      | %/V    |

NOTES: 1. Calculated using the box method:  $(\text{MAX}(-40\dots85^{\circ}\text{C}) - \text{MIN}(-40\dots85^{\circ}\text{C})) / (\text{MIN}(-40\dots85^{\circ}\text{C}) / (85^{\circ}\text{C} - (-40^{\circ}\text{C})))$   
2. Calculated using the box method:  $(\text{MAX}(2.5\dots3.6\text{V}) - \text{MIN}(2.5\dots3.6\text{V})) / (\text{MIN}(2.5\dots3.6\text{V}) / (3.6\text{V} - 2.5\text{V}))$

**SD16\_A, performance ( $f_{SD16} = 1\text{MHz}$ ,  $SD16OSRx = 256$ ,  $SD16REFON = 1$ ,  $SD16BUFx = 00$ )**

| PARAMETER                                                    | TEST CONDITIONS                                                                                       | V <sub>CC</sub> | MIN   | TYP   | MAX   | UNIT       |
|--------------------------------------------------------------|-------------------------------------------------------------------------------------------------------|-----------------|-------|-------|-------|------------|
| SINAD<br>Signal-to-noise + distortion ratio                  | SD16GAINx = 1, Signal Amplitude = 500mV                                                               | 3 V             | 83.5  | 85    |       | dB         |
|                                                              | SD16GAINx = 2, Signal Amplitude = 250mV                                                               | 3 V             | 81.5  | 84    |       |            |
|                                                              | SD16GAINx = 4, Signal Amplitude = 125mV                                                               | 3 V             | 76    | 79.5  |       |            |
|                                                              | SD16GAINx = 8, Signal Amplitude = 62mV                                                                | 3 V             | 73    | 76.5  |       |            |
|                                                              | SD16GAINx = 16, Signal Amplitude = 31mV                                                               | 3 V             | 69    | 73    |       |            |
|                                                              | SD16GAINx = 32, Signal Amplitude = 15mV                                                               | 3 V             | 62    | 69    |       |            |
| G<br>Nominal gain                                            | SD16GAINx = 1                                                                                         | 3 V             | 0.97  | 1.00  | 1.02  |            |
|                                                              | SD16GAINx = 2                                                                                         | 3 V             | 1.90  | 1.96  | 2.02  |            |
|                                                              | SD16GAINx = 4                                                                                         | 3 V             | 3.76  | 3.86  | 3.96  |            |
|                                                              | SD16GAINx = 8                                                                                         | 3 V             | 7.36  | 7.62  | 7.84  |            |
|                                                              | SD16GAINx = 16                                                                                        | 3 V             | 14.56 | 15.04 | 15.52 |            |
|                                                              | SD16GAINx = 32                                                                                        | 3 V             | 27.20 | 28.35 | 29.76 |            |
| E <sub>OS</sub><br>Offset error                              | SD16GAINx = 1                                                                                         | 3 V             |       |       | ±0.2  | %FSR       |
|                                                              | SD16GAINx = 32                                                                                        | 3 V             |       |       | ±1.5  |            |
| dE <sub>OS</sub> /dT<br>Offset error temperature coefficient | SD16GAINx = 1                                                                                         | 3 V             |       | ±4    | ±20   | ppm FSR/°C |
|                                                              | SD16GAINx = 32                                                                                        | 3 V             |       | ±20   | ±100  |            |
| CMRR<br>Common-mode rejection ratio                          | SD16GAINx = 1, Common-mode input signal:<br>V <sub>ID</sub> = 500 mV, f <sub>IN</sub> = 50 Hz, 100 Hz | 3 V             |       | >90   |       | dB         |
|                                                              | SD16GAINx = 32, Common-mode input signal:<br>V <sub>ID</sub> = 16 mV, f <sub>IN</sub> = 50 Hz, 100 Hz | 3 V             |       | >75   |       |            |
| PSRR<br>Power supply rejection ratio                         | SD16GAINx = 1                                                                                         | 3 V             |       | >80   |       | dB         |

NOTES: 1. Calculated using the box method:  $(\text{MAX}(-40\dots85^{\circ}\text{C}) - \text{MIN}(-40\dots85^{\circ}\text{C})) / (\text{MIN}(-40\dots85^{\circ}\text{C}) / (85^{\circ}\text{C} - (-40^{\circ}\text{C})))$   
2. Calculated using the ADC output code and the box method:  
 $(\text{MAX-code}(2.5\dots3.6\text{V}) - \text{MIN-code}(2.5\dots3.6\text{V})) / (\text{MIN-code}(2.5\dots3.6\text{V}) / (3.6\text{V} - 2.5\text{V}))$

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER


SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)**

**SD16\_A, linearity ( $f_{SD16} = 1\text{MHz}$ ,  $SD16REFON = 1$ ,  $SD16BUFx = 00$ )**

| PARAMETER                      | TEST CONDITIONS                                                | V <sub>CC</sub> | MIN | TYP | MAX | UNIT |
|--------------------------------|----------------------------------------------------------------|-----------------|-----|-----|-----|------|
| INL     Integral non-linearity | SD16OSR = 256, SD16GAINx = 000b,<br>Signal Amplitude = 500 mV  | 3 V             |     | 1.5 |     | LSB  |
|                                | SD16OSR = 256, SD16GAINx = 101b,<br>Signal Amplitude = 15 mV   | 3 V             |     | 6   |     |      |
|                                | SD16OSR = 1024, SD16GAINx = 000b,<br>Signal Amplitude = 500 mV | 3 V             |     | 0.8 |     | LSB  |
|                                | SD16OSR = 1024, SD16GAINx = 101b,<br>Signal Amplitude = 15 mV  | 3 V             |     | 3.5 |     |      |

**typical characteristics - SD16\_A SINAD performance over OSR**



**Figure 19. SINAD performance over OSR,  $f_{SD16} = 1\text{MHz}$ ,  $SD16REFON = 1$ ,  $SD16GAINx = 1$**

**SD16\_A, temperature sensor and built-in V<sub>CC</sub> sense**

| PARAMETER                                                | TEST CONDITIONS                                                 | V <sub>CC</sub> | MIN  | TYP  | MAX  | UNIT |
|----------------------------------------------------------|-----------------------------------------------------------------|-----------------|------|------|------|------|
| TC <sub>Sensor</sub> Sensor temperature coefficient      | See Note 1                                                      |                 | 1.18 | 1.32 | 1.46 | mV/K |
| V <sub>Offset,sensor</sub> Sensor offset voltage         | See Note 1                                                      |                 | -100 |      | 100  | mV   |
| V <sub>Sensor</sub> Sensor output voltage (see Note 3)   | Temperature sensor voltage at T <sub>A</sub> = 85°C             | 3 V             | 435  | 475  | 515  | mV   |
|                                                          | Temperature sensor voltage at T <sub>A</sub> = 25°C             | 3 V             | 355  | 395  | 435  |      |
|                                                          | Temperature sensor voltage at T <sub>A</sub> = 0°C (see Note 1) | 3 V             | 320  | 360  | 400  |      |
| V <sub>CC,Sense</sub> V <sub>CC</sub> divider at input 5 | $f_{SD16} = 32\text{kHz}$ , $SD16OSRx = 256$ , $SD16REFON = 1$  |                 | 0.08 | 1/11 | 0.1  | V    |

- NOTES: 1. Not production tested, limits characterized.  
2. The following formula can be used to calculate the temperature sensor output voltage:  
 $V_{\text{Sensor,typ}} = TC_{\text{Sensor}} (273 + T [^{\circ}\text{C}]) + V_{\text{Offset,sensor}} [\text{mV}]$   
3. Results based on characterization and/or production test, not TC<sub>Sensor</sub> or V<sub>Offset,sensor</sub>.

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)**

**SD16\_A, built-in voltage reference**

| PARAMETER         |                                          | TEST CONDITIONS                                           | V <sub>CC</sub> | MIN  | TYP  | MAX  | UNIT  |
|-------------------|------------------------------------------|-----------------------------------------------------------|-----------------|------|------|------|-------|
| V <sub>REF</sub>  | Internal reference voltage               | SD16REFON = 1, SD16VMIDON = 0                             | 3 V             | 1.14 | 1.20 | 1.26 | V     |
| I <sub>REF</sub>  | Reference supply current                 | SD16REFON = 1, SD16VMIDON = 0                             | 3 V             |      | 175  | 260  | μA    |
| TC                | Temperature coefficient                  | SD16REFON = 1, SD16VMIDON = 0 (see Note 1)                | 3 V             |      | 18   | 50   | ppm/K |
| C <sub>REF</sub>  | V <sub>REF</sub> load capacitance        | SD16REFON = 1, SD16VMIDON = 0 (see Note 2)                |                 |      | 100  |      | nF    |
| I <sub>LOAD</sub> | V <sub>REF(I)</sub> maximum load current | SD16REFON = 1, SD16VMIDON = 0                             | 3 V             |      |      | ±200 | nA    |
| t <sub>ON</sub>   | Turn on time                             | SD16REFON = 0→1, SD16VMIDON = 0, C <sub>REF</sub> = 100nF | 3 V             |      | 5    |      | ms    |
| PSRR              | Line regulation                          | SD16REFON = 1, SD16VMIDON = 0                             | 3 V             |      | 100  |      | uV/V  |

NOTES: 1. Calculated using the box method: (MAX(−40...85°C) – MIN(−40...85°C))/MIN(−40...85°C)/(85°C – (−40°C))  
2. There is no capacitance required on V<sub>REF</sub>. However, a capacitance of at least 100nF is recommended to reduce any reference voltage noise.

**SD16\_A, reference output buffer**

| PARAMETER             |                                                              | TEST CONDITIONS                                           | V <sub>CC</sub> | MIN | TYP | MAX | UNIT |
|-----------------------|--------------------------------------------------------------|-----------------------------------------------------------|-----------------|-----|-----|-----|------|
| V <sub>REF,BUF</sub>  | Reference buffer output voltage                              | SD16REFON = 1, SD16VMIDON = 1                             | 3 V             |     | 1.2 |     | V    |
| I <sub>REF,BUF</sub>  | Reference Supply + Reference output buffer quiescent current | SD16REFON = 1, SD16VMIDON = 1                             | 3 V             |     | 385 | 600 | μA   |
| C <sub>REF(O)</sub>   | Required load capacitance on V <sub>REF</sub>                | SD16REFON = 1, SD16VMIDON = 1                             |                 | 470 |     |     | nF   |
| I <sub>LOAD,Max</sub> | Maximum load current on V <sub>REF</sub>                     | SD16REFON = 1, SD16VMIDON = 1                             | 3 V             |     |     | ±1  | mA   |
|                       | Maximum voltage variation vs load current                    | I <sub>LOAD</sub>   = 0 to 1mA                            | 3 V             | −15 |     | +15 | mV   |
| t <sub>ON</sub>       | Turn on time                                                 | SD16REFON = 0→1, SD16VMIDON = 1, C <sub>REF</sub> = 470nF | 3 V             |     | 100 |     | μs   |

**SD16\_A, external reference input**

| PARAMETER           |                     | TEST CONDITIONS | V <sub>CC</sub> | MIN | TYP  | MAX | UNIT |
|---------------------|---------------------|-----------------|-----------------|-----|------|-----|------|
| V <sub>REF(I)</sub> | Input voltage range | SD16REFON = 0   | 3 V             | 1.0 | 1.25 | 1.5 | V    |
| I <sub>REF(I)</sub> | Input current       | SD16REFON = 0   | 3 V             |     |      | 50  | nA   |

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)**

### 12-bit DAC, supply specifications

| PARAMETER                                                | TEST CONDITIONS                                                                              | V <sub>CC</sub> | MIN  | TYP | MAX  | UNIT |
|----------------------------------------------------------|----------------------------------------------------------------------------------------------|-----------------|------|-----|------|------|
| AV <sub>CC</sub> Analog supply voltage                   | AV <sub>CC</sub> = DV <sub>CC</sub> ,<br>AV <sub>SS</sub> = DV <sub>SS</sub> = 0 V           |                 | 2.20 |     | 3.60 | V    |
| I <sub>DD</sub> Supply current<br>(see Notes 1 and 2)    | DAC12AMPx = 2, DAC12IR = 0,<br>DAC12_xDAT = 0800h                                            | 2.2 V/3 V       |      | 50  | 110  | μA   |
|                                                          | DAC12AMPx = 2, DAC12IR = 1,<br>DAC12_xDAT = 0800h, V <sub>REF,DAC12</sub> = AV <sub>CC</sub> | 2.2 V/3 V       |      | 50  | 110  |      |
|                                                          | DAC12AMPx = 5, DAC12IR = 1,<br>DAC12_xDAT = 0800h, V <sub>REF,DAC12</sub> = AV <sub>CC</sub> | 2.2 V/3 V       |      | 200 | 440  |      |
|                                                          | DAC12AMPx = 7, DAC12IR = 1,<br>DAC12_xDAT = 0800h, V <sub>REF,DAC12</sub> = AV <sub>CC</sub> | 2.2 V/3 V       |      | 700 | 1500 |      |
| PSRR Power supply rejection<br>ratio (see Notes 3 and 4) | DAC12_xDAT = 800h, V <sub>REF,DAC12</sub> = 1.2 V,<br>ΔAV <sub>CC</sub> = 100 mV             | 2.7 V           |      | 70  |      | dB   |


- NOTES: 1. No load at the output pin assuming that the control bits for the shared pins are set properly.  
2. Current into reference terminals not included. If DAC12IR = 1 current flows through the input divider; see Reference Input specifications.  
3. PSRR = 20\*log{ΔAV<sub>CC</sub>/ΔV<sub>DAC12\_xOUT</sub>}.  
4. V<sub>REF</sub> is applied externally. The internal reference is not used.

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)**

**12-bit DAC, linearity specifications (see Figure 20)**

| PARAMETER               |                                                           | TEST CONDITIONS                                                                              | V <sub>CC</sub> | MIN | TYP  | MAX   | UNIT             |
|-------------------------|-----------------------------------------------------------|----------------------------------------------------------------------------------------------|-----------------|-----|------|-------|------------------|
| INL                     | Integral nonlinearity<br>(see Note 1)                     | V <sub>REF,DAC12</sub> = 1.2 V or V <sub>REF,ext</sub> = 2.5 V<br>DAC12AMPx = 7, DAC12IR = 1 | 2.7 V           |     | ±2.0 | ±8.0  | LSB              |
| DNL                     | Differential nonlinearity<br>(see Note 1)                 | V <sub>REF,ext</sub> = 1.2 V<br>DAC12AMPx = 7, DAC12IR = 1                                   | 2.7 V           | -1  | ±0.4 | +1.3  | LSB              |
|                         |                                                           | V <sub>REF,ext</sub> = 2.5 V<br>DAC12AMPx = 7, DAC12IR = 1                                   | 2.7 V           |     | ±0.4 | ±1.0  | LSB              |
| DNL                     | Differential nonlinearity<br>(see Note 1)                 | V <sub>REF,DAC12</sub> = 1.2 V<br>DAC12AMPx = 7, DAC12IR = 1                                 | 2.7 V           |     | ±0.4 | ±1.0  | LSB              |
| E <sub>O</sub>          | Offset voltage without<br>calibration<br>(see Notes 1, 2) | V <sub>REF,DAC12</sub> = 1.2 V<br>DAC12AMPx = 7, DAC12IR = 1                                 | 2.7 V           |     |      | ±20   | mV               |
|                         | Offset voltage with<br>calibration<br>(see Notes 1, 2)    | V <sub>REF,DAC12</sub> = 1.2 V<br>DAC12AMPx = 7, DAC12IR = 1                                 | 2.7 V           |     |      | ±2.5  |                  |
| dE(O)/dT                | Offset error temperature<br>coefficient (see Note 1)      |                                                                                              | 2.7 V           |     | ±30  |       | µV/°C            |
| E <sub>G</sub>          | Gain error (see Note 1)                                   | V <sub>REF,DAC12</sub> = 1.2 V                                                               | 2.7 V           |     |      | ±3.50 | % FSR            |
| dE(G)/dT                | Gain temperature<br>coefficient (see Note 1)              |                                                                                              | 2.7 V           |     | 10   |       | ppm of<br>FSR/°C |
| t <sub>Offset_Cal</sub> | Time for offset calibration<br>(see Note 3)               | DAC12AMPx = 2                                                                                | 2.7 V           |     |      | 100   | ms               |
|                         |                                                           | DAC12AMPx = 3,5                                                                              | 2.7 V           |     |      | 32    |                  |
|                         |                                                           | DAC12AMPx = 4,6,7                                                                            | 2.7 V           |     |      | 6     |                  |

NOTES: 1. Parameters calculated from the best-fit curve from 0x0A to 0xFFF. The best-fit curve method is used to deliver coefficients “a” and “b” of the first order equation:  $y = a + b \cdot x$ .  $V_{DAC12\_xOUT} = E_O + (1 + E_G) \cdot (V_{REF,DAC12}/4095) \cdot DAC12\_xDAT$ , DAC12IR = 1.  
2. The offset calibration works on the output operational amplifier. Offset Calibration is triggered setting bit DAC12CALON  
3. The offset calibration can be done if DAC12AMPx = {2, 3, 4, 5, 6, 7}. The output operational amplifier is switched off with DAC12AMPx = {0, 1}. It is recommended that the DAC12 module be configured prior to initiating calibration. Port activity during calibration may effect accuracy and is not recommended.



**Figure 20. Linearity Test Load Conditions and Gain/Offset Definition**



# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)

12-bit DAC, linearity specifications (continued)






**electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)**

**12-bit DAC, output specifications**

| PARAMETER                                                          | TEST CONDITIONS                                                                                                            | V <sub>CC</sub>                                                                                   | MIN                    | TYP | MAX              | UNIT |
|--------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|------------------------|-----|------------------|------|
| V <sub>O</sub><br><br>Output voltage range (see Note 1, Figure 23) | No Load, V <sub>REF,DAC12</sub> = AV <sub>CC</sub> ,<br>DAC12_xDAT = 0h, DAC12IR = 1,<br>DAC12AMPx = 7                     | 2.2 V/3 V                                                                                         | 0                      |     | 0.005            | V    |
|                                                                    | No Load, V <sub>REF,DAC12</sub> = AV <sub>CC</sub> ,<br>DAC12_xDAT = 0FFFh, DAC12IR = 1,<br>DAC12AMPx = 7                  | 2.2 V/3 V                                                                                         | AV <sub>CC</sub> -0.05 |     | AV <sub>CC</sub> |      |
|                                                                    | R <sub>Load</sub> = 3 kΩ, V <sub>REF,DAC12</sub> = AV <sub>CC</sub> ,<br>DAC12_xDAT = 0h, DAC12IR = 1,<br>DAC12AMPx = 7    | 2.2 V/3 V                                                                                         | 0                      |     | 0.1              |      |
|                                                                    | R <sub>Load</sub> = 3 kΩ, V <sub>REF,DAC12</sub> = AV <sub>CC</sub> ,<br>DAC12_xDAT = 0FFFh, DAC12IR = 1,<br>DAC12AMPx = 7 | 2.2 V/3 V                                                                                         | AV <sub>CC</sub> -0.13 |     | AV <sub>CC</sub> |      |
| C <sub>L(DAC12)</sub>                                              | Max DAC12 load capacitance                                                                                                 | 2.2 V/3 V                                                                                         |                        |     | 100              | pF   |
| I <sub>L(DAC12)</sub>                                              | Max DAC12 load current                                                                                                     | 2.2V                                                                                              | -0.5                   |     | +0.5             | mA   |
|                                                                    |                                                                                                                            | 3V                                                                                                | -1.0                   |     | +1.0             |      |
| R <sub>O/P(DAC12)</sub>                                            | Output resistance (see Figure 23)                                                                                          | R <sub>Load</sub> = 3 kΩ, V <sub>O/P(DAC12)</sub> < 0.3 V,<br>DAC12AMPx = 2, DAC12_xDAT = 0h      | 2.2 V/3 V              | 150 | 250              | Ω    |
|                                                                    |                                                                                                                            | R <sub>Load</sub> = 3 kΩ, V <sub>O/P(DAC12)</sub> > AV <sub>CC</sub> -0.3 V<br>DAC12_xDAT = 0FFFh | 2.2 V/3 V              | 150 | 250              |      |
|                                                                    |                                                                                                                            | R <sub>Load</sub> = 3 kΩ,<br>0.3V ≤ V <sub>O/P(DAC12)</sub> ≤ AV <sub>CC</sub> - 0.3V             | 2.2 V/3 V              | 1   | 4                |      |

NOTES: 1. Data is valid after the offset calibration of the output amplifier.



**Figure 23. DAC12\_x Output Resistance Tests**

# MSP430FG47x MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted)**

## 12-bit DAC, reference input specifications


| PARAMETER                                                     | TEST CONDITIONS                          | V <sub>CC</sub> | MIN | TYP                 | MAX                   | UNIT |
|---------------------------------------------------------------|------------------------------------------|-----------------|-----|---------------------|-----------------------|------|
| V <sub>REF</sub> Reference input voltage range                | DAC12IR = 0 (see Notes 1 and 2)          | 2.2 V/3 V       |     | AV <sub>CC</sub> /3 | AV <sub>CC</sub> +0.2 | V    |
|                                                               | DAC12IR = 1 (see Notes 3 and 4)          | 2.2 V/3 V       |     | AV <sub>CC</sub>    | AV <sub>CC</sub> +0.2 |      |
| R <sub>i</sub> (V <sub>REF</sub> ) Reference input resistance | DAC12IR = 0, SD16VMIDON = 1 (see Note 5) | 2.2 V/3 V       | 20  |                     |                       | MΩ   |
|                                                               | DAC12IR = 1, SD16VMIDON = 1              | 2.2 V/3 V       | 40  | 48                  | 56                    | kΩ   |

- NOTES: 1. For a full-scale output, the reference input voltage can be as high as 1/3 of the maximum output voltage swing (AV<sub>CC</sub>).  
2. The maximum voltage applied at reference input voltage terminal V<sub>REF</sub> = [AV<sub>CC</sub> - V<sub>E(O)</sub>] / [3\*(1 + E<sub>G</sub>)].  
3. For a full-scale output, the reference input voltage can be as high as the maximum output voltage swing (AV<sub>CC</sub>).  
4. The maximum voltage applied at reference input voltage terminal V<sub>REF</sub> = [AV<sub>CC</sub> - V<sub>E(O)</sub>] / (1 + E<sub>G</sub>).  
5. Characterized, not production tested

## 12-bit DAC, dynamic specifications (V<sub>REF</sub>, DAC12 = AV<sub>CC</sub>, DAC12IR = 1) (see Figure 24 and Figure 25)


| PARAMETER                                       | TEST CONDITIONS                                                             | V <sub>CC</sub>           | MIN       | TYP  | MAX  | UNIT |
|-------------------------------------------------|-----------------------------------------------------------------------------|---------------------------|-----------|------|------|------|
| t <sub>ON</sub> DAC12 on-time                   | DAC12_xDAT = 800h, Error <sub>V(O)</sub> < ±0.5 LSB (see Note 1, Figure 24) | DAC12AMPx = 0 → {2, 3, 4} | 2.2 V/3 V | 60   | 120  | μs   |
|                                                 |                                                                             | DAC12AMPx = 0 → {5, 6}    | 2.2 V/3 V | 15   | 30   |      |
|                                                 |                                                                             | DAC12AMPx = 0 → 7         | 2.2 V/3 V | 6    | 12   |      |
| t <sub>S(FS)</sub> Settling time, full-scale    | DAC12_xDAT = 80h → F7Fh → 80h                                               | DAC12AMPx = 2             | 2.2 V/3 V | 100  | 200  | μs   |
|                                                 |                                                                             | DAC12AMPx = 3,5           | 2.2 V/3 V | 40   | 80   |      |
|                                                 |                                                                             | DAC12AMPx = 4,6,7         | 2.2 V/3 V | 15   | 30   |      |
| t <sub>S(C-C)</sub> Settling time, code to code | DAC12_xDAT = 3F8h → 408h → 3F8h<br>BF8h → C08h → BF8h                       | DAC12AMPx = 2             | 2.2 V/3 V | 5    |      | μs   |
|                                                 |                                                                             | DAC12AMPx = 3,5           | 2.2 V/3 V | 2    |      |      |
|                                                 |                                                                             | DAC12AMPx = 4,6,7         | 2.2 V/3 V | 1    |      |      |
| SR Slew Rate                                    | DAC12_xDAT = 80h → F7Fh → 80h                                               | DAC12AMPx = 2             | 2.2 V/3 V | 0.05 | 0.12 | V/μs |
|                                                 |                                                                             | DAC12AMPx = 3,5           | 2.2 V/3 V | 0.35 | 0.7  |      |
|                                                 |                                                                             | DAC12AMPx = 4,6,7         | 2.2 V/3 V | 1.5  | 2.7  |      |
| Glitch energy: full-scale                       | DAC12_xDAT = 80h → F7Fh → 80h                                               | DAC12AMPx = 2             | 2.2 V/3 V | 600  |      | nV-s |
|                                                 |                                                                             | DAC12AMPx = 3,5           | 2.2 V/3 V | 150  |      |      |
|                                                 |                                                                             | DAC12AMPx = 4,6,7         | 2.2 V/3 V | 30   |      |      |

- NOTES: 1. R<sub>Load</sub> and C<sub>Load</sub> connected to AV<sub>SS</sub> (not AV<sub>CC</sub>/2) in Figure 24.  
2. Slew rate applies to output voltage steps > = 200 mV.



**Figure 24. Settling Time and Glitch Energy Testing**

electrical characteristics over recommended operating free-air temperature (unless otherwise noted)




**Figure 25. Slew Rate Testing**

**12-bit DAC, dynamic specifications continued ( $T_A = 25^\circ\text{C}$  unless otherwise noted)**

| PARAMETER                                                                                                         | TEST CONDITIONS                                                          | $V_{CC}$  | MIN | MAX | UNIT |
|-------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------|-----------|-----|-----|------|
| BW <sub>-3dB</sub><br><br>3-dB bandwidth,<br>$V_{DC} = 1.5\text{ V}$ ,<br>$V_{AC} = 0.1V_{PP}$<br>(see Figure 26) | DAC12AMPx = {2, 3, 4}, DAC12SREFx = 2, DAC12IR = 1,<br>DAC12_xDAT = 800h | 2.2 V/3 V | 40  |     | kHz  |
|                                                                                                                   | DAC12AMPx = {5, 6}, DAC12SREFx = 2, DAC12IR = 1,<br>DAC12_xDAT = 800h    | 2.2 V/3 V | 180 |     |      |
|                                                                                                                   | DAC12AMPx = 7, DAC12SREFx = 2,<br>DAC12IR = 1, DAC12_xDAT = 800h         | 2.2 V/3 V | 550 |     |      |

NOTES: 1.  $R_{LOAD} = 3\text{ k}\Omega$ ,  $C_{LOAD} = 100\text{ pF}$



**Figure 26. Test Conditions for 3-dB Bandwidth Specification**

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

**electrical characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (continued)**

### operational amplifier OA, supply specifications

| PARAMETER       | TEST CONDITIONS              | V <sub>CC</sub> | MIN | TYP | MAX | UNIT |
|-----------------|------------------------------|-----------------|-----|-----|-----|------|
| V <sub>CC</sub> | Supply voltage range         |                 | 2.2 |     | 3.6 | V    |
| I <sub>CC</sub> | Fast Mode                    | 2.2 V/3 V       |     | 180 | 290 | μA   |
|                 | Medium Mode                  |                 |     | 110 | 190 |      |
|                 | Slow Mode                    |                 |     | 50  | 80  |      |
| PSRR            | Power supply rejection ratio | 2.2 V/3 V       |     | 70  |     | dB   |

NOTES: 1. Corresponding pins configured as OA inputs and outputs respectively.

### operational amplifier OA, input/output specification



| PARAMETER        | TEST CONDITIONS                          | V <sub>CC</sub>              | MIN                  | TYP                  | MAX             | UNIT   |
|------------------|------------------------------------------|------------------------------|----------------------|----------------------|-----------------|--------|
| V <sub>I/P</sub> | Input voltage range                      |                              | -0.1                 | V <sub>CC</sub> -1.2 |                 | V      |
| I <sub>Ikg</sub> | T <sub>A</sub> = -40 to +55°C            | 2.2 V/3 V                    | -5                   | ±0.5                 | 5               | nA     |
|                  | T <sub>A</sub> = +55 to +85°C            |                              | -20                  | ±5                   | 20              |        |
| V <sub>n</sub>   | Fast Mode                                | f <sub>V(I/P)</sub> = 1 kHz  |                      | 50                   |                 | nV/√Hz |
|                  | Medium Mode                              |                              |                      | 80                   |                 |        |
|                  | Slow Mode                                |                              |                      | 140                  |                 |        |
|                  | Fast Mode                                | f <sub>V(I/P)</sub> = 10 kHz |                      | 30                   |                 |        |
|                  | Medium Mode                              |                              |                      | 50                   |                 |        |
|                  | Slow Mode                                |                              |                      | 65                   |                 |        |
| V <sub>IO</sub>  | Offset voltage, I/P                      | 2.2 V/3 V                    |                      |                      | ±10             | mV     |
|                  | Offset temperature drift, I/P            | 2.2 V/3 V                    |                      | ±10                  |                 | μV/°C  |
|                  | Offset voltage drift with supply, I/P    | 2.2 V/3 V                    |                      |                      | ±1.5            | mV/V   |
| V <sub>OH</sub>  | Fast Mode, I <sub>SOURCE</sub> ≤ -500 μA | 2.2 V/3 V                    | V <sub>CC</sub> -0.2 |                      | V <sub>CC</sub> | V      |
|                  | Slow Mode, I <sub>SOURCE</sub> ≤ -150 μA |                              | V <sub>CC</sub> -0.1 |                      | V <sub>CC</sub> |        |
| V <sub>OL</sub>  | Fast Mode, I <sub>SOURCE</sub> ≤ +500 μA | 2.2 V/3 V                    | V <sub>SS</sub>      |                      | 0.2             | V      |
|                  | Slow Mode, I <sub>SOURCE</sub> ≤ +150 μA |                              | V <sub>SS</sub>      |                      | 0.1             |        |
| CMRR             | Common-mode rejection ratio              | 2.2 V/3 V                    |                      | 70                   |                 | dB     |

NOTES: 1. ESD damage can degrade input current leakage.  
2. The input bias current is overridden by the input leakage current.  
3. Calculated using the box method  
4. Specification valid for voltage-follower OAx configuration

**electrical characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (continued)**

**operational amplifier OA, dynamic specifications**

| PARAMETER              |                                                         | TEST CONDITIONS                                                              | V <sub>CC</sub> | MIN | TYP | MAX  | UNIT |
|------------------------|---------------------------------------------------------|------------------------------------------------------------------------------|-----------------|-----|-----|------|------|
| SR                     | Slew rate                                               | Fast Mode                                                                    |                 | 1.2 |     | V/μs |      |
|                        |                                                         | Medium Mode                                                                  |                 | 0.8 |     |      |      |
|                        |                                                         | Slow Mode                                                                    |                 | 0.3 |     |      |      |
| Open-loop voltage gain |                                                         |                                                                              |                 | 100 |     | dB   |      |
| φ <sub>m</sub>         | Phase margin                                            | C <sub>L</sub> = 50 pF                                                       |                 | 60  |     | deg  |      |
| Gain margin            |                                                         | C <sub>L</sub> = 50 pF                                                       |                 | 20  |     | dB   |      |
| GBW                    | Gain-bandwidth product<br>(see Figure 27 and Figure 28) | Noninverting, Fast Mode,<br>R <sub>L</sub> = 47 kΩ, C <sub>L</sub> = 50 pF   | 2.2 V/3 V       | 2.2 |     | MHz  |      |
|                        |                                                         | Noninverting, Medium Mode,<br>R <sub>L</sub> = 300 kΩ, C <sub>L</sub> = 50pF |                 | 1.4 |     |      |      |
|                        |                                                         | Non-inverting, Slow Mode,<br>R <sub>L</sub> = 300 kΩ, C <sub>L</sub> = 50pF  |                 | 0.5 |     |      |      |
| t <sub>en(on)</sub>    | Enable time on                                          | t <sub>on</sub> , Noninverting, Gain = 1                                     | 2.2 V/3 V       | 10  | 20  | μs   |      |
| t <sub>en(off)</sub>   | Enable time off                                         |                                                                              | 2.2 V/3 V       | 1   |     | μs   |      |



MSP430FG47x  
MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

electrical characteristics over recommended operating free-air temperature (unless otherwise noted) (continued)

switches between OA terminals and pins

| PARAMETER        | TEST CONDITIONS                       | V <sub>CC</sub>          | MIN | TYP | MAX | UNIT |
|------------------|---------------------------------------|--------------------------|-----|-----|-----|------|
| V <sub>CC</sub>  | Supply voltage range                  | -                        | 2.2 |     | 3.6 | V    |
| I <sub>Ikg</sub> | Input leakage current<br>(see Note 1) |                          |     | ±1  | ±10 | nA   |
|                  |                                       |                          |     |     | ±50 |      |
| I <sub>IN</sub>  | Input current                         | Input switched to ON     | 0   |     | 100 | μA   |
| R <sub>ON</sub>  | On resistance                         | I <sub>IN</sub> = 100 μA |     | 1   |     | kΩ   |

NOTES: 1. ESD damage can degrade input current leakage.

typical characteristics




Figure 29




Figure 30

**electrical characteristics over recommended operating free-air temperature (unless otherwise noted)**

**Timer\_A**

| PARAMETER           |                         | TEST CONDITIONS                                                            | V <sub>CC</sub> | MIN | MAX | UNIT |
|---------------------|-------------------------|----------------------------------------------------------------------------|-----------------|-----|-----|------|
| f <sub>TA</sub>     | Timer_A clock frequency | Internal: SMCLK, ACLK,<br>External: TACLK, INCLK,<br>Duty cycle = 50% ±10% | 2.2 V           |     | 8   | MHz  |
|                     |                         |                                                                            | 3 V             |     | 10  |      |
| t <sub>TA,cap</sub> | Timer_A, capture timing | TA0, TA1, TA2                                                              | 2.2 V/3 V       | 20  |     | ns   |

**Timer\_B**

| PARAMETER           |                         | TEST CONDITIONS                                                     | V <sub>CC</sub> | MIN | MAX | UNIT |
|---------------------|-------------------------|---------------------------------------------------------------------|-----------------|-----|-----|------|
| f <sub>TB</sub>     | Timer_B clock frequency | Internal: SMCLK, ACLK,<br>External: TBCLK,<br>Duty cycle = 50% ±10% | 2.2 V           |     | 8   | MHz  |
|                     |                         |                                                                     | 3 V             |     | 10  |      |
| t <sub>TB,cap</sub> | Timer_B, capture timing | TB0, TB1, TB2                                                       | 2.2 V/3 V       | 20  |     | ns   |

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

**electrical characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (continued)**

### USCI (UART mode)

| PARAMETER                                                                                      | TEST CONDITIONS                                                   | V <sub>CC</sub> | MIN | TYP                 | MAX | UNIT |
|------------------------------------------------------------------------------------------------|-------------------------------------------------------------------|-----------------|-----|---------------------|-----|------|
| f <sub>USCI</sub> USCI input clock frequency                                                   | Internal: SMCLK, ACLK<br>External: UCLK<br>Duty cycle = 50% ± 10% |                 |     | f <sub>SYSTEM</sub> |     | MHz  |
| f <sub>max,BITCLK</sub> Maximum BITCLK clock frequency (equals baudrate in MBaud) (see Note 1) |                                                                   | 2.2V /3 V       | 2   |                     |     | MHz  |
| t <sub>r</sub> UART receive deglitch time (see Note NO TAG)                                    |                                                                   | 2.2 V           | 50  | 150                 |     | ns   |
|                                                                                                |                                                                   | 3 V             | 50  | 100                 |     | ns   |

NOTES: 1. The DCO wake-up time must be considered in LPM3/4 for baudrates above 1 MHz.  
2. Pulses on the UART receive input (UCxRX) shorter than the UART receive deglitch time are suppressed.

### USCI (SPI master mode) (see Figure 31 and Figure 32)

| PARAMETER                                         | TEST CONDITIONS                                 | V <sub>CC</sub> | MIN                 | MAX | UNIT |
|---------------------------------------------------|-------------------------------------------------|-----------------|---------------------|-----|------|
| f <sub>USCI</sub> USCI input clock frequency      | SMCLK, ACLKm<br>Duty cycle = 50% ± 10%          |                 | f <sub>SYSTEM</sub> |     | MHz  |
| t <sub>SU,MI</sub> SOMI input data setup time     |                                                 | 2.2 V           | 110                 |     | ns   |
|                                                   |                                                 | 3 V             | 75                  |     | ns   |
| t <sub>HD,MI</sub> SOMI input data hold time      |                                                 | 2.2 V           | 0                   |     | ns   |
|                                                   |                                                 | 3 V             | 0                   |     | ns   |
| t <sub>VALID,MO</sub> SIMO output data valid time | UCLK edge to SIMO valid, C <sub>L</sub> = 20 pF | 2.2 V           |                     | 30  | ns   |
|                                                   |                                                 | 3 V             |                     | 20  | ns   |

NOTE:  $f_{UCXCLK} = \frac{1}{2t_{LO/HI}}$  with  $t_{LO/HI} \geq \max(t_{VALID,MO(USCI)} + t_{SU,SI(Slave)}, t_{SU,MI(USCI)} + t_{VALID,SO(Slave)})$ .

For the slave's parameters t<sub>SU,SI(Slave)</sub> and t<sub>VALID,SO(Slave)</sub> refer to the SPI parameters of the attached slave.

### USCI (SPI slave mode) (see Figure 33 and Figure 34)

| PARAMETER                                                                | TEST CONDITIONS                                    | V <sub>CC</sub> | MIN | TYP | MAX | UNIT |
|--------------------------------------------------------------------------|----------------------------------------------------|-----------------|-----|-----|-----|------|
| t <sub>STE,LEAD</sub> STE lead time<br>STE low to clock                  |                                                    | 2.2 V/3 V       |     | 50  |     | ns   |
| t <sub>STE,LAG</sub> STE lag time<br>Last clock to STE high              |                                                    | 2.2 V/3 V       | 10  |     |     | ns   |
| t <sub>STE,ACC</sub> STE access time<br>STE low to SOMI data out         |                                                    | 2.2 V/3 V       |     | 50  |     | ns   |
| t <sub>STE,DIS</sub> STE disable time<br>STE high to SOMI high impedance |                                                    | 2.2 V/3 V       |     | 50  |     | ns   |
| t <sub>SU,SI</sub> SIMO input data setup time                            |                                                    | 2.2 V           | 20  |     |     | ns   |
|                                                                          |                                                    | 3 V             | 15  |     |     | ns   |
| t <sub>HD,SI</sub> SIMO input data hold time                             |                                                    | 2.2 V           | 10  |     |     | ns   |
|                                                                          |                                                    | 3 V             | 10  |     |     | ns   |
| t <sub>VALID,SO</sub> SOMI output data valid time                        | UCLK edge to SOMI valid,<br>C <sub>L</sub> = 20 pF | 2.2 V           |     | 75  | 110 | ns   |
|                                                                          |                                                    | 3 V             |     | 50  | 75  | ns   |


NOTE:  $f_{UCXCLK} = \frac{1}{2t_{LO/HI}}$  with  $t_{LO/HI} \geq \max(t_{VALID,MO(Master)} + t_{SU,SI(USCI)}, t_{SU,MI(Master)} + t_{VALID,SO(USCI)})$ .

For the master's parameters t<sub>SU,MI(Master)</sub> and t<sub>VALID,MO(Master)</sub> refer to the SPI parameters of the attached master.






electrical characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (continued)



**Figure 31. SPI Master Mode, CKPH = 0**





**Figure 32. SPI Master Mode, CKPH = 1**

# MSP430FG47x MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011


electrical characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (continued)



**electrical characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (continued)**

**USCI (I2C mode) (see Figure 35)**

| PARAMETER                                                        | TEST CONDITIONS                                                   | V <sub>CC</sub> | MIN | TYP                 | MAX | UNIT |
|------------------------------------------------------------------|-------------------------------------------------------------------|-----------------|-----|---------------------|-----|------|
| f <sub>USCI</sub> USCI input clock frequency                     | Internal: SMCLK, ACLK<br>External: UCLK<br>Duty cycle = 50% ± 10% |                 |     | f <sub>SYSTEM</sub> |     | MHz  |
| f <sub>SCL</sub> SCL clock frequency                             |                                                                   | 2.2 V/3 V       | 0   |                     | 400 | kHz  |
| t <sub>HD,STA</sub> Hold time (repeated) START                   | f <sub>SCL</sub> ≤ 100kHz                                         | 2.2 V/3 V       | 4.0 |                     |     | μs   |
|                                                                  | f <sub>SCL</sub> > 100kHz                                         | 2.2 V/3 V       | 0.6 |                     |     | μs   |
| t <sub>SU,STA</sub> Setup time for a repeated START              | f <sub>SCL</sub> ≤ 100kHz                                         | 2.2 V/3 V       | 4.7 |                     |     | μs   |
|                                                                  | f <sub>SCL</sub> > 100kHz                                         | 2.2 V/3 V       | 0.6 |                     |     | μs   |
| t <sub>HD,DAT</sub> Data hold time                               |                                                                   | 2.2 V/3 V       | 0   |                     |     | ns   |
| t <sub>SU,DAT</sub> Data setup time                              |                                                                   | 2.2 V/3 V       | 250 |                     |     | ns   |
| t <sub>SU,STO</sub> Setup time for STOP                          |                                                                   | 2.2 V/3 V       | 4.0 |                     |     | μs   |
| t <sub>SP</sub> Pulse width of spikes suppressed by input filter |                                                                   | 2.2 V           | 50  | 150                 | 600 | ns   |
|                                                                  |                                                                   | 3 V             | 50  | 100                 | 600 | ns   |



**Figure 35. I2C Mode Timing**

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

**electrical characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (continued)**

### flash memory

| PARAMETER                                                                    | TEST CONDITIONS       | V <sub>CC</sub> | MIN             | TYP             | MAX | UNIT             |
|------------------------------------------------------------------------------|-----------------------|-----------------|-----------------|-----------------|-----|------------------|
| V <sub>CC(PGM/ERASE)</sub> Program and Erase supply voltage                  |                       |                 | 2.2             |                 | 3.6 | V                |
| f <sub>FTG</sub> Flash Timing Generator frequency                            |                       |                 | 257             |                 | 476 | kHz              |
| I <sub>PGM</sub> Supply current from DV <sub>CC</sub> during program         |                       | 2.5 V/3.6V      |                 | 3               | 5   | mA               |
| I <sub>ERASE</sub> Supply current from DV <sub>CC</sub> during erase         |                       | 2.5 V/3.6V      |                 | 3               | 7   | mA               |
| t <sub>CPT</sub> Cumulative program time                                     | see Note 1            | 2.5 V/3.6V      |                 |                 | 10  | ms               |
| t <sub>CMErase</sub> Cumulative mass erase time                              | see Note 2            | 2.5 V/3.6V      | 200             |                 |     | ms               |
| Program/Erase endurance                                                      |                       |                 | 10 <sup>4</sup> | 10 <sup>5</sup> |     | cycles           |
| t <sub>Retention</sub> Data retention duration                               | T <sub>J</sub> = 25°C |                 | 100             |                 |     | years            |
| t <sub>Word</sub> Word or byte program time                                  | see Note 3            |                 |                 | 35              |     | t <sub>FTG</sub> |
| t <sub>Block, 0</sub> Block program time for 1 <sup>st</sup> byte or word    |                       |                 |                 | 30              |     |                  |
| t <sub>Block, 1-63</sub> Block program time for each additional byte or word |                       |                 |                 | 21              |     |                  |
| t <sub>Block, End</sub> Block program end-sequence wait time                 |                       |                 |                 | 6               |     |                  |
| t <sub>Mass Erase</sub> Mass erase time                                      |                       |                 |                 | 5297            |     |                  |
| t <sub>Seq Erase</sub> Segment erase time                                    |                       |                 |                 | 4819            |     |                  |

- NOTES: 1. The cumulative program time must not be exceeded when writing to a 64-byte flash block. This parameter applies to all programming methods: individual word/byte write and block write modes.
2. The mass erase duration generated by the flash timing generator is at least 11.1 ms ( = 5297x1/f<sub>FTG,max</sub> = 5297x1/476kHz). To achieve the required cumulative mass erase time the Flash Controller's mass erase operation can be repeated until this time is met. (A worst case minimum of 19 cycles are required).
3. These values are hardwired into the Flash Controller's state machine (t<sub>FTG</sub> = 1/f<sub>FTG</sub>).

### JTAG interface

| PARAMETER                                                               | TEST CONDITIONS | V <sub>CC</sub> | MIN | TYP | MAX | UNIT |
|-------------------------------------------------------------------------|-----------------|-----------------|-----|-----|-----|------|
| f <sub>TCK</sub> TCK input frequency                                    | See Note 1      | 2.2 V           | 0   |     | 5   | MHz  |
|                                                                         |                 | 3 V             | 0   |     | 10  | MHz  |
| R <sub>Internal</sub> Internal pull-up resistance on TMS, TCK, TDI/TCLK | See Note 2      | 2.2 V/ 3 V      | 25  | 60  | 90  | kΩ   |

- NOTES: 1. f<sub>TCK</sub> may be restricted to meet the timing requirements of the module selected.
2. TMS, TDI/TCLK, and TCK pull-up resistors are implemented in all versions.


### JTAG fuse (see Note 1)

| PARAMETER                                                           | TEST CONDITIONS       | V <sub>CC</sub> | MIN | MAX | UNIT |
|---------------------------------------------------------------------|-----------------------|-----------------|-----|-----|------|
| V <sub>CC(FB)</sub> Supply voltage during fuse-blow condition       | T <sub>A</sub> = 25°C |                 | 2.5 |     | V    |
| V <sub>FB</sub> Voltage level on TDI/TCLK for fuse-blow: F versions |                       |                 | 6   | 7   | V    |
| I <sub>FB</sub> Supply current into TDI/TCLK during fuse blow       |                       |                 |     | 100 | mA   |
| t <sub>FB</sub> Time to blow fuse                                   |                       |                 |     | 1   | ms   |

- NOTES: 1. Once the fuse is blown, no further access to the MSP430 JTAG/Test and emulation features is possible. The JTAG block is switched to bypass mode.

## APPLICATION INFORMATION

### Port P1 pin schematic: P1.0, input/output with Schmitt trigger



### Port P1 (P1.0) pin functions


| PIN NAME (P1.X) | X | FUNCTION       | CONTROL BITS / SIGNALS |            |         |          |
|-----------------|---|----------------|------------------------|------------|---------|----------|
|                 |   |                | CAPD.x                 | P1DIR.x    | P1SEL.x | P1SEL2.x |
| P1.0/TA0/OA0RFB | 0 | P1.x (I/O)     | 0                      | I: 0, O: 1 | 0       | 0        |
|                 |   | Timer_A3.CCI0A | 0                      | 0          | 1       | 0        |
|                 |   | Timer_A3.TA0   | 0                      | 1          | 1       | 0        |
|                 |   | OA0RFB         | x                      | x          | 1       | 1        |

MSP430FG47x  
MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

APPLICATION INFORMATION


Port P1 pin schematic: P1.1, input/output with Schmitt trigger



Port P1 (P1.1) pin functions

| PIN NAME (P1.X)         | X | FUNCTION       | CONTROL BITS / SIGNALS |            |         |          |
|-------------------------|---|----------------|------------------------|------------|---------|----------|
|                         |   |                | CAPD.x                 | P1DIR.x    | P1SEL.x | P1SEL2.x |
| P1.1/TA0/MCLK<br>OA1RFB | 1 | P1.x (I/O)     | 0                      | I: 0, O: 1 | 0       | 0        |
|                         |   | Timer_A3.CCI0A | 0                      | 0          | 1       | 0        |
|                         |   | Timer_A3.TA0   | 0                      | 1          | 1       | 0        |
|                         |   | OA1RFB         | x                      | 0          | 1       | 1        |
|                         |   | MCLK           | 0                      | 1          | 1       | 1        |

### Port P1 pin schematic: P1.2 input/output with Schmitt trigger




NOTES: 1. x: Don't care.

MSP430FG47x  
MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

APPLICATION INFORMATION

Port P1 pin schematic: P1.3, input/output with Schmitt trigger



Port P1 (P1.3) pin functions


| PIN NAME (P1.X)                  | X | FUNCTION   | CONTROL BITS / SIGNALS |            |         |                           |                          |
|----------------------------------|---|------------|------------------------|------------|---------|---------------------------|--------------------------|
|                                  |   |            | CAPD.x                 | P1DIR.x    | P1SEL.x | P1SEL2.x = 0<br>OAN (OA1) | P1SEL2.x = 0<br>SD16AE.x |
| P1.3/TBOUTH/<br>SVSOUT/A4+/OA1I3 | 3 | P1.x (I/O) | 0                      | I: 0, O: 1 | 0       | xx                        | 0                        |
|                                  |   | TBOUTH     | 0                      | 0          | 1       | xx                        | 0                        |
|                                  |   | SVSOUT     | 0                      | 1          | 1       | xx                        | 0                        |
|                                  |   | A4+        | x                      | x          | x       | xx                        | 1                        |
|                                  |   | OA1I3      | x                      | x          | x       | 10                        | 1                        |

NOTES: 1. x: Don't care.



**APPLICATION INFORMATION**

**Port P1 pin schematic: P1.4, input/output with Schmitt trigger**



**Port P1 (P1.4) pin functions**

| PIN NAME (P1.X)                    | X | FUNCTION   | CONTROL BITS / SIGNALS |            |         |                          |                           |                                       |
|------------------------------------|---|------------|------------------------|------------|---------|--------------------------|---------------------------|---------------------------------------|
|                                    |   |            | CAPD.x                 | P1DIR.x    | P1SEL.x | P1SEL2.x = 0<br>SD16AE.x | P1SEL2.x = 0<br>OAP (OA1) | P1SEL2.x = 0<br>DAC12OPS<br>(DAC12_1) |
| P1.4TBCLK/SMCLK/<br>A3-/OA1I0/DAC1 | 4 | P1.x (I/O) |                        | I: 0, O: 1 | 0       | 0                        | xx                        | 0                                     |
|                                    |   | TBCLK      |                        | 0          | 1       | 0                        | xx                        | 0                                     |
|                                    |   | SMCLK      |                        | 1          | 1       | 0                        | xx                        | 0                                     |
|                                    |   | A3-        |                        | x          | x       | 1                        | xx                        | 0                                     |
|                                    |   | OA1I0      |                        | x          | x       | 1                        | 00                        | 0                                     |
|                                    |   | DAC1       |                        | x          | x       | x                        | xx                        | 1                                     |


NOTES: 1. x: Don't care.

MSP430FG47x  
MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

APPLICATION INFORMATION

Port P1 pin schematic: P1.5, input/output with Schmitt trigger




Port P1 (P1.5) pin functions

| PIN NAME (P1.X)         | X | FUNCTION   | CONTROL BITS / SIGNALS |            |         |                          |
|-------------------------|---|------------|------------------------|------------|---------|--------------------------|
|                         |   |            | CAPD.x                 | P1DIR.x    | P1SEL.x | P1SEL2.x = 0<br>SD16AE.x |
| P1.5/TACLK/ACLK/<br>A3+ | 5 | P1.x (I/O) | 0                      | I: 0, O: 1 | 0       | 0                        |
|                         |   | TACLK      | 0                      | 0          | 1       | 0                        |
|                         |   | ACLK       | 0                      | 1          | 1       | 0                        |
|                         |   | A3+        | x                      | x          | x       | 1                        |

NOTES: 1. x: Don't care.

### Port P1 pin schematic: P1.6, input/output with Schmitt trigger



# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011


### Port P1 (P1.6) pin functions

| PIN NAME (P1.X)             | X | FUNCTION   | CONTROL BITS / SIGNALS |         |                        |                          |                           |                                       |
|-----------------------------|---|------------|------------------------|---------|------------------------|--------------------------|---------------------------|---------------------------------------|
|                             |   |            | P1DIR.x                | P1SEL.x | P1SEL2.x = 0<br>CAPD.x | P1SEL2.x = 0<br>SD16AE.x | P1SEL2.x = 0<br>OAP (OA0) | P1SEL2.x = 0<br>DAC12OPS<br>(DAC12_0) |
| P1.6/CA0/A2-/OA0I0/<br>DAC0 | 6 | P1.x (I/O) | I: 0, O: 1             | 0       | 0                      | 0                        | xx                        | 0                                     |
|                             |   | CA0        | x                      | x       | 1 or selected          | x                        | xx                        | x                                     |
|                             |   | A2-        | x                      | x       | x                      | 1                        | xx                        | x                                     |
|                             |   | OA0I0      | x                      | x       | x                      | x                        | 00                        | x                                     |
|                             |   | DAC0       | x                      | x       | x                      | x                        | xx                        | 1                                     |

NOTES: 1. x: Don't care.

**APPLICATION INFORMATION**

**Port P1 pin schematic: P1.7, input/output with Schmitt trigger**



**Port P1 (P1.7) pin functions**

| PIN NAME (P1.X) | X | FUNCTION   | CONTROL BITS / SIGNALS |         |                        |                          |
|-----------------|---|------------|------------------------|---------|------------------------|--------------------------|
|                 |   |            | P1DIR.x                | P1SEL.x | P1SEL2.x = 0<br>CAPD.x | P1SEL2.x = 0<br>SD16AE.x |
| P1.7/CA1/A2+    | 7 | P1.x (I/O) | I: 0, O: 1             | 0       | 0                      | 0                        |
|                 |   | CA1        | x                      | x       | 1 or selected          | x                        |
|                 |   | A2+        | x                      | x       | x                      | 1                        |

NOTES: 1. x: Don't care.


MSP430FG47x

MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

APPLICATION INFORMATION

Port P2 pin schematic: P2.0 to P2.1, input/output with Schmitt trigger




Port P2 (P2.0 to P2.1) pin functions

| PIN NAME (P2.X) | X | FUNCTION       | CONTROL BITS / SIGNALS |         |       |
|-----------------|---|----------------|------------------------|---------|-------|
|                 |   |                | P2DIR.x                | P2SEL.x | LCDS0 |
| P2.0/TA2/S1     | 0 | P2.x (I/O)     | I: 0, O: 1             | 0       | 0     |
|                 |   | Timer_A3.CCI2A | 0                      | 1       | 0     |
|                 |   | Timer_A3.TA2   | 1                      | 1       | 0     |
|                 |   | S1             | x                      | x       | 1     |
| P2.1/TB0/S0     | 1 | P2.x (I/O)     | I: 0, O: 1             | 0       | 0     |
|                 |   | Timer_B3.CCI0A | 0                      | 1       | 0     |
|                 |   | Timer_B3.TB0   | 1                      | 1       | 0     |
|                 |   | S0             | x                      | x       | 1     |

NOTES: 1. x: Don't care.

## APPLICATION INFORMATION

### Port P2 pin schematic: P2.2 to P2.3, input/output with Schmitt trigger



### Port P2 (P2.2 to P2.3) pin functions


| PIN NAME (P2.X) | X | FUNCTION       | CONTROL BITS / SIGNALS |         |
|-----------------|---|----------------|------------------------|---------|
|                 |   |                | P2DIR.x                | P2SEL.x |
| P2.2/TB1        | 2 | P2.x (I/O)     | I: 0, O: 1             | 0       |
|                 |   | Timer_B3.CCI1A | 0                      | 1       |
|                 |   | Timer_B3.TB1   | 1                      | 1       |
| P2.3/TB2        | 3 | P2.x (I/O)     | I: 0, O: 1             | 0       |
|                 |   | Timer_B3.CCI2A | 0                      | 1       |
|                 |   | TimerB3.TB2    | 1                      | 1       |

MSP430FG47x  
MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

APPLICATION INFORMATION

Port P2 pin schematic: P2.4 and P2.5, input/output with Schmitt trigger



Port P2 (P2.4 and P2.5) pin functions


| PIN NAME (P2.X)           | X | FUNCTION                       | CONTROL BITS / SIGNALS |         |
|---------------------------|---|--------------------------------|------------------------|---------|
|                           |   |                                | P2DIR.x                | P2SEL.x |
| P2.4/UCA0TXD/<br>UCA0SIMO | 4 | P2.x (I/O)                     | I: 0, O: 1             | 0       |
|                           |   | UCA0TXD/UCA0SIMO (see Notes 2) | x                      | 1       |
| P2.5/UCA0RXD/<br>UCA0SOMI | 5 | P2.x (I/O)                     | I: 0, O: 1             | 0       |
|                           |   | UCA0RXD/UCA0SOMI (see Notes 2) | x                      | 1       |

NOTES: 1. x: Don't care.  
2. The pin direction is controlled by the USCI module.



APPLICATION INFORMATION

Port P2 pin schematic: P2.6 and P2.7, input/output with Schmitt trigger



Port P2 (P2.6 and P2.7) pin functions

| PIN NAME (P2.X) | X | FUNCTION        | CONTROL BITS / SIGNALS |         |       |
|-----------------|---|-----------------|------------------------|---------|-------|
|                 |   |                 | P2DIR.x                | P2SEL.x | LCDS0 |
| P2.6/CAOUT/S2   | 6 | P2.x (I/O)      | I: 0, O: 1             | 0       | 0     |
|                 |   | CAOUT           | 1                      | 1       | 0     |
|                 |   | S2              | x                      | x       | 1     |
| P2.7/S3         | 7 | P2.x (I/O)      | I: 0, O: 1             | 0       | 0     |
|                 |   | V <sub>ss</sub> | 1                      | 1       | 0     |
|                 |   | S3              | x                      | x       | 1     |

NOTES: 1. x: Don't care.


# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D - OCTOBER 2008 - REVISED MARCH 2011

## APPLICATION INFORMATION

### Port P3 pin schematic: P3.0 and P3.3, input/output with Schmitt trigger



### Port P3 (P3.0 and P3.3) pin functions


| PIN NAME (P3.X)          | X | FUNCTION                     | CONTROL BITS / SIGNALS |         |
|--------------------------|---|------------------------------|------------------------|---------|
|                          |   |                              | P3DIR.x                | P3SEL.x |
| P3.0/UCB0STE/<br>UCA0CLK | 0 | P3.x (I/O)                   | I: 0, O: 1             | 0       |
|                          |   | UCB0STE/UCA0CLK (see Note 2) | x                      | 1       |
| P3.3/UCB0CLK/<br>UCA0STE | 3 | P3.x (I/O)                   | I: 0, O: 1             | 0       |
|                          |   | UCB0CLK/UCA0STE (see Note 2) | x                      | 1       |

NOTES: 1. x: Don't care.

2. The pin direction is controlled by the USCI module.

## APPLICATION INFORMATION

### Port P3 pin schematic: P3.1 and P3.2, input/output with Schmitt trigger



### Port P3 (P3.1 and P3.2) pin functions

| PIN NAME (P3.X)               | X | FUNCTION                             | CONTROL BITS / SIGNALS |         |        |
|-------------------------------|---|--------------------------------------|------------------------|---------|--------|
|                               |   |                                      | P3DIR.x                | P3SEL.x | LCDS24 |
| P3.1/UCB0SIMO/<br>UCB0SDA/S26 | 1 | P3.x (I/O)                           | I: 0, O: 1             | 0       | 0      |
|                               |   | UCB0SIMO/UCB0SDA (see Notes 2 and 3) | x                      | 1       | 0      |
|                               |   | S26                                  | x                      | x       | 1      |
| P3.2/UCB0SOMI/<br>UCB0SCL/S27 | 2 | P3.x (I/O)                           | I: 0, O: 1             | 0       | 0      |
|                               |   | UCB0SOMI/UCB0SCL (see Notes 2 and 3) | x                      | 1       | 0      |
|                               |   | S27                                  | x                      | x       | 1      |


NOTES: 1. x: Don't care.  
2. The pin direction is controlled by the USCI module.  
3. In case the I2C functionality is selected the output drives only the logical 0 to  $V_{SS}$  level.

MSP430FG47x  
MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

APPLICATION INFORMATION

Port P3 pin schematic: P3.4 to P3.7, input/output with Schmitt trigger




Port P3 (P3.4 to P3.7) pin functions

| PIN NAME (P3.X) | X | FUNCTION   | CONTROL BITS / SIGNALS |         |         |
|-----------------|---|------------|------------------------|---------|---------|
|                 |   |            | P3DIR.x                | P3SEL.x | LCD S28 |
| P3.4/S28        | 4 | P3.x (I/O) | I: 0, O: 1             | 0       | 0       |
|                 |   | S28        | x                      | x       | 1       |
| P3.5/S29        | 5 | P3.x (I/O) | I: 0, O: 1             | 0       | 0       |
|                 |   | S29        | x                      | x       | 1       |
| P3.6/S30        | 6 | P3.x (I/O) | I: 0, O: 1             | 0       | 0       |
|                 |   | S30        | x                      | x       | 1       |
| P3.7/S31        | 7 | P3.x (I/O) | I: 0, O: 1             | 0       | 0       |
|                 |   | S31        | x                      | x       | 1       |

NOTES: 1. x: Don't care.

## APPLICATION INFORMATION

### Port P4 pin schematic: P4.0 to P4.7, input/output with Schmitt trigger



### Port P4 (P4.0 and P4.7) pin functions

| PIN NAME (P4.X) | X | FUNCTION   | CONTROL BITS / SIGNALS |         |           |
|-----------------|---|------------|------------------------|---------|-----------|
|                 |   |            | P4DIR.x                | P4SEL.x | LCDS4/8   |
| P4.0/S11        | 0 | P4.x (I/O) | I: 0, O: 1             | 0       | 0 (LCDS8) |
|                 |   | S11        | x                      | x       | 1 (LCDS8) |
| P4.1/S10        | 1 | P4.x (I/O) | I: 0, O: 1             | 0       | 0 (LCDS8) |
|                 |   | S10        | x                      | x       | 1 (LCDS8) |
| P4.2/S9         | 2 | P4.x (I/O) | I: 0, O: 1             | 0       | 0 (LCDS8) |
|                 |   | S9         | x                      | x       | 1 (LCDS8) |
| P4.3/S8         | 3 | P4.x (I/O) | I: 0, O: 1             | 0       | 0 (LCDS8) |
|                 |   | S8         | x                      | x       | 1 (LCDS8) |
| P4.4/S7         | 4 | P4.x (I/O) | I: 0, O: 1             | 0       | 0 (LCDS4) |
|                 |   | S7         | x                      | x       | 1 (LCDS4) |
| P4.5/S6         | 5 | P4.x (I/O) | I: 0, O: 1             | 0       | 0 (LCDS4) |
|                 |   | S6         | x                      | x       | 1 (LCDS4) |
| P4.6/S5         | 6 | P4.x (I/O) | I: 0, O: 1             | 0       | 0 (LCDS4) |
|                 |   | S5         | x                      | x       | 1 (LCDS4) |
| P4.7/S4         | 7 | P4.x (I/O) | I: 0, O: 1             | 0       | 0 (LCDS4) |
|                 |   | S4         | x                      | x       | 1 (LCDS4) |

NOTES: 1. x: Don't care.


MSP430FG47x

MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

APPLICATION INFORMATION

Port P5 pin schematic: P5.0 and P5.1, input/output with Schmitt trigger




Port P5 (P5.0 and P5.1) pin functions

| PIN NAME (P5.X) | X | FUNCTION   | CONTROL BITS / SIGNALS |         |        |
|-----------------|---|------------|------------------------|---------|--------|
|                 |   |            | P5DIR.x                | P5SEL.x | LCDS20 |
| P5.0/S20        | 0 | P5.x (I/O) | I: 0, O: 1             | 0       | 0      |
|                 |   | S20        | x                      | x       | 1      |
| P5.1/S21        | 1 | P5.x (I/O) | I: 0, O: 1             | 0       | 0      |
|                 |   | S21        | x                      | x       | 1      |

NOTES: 1. x: Don't care.

## APPLICATION INFORMATION

### Port P5 pin schematic: P5.2 to P5.7, input/output with Schmitt trigger



### Port P5 (P5.2 to P5.7) pin functions

| PIN NAME (P5.X) | X | FUNCTION      | CONTROL BITS / SIGNALS |         |
|-----------------|---|---------------|------------------------|---------|
|                 |   |               | P5DIR.x                | P5SEL.x |
| P5.2/COM1       | 2 | P5.x (I/O)    | I: 0, O: 1             | 0       |
|                 |   | COM1          | x                      | 1       |
| P5.3/COM2       | 3 | P5.x (I/O)    | I: 0, O: 1             | 0       |
|                 |   | COM2          | x                      | 1       |
| P5.4/COM3       | 4 | P5.x (I/O)    | I: 0, O: 1             | 0       |
|                 |   | COM3          | x                      | 1       |
| P5.5/R23        | 5 | P5.x (I/O)    | I: 0, O: 1             | 0       |
|                 |   | R23           | x                      | 1       |
| P5.6/LCDREF/R13 | 6 | P5.x (I/O)    | I: 0, O: 1             | 0       |
|                 |   | R13 or LCDREF | x                      | 1       |
| P5.7/R03        | 7 | P5.x (I/O)    | I: 0, O: 1             | 0       |
|                 |   | R03           | x                      | 1       |


NOTES: 1. x: Don't care.

MSP430FG47x  
MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

APPLICATION INFORMATION

Port P6 pin schematic: P6.0 and P6.3, input/output with Schmitt trigger



Port P6 (P6.0 and P6.3) pin functions


| PIN NAME (P6.X) | X | FUNCTION   | CONTROL BITS / SIGNALS |         |
|-----------------|---|------------|------------------------|---------|
|                 |   |            | P6DIR.x                | P6SEL.x |
| P6.0/A0+/OA00   | 0 | P6.x (I/O) | I: 0, O: 1             | 0       |
|                 |   | A0+        | x                      | 1       |
|                 |   | OA00       | x                      | 1       |
| P6.3/A1+/OA10   | 3 | P6.x (I/O) | I: 0, O: 1             | 0       |
|                 |   | A1+        | x                      | 1       |
|                 |   | OA10       | x                      | 1       |

NOTES: 1. x: Don't care.



APPLICATION INFORMATION

Port P6 pin schematic: P6.1 and P6.4, input/output with Schmitt trigger



Port P6 (P6.1 and P6.4) pin functions

| PIN NAME (P6.X) | X | FUNCTION   | CONTROL BITS / SIGNALS |         |
|-----------------|---|------------|------------------------|---------|
|                 |   |            | P6DIR.x                | P6SEL.x |
| P6.1/A0-/OA0FB  | 1 | P6.x (I/O) | I: 0, O: 1             | 0       |
|                 |   | A0-        | x                      | 1       |
|                 |   | OA0FB      | x                      | 1       |
| P6.4/A1-/OA1FB  | 4 | P6.x (I/O) | I: 0, O: 1             | 0       |
|                 |   | A1-        | x                      | 1       |
|                 |   | OA1FB      | x                      | 1       |


NOTES: 1. x: Don't care.

MSP430FG47x  
MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

APPLICATION INFORMATION

Port P6 pin schematic: P6.2, P6.5 and P6.6, input/output with Schmitt trigger




Port P6 (P6.2, P6.5 and P6.6) pin functions

| PIN NAME (P6.X) | X | FUNCTION   | CONTROL BITS / SIGNALS |         |
|-----------------|---|------------|------------------------|---------|
|                 |   |            | P6DIR.x                | P6SEL.x |
| P6.2/OA0I1      | 2 | P6.x (I/O) | I: 0, O: 1             | 0       |
|                 |   | OA0I1      | x                      | 1       |
| P6.5/OA0I2      | 5 | P6.x (I/O) | I: 0, O: 1             | 0       |
|                 |   | OA0I2      | x                      | 1       |
| P6.6/OA1I1      | 6 | P6.x (I/O) | I: 0, O: 1             | 0       |
|                 |   | OA1I1      | x                      | 1       |

NOTES: 1. x: Don't care.

APPLICATION INFORMATION

Port P6 pin schematic: P6.7, input/output with Schmitt trigger



Port P6 (P6.7) pin functions

| PIN NAME (P6.X)  | X | FUNCTION   | CONTROL BITS / SIGNALS |         |      |
|------------------|---|------------|------------------------|---------|------|
|                  |   |            | P6DIR.x                | P6SEL.x | VLDx |
| P6.7/OA1I2/SVSIN | 7 | P6.x (I/O) | I: 0, O: 1             | 0       | x    |
|                  |   | OA1I2      | x                      | 1       | x    |
|                  |   | SVSIN      | x                      | 1       | 1111 |


NOTES: 1. x: Don't care.

MSP430FG47x  
MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

APPLICATION INFORMATION


Segment pin schematic: Sx, dedicated Segment Pins



Sx pin functions

| PIN NAME | X  | FUNCTION | CONTROL BITS / SIGNALS |
|----------|----|----------|------------------------|
|          |    |          | LCDSy                  |
| Sx       | 12 | Sx       | 1 (LCDS12)             |
|          |    | 3-state  | 0 (LCDS12)             |
| Sx       | 13 | Sx       | 1 (LCDS12)             |
|          |    | 3-state  | 0 (LCDS12)             |
| Sx       | 14 | Sx       | 1 (LCDS12)             |
|          |    | 3-state  | 0 (LCDS12)             |
| Sx       | 15 | Sx       | 1 (LCDS12)             |
|          |    | 3-state  | 0 (LCDS12)             |
| Sx       | 16 | Sx       | 1 (LCD16)              |
|          |    | 3-state  | 0 (LCD16)              |
| Sx       | 17 | Sx       | 1 (LCD16)              |
|          |    | 3-state  | 0 (LCD16)              |
| Sx       | 18 | Sx       | 1 (LCD16)              |
|          |    | 3-state  | 0 (LCD16)              |
| Sx       | 19 | Sx       | 1 (LCDS16)             |
|          |    | 3-state  | 0 (LCDS16)             |
| Sx       | 22 | Sx       | 1 (LCDS20)             |
|          |    | 3-state  | 0 (LCDS20)             |
| Sx       | 23 | Sx       | 1 (LCDS20)             |
|          |    | 3-state  | 0 (LCDS20)             |
| Sx       | 24 | Sx       | 1 (LCDS24)             |
|          |    | 3-state  | 0 (LCDS24)             |
| Sx       | 25 | Sx       | 1 (LCDS24)             |
|          |    | 3-state  | 0 (LCDS24)             |

Segment pin schematic: COM0, dedicated COM0 pin




Sx pin functions

| PIN NAME | X | FUNCTION |
|----------|---|----------|
| COM0     | - | COM0     |

## APPLICATION INFORMATION

JTAG pins: TMS, TCK, TDI/TCLK, TDO/TDI, input/output with Schmitt trigger



During Programming Activity and During Blowing of the Fuse, Pin TDO/TDI Is Used to Apply the Test Input Data for JTAG Circuitry

### JTAG fuse check mode

For details on the JTAG fuse check mode, see the *MSP430 Memory Programming User's Guide* (SLAU265) chapter "Fuse Check and Reset of the JTAG State Machine (TAP Controller)".

# MSP430FG47x

## MIXED SIGNAL MICROCONTROLLER

SLAS580D – OCTOBER 2008 – REVISED MARCH 2011

---

### Data Sheet Revision History

| LITERATURE<br>NUMBER | SUMMARY                                                                                                                                           |
|----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|
| SLAS580              | Product Preview release                                                                                                                           |
| SLAS580A             | Changes throughout to update Product Preview                                                                                                      |
| SLAS580B             | Production Data release                                                                                                                           |
| SLAS580C             | In recommended operating conditions table, changed maximum LFXT1 crystal frequency, $f_{(LFXT1)}$ with XT1 selected from 8 MHz to 6 MHz (page 24) |
| SLAS580D             | Changed limits on $t_{d(SVSON)}$ parameter (page 32)<br>Corrected measurement pin name for "Duty cycle, LF mode" parameter (page 37)              |



**PACKAGING INFORMATION**

| Orderable Device | Status <sup>(1)</sup> | Package Type               | Package Drawing | Pins | Package Qty | Eco Plan <sup>(2)</sup>    | Lead/<br>Ball Finish | MSL Peak Temp <sup>(3)</sup> | Samples<br>(Requires Login) |
|------------------|-----------------------|----------------------------|-----------------|------|-------------|----------------------------|----------------------|------------------------------|-----------------------------|
| MSP430FG477IPN   | ACTIVE                | LQFP                       | PN              | 80   | 119         | Green (RoHS<br>& no Sb/Br) | CU NIPDAU            | Level-3-260C-168 HR          |                             |
| MSP430FG477IPNR  | ACTIVE                | LQFP                       | PN              | 80   | 1000        | Green (RoHS<br>& no Sb/Br) | CU NIPDAU            | Level-3-260C-168 HR          |                             |
| MSP430FG477IZQW  | ACTIVE                | BGA<br>MICROSTAR<br>JUNIOR | ZQW             | 113  | 250         | Green (RoHS<br>& no Sb/Br) | SNAGCU               | Level-3-260C-168 HR          |                             |
| MSP430FG477IZQWR | ACTIVE                | BGA<br>MICROSTAR<br>JUNIOR | ZQW             | 113  | 2500        | Green (RoHS<br>& no Sb/Br) | SNAGCU               | Level-3-260C-168 HR          |                             |
| MSP430FG478IPN   | ACTIVE                | LQFP                       | PN              | 80   | 119         | Green (RoHS<br>& no Sb/Br) | CU NIPDAU            | Level-3-260C-168 HR          |                             |
| MSP430FG478IPNR  | ACTIVE                | LQFP                       | PN              | 80   | 1000        | Green (RoHS<br>& no Sb/Br) | CU NIPDAU            | Level-3-260C-168 HR          |                             |
| MSP430FG478IZQW  | ACTIVE                | BGA<br>MICROSTAR<br>JUNIOR | ZQW             | 113  | 250         | Green (RoHS<br>& no Sb/Br) | SNAGCU               | Level-3-260C-168 HR          |                             |
| MSP430FG478IZQWR | ACTIVE                | BGA<br>MICROSTAR<br>JUNIOR | ZQW             | 113  | 2500        | Green (RoHS<br>& no Sb/Br) | SNAGCU               | Level-3-260C-168 HR          |                             |
| MSP430FG479IPN   | ACTIVE                | LQFP                       | PN              | 80   | 119         | Green (RoHS<br>& no Sb/Br) | CU NIPDAU            | Level-3-260C-168 HR          |                             |
| MSP430FG479IPNR  | ACTIVE                | LQFP                       | PN              | 80   | 1000        | Green (RoHS<br>& no Sb/Br) | CU NIPDAU            | Level-3-260C-168 HR          |                             |
| MSP430FG479IZQW  | ACTIVE                | BGA<br>MICROSTAR<br>JUNIOR | ZQW             | 113  | 250         | Green (RoHS<br>& no Sb/Br) | SNAGCU               | Level-3-260C-168 HR          |                             |
| MSP430FG479IZQWR | ACTIVE                | BGA<br>MICROSTAR<br>JUNIOR | ZQW             | 113  | 2500        | Green (RoHS<br>& no Sb/Br) | SNAGCU               | Level-3-260C-168 HR          |                             |

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

---

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.


**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



## ZQW (S-PBGA-N113)


## PLASTIC BALL GRID ARRAY



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Falls within JEDEC MO-225
  - D. This is a lead-free solder ball design.

## PN (S-PQFP-G80)

## PLASTIC QUAD FLATPACK



- NOTES: A. All linear dimensions are in millimeters.  
 B. This drawing is subject to change without notice.  
 C. Falls within JEDEC MS-026

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

|                             |                                                                    |
|-----------------------------|--------------------------------------------------------------------|
| Audio                       | <a href="http://www.ti.com/audio">www.ti.com/audio</a>             |
| Amplifiers                  | <a href="http://amplifier.ti.com">amplifier.ti.com</a>             |
| Data Converters             | <a href="http://dataconverter.ti.com">dataconverter.ti.com</a>     |
| DLP® Products               | <a href="http://www.dlp.com">www.dlp.com</a>                       |
| DSP                         | <a href="http://dsp.ti.com">dsp.ti.com</a>                         |
| Clocks and Timers           | <a href="http://www.ti.com/clocks">www.ti.com/clocks</a>           |
| Interface                   | <a href="http://interface.ti.com">interface.ti.com</a>             |
| Logic                       | <a href="http://logic.ti.com">logic.ti.com</a>                     |
| Power Mgmt                  | <a href="http://power.ti.com">power.ti.com</a>                     |
| Microcontrollers            | <a href="http://microcontroller.ti.com">microcontroller.ti.com</a> |
| RFID                        | <a href="http://www.ti-rfid.com">www.ti-rfid.com</a>               |
| RF/IF and ZigBee® Solutions | <a href="http://www.ti.com/lprf">www.ti.com/lprf</a>               |

### Applications

|                               |                                                                                          |
|-------------------------------|------------------------------------------------------------------------------------------|
| Communications and Telecom    | <a href="http://www.ti.com/communications">www.ti.com/communications</a>                 |
| Computers and Peripherals     | <a href="http://www.ti.com/computers">www.ti.com/computers</a>                           |
| Consumer Electronics          | <a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>                   |
| Energy and Lighting           | <a href="http://www.ti.com/energy">www.ti.com/energy</a>                                 |
| Industrial                    | <a href="http://www.ti.com/industrial">www.ti.com/industrial</a>                         |
| Medical                       | <a href="http://www.ti.com/medical">www.ti.com/medical</a>                               |
| Security                      | <a href="http://www.ti.com/security">www.ti.com/security</a>                             |
| Space, Avionics and Defense   | <a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a> |
| Transportation and Automotive | <a href="http://www.ti.com/automotive">www.ti.com/automotive</a>                         |
| Video and Imaging             | <a href="http://www.ti.com/video">www.ti.com/video</a>                                   |
| Wireless                      | <a href="http://www.ti.com/wireless-apps">www.ti.com/wireless-apps</a>                   |

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated