

ATUM-32/8-0-STK Product Details



ATUM-32/8-0-STK

TE Internal Number: 4951522003



Heat Shrink Tubing

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Heat Shrinkable Tubing
- Product Name = ATUM
- Product Source = U.K., U.S.
- Semiflexible
- Thin Wall Style

Documentation & Additional Information	
Product Drawings: • None Available Catalog Pages/Data Sheets: • RAYCHEM_TUBING_CATALOG_SECT1_PRODUCTS_A-H (PDF, English) Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available	Related Products: • Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Product Type = Heat Shrinkable Tubing • Color = Black Electrical Characteristics: • Product Source = U.K., U.S. • Recovered ID, Max. (mm [in]) = 8.00 [0.315] • Product Use = Cable Breakouts, Cable Ends, Connector-to-Cable Transitions, Electronic Components, Harnesses, Wire Breakouts, Wire Splices Dimensions: • Expanded ID, Min. (mm [in]) = 32.00 [1.260] • Cut Length (mm [in]) = 1220.00 [48.068] Body Features: • Product Name = ATUM • Pliancy = Semiflexible • Wall Style = Thin • Wall Type = Dual • Lining Type = Adhesive • Material = Crosslinked Polyolefin • Shrink Ratio = 4:1 • Fluid Type = Aviation Fuel, Brake Fluid, Chemicals/Solvents, Hydraulic Fluid, Lubricating Oil, Water • Resistant To = Fluids, Mechanical Damage, Strain • Wall Thickness - Full Recovery (Nominal) (mm [in]) = 2.54 [0.100] Housing Features: • Material Systems = No	Industry Standards: • Government/Industry Qualification = No • Flammability Rating Type = Flame-Retardant • UL Rating = Recognized • CSA Certified = No • Approved Standards = UL E85381 • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant Environmental: • Fluid Resistance = Moisture, Splash Protection • Operating Temperature (°C) = -55 - +110 Conditions for Usage: • Full Recovery Temperature (°C) = 110 • Shrink Temperature, Min. (°C) = 80 • High Temperature Compatible = No Operation/Application: • Application = Cable Jacket Repair Sleeve, Cable Jacketing, Insulation and Protection, Sealing • Emission Free = No Packaging Features: • Packaging Method = Stick Other: • Brand = Raychem