


*** UNCONTROLLED DOCUMENT * FOR REFERENCE ONLY**

Steward



CORE DIMENSIONS				
UNCOATED CORE			40T0501-100	
	MM	INCHES	MM	INCHES
OD	12.70	(.500)	± 0.38	(.015)
ID	7.14	(.281)	± 0.38	(.015)
TH	6.35	(.250)	± 0.18	(.007)
EPOXY COATING			40T0501-10H	
OD	13.84	(.545)	max.	
ID	5.99	(.236)	min.	
TH	7.29	(.287)	max.	

WEIGHT / K 2.6840 KGS 5.9172 LBS
INITIAL PERMEABILITY **10000**

ELECTRICAL SPECIFICATION								
	MIN TOL.	MIN (μH)	NOM (μH)	MAX (μH)	MAX TOL.	FREQ. (kHz)	VOLT. (V)	TURNS
L1	(-30.0%)	5.123	7.318	9.514	(+30.0%)	100	≤ .0076	1
L2	(-30.0%)	512.3	731.8	951.4	(+30.0%)	100	≤ .0763	10
Q		4.0	-	-	-	100	≤ .0076	1

COATING SPECIFICATIONS					
		Max. Coating Thickness (mm)	Min. DLB VAC	Min. DLB VDC	TEST FORCE (LB)
40T0501-10H	EPOXY	0.76	1000	1333	1.34

Steward

THIS DOCUMENT CONTAINS INFORMATION WHICH IS PROPRIETARY TO STEWARD. NO PRODUCTION OR PUBLICATION OF THIS DOCUMENT IN WHOLE OR IN PART SHALL BE MADE WITHOUT WRITTEN AUTHORIZATION FROM STEWARD.

Date:	01/05/2006	DWG #:	40T0501-10H-D	Title:		REV:	
Drawn By:	TMB			40T0501-10H		D	

REV	Description	ECN #	Date	INT
D	Change coating to Epoxy		01/05/2006	TMB