



Heavy-Wall Heat-Shrinkable Tubing

T&B Catalog Number:

HS6-1-25

UPC Number:

78621077607

Status:

Active

Description:

Heavy-Wall Heat-Shrinkable Tubing for Cable Range 6 - 2 AWG, Expanded Dia. 0.75 in., Length 25 feet reel, rated for 600V, 90 degree continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

Features

Made of thermally stabilized cross-linked polyolefin, enabling a recovered wall thickness greater than that of the cable jacket replaced.

Withstands severe mechanical requirements of U.R.D., submersible, and direct burial installations.

General

Style	HS Series - 25 ft. Roll
Color	Black
Temperature Range	-55°C - 110°C
Shrink Ratio	3:1

Dimension Information

Length (feet)	25
Minimum Expanded I.D. (inches)	0.75
Maximum Recovered I.D. (inches)	0.24
Nominal Recovered Wall (inches)	0.09
Cable Range	6 - 2 AWG

Specifications

Shrink Temperature	120°C
Voltage Rating	600V

Packaging

T&B Order Multiple	1
Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	320 lbs. per 100

Application Support

MSDS Number	msds-0012-tb2msds-0127-tb2
T&B Sales Drawings	wsd-000473
Specifications	Available on Website
Overview	Available on Website

Notes

Not supplied with factory-applied sealant.

Order by reel, not by feet. 25 feet reels not supplied with factory applied sealant.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com