

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19

© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.



| MOD | LOC | DIST | P | F | REVISIONS |     |                      |         |      |
|-----|-----|------|---|---|-----------|-----|----------------------|---------|------|
|     |     |      |   |   | ZONE      | LTR | DESCRIPTION          | DATE    | APPD |
|     | GP  | 00   |   |   |           | K   | REV PER OUE0-0037-01 | 17OCT01 | JR   |
|     |     |      |   |   |           |     |                      |         |      |

D

C

B

A



- 1 TO PREVENT THREAD STRIPPING, SCREW TORQUE SHOULD NOT EXCEED 9 IN LBS.
- 2 TAP HOLE IS 6-32UNC-2B, TWO MIN THREADS.
- 3 PACKAGED BULK.
- 4 PACKAGED INDIVIDUALLY.

|           |   |                           |       |         |
|-----------|---|---------------------------|-------|---------|
| OBSOLETE  | 4 | YES                       | YES   | 55557-5 |
|           | 3 | YES                       | YES   | 55557-4 |
|           | 3 | YES                       | NO    | 55557-3 |
| OBSOLETE  | - | NO                        | YES   | 55557-2 |
|           | - | NO                        | NO    | 55557-1 |
| PACKAGING |   | HOUSING AND TAP ASSEMBLED | SCREW | PART NO |

.050±.005 DIA

SECTION A-A

SCALE 10:1

10 PLACES

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON:  
2 PLC DEC ±  
3 PLC DEC ± .010  
ANGLES ±

MATERIAL  
HOUSING: NYLON  
TAP: COPPER ALLOY 725, .025 THICK

FINISH  
TAP: .000150 TIN-LEAD OVER .000050 NICKEL

DR J. McCLINTON 1/11/88  
CHK R. STONE 1/11/88  
APPD M. GALLOWAY 1/15/88  
APPD M. GALLOWAY 1/15/88  
PRODUCT SPEC  
APPLICATION SPEC  
WEIGHT

AMP INCORPORATED  
Harrisburg, Pa. 17105

TAP ASSEMBLY, POWER DISTRIBUTION

SIZE B FSCM NO 00779 DRAWING NO 55557  
SCALE 4:1 SHEET 1 OF 1