


VIEW B ROTATED 180°	
POST-FEED 40 mm STROKE	POST-FEED 30 mm STROKE
	
LEADMAKER OR BENCH G	K TERMINATOR BENCH MACHINE



		-77-71		-1		PART NO		DESCRIPTION		ITEM NO	
						←		REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)			
QTY REQD PER ASSY											
		DIMENSIONS: mm [INCHES]		MATL		HT TR		FIN			
		DO NOT SCALE PRINT.		-		-		-		-	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DR 12MAY04		APP 12MAY04		-		-	
		1 PLC DEC ±-		L.LOFHOUSE		F.BACHURST		-		-	
		2 PLC DEC ±-		CHK -		REL 12JUL04		-		-	
		3 PLC DEC ±-				L.LOFHOUSE		-		-	
		ANGLES ±-						AMP		Tyco Electronics Harrisburg, PA 17105-3608	
		SURF TEXTURE: ✓		NAME		END FEED HD-I APPLICATOR				MACHINE REF HD-I APPL	
LJL JUL04		REMOVE BURRS, BREAK SHARP EDGES 0.38 MAX		SCALE		D		DWG NO		1339740	
APP DATE				-						SHEET 1 OF 1	
		CASE CODE		00779		CUSTOMER AND ASSEMBLY DRAWING				RESTRICTED TO -	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1339740-1](#)