


Surface Mount, Molded Inductor



STANDARD ELECTRICAL SPECIFICATIONS						
IND. (μH)	TOL.	Q MIN.	TEST FREQ. L & Q (MHz)	SELF-RESONANT FREQ. MIN. (MHz)	DCR MAX. (Ohms)	RATED* DC CURRENT (mA)
0.010	± 20 %	30	50.0	1000	0.13	734
0.012	± 20 %	30	50.0	1000	0.14	707
0.015	± 20 %	30	50.0	1000	0.16	661
0.018	± 20 %	30	50.0	1000	0.18	624
0.022	± 20 %	30	50.0	1000	0.20	592
0.027	± 20 %	30	50.0	1000	0.22	564
0.033	± 20 %	30	50.0	1000	0.24	540
0.039	± 20 %	30	50.0	1000	0.27	530
0.047	± 20 %	30	50.0	1000	0.30	483
0.056	± 20 %	30	50.0	1000	0.33	470
0.068	± 20 %	30	50.0	1000	0.36	450
0.082	± 20 %	30	50.0	900	0.40	450
0.10	± 20 %	30	50.0	700	0.44	450
0.12	± 20 %	30	25.2	500	0.22	584
0.15	± 20 %	30	25.2	450	0.25	548
0.18	± 20 %	30	25.2	400	0.28	518
0.22	± 20 %	30	25.2	350	0.32	484
0.27	± 20 %	30	25.2	320	0.36	456
0.33	± 20 %	30	25.2	300	0.40	453
0.39	± 20 %	30	25.2	250	0.45	450
0.47	± 20 %	30	25.2	220	0.50	450
0.56	± 20 %	30	25.2	180	0.55	450
0.68	± 20 %	30	25.2	160	0.60	450
0.82	± 20 %	30	25.2	140	0.67	450
1.0	± 10 %	30	7.96	120	0.70	400
1.2	± 10 %	30	7.96	100	0.75	390
1.5	± 10 %	30	7.96	85.0	0.85	370
1.8	± 10 %	30	7.96	80.0	0.90	350
2.2	± 10 %	30	7.96	75.0	1.0	320
2.7	± 10 %	30	7.96	70.0	1.1	290
3.3	± 10 %	30	7.96	60.0	1.2	260
3.9	± 10 %	30	7.96	55.0	1.3	250
4.7	± 10 %	30	7.96	50.0	1.5	224
5.6	± 10 %	30	7.96	45.0	1.6	217
6.8	± 10 %	30	7.96	40.0	1.8	204
8.2	± 10 %	30	7.96	38.0	2.0	194
10.0	± 10 %	30	2.52	33.0	2.1	189
12.0	± 10 %	30	2.52	30.0	2.5	173
15.0	± 10 %	30	2.52	21.0	2.8	164
18.0	± 10 %	30	2.52	20.0	3.3	151
22.0	± 10 %	30	2.52	19.0	3.7	145
27.0	± 10 %	30	2.52	18.0	5.0	122
33.0	± 10 %	30	2.52	16.0	6.0	112
39.0	± 10 %	30	2.52	15.0	7.0	104
47.0	± 10 %	30	2.52	14.0	9.0	91
56.0	± 10 %	30	2.52	12.0	10.0	87
68.0	± 10 %	30	2.52	11.0	11.0	83
82.0	± 10 %	30	2.52	10.0	12.0	79
100.0	± 10 %	20	0.796	9.0	14.0	73
120.0	± 10 %	15	0.796	8.0	11.0	70
150.0	± 10 %	15	0.796	6.5	15.0	65
180.0	± 10 %	15	0.796	6.0	17.0	60
220.0	± 10 %	15	0.796	6.0	21.0	50

*Rated DC Current based on the maximum temperature rise, not to exceed 40 °C at + 85 °C ambient.

FEATURES

- Printed marking
- Compatible with vapor phase and infrared reflow soldering
- Molded construction provides superior strength and moisture resistance
- Tape and reel packaging for automatic handling, 2000/reel, EIA 481
- 100 % lead (Pb)-free and RoHS compliant



RoHS
COMPLIANT

ELECTRICAL SPECIFICATIONS

Inductance Range: 0.01 μH to 220 μH

Inductance Tolerance: ± 20 % for 0.01 μH to 0.82 μH
± 10 % for 1.0 μH to 220 μH standard. Special tolerances available


Temperature Range: - 55 °C to + 125 °C

Coilform Material: Non-magnetic for 0.01 μH to 0.10 μH
Powdered Iron for 0.12 μH to 100 μH. Ferrite for 120 μH through 220 μH

TEST EQUIPMENT

- H/P 4342A Q meter with Vishay Dale test fixture or equivalent
- H/P 4191A RF Impedance Analyzer (for SRF measurements)
- Wheatstone bridge

DIMENSIONS in inches [millimeters]



*Recommended spacing between components

PART MARKING

- Vishay Dale
- Inductance value
- Date code

DESCRIPTION				
IMC-1210 MODEL	10 μH INDUCTANCE VALUE	± 10 % INDUCTANCE TOLERANCE	ER PACKAGE CODE	e3 JEDEC LEAD (Pb)FREE STANDARD
GLOBAL PART NUMBER				
I	M	C	1	0
PRODUCT FAMILY			E	R
SIZE			1	0
PACKAGE CODE			1	0
INDUCTANCE VALUE			1	0
TOL.			K	



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[IMC1210 22 5%TR](#) [IMC1210 5.6 5%TR](#)