



DESCRIPTION: R/A .318" FEMALE ECONOMY D-SUB



	A	B	C	D
9	1.213	.984	.642	.030
	30.81	24.99	16.30	0.76
15	1.541	1.312	.971	.030
	39.14	33.32	24.65	0.76
25	2.088	1.852	1.512	.030
	53.04	47.04	38.40	0.76
37	2.729	2.500	2.157	.030
	69.32	63.50	54.80	0.76



SPECIFICATIONS:

MATERIALS:

- SHELL: STEEL, TIN PLATED
- INSULATOR: UL 94V-0 RATED BLACK GLASS-FILLED POLYESTER - UL 94V-0
- CONTACTS: BRASS OR PHOSPHOR BRONZE








ELECTRICALS:

- CURRENT RATING: 5 AMPS
- DIELECTRIC STRENGTH: 1000V AC RMS
- INSULATOR RESISTANCE: 1000 MOHMS MIN
- TEMPERATURE: -55°C TO +105°C

SERIES 182-XXX-21X-XX1
NUMBER OF CONTACTS _____
GENDER _____
2 = FEMALE
PC MOUNT _____
SHELL _____
0 = PLASTIC (9 & 25 POSITION ONLY)
2 = TIN SHELL
HARDWARE OPTIONS: _____
(SEE PAGE 2)
PLATING: _____
1 = GOLD FLASH

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS	DATE: 9-24-98
		CHECKED:	DATE:
	SCALE: 1:1		SHEET 1 OF 1
NorComp		DWG NO. 182-XXX-21X-XX1	

DESCRIPTION: R/A HARDWARE OPTIONS

	 METAL SHELL WITH INSIDE GROUND STRAPS	 METAL SHELL	 METAL SHELL FORK BOARD LOCKS
 .120" DIA. HOLE	16	43	N/A
 4-40 FLUSH INSERT	17	45	53 BOARD LOCKS IN HOLE
 4-40 HEX STANDOFF FEMALE SCREWLOCK	18	48	56 BOARD LOCKS IN HOLE
 4-40 ROUND STANDOFF FEMALE SCREWLOCK	N/A	N/A	N/A



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
WAYNE ROBBINS

CHECKED:
PAM JENKINS

SCALE:

DATE:
8-23-98

DATE:
8-24-98

SHEET
1 OF
1

REV
6

NorComp

DWG NO.
182 HARDWARE