



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG


## REVISIONS

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1906	A	RELEASED	EO	04/17/06	TL	05/25/06	HO	05/25/06



RoHS  
Compliant



## NOTES:

- 1.CABLE: SVT, 18AWG\*3C, COLOR: BLACK
- 2.RATED VOLTAGE/RATED CURRENT:125V/10A
- 3.TEMPERATURE: 75°C
- 4.SAFE REGULATIONS: UL

SPC TYPE No.	LENGTH (ft)	LENGTH (mm)
SPC19905	1	305±25.4
SPC19906	12	3658±50.8
SPC19907	6	1829±25.4

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

## TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
EKLAS ODISH	04/17/06
CHECKED BY:	DATE:
THOMAS LEE	05/25/06
APPROVED BY:	DATE:
HISHAM ODISH	05/25/06

## DRAWING TITLE:

AC ADAPTER CABLE, NEMA 5-15P to IEC 320-C14

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-721	TA-721.DWG	A

SCALE: NTS

U.O.M.: millimeters

SHEET: 1 OF 1