

DWG. NO.
SD-54729-009

F

D

V

C

B

DO NOT SCALE DRAWING

8

7

6

5

4

3

2

1

F




E

D

C

B

A



注記 NOTES

1. 材質 MATERIAL
ハウジング : 液晶ポリマーガラス充填, 黒色, UL94V-0
HOUSING : LIQUID CRYSTAL POLYMER GLASS FILLED
COLOR BLACK, UL94V-0
ターミナル : 燐青銅 (t=0.15)
TERMINAL : PHOSPHOR BRONZE (t=0.15)
2. メッキ仕様 PLATING
金メッキ 0.25マイクロメートル以上。(コンタクト部)
GOLD 0.25MICROMETER MINIMUM (CONTACT AREA)
金メッキ 0.4マイクロメートル以下。(テール部)
GOLD 0.4MICROMETER MAXIMUM (TAIL AREA)
下地メッキ : ニッケルメッキ 2.5マイクロメートル以上。
UNDER-PLATING : NICKEL 2.5MICROMETER MINIMUM

3. 嵌合相手 : 55559 シリーズ
MATES WITH : 55559 SERIES
4. テール平坦度は 0.1以下。
TAIL COPLANARITY TO BE 0.1 MAXIMUM
5. パターン書き込み禁止エリア
NO FOOT PRINT AREA.

5.5	7.7	54729-0241	24
3.5	5.7	54729-0161	16
B	A	MATERIAL NO.	CKT. NO.

EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	RELEASED/REVISED '04/02/04 EC NO. J2004-0314 DRWN: R. SUMIYA CHK: S. AIHARA APPR: M. SASAO	PROPOSED '01/04/11 EC NO. JC2001-0282 DRWN: M. HAYASHI CHK: T. ITO APPR: T. YAMAGUCHI	DESCRIPTION MATERIAL 材料 注記参照 SEE NOTES	FINISH 仕上付 注記参照 SEE NOTES	WIRE RANGE 適用電線範囲 —	INS. RANGE 被覆外径 —	GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差		SCALE —	DESIGN UNITS ☒ mm ☐ INCH	☒ THIRD ANGLE ☐ PROJECTION	☐ mm ☐ INCH	☐ mm ☐ INCH	☒ mm ONLY	REVISE ON CAD ONLY	
									10 UNDER 未満	±0.2	DRAWN BY & DATE M. HAYASHI '01/04/11		TITLE: 0.5 B-To-B Rec Hsg Assy (Hgt=2mm)					
									10 OVER 以上	30 UNDER 未満	±0.25	CHECKED BY & DATE T. ITO '01/04/11						
									30 OVER 以上	±0.3	APPROVED BY & DATE T. YAMAGUCHI '01/04/11		MOLEX INCORPORATED					
									CAD FILENAME 54729009.S01		MATERIAL NO. SEE CHART		DRAWING NO. SD-54729-009		SHEET NO. 1 OF 1		SIZE B	
									THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.									

8

7

6

5

4

3

2

EN-02J(097) MXJ-54