

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION

BELDEN
SENDING ALL THE RIGHT SIGNALS

1278R Coax - Mini Hi-Res Component Video Cable



For more Information
please call

1-800-Belden1



General Description:

25 AWG solid .018" tinned copper conductors, Gas-injected FHDPE insulation, Duobond® foil plus a tinned copper interlocked serve shield (95% coverage), PVC inner jacket, PVC jacket.

Usage (Overall)

Suitable Applications: RGB Projectors, LCD Projectors, Video Distribution, Component Video, Graphic Displays, Special Effects Editing, Animation, Video Post Production, Home Theater, Offices, Boardrooms, Auditoriums, Teleconferencing, Theaters

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
4	25	Solid	TC - Tinned Copper	.018

Total Number of Conductors:

4

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	0.074

Inner Shield

Inner Shield Material:

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Aluminum Foil-Polyester Tape Lightly bonded to dielectric	100
2		Interlocked Serve	TC - Tinned Copper	95

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (in.)
PVC - Polyvinyl Chloride	.114

Inner Jacket Color Code Chart:

Number	Color
1	Red
2	Green
3	Blue
4	Yellow

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.351 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +75°C

UL Temperature Rating: 60°C

Non-UL Temperature Rating: 75°C

Bulk Cable Weight: 55 lbs/1000 ft.

Max. Recommended Pulling Tension: 110 lbs.

Min. Bend Radius (Each Coax): 1.100 in.

Min. Bend Radius (Overall): 3.500 in.

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

1278R Coax - Mini Hi-Res Component Video Cable

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/UL Specification:	CMR
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
----------------	-----------------------

Suitability

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Inductance:

Inductance (μ H/ft)
.087

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
17.0

Nominal Velocity of Propagation:

VP (%)
80

Nominal Delay:

Delay (ns/ft)
1.24

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
34

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
5.4

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	0.52
5	1.17
50	3.7
100	4.9
200	6.7
400	9.5
750	13.4
900	15.0
1000	15.8
3000	31.2

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Operating Voltage - Non-UL:

Voltage

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

1278R Coax - Mini Hi-Res Component Video Cable

300 V RMS

Minimum Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
		5	850	20

Sweep Test

Sweep Testing: 5 - 850 MHz

Misc. Information (Overall)

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1278R B591000	1,000 FT	60.000 LB	BLACK, MATTE	C	4#25LDPE/GIFHLDPE SH FRPVCPVC
1278R B59500	500 FT	31.500 LB	BLACK, MATTE	C	4#25LDPE/GIFHLDPE SH FRPVCPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 08-15-2012

© 2014 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1278R B591000](#) [1278R B59500](#)