





FCIconnect.com

Copyright FCI




Part Number & Date Code Printing
PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



Pull Parts							
SHELL	A±0.38	B±0.12	C±0.10	D±0.25	PART NUMBER	LEAD FREE P/N	
09	30.81	24.99	16.96	16.21	D09S13A*GL00	D09S13A*GL00LF	
15	39.14	33.32	25.18	24.54	D15S13A*GL00	D15S13A*GL00LF	
25	53.03	47.04	39.12	38.25	D25S13A*GL00	D25S13A*GL00LF	
37	69.32	63.50	55.68	54.71	D37S13A*GL00	D37S13A*GL00LF	

4-200 MATING CYCLES
6-500 MATING CYCLES

GENERAL CHARACTERISTICS : SEE DRAWING C01-8646-0000

mat'l. code SEE.NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D-SUB												
ltr	ecn no		dr	date		tolerances unless otherwise specified				title SOCKET CONNECT.DELTA D RIGHT ANGLE WITH NUT,HARPON and metal plate.												
G	[05-0124]		JS	2005/07/27		angles linear	O.X ±0.1		scale 1:1													
H	[06-0074]		SK	2006/06/08			O.XX ±0.1															
J	ELXI-I-15060		AB	2013/06/25			O.XXX±0.1															
K	ELX-I-18948		AB	2014/09/29		dr	JOHN.SLEEBA		1994/10/14				dwg no				sheet 1 of 1				size	
						engr	ALIAS.BABU		2014/09/29				C01-8646-0165				A3					
						chr	MITHUN.PAUL		2014/09/29				type CUSTOMER Drawing									
						appd	BIJU.K.PAUL		2014/09/29													
sheet index		revision		K																		
		sheet		1																		