

D6L20U

200V 6A


FEATURES

- Low noise
- trr35ns
- Fully Isolated Molding

APPLICATION

- Switching power supply
- Free Wheel
- Home Appliances, Office Equipment
- Telecommunication, Factory Automation

OUTLINE DIMENSIONS



RATINGS

● Absolute Maximum Ratings (If not specified Tc=25°C)


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-40~150	°C
Operating Junction Temperature	Tj		150	°C
Maximum Reverse Voltage	VRM		200	V
Average Rectified Forward Current	Io	50Hz sine wave, R-load, Tc=118°C	6	A
Peak Surge Forward Current	IFSM	50Hz sine wave, Non-repetitive 1 cycle peak value, Tj=25°C	80	A
Dielectric Strength	Vdis	Terminals to case, AC 1 minute	1.5	kV
Mounting Torque	TOR	(Recommended torque: N·m)	0.5	N·m

● Electrical Characteristics (If not specified Tc=25°C)

Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	VF	IF=6A, Pulse measurement	Max 1.1	V
Reverse Current	IR	VR=VRM, Pulse measurement	Max 10	μA
Reverse Recovery Time	trr	IF=0.5A, IR=1A	Max 35	ns
Thermal Resistance	θjc	junction to case	Max 4.2	°C/W
	θjf	junction to heatsink (Reference value)	Max 5.7	


D6L20U

Forward Voltage




D6L20U

Forward Power Dissipation




$T_j = T_{jmax}$




D6L20U

Derating Curve




$$V_R = V_{RM}$$



D6L20U

Peak Surge Forward Capability



D6L20U Junction Capacitance

