

Thick Film Chip Resistors

Type: **ERJ XG, 1G, 2G, 3G, 6G, 8G, 14, 12, 12Z, 1T**



Features

- Small size and lightweight
- High reliability
Metal glaze thick film resistive element and three layers of electrodes
- Compatible with placement machines
Taping packaging available
- Suitable for both reflow and flow soldering
- Reference Standards
IEC 60115-8, JIS C 5201-8, EIAJ RC-2134B
- AEC-Q200 qualified (Exemption ERJXG)
- RoHS compliant

■ **As for Packaging Methods, Land Pattern, Soldering Conditions and Safety Precautions,**
Please see Data Files

Explanation of Part Numbers

- ERJXGN, 1GN, 2GE, 3GE, 6GE, 8GE, 14, 12, 12Z, 1T Type, $\pm 5\%$


	1	2	3	4	5	6	7	8	9	10	11	12
	E	R	J	3	G	E	Y	J	1	0	2	V

Product Code	Size, Power Rating			Marking		Resistance Tolerance		Packaging Methods					
Thick Film Chip Resistors	Code	Inch	Power R.	Code	Marking	Code	Tolerance	Code	Packaging	Part No.			
	XGN	01005	0.031 W	Y	Value Marking on black side	J	±5 %	Y	Pressed Carrier Taping W8P2, 20,000 pcs.	ERJXGN			
	1GN	0201	0.05 W			0	Jumper	U	Embossed Carrier Taping W4P1, 40,000 pcs.				
	2GE	0402	0.1 W	Resistance Value The first two digits are significant figures of resistance and the third one denotes number of zeros following. Decimal Point is expressed by R as 4.7 = 4R7. Jumper is expressed by R00.							C	Pressed Carrier Taping 2 mm pitch, 15,000 pcs.	ERJ1GN
	3GE	0603	0.1 W								X	Punched Carrier Taping 2 mm pitch, 10,000 pcs.	ERJ2GE
	6GE	0805	0.125 W								Y	Punched Carrier Taping 2 mm pitch, 20,000 pcs.	
	8GE	1206	0.25 W								V	Punched Carrier Taping 4 mm pitch, 5,000 pcs.	ERJ3GE ERJ6GE ERJ8GE
	14	1210	0.5 W								U	Embossed Carrier Taping 4 mm pitch, 5,000 pcs.	ERJ14 ERJ12 ERJ12Z
	12	1812	0.75 W									Embossed Carrier Taping 4 mm pitch, 4,000 pcs.	ERJ1T
	12Z	2010	0.75 W										
	1T	2512	1 W										


* When omitted, the rest of the P/N factors shall be moved up respectively.
(Only XGN, 1GN, 2GE type)

* When omitted, the rest of the P/N factors shall be moved up respectively.
(Only XGN, 1GN, 2GE type)

Construction



Dimensions in mm (not to scale)



Part No. (inch size)	Dimensions (mm)					Mass (Weight) (g/1000 pcs.)
	L	W	a	b	t	
ERJXG (01005)	0.40 $\pm$ 0.02	0.20 $\pm$ 0.02	0.10 $\pm$ 0.03	0.10 $\pm$ 0.03	0.13 $\pm$ 0.02	0.04
ERJ1G (0201)	0.60 $\pm$ 0.03	0.30 $\pm$ 0.03	0.10 $\pm$ 0.05	0.15 $\pm$ 0.05	0.23 $\pm$ 0.03	0.15
ERJ2G (0402)	1.00 $\pm$ 0.05	0.50 $\pm$ 0.05	0.20 $\pm$ 0.10	0.25 $\pm$ 0.05	0.35 $\pm$ 0.05	0.8
ERJ3G (0603)	1.60 $\pm$ 0.15	0.80 $\pm$ 0.15	0.30 $\pm$ 0.20	0.30 $\pm$ 0.15	0.45 $\pm$ 0.10	2
ERJ6G (0805)	2.00 $\pm$ 0.20	1.25 $\pm$ 0.10	0.40 $\pm$ 0.20	0.40 $\pm$ 0.20	0.60 $\pm$ 0.10	4
ERJ8G (1206)	3.20 $\pm$ 0.05	1.60 $\pm$ 0.15	0.50 $\pm$ 0.20	0.50 $\pm$ 0.20	0.60 $\pm$ 0.10	10
ERJ14 (1210)	3.20 $\pm$ 0.20	2.50 $\pm$ 0.20	0.50 $\pm$ 0.20	0.50 $\pm$ 0.20	0.60 $\pm$ 0.10	16
ERJ12 (1812)	4.50 $\pm$ 0.20	3.20 $\pm$ 0.20	0.50 $\pm$ 0.20	0.50 $\pm$ 0.20	0.60 $\pm$ 0.10	27
ERJ12Z (2010)	5.00 $\pm$ 0.20	2.50 $\pm$ 0.20	0.60 $\pm$ 0.20	0.60 $\pm$ 0.20	0.60 $\pm$ 0.10	27
ERJ1T (2512)	6.40 $\pm$ 0.20	3.20 $\pm$ 0.20	0.65 $\pm$ 0.20	0.60 $\pm$ 0.20	0.60 $\pm$ 0.10	45

Ratings

[For Resistor]

Part No. (inch size)	Power Rating at 70 °C (W)	Limiting Element Voltage ⁽¹⁾ (V)	Maximum Overload Voltage ⁽²⁾ (V)	Resistance Tolerance (%)	Resistance Range (Ω)	T.C.R. ($\times 10^{-6}/^{\circ}\text{C}$)	Category Temperature Range ($^{\circ}\text{C}$)
ERJXG (01005)	0.031	15	30	± 5	4.7 to 1 M (E24)	<10 Ω : -100 to +600 10 Ω to 100 Ω : ± 300 100 Ω <: ± 200	-55 to +125
ERJ1G (0201)	0.05	25	50	± 5	1 to 10 M (E24)	<10 Ω : -100 to +600	-55 to +125
ERJ2G (0402)	0.1	50	100	± 5	1 to 10 M (E24)		-55 to +155
ERJ3G (0603)	0.1	75	150	± 5	1 to 10 M (E24)		-55 to +155
ERJ6G (0805)	0.125	150	200	± 5	1 to 10 M (E24)		-55 to +155
ERJ8G (1206)	0.25	200	400	± 5	1 to 10 M (E24)		-55 to +155
ERJ14 (1210)	0.5	200	400	± 5	1 to 10 M (E24)	10 Ω to 1 M Ω : ± 200	-55 to +155
ERJ12 (1812)	0.75	200	500	± 5	1 to 10 M (E24)	1 M Ω <: -400 to +150	-55 to +155
ERJ12Z (2010)	0.75	200	500	± 5	1 to 10 M (E24)		-55 to +155
ERJ1T (2512)	1	200	500	± 5	1 to 1 M (E24)		-55 to +155

(1) Rated Continuous Working Voltage (RCWV) shall be determined from $\text{RCWV} = \sqrt{\text{Power Rating} \times \text{Resistance Values}}$, or Limiting Element Voltage listed above, whichever less.


(2) Overload (Short-time Overload) Test Voltage (SOTV) shall be determined from $\text{SOTV} = 2.5 \text{ (Only ERJ2G=2.0)} \times \text{RCWV}$ or max. Overload Voltage listed above whichever less.

[For Jumper]

Part No. (inch size)	Rated Current (A)	Maximum Overload Current (A)
ERJXG (01005)	0.5	1
ERJ1G (0201)		
ERJ2G (0402)		
ERJ3G (0603)	1	2
ERJ6G (0805)		
ERJ8G (1206)		
ERJ14 (1210)	2	4
ERJ12 (1812)		
ERJ12Z (2010)		
ERJ1T (2512)		

Power Derating Curve

For resistors operated in ambient temperatures above 70 °C, power rating shall be derated in accordance with the figure below.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[ERJ-12ZYJ390U](#) [ERJ-12ZYJ100U](#) [ERJ-14YJ331U](#) [ERJ-1TY0R00U](#) [ERJ-1TYJ910U](#) [ERJ-12ZYJ330U](#) [ERJ-14YJ1R6U](#) [ERJ-12ZYJ221U](#) [ERJ-12ZYJ4R7U](#) [ERJ-1TYJ301U](#) [ERJ-1TYJ560U](#) [ERJ-14YJ181U](#) [ERJ-12ZYJ473U](#) [ERJ-1TYJ133U](#) [ERJ-1TYJ821U](#) [ERJ-14YJ472U](#) [ERJ-1TYJ131U](#) [ERJ-14YJ151U](#) [ERJ-1TYJ130U](#) [ERJ-12ZYJ471U](#) [ERJ-12ZYJ1R5U](#) [ERJ-1TYJ5R1U](#) [ERJ-12YJ160U](#) [ERJ-12YJ750U](#) [ERJ-1TYJ123U](#) [ERJ-1TYJ2R4U](#) [ERJ-14YJ7R5U](#) [ERJ-1TYJ132U](#) [ERJ-1TYJ182U](#) [ERJ-1TYJ751U](#) [ERJ-XGNJ100Y](#) [ERJ-1TYJ222U](#) [ERJ-14YJ9R1U](#) [ERJ-1TYF102U](#) [ERJ-1TYJ302U](#) [ERJ-14YJ100U](#) [ERJ-14YJ101U](#) [ERJ-14YJ103U](#) [ERJ-14YJ203U](#) [ERJ-1TYJ360U](#) [ERJ-14YJ152U](#) [ERJ-14YJ750U](#) [ERJ-1TYJ200U](#) [ERJ-1TYJ363U](#) [ERJ-14YJ221U](#) [ERJ-14YJ430U](#) [ERJ-14YJ512U](#) [ERJ-12ZYJ391U](#) [ERJ-12ZYJ680U](#) [ERJ-12ZYJ750U](#) [ERJ-12ZYJ820U](#) [ERJ-12ZYJ470U](#) [ERJ-12ZYJ752U](#) [ERJ-12ZYJ112U](#) [ERJ-12ZYJ152U](#) [ERJ-12YJ102U](#) [ERJ-12YJ121U](#) [ERJ-12YJ561U](#) [ERJ-12ZYJ101U](#) [ERJ-12ZYJ102U](#) [ERJ-12ZYJ121U](#) [ERJ-12ZYJ132U](#) [ERJ-12ZYJ151U](#) [ERJ-12ZYJ154U](#) [ERJ-12ZYJ182U](#) [ERJ-12ZYJ1R0U](#) [ERJ-12ZYJ201U](#) [ERJ-12ZYJ222U](#) [ERJ-12ZYJ241U](#) [ERJ-12ZYJ272U](#) [ERJ-12ZYJ2R0U](#) [ERJ-12ZYJ331U](#) [ERJ-12ZYJ332U](#) [ERJ-12ZYJ511U](#) [ERJ-12ZYJ621U](#) [ERJ-12ZYJ622U](#) [ERJ-12ZYJ9R1U](#) [ERJ-14Y0R00U](#) [ERJ-14YJ102U](#) [ERJ-14YJ106U](#) [ERJ-14YJ121U](#) [ERJ-14YJ150U](#) [ERJ-14YJ1R0U](#) [ERJ-14YJ1R8U](#) [ERJ-14YJ220U](#) [ERJ-14YJ225U](#) [ERJ-14YJ240U](#) [ERJ-14YJ271U](#) [ERJ-14YJ302U](#) [ERJ-14YJ330U](#) [ERJ-14YJ3R3U](#) [ERJ-14YJ510U](#) [ERJ-1TYJ101U](#) [ERJ-1TYJ102U](#) [ERJ-1TYJ103U](#) [ERJ-1TYJ152U](#) [ERJ-1TYJ153U](#) [ERJ-1TYJ1R0U](#) [ERJ-1TYJ1R8U](#) [ERJ-1TYJ242U](#)