




Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

ALL METAL PARTS SILVER PLATED



NOTE: TORQUE 1 - 4 OZ. IN.

ORDERING INFORMATION

Tusonix Style	538-093
Capacitance	9.0 - 35 pF
Capacitance Tol.	SHALL MEET RATED MIN/ MAX CAPACITANCE
Dielectric Type Code	D
Voltage Rating	200 VDC TO + 85°C, 100VDC TO +125°C
DWV	500 VDC
IR Min.	10 Gohms
Operating Temperature Range:	-55°C TO + 125°C
To Tusonix Spec Unless Stated Otherwise	

X-2015 Rev-0

REVISION RECORD

0
Original Release
C.O. 20030807-2-01

TOLERANCES
unless otherwise specified

2 PLC.
DECIMAL ±
3 PLC.
DECIMAL ± .010 [0.25]

ANGLES ± 10°

TUSONIX
TUCSON, ARIZONA

Title

**CERAMIC
TRIMMER**

Drawn E.C. 08-07-03

Approved T.C. 08-07-03

A

538-093 D 9.0 - 35