




REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		PROPOSAL	Jan 17.07	L.CHAN
B		PROPOSAL	Jan 26.07	L.CHAN

NOTES:

1. MATERIALS:
HOUSING: GLASS REINFORCED HIGH TEMPERATURE THERMOPLASTIC
 FLAMMABILITY UL94V-0
 COLOUR: BLACK
CONTACTS: COPPER ALLOY.
 PLATING: 1.27 MICRONS [50 u"] MIN NICKEL UNDERPLATE OVERALL.
 0.76 MICRONS [30u"] PLATED ON MATING AREA.
 TIN ON CONTACT TAILS.
SHELL: STEEL , NICKEL PLATED.
2. TOLERANCE UNLESS INDICATED OTHERWISE: ± 0.30 [.012]. $\pm 3^\circ$.

AMPHENOL PART NUMBER: **UE32-AN0-000**

SERIES **UE3**=FIREWIRE SERIAL CONTACT
 TYPE **2**=PLUG
 NUMBER OF CONTACT **A**=6 CONTACTS
 CONFIGURATION **N**=PLUG ASSEMBLY AND SOLDER CONTACTS INSTALLED

MODIFIER **0**=STANDARD PRODUCT
 DEVIATIONS **0**=PLUG
 SHIELD DEVIATIONS **0**=PLUG
 CONTACT PLATING **0**=0.76 MICRONS [30u"]

MATERIAL	DRAWN	MT.Chen	DATE	Jan 17.07	Amphenol Canada Corp.	
	DESIGNED	L.CHAN	DATE	Jan 17.07		
	CHECKED					
	I. E. APPRD.					
SEE NOTES	Q. A. APPRD.				TITLE IEEE 1394 FIREWIRE PLUG 6 POSITION SOLDER TYPE	
	DWG. APPRD.					
PLATING	ENG. REL. NO.				DWG C	
SEE NOTES	REF. EAR #13018					DRAWING NO. P-UE32-AN0-000
		DIMENSIONS ARE IN mm	CODE ID. NO.	03554	SCALE	N/A
					WT.	-----
					SURF.	-----
					SHEET	1 OF 1