





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AJ	16	P		REVISED PER ECO-11-005030	11MAR11	RK HMR



- 1 BRASS PER ASTM B 16.
- 2 BRASS PER ASTM B 36.
- 3 COPPER PER ASTM B 152.
- 4 POLYETHYLENE PER LP-390.
- 5 POLYESTER PER MIL-T-43435, COLOR NATURAL.
- 6 GOLD PLATE PER ASTM B 488, 0.76 μm [0.000030] MINIMUM THICK.
- 7 NICKEL PLATE PER QQ-N-290, 1.27 μm [0.000050] MINIMUM THICK.
- 8 TIN PLATE PER ASTM B 545, 2.54 μm [0.000100] MINIMUM THICK.
- 9 TIN PLATE PER ASTM B 545, 3.81 μm [0.000150] MINIMUM THICK.
- 10 VALUE MARKED ON CONNECTOR BODY AS SHOWN (SEE TABLE).
- 11 16 GAUGE INSULATED GROUND WIRE.
- 12 ZINC PER ASTM B 86.

1	1%	50	50Ω 1W	C	1-5221629-6
1	1%	50	50Ω 1W	B	5221629-9
1	1%	93	93Ω 1W	B	5221629-6
1	1%	75	75Ω 1W	B	5221629-5
1	1%	50	50Ω 1W	B	5221629-4
1	1%	75	75Ω 1W	A	5221629-2
1	1%	50	50Ω 1W	A	5221629-1
WATT	TOLERANCE	OHM	MARKING 10		VIEW
RESISTOR SPECIFICATIONS			PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN J. HAVENER 13DEC2005	 TE Connectivity			
			CHK J. LIPPERT 13DEC2005				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 3.18 [-125] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -	APVD J. LIPPERT 13DEC2005	NAME TERMINATOR, PLUG, COMMERCIAL BNC			
			PRODUCT SPEC				
			APPLICATION SPEC				
			SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
			A1		00779	C=5221629	-
MATERIAL -			WEIGHT -	CUSTOMER DRAWING			
				SCALE	4:1	SHEET 1 of 1	REV P