


COMPATIBLE WITH STANDARD TTL INTEGRATED CIRCUITS


- Gallium-Arsenide-Diode Infrared Source
Optically Coupled to a Silicon npn
Phototransistor
- High Direct-Current Transfer Ratio
- High-Voltage Electrical Isolation
1.5-kV, 2.5-kV, or 3.55-kV Rating
- High-Speed Switching
 $t_r = 7 \mu s$, $t_f = 7 \mu s$ Typical
- Typical Applications Include Remote
Terminal Isolation, SCR and Triac Triggers,
Mechanical Relays and Pulse Transformers
- Safety Regulatory Approval
UL/CUL, File No. E65085

DCJ[†] OR 6-TERMINAL DUAL-IN-LINE PACKAGE
(TOP VIEW)



[†]4N35 only
NC – No internal connection

schematic



absolute maximum ratings at 25°C free-air temperature (unless otherwise noted)[†]

Input-to-output peak voltage (8-ms half sine wave):	4N35	3.55 kV
	4N36	2.5 kV
	4N37	1.5 kV
Input-to-output root-mean-square voltage (8-ms half sine wave):	4N35	2.5 kV
	4N36	1.75 kV
	4N37	1.05 kV
Collector-base voltage		70 V
Collector-emitter voltage (see Note 1)		30 V
Emitter-base voltage		7 V
Input-diode reverse voltage		6 V
Input-diode forward current: Continuous		60 mA
Peak (1 μs , 300 pps)		3 A
Phototransistor continuous collector current		100 mA
Continuous total power dissipation at (or below) 25°C free-air temperature:		
Infrared-emitting diode (see Note 2)		100 mW
Phototransistor (see Note 3)		300 mW
Continuous power dissipation at (or below) 25°C lead temperature:		
Infrared-emitting diode (see Note 4)		100 mW
Phototransistor (see Note 5)		500 mW
Operating temperature range, T_A		–55°C to 100°C
Storage temperature range, T_{stg}		–55°C to 150°C
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds		260°C

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES:
1. This value applies when the base-emitter diode is open-circuited.
 2. Derate linearly to 100°C free-air temperature at the rate of 1.33 mW/°C.
 3. Derate linearly to 100°C free-air temperature at the rate of 4 mW/°C.
 4. Derate linearly to 100°C lead temperature at the rate of 1.33 mW/°C. Lead temperature is measured on the collector lead 0.8 mm (1/32 inch) from the case.
 5. Derate linearly to 100°C lead temperature at the rate of 6.7 mW/°C.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 1998, Texas Instruments Incorporated

4N35, 4N36, 4N37 OPTOCOUPERS

SOES021C – NOVEMBER 1981 – REVISED APRIL 1998

electrical characteristics at 25°C free-air temperature (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
$V_{(BR)CBO}$ Collector-base breakdown voltage	$I_C = 100 \mu A$, $I_E = 0$, $I_F = 0$	$70^\dagger$			V
$V_{(BR)CEO}$ Collector-emitter breakdown voltage	$I_C = 10 \text{ mA}$, $I_B = 0$, $I_F = 0$	$30^\dagger$			V
$V_{(BR)EBO}$ Emitter-base breakdown voltage	$I_E = 100 \mu A$, $I_C = 0$, $I_F = 0$	$7^\dagger$			V
I_R Input diode static reverse current	$V_R = 6 \text{ V}$			$10^\dagger$	μA
I_{IO} Input-to-output current	$V_{IO} = \text{rated peak value}$, $t = 8 \text{ ms}$			100	mA
$I_{C(on)}$ On-state collector current	$V_{CE} = 10 \text{ V}$, $I_F = 10 \text{ mA}$, $I_B = 0$	$10^\dagger$			mA
	$V_{CE} = 10 \text{ V}$, $I_F = 10 \text{ mA}$, $I_B = 0$, $T_A = -55^\circ C$	$4^\dagger$			
	$V_{CE} = 10 \text{ V}$, $I_F = 10 \text{ mA}$, $I_B = 0$, $T_A = 100^\circ C$	$4^\dagger$			
$I_{C(off)}$ Off-state collector current	$V_{CE} = 10 \text{ V}$, $I_F = 0$, $I_B = 0$		1	50	nA
	$V_{CE} = 30 \text{ V}$, $I_F = 0$, $I_B = 0$, $T_A = 100^\circ C$			$500^\dagger$	μA
h_{FE} Transistor static forward current transfer ratio	$V_{CE} = 5 \text{ V}$, $I_C = 10 \text{ mA}$, $I_F = 0$		500		
V_F Input diode static forward voltage	$I_F = 10 \text{ mA}$	$0.8^\dagger$		$1.5^\dagger$	V
	$I_F = 10 \text{ mA}$, $T_A = -55^\circ C$	$0.9^\dagger$		$1.7^\dagger$	
	$I_F = 10 \text{ mA}$, $T_A = 100^\circ C$	$0.7^\dagger$		$1.4^\dagger$	
$V_{CE(sat)}$ Collector-emitter saturation voltage	$I_C = 0.5 \text{ mA}$, $I_F = 10 \text{ mA}$, $I_B = 0 \text{ mA}$			$0.3^\dagger$	V
r_{IO} Input-to-output internal resistance	$V_{IO} = 500 \text{ V}$, See Note 6	$10^{11}^\dagger$			Ω
C_{io} Input-to-output capacitance	$V_{IO} = 0$, $f = 1 \text{ MHz}$, See Note 6		1	$2.5^\dagger$	pF

† JEDEC registered data

NOTE 6: These parameters are measured between both input-diode leads shorted together and all the phototransistor leads shorted together.

switching characteristics at 25°C free-air temperature †


PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
t_{on} Time-on time	$V_{CC} = 10 \text{ V}$, $I_{C(on)} = 2 \text{ mA}$, $R_L = 100 \Omega$, See Figure 1		7	10	μs
t_{off} Turn-off time			7	10	

† JEDEC registered data




POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

PARAMETER MEASUREMENT INFORMATION



TEST CIRCUIT



VOLTAGE WAVEFORMS

- NOTES: A. The input waveform is supplied by a generator with the following characteristics: $Z_O = 50 \Omega$, $t_r \leq 15 \text{ ns}$, duty cycle $\approx 1\%$, $t_W = 100 \mu\text{s}$.
B. The output waveform is monitored on an oscilloscope with the following characteristics: $t_r \leq 12 \text{ ns}$, $R_{in} \geq 1 \text{ M}\Omega$, $C_{in} \leq 20 \text{ pF}$.

Figure 1. Switching Times

TYPICAL CHARACTERISTICS




Figure 2




Figure 3

TYPICAL CHARACTERISTICS




Figure 4




Figure 5





Figure 6



NOTE A. Pulse operation of input diode is required for operation beyond limits shown by dotted lines.


Figure 7

TYPICAL CHARACTERISTICS

ON-STATE COLLECTOR CURRENT
(RELATIVE TO VALUE AT 25°C)

VS

FREE-AIR TEMPERATURE



NOTE A. These parameters were measured using pulse techniques, $t_W = 1\text{ ms}$, duty cycle $\leq 2\%$.


Figure 8

4N35, 4N36, 4N37 OPTOCOUPERS

SOES021C – NOVEMBER 1981 – REVISED APRIL 1998

APPLICATION INFORMATION

The devices consist of a gallium-arsenide infrared-emitting diode and an npn silicon phototransistor. Each device is available in a 6-terminal plastic dual-in-line package, shown in Figure 9, or in a DCJ plastic dual surface-mount optocoupler package (see Mechanical Data).




- NOTES: A. Terminals are within 0.005 (0,13) radius of true position (T.P.) with maximum material condition and unit installed.
 B. Terminal 1 identified by index dot.
 C. The dimensions given fall within JEDEC MO-001 AM dimensions.
 D. All linear dimensions are in inches (millimeters).

Figure 9. Plastic Dual-in-Line Package

MECHANICAL DATA

DCJ (R-PDSO-G6)

PLASTIC DUAL SMALL-OUTLINE OPTOCOUPLER



- NOTES: A. All linear dimensions are in inches (millimeters)
B. This drawing is subject to change without notice.
C. Terminal 1 identified by index dot.

PACKAGING INFORMATION

Orderable Device	Status ⁽¹⁾	Package Type	Package Drawing	Pins	Package Qty	Eco Plan ⁽²⁾	Lead/Ball Finish	MSL Peak Temp ⁽³⁾
4N35	OBSOLETE	PDIP	N	6		TBD	Call TI	Call TI
4N35DCJ	OBSOLETE	OPTO	DCJ	6		TBD	Call TI	Call TI
4N36	OBSOLETE	PDIP	N	6		TBD	Call TI	Call TI
4N37	OBSOLETE	PDIP	N	6		TBD	Call TI	Call TI

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS) or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

⁽³⁾ MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DSP	dsp.ti.com	Broadband	www.ti.com/broadband
Interface	interface.ti.com	Digital Control	www.ti.com/digitalcontrol
Logic	logic.ti.com	Military	www.ti.com/military
Power Mgmt	power.ti.com	Optical Networking	www.ti.com/opticalnetwork
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
		Telephony	www.ti.com/telephony
		Video & Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments
Post Office Box 655303 Dallas, Texas 75265

Copyright © 2005, Texas Instruments Incorporated