

PU610 DG

DESCRIPTION

- Industrial protective glove.
- Synthetic coating on a synthetic textile liner.
- Elastic knit wrist to ensure snug fit.
- 5 sizes available : 6, 7, 8, 9 and 10.
- Trade unit : 10 pairs, 300 pairs in a transit case.

CHARACTERISTICS

- Glove knitted with a seamless non-stop process.
- Textile liner made of high-tenacity polyamid white yarn.
- Fine and stretchable stitches for an excellent comfort.
- PU coating on the fingertips.

PERFORMANCES

- Excellent comfort and dexterity.
- Low lint glove.
- In compliance with standards EN420 (General requirements) and EN388 (Mechanical Hazards) by the our internal laboratory.

APPLICATIONS

- Ideal for fine tactile handling, light assembly, electronics industry and photographic laboratory.

LIMITATIONS

- Do not use for handling liquids and pointed objects.
- Do not use with a rotating machine in which glove may get caught.
- Limited protection at the wrist.



This glove is certified to comply with the essential requirements of European Directive EEC/89/686 of December 21st, 1989 relative to personal protective equipment submitted to an auto-certification realised in our internal laboratory, who certifies the conformity of this glove with the EN standards to which it responds.



EN 420

EN 420

5 Dexterity



112X

EN 388
Mechanical hazards

EN 388

1 Abrasion

1 Cut

2 Tear

X Puncture

			Order codes		
Sizes	6 (XS)	7 (S)	8 (M)	9 (L)	10 (XL)
PU610 DG	181C027000	181C021000	181C022000	181C023000	181C024000



COMASEC

