




AC Adapter 12VDC/500mA

412-112054



Dimensions: in. (except where noted)

■ SPECIFICATIONS

- Primary voltage: 120VAC 60Hz 15W
- Primary exciting current: 20mA
- Primary fuse rating: 1A
- Exciting current, open circuit: 120mA max.
- DC resistance $\pm 10\%$: 125Ω
- Secondary, no load voltage: 17.7VDC
- Loaded voltage: 12VDC @ 500mA
- DC resistance $\pm 10\%$: 1Ω
- Insulation resistance: $100M\Omega$ @ 500VDC
- Dielectric strength: primary-secondary: 1,500VAC for 1 minute
primary-core: 1,500VAC for 1 minute
secondary-core: 500VAC for 1 minute
- Temperature rise: 65°C max. @ rated load
- Safety shut down temperature: $115^\circ\text{C} \pm 3^\circ\text{C}$
- Cord length: $1850\text{ mm} \pm 50\text{ mm}$ (approx. 6ft.)
- Wire gauge: 22AWG 2 conductor
- DC plug polarity: positive

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

412-112054