

Panel feed-through - CIOC 4-20-1,6-FL - 1701317

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Plug component, Nominal current: 3 A, Rated voltage (III/2): 32 V, Number of positions: 4, Pitch: 2 mm, Connection method: Insulation displacement connection QUICKON, Color: blue, Contact surface: Gold



Product Features

- ✓ Additional CIOC 3-2...-FL versions available on request
- ✓ Connection of AWG conductors with 7-strand conductor structure and PVC insulation, other conductor types can be used on request
- ✓ Conductor connection using standard pliers
- ✓ Colored, transparent hoods for checking correct contacting of the displacement connection
- ✓ Quick and reliable connection thanks to displacement connection
- ✓ Gold-plated contact system
- ✓ For sensor/actuator wiring
- ✓ Panel feed-through with CIOC ...-FL



Key commercial data

Packing unit	1 pc
Minimum order quantity	50 pc
Weight per Piece (excluding packing)	2.54 GRM
Custom tariff number	85366990
Country of origin	Japan

Technical data

Dimensions

Pitch	2 mm
Dimension a	6 mm

General

Range of articles	CIOC-FL
Rated voltage (III/2)	32 V

Panel feed-through - CIOC 4-20-1,6-FL - 1701317

Technical data

General

Connection in acc. with standard	EN-VDE
Nominal current I_N	3 A
Nominal cross section	0.5 mm ²
Maximum load current	3 A
Insulating material	PBT/PC
Inflammability class according to UL 94	V0
Number of positions	4

Connection data

Conductor cross section stranded min.	0.25 mm ²
Conductor cross section stranded max.	0.5 mm ²
Conductor cross section AWG/kcmil min.	22
Conductor cross section AWG/kcmil max	20
Wire diameter incl. insulation	1.6 mm (Terminal block is tested with PVC insulation - other insulation materials available on request)

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260705
eCl@ss 7.0	27440309
eCl@ss 8.0	27440309

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002638
ETIM 5.0	EC002638


UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409


Panel feed-through - CIOC 4-20-1,6-FL - 1701317

Drawings

Dimensioned drawing




Dimensioned drawing



$a=6.5$

Dimensioned drawing



$a=6.5$