



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	WEIGHT (APPROX.)
DP245E88TGY	1.25 lb (567 g)

NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
2. MATERIAL:
PANEL HOUSING: STEEL
RJ45 MODULE: THERMOPLASTIC RESIN UL94V-0
PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
3. 24 PORT PATCH PANEL 8 POSITION 8 WIRE.
4. THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
5. FOUR (4) 12-24 X 1 1/2" ROUND HEAD SCREWS AND (4) METRIC M6x1x15MM SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
6. DIMENSIONS IN [] ARE IN METRIC.
7. USE 110 STYLE TERMINATION TOOL FOR PUNCH DOWN.
8. RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.

PART NUMBER	DP245E88TGY		
TITLE	DP5E 24 PORT PATCH PANEL		
CUSTOMER DRAWING			
ITEM REVISION NAME	M02479JJ/00		
DATASET FILE NAME	M02479JJ_DC246/00C	MATERIAL:	PANDUIT
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			SEE NOTES
.0X ± .031 [.8]		.0XX ± .010 [.3]	
ANGLES ±		THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE
LZ	3-4-06	CEF	NONE
DRAWING NUMBER:	02479-246		
REV	DATE	BY	CHK
APR			
DESCRIPTION			SIZE
ECN			A