

TABLE 1									
DASH NO	CABLES ACCOMMODATED	A DIM	B DIM	C FLATS	D FLATS	E DIA	CABLE ENTRY DIA	ASSEMBLY PER	CABLE TYPE
-7	TRC-50-2, M17/134-00001 TRC-75-2	1.135	.096	.438	.438	.500	.274	TAI-189	TRIAx
-8	8227, BELDEN	1.716	.130	.625	.688	.750	.345	TAI-103	TWINAX
-9	TWC-78-2 TWC-124-2, M17/45-RG 308	1.135	.096	.438		.500	.285	TAI-102	
-A9	BL782, TIMES BL982, TIMES BL1242, TIMES		3	3					
-10	RG-22	1.716					.455	TAI-103	
-11	754E, AT&T 760A, AT&T						.345		TRIAx
-12	16PEVL, AT&T VI-AL, GENERAL		.130	.625	.688	.750	.485	TAI-128	
-13	TRF-59, TIMES						.362	TAI-129	
-13A	8232, BELDEN						.352	TAI-165	
-14	8233, BELDEN						.510	TAI-129	TWINAX
-23	250-3884, MICRODOT						.183	TAI-189	
-24	202-3934, MICRODOT						.191	TAI-102	
-24A	9530A5117, RAYCHEM						.200	TAI-189	
-25	T-43M, GENERAL						.285	TAI-102	TRIAx
-25A	5021H5331, RAYCHEM						.183	TAI-189	
-26	7028A5518, RAYCHEM						.145		
-27	119TPS12619EN, WOVEN 202-3927, MICRODOT 202-3942, MICRODOT						.191	TAI-102	
-29	TWC-78-1/TWC-124-1A	1.135	.096	.438	.438	.500	.235		TWINAX
-30	761A, AT&T 8441, BELDEN						.191		
-32	TRC-50-1						.217		
-33	TRC-75-1						.300	TAI-189	
-42	21-204, ESSEX 4463, CONSOLIDATED						.200		TWINAX
-43	250-4044/250-4045 293-3930, MICRODOT						.183	TAI-102	
-45	M27500-22TE2T14 1100-66F, STANDARD	1.716	.130	.625	.688	.750	.475	TAI-103	
-46	9860, BELDEN	1.135	.096	.438	.438	.500	.164	TAI-102	
-47	M17/176-00002	1.716	.130	.625	.688	.750	.132	TAI-103	TRIAx
-49	TWAC-78-1F2						.323	TAI-102	
-54	89207, BELDEN						.250		
-55	89272, BELDEN						.191	TAI-189	
-56	GC875GCI, GRUMMAN	1.135	.096	.438	.438	.500	.198	TAI-102	QUADRAx
-57	GC875GBI, GRUMMAN								
-58	GC875TM24H, GRUMMAN								
-59	GC875LNI, GRUMMAN								
-60	M17/177-00002, THERMATICS 380-10045, BOEING						.217	TAI-189	TRIAx
-64	7528A5314, RAYCHEM						.183		



DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO EMERSON CONNECTIVITY SOLUTIONS AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROMOTION OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION

REVISIONS

REV	DESCRIPTIONS	DATE	APPROVED
BS	ECO 52461	6/18/10	C. MONAHAN

TABLE 3

KEYING LETTER	F DEGREES	G DEGREES	H DEGREES	COLOR BAND
NONE	120°	120°	120°	NONE
T	100°	150°	110°	RED
U	120°	130°	110°	ORANGE
V	115°	130°	115°	YELLOW
W	125°	110°	125°	GREEN
X	130°	100°	130°	BLUE
Y	110°	140°	110°	VIOLET
Z	100°	160°	100°	GRAY
S	135°	135°	90°	WHITE



5. EXAMPLE OF COMPLETE MODEL NO:
- PL75 T -9 BR 4
- BASIC MODEL NO. BEND RELIEF (OMIT IF NOT REQD)
- POLARIZATION LETTER DASH NO (CABLE GROUP, SEE TABLE 1)
- NONE REQD FOR STD POLARIZATION (SEE TABLE 3)

4 IF BEND RELIEF SPRING REQUIRED (SEE FIG 1) ADD SUFFIX "BR" TO MODEL NUMBER (NOT AVAILABLE WITH CABLE GROUPS -8, -10, -11, -12, -13, -13A, -14, -46, & -54)

3 CLAMP NUT OMITTED

2. CONCENTRIC TWINAX/TRIAx 3-LUG TRB CABLE PLUG

1. PLATING: 310-0002-XX PER TFS-1 OR -U
- NOTES: UNLESS OTHERWISE SPECIFIED. FOR UNPLATED

INTERPRET DRAWING PER MIL-STD-100. DIMENSIONS ARE IN INCHES AND INCLUDE FINISH THICKNESS UNLESS OTHERWISE SPECIFIED.		TOL: UNLESS SPECIFIED. .XX ± .02 .XXX ± .010 ANGLE ± 1°		Connectivity Solutions 299 Johnson Ave. Ste. 100 Waseca, MN 56093 1-800-247-8256	
DRW	M. JOHNSON	3-18-09	MATERIAL:	TITLE:	
CHK	LM	4/1/09	FINISH:	PL75/T/U/V/W/ X/Y/Z/S/BR	
QUALITY					
MANUF					
APPROVED			SIZE	CAGE CODE	DRAWING NO.
SURFACE AREA		PROT FILE NO. 310-0002	DO NOT SCALE DWG	SCALE 1/1	DATE 1-12-66
				REV. BS	SHEET 1 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Emerson Connectivity Solutions:](#)

[PL75-54](#)