




SECTION A-A



DETAIL B - 90° ROTATED
(OPTIONAL DESIGN
BERG TAIWAN ONLY)

(OPTIONAL RECESS)

DETAIL C



NOTE 3


mat'l. code				surface ISO1302 ✓		tolerance ISO1101 ISO406		projection 		product family MOD JACK				
ltr		ecn nodr		date		tolerances unless otherwise specified		wiset specified		title				
N	S90142		JSR		10/4/'99		angle		0.X±0.3				4 POS VERTICAL P.C.B. MOD JACK ASSY	
P	N05-0002		YS		01/06/05		linear		0.XX±0.15					
R	N08-0170		SH WAO		10/10/08		0'±2"		0.XXX±0.05					
S	N09-0092		SH WAO		05/25/09		dr		c L FENG		02/21/97		dwg no sheet 1 of 2 size 69253 A4	
T	ELX-N-010701		SH WAO		03/14/12		engr		TONY CHIEN		02/21/97			
							chr		TONY CHIEN		02/21/97			
							appd		JENN TSAO		02/21/97		type Product Customer Drawing	
sheet		revision		T		T								
index		sheet		1		2								

PRODUCT NO.	POSITIONS LOADED	CONTACT PLATING	HOUSING COLOR	NOTES
69253-001 -001LF -011LF	ALL	5u" Au + high performance lubricant	BLACK	-
-002 -002LF -012LF	ALL	5u" Au + high performance lubricant	BLACK	-
-003 -003LF -013LF	ALL	5u" Au + high performance lubricant	BLACK	NOTE 1
-004 -004LF -014LF	ALL	50u" /1,27u GXT	BLACK	-
-005 -005LF -015LF	ALL	5u" Au + high performance lubricant	GREY	-
-006 -006LF -016LF	ALL	15u" GXT	BLACK	-

LEAD FREE PRODUCT NO.

0: MEETS WAVE SOLDER PROCESS PRODUCT NO.

1: MEETS PIP PROCESS PRODUCT NO.

BOARD LAYOUT
VIEWED FROM TOP

NOTE :

- ① SPECIAL PACKAGING.
- 2 GXT IS 0,76um / 30u" OR 0,28um / 15u" MIN GXT WITH Au FLASH OVER 1,27um / 50u" MIN Ni.
- ③ THIS PIN NUMBERING IS OPPOSITE TO FCC, PART 68, SUBPART F REQUIREMENTS.
- 4 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 5 THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MINIMUM THICK CIRCUIT BOARD.
- 6 IF LF P/N PACKAGING MEETS GS-14-920 SPECIFICATION.
- ⑦ PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code	surface ISO1302	tolerance ISO1101 ISO406	projection ISO1101	product family MOD JACK
ltn ecn nodr	date	tolerances unless otherwise specified	mm	title
N S90142 JSR 10/4/'99	angle	0.X±0.3	mm	4 POS VERTICAL
P N05-0002 YS 01/06/05	0°±2'	0.XX±0.15	scale 2.0	P.C.B. MOD JACK ASSY
R N08-0170 SH MNO 10/10/08	0°±2'	0.XXX±0.05	scale 2.0	dwg no
S N09-0092 SH MNO 05/25/09	dr C L FENG 02/21/97			sheet 2 of 2
T ELX-N-010701 SH MNO 03/14/12	engr TONY CHIEN 02/21/97			size A4
	chr TONY CHIEN 02/21/97			
	appd JENN TSAO 02/21/97			
sheet index	revision sheet			type Product Customer Drawing