

Switch Language

English

Need Assistance?

[Contact Us](#)
[Find a Distributor](#)
[Order Samples](#)
[Tech Library](#)

Printer-friendly page

Email this page

[Home](#) [Datasheet](#)

Part Number: 0191300044

Status: Active

Description: BLOCK SPADE INSULKRIMP (B-2781-06X)

Documents:

Note - Please disable browser pop-up blockers for documents on www.molex.com

[Drawing \(PDF\)](#)

Order Products:

[Check Distributor Inventory](#) [Add to My Parts](#)

Part Detail: [\(show all\)](#)

[Physical](#) [Electrical](#) [Material Info](#)

Product Family Molex Parts
Series [19130](#)

Physical

Flammability 94-V2

Electrical

CSA LR18689
UL E32244

Material Info

Old Part Number B-2781-06X



EU RoHS
ELV and RoHS Compliant

China RoHS



Need more information on product compliance?



Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[19130](#) Series

10		9		8		7		6		5		4		3		2		SD-19130-003	
F	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S" ±.005/(0.13)	PACKAGING														
	191420043	B-2781-04X	4	.119/(3.02)	LOOSE PIECE														
	191300044	B-2781-06X	6	.146/(3.71)															
	191300045	B-2781-08X	8	.173/(4.39)															
	191300046	B-2781-10X	10	.198/(5.03)															
	191420174	B-2781-04XT	4	.119/(3.02)															
	191300012	B-2781-06XT	6	.146/(3.71)															
	191300013	B-2781-08XT	8	.173/(4.39)															
191300046	B-2781-10XT	10	.198/(5.03)																



SALES DRAWING

NOTES:

1. MATERIAL: COPPER .032/.030(.81/.76) THICK.
2. PLATING: ELECTRO-TIN.
3. INSULATION: MOLDED PVC (BLUE).
5. MWID=MAXIMUM WIRE INSULATION DIAMETER.

NAME CHANGE				EC NO. ETC2002-0070				DRWN: BRE 01/09/06		CHK: RWD 01/09/06		APPR: RWD 01/09/06		DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES: (UNLESS SPECIFIED)			SCALE 4: 1		DESIGN UNITS ☐ mm ☒ INCH		 THIRD ANGLE PROJECTION		DIMENSIONS: ☐ mm ☒ INCH ☐ mm ONLY				SHT	REV	
A I		REV		MAJOR  = 0		CRITICAL  = 0		4 PLACES		±0.		±.				DRAWN BY & DATE BRE 01/08/15		CHECKED BY & DATE RWD 01/08/15		APPROVED BY & DATE RWD 01/08/15		TITLE: SPADE TONGUE TERMINAL INSULKRIMP (A1) 16-14 AWG						MOLEX INCORPORATED					
								3 PLACES		±0.		±.																					
								2 PLACES		±0.		±.																					
								1 PLACE		±0.		±.																					
								ANGULAR: ± 1/2 °				CAD FILENAME SD-19130-003.DGN																					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.										SIZE B													