

## Nut - A-INL-PG16-P-GY - 1411225

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Nut, PA 6 GF 30, For threads Pg16, Color: silver grey



### Key Commercial Data

|                        |          |
|------------------------|----------|
| Packing unit           | 1 pc     |
| Minimum order quantity | 5 pc     |
| Custom tariff number   | 39269097 |
| Country of origin      | Turkey   |

### Technical data

#### Dimensions

|                               |         |
|-------------------------------|---------|
| Length                        | 6 mm    |
| Connecting thread diameter    | 22.5 mm |
| Wrench size, counter nut      | 30 mm   |
| Hexagon angular dimension GRP | 33 mm   |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -20 °C ... 100 °C |
|---------------------------------|-------------------|

#### General

|                                        |                      |
|----------------------------------------|----------------------|
| Material                               | PA 6 GF 30           |
| Flammability rating according to UL 94 | V2                   |
| Color                                  | silver-grey RAL 7001 |
|                                        | silver grey          |

#### Standards and Regulations

|                                        |    |
|----------------------------------------|----|
| Flammability rating according to UL 94 | V2 |
|----------------------------------------|----|

## Nut - A-INL-PG16-P-GY - 1411225

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 5.1 | 27149109 |
| eCl@ss 6.0 | 27149109 |
| eCl@ss 8.0 | 23110701 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC000032 |
| ETIM 5.0 | EC000129 |

### Drawings

Dimensional drawing

