

Inductors

For Power Line SMD

NLC Series NLC3225 Type

(We currently recommend that you switch to the NLCV32 type.)

FEATURES

- The NLC series feature low DC resistance and high current handling capacities, making them ideal for power supply line applications.
- They are available in ranging from 2520 to 5650 types.

APPLICATIONS

Portable telephones, personal computers, hard disk drives, and other electronic equipment.


SPECIFICATIONS

Operating temperature range	-40 to +85°C
Storage temperature range	-40 to +85°C [Unit of products]


RECOMMENDED SOLDERING CONDITIONS

(LEAD-CONTAINING SOLDER)

REFLOW SOLDERING




FLOW SOLDERING



IRON SOLDERING

Perform soldering at 250°C on 30W max. within 5 seconds.

VAPOR-PHASING



FLUX AND CLEANING

Rosin-based flux is recommended.

Cleaning Conditions

Solvent	Please select the solvent of this product avoiding a strong acid and a strong alkali, and considering the environments.
Time	2min max.

PRODUCT IDENTIFICATION

NLC 322522 T- 2R2 M
(1) (2) (3) (4) (5)

(1) Series name

(2) Dimensions L×W×T

322522 3.2×2.5×2.2mm

(3) Packaging style

T Taping(reel)

(4) Inductance value

1R0	1μH
330	33μH

(5) Inductance tolerance

K	±10%
M	±20%

PACKAGING STYLE AND QUANTITIES

Packaging style	Quantity
Taping	2000 pieces/reel



Inductors

For Power Line SMD

NLC Series NLC3225 Type

(We currently recommend that you switch to the NLCV32 type.)

SHAPES AND DIMENSIONS/RECOMMENDED PC BOARD PATTERN



ELECTRICAL CHARACTERISTICS

Inductance (μ H)	Inductance tolerance	Q ref.	Test frequency L, Q (MHz)	Self-resonant frequency (MHz)min.	DC resistance (Ω) \pm 30%	Rated current (mA)max.	Part No.
1	\pm 20%	10	7.96	100	0.08	850	NLC322522T-1R0M
1.5	\pm 20%	10	7.96	80	0.11	700	NLC322522T-1R5M
2.2	\pm 20%	10	7.96	68	0.13	600	NLC322522T-2R2M
3.3	\pm 20%	10	7.96	54	0.16	500	NLC322522T-3R3M
4.7	\pm 20%	15	7.96	46	0.2	430	NLC322522T-4R7M
6.8	\pm 20%	15	7.96	38	0.27	360	NLC322522T-6R8M
10	\pm 10%	15	2.52	30	0.36	300	NLC322522T-100K
15	\pm 10%	15	2.52	26	0.56	250	NLC322522T-150K
22	\pm 10%	15	2.52	21	0.77	210	NLC322522T-220K
33	\pm 10%	15	2.52	17	1.1	170	NLC322522T-330K
47	\pm 10%	15	2.52	14	1.64	150	NLC322522T-470K
68	\pm 10%	15	2.52	12	2.8	120	NLC322522T-680K
100	\pm 10%	15	0.796	10	3.7	100	NLC322522T-101K
150	\pm 10%	20	0.796	8	6.1	85	NLC322522T-151K
220	\pm 10%	20	0.796	7	8.4	70	NLC322522T-221K
330	\pm 10%	20	0.796	6	12.3	60	NLC322522T-331K

• Test equipment L, Q: YHP4194A IMPEDANCE ANALYZER+YHP16085A+YHP16093B+TF-1, or equivalent


SRF: HP8753C NETWORK ANALYZER ($Z_{in}=Z_{out}=50\Omega$), or equivalent

Rdc: MATSUSHITA VP-2941A DIGITAL MILLIOHM METER, or equivalent

• Marking: Inductance tolerance is omitted to distinguish NL series.

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE CHANGE vs. DC SUPERPOSITION CHARACTERISTICS



IMPEDANCE vs. FREQUENCY CHARACTERISTICS

