

NSTB1002DXV5T1G, NSTB1002DXV5T5G

Preferred Devices

Dual Common Base-Collector Bias Resistor Transistors NPN and PNP Silicon Surface Mount Transistors with Monolithic Bias Resistor Network

The BRT (Bias Resistor Transistor) contains a single transistor with a monolithic bias network consisting of two resistors; a series base resistor and a base-emitter resistor. These digital transistors are designed to replace a single device and its external resistor bias network. The BRT eliminates these individual components by integrating them into a single device. In the NSTB1002DXV5T1G series, two complementary devices are housed in the SOT-553 package which is ideal for low power surface mount applications where board space is at a premium.

- Simplifies Circuit Design
- Reduces Board Space
- Reduces Component Count
- Available in 8 mm, 7 inch Tape and Reel
- These are Pb-Free Devices

MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted, common for Q_1 and Q_2 , – minus sign for Q_1 (PNP) omitted)

Rating	Symbol	Value		Unit
		Q1	Q2	
Collector-Base Voltage	V_{CBO}	–40	50	Vdc
Collector-Emitter Voltage	V_{CEO}	–40	50	Vdc
Collector Current	I_C	–200	100	mAdc

THERMAL CHARACTERISTICS

Characteristic (One Junction Heated)	Symbol	Max	Unit
Total Device Dissipation $T_A = 25^\circ\text{C}$ Derate above 25°C	P_D	357 (Note 1) 2.9 (Note 1)	mW mW/ $^\circ\text{C}$
Thermal Resistance – Junction-to-Ambient	$R_{\theta JA}$	350 (Note 1)	$^\circ\text{C}/\text{W}$
Characteristic (Both Junctions Heated)	Symbol	Max	Unit
Total Device Dissipation $T_A = 25^\circ\text{C}$ Derate above 25°C	P_D	500 (Note 1) 4.0 (Note 1)	mW mW/ $^\circ\text{C}$
Thermal Resistance – Junction-to-Ambient	$R_{\theta JA}$	250 (Note 1)	$^\circ\text{C}/\text{W}$
Junction and Storage Temperature	T_J, T_{stg}	–55 to +150	$^\circ\text{C}$


Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

1. FR-4 @ Minimum Pad




ON Semiconductor®

<http://onsemi.com>



1
SOT-553
CASE 463B

MARKING DIAGRAM



U9 = Specific Device Code
M = Date Code
▪ = Pb-Free Package
(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping
NSTB1002DXV5T1G	SOT-553 (Pb-Free)	4 mm pitch 4000/Tape & Reel
NSTB1002DXV5T5G	SOT-553 (Pb-Free)	2 mm pitch 8000/Tape & Reel

Preferred devices are recommended choices for future use and best overall value.

NSTB1002DXV5T1G, NSTB1002DXV5T5G

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Characteristic	Symbol	Min	Typ	Max	Unit
Q1 TRANSISTOR: PNP OFF CHARACTERISTICS					
Collector-Emitter Breakdown Voltage (Note 2)					
Collector-Base Breakdown Voltage	$V_{(\text{BR})\text{CBO}}$	-40	-	-	Vdc
Emitter-Base Breakdown Voltage	$V_{(\text{BR})\text{EBO}}$	-5.0	-	-	Vdc
Base Cutoff Current	I_{BL}	-	-50	-	nAdc
Collector Cutoff Current	I_{CEX}	-	-50	-	nAdc
ON CHARACTERISTICS (Note 2)					
DC Current Gain ($I_C = -0.1 \text{ mA}\text{dc}$, $V_{CE} = -1.0 \text{ Vdc}$) ($I_C = -1.0 \text{ mA}\text{dc}$, $V_{CE} = -1.0 \text{ Vdc}$) ($I_C = -10 \text{ mA}\text{dc}$, $V_{CE} = -1.0 \text{ Vdc}$) ($I_C = -50 \text{ mA}\text{dc}$, $V_{CE} = -1.0 \text{ Vdc}$) ($I_C = -100 \text{ mA}\text{dc}$, $V_{CE} = -1.0 \text{ Vdc}$)	h_{FE}	60 80 100 60 30	- - 300 - -	-	-
Collector-Emitter Saturation Voltage ($I_C = -10 \text{ mA}\text{dc}$, $I_B = -1.0 \text{ mA}\text{dc}$) ($I_C = -50 \text{ mA}\text{dc}$, $I_B = -5.0 \text{ mA}\text{dc}$)	$V_{CE(\text{sat})}$	- -	-0.25 -0.4	-	Vdc
Base-Emitter Saturation Voltage ($I_C = -10 \text{ mA}\text{dc}$, $I_B = -1.0 \text{ mA}\text{dc}$) ($I_C = -50 \text{ mA}\text{dc}$, $I_B = -5.0 \text{ mA}\text{dc}$)	$V_{BE(\text{sat})}$	-0.65 -	-0.85 -0.95	-	Vdc
SMALL-SIGNAL CHARACTERISTICS					
Current-Gain - Bandwidth Product	f_T	250	-	-	MHz
Output Capacitance	C_{obo}	-	4.5	-	pF
Input Capacitance	C_{ibo}	-	10.0	-	pF
Input Impedance ($V_{CE} = -10 \text{ Vdc}$, $I_C = -1.0 \text{ mA}\text{dc}$, $f = 1.0 \text{ kHz}$)	h_{ie}	2.0	12	-	k Ω
Voltage Feedback Ratio ($V_{CE} = -10 \text{ Vdc}$, $I_C = -1.0 \text{ mA}\text{dc}$, $f = 1.0 \text{ kHz}$)	h_{re}	0.1	10	-	$\times 10^{-4}$
Small-Signal Current Gain ($V_{CE} = -10 \text{ Vdc}$, $I_C = -1.0 \text{ mA}\text{dc}$, $f = 1.0 \text{ kHz}$)	h_{fe}	100	400	-	-
Output Admittance ($V_{CE} = -10 \text{ Vdc}$, $I_C = -1.0 \text{ mA}\text{dc}$, $f = 1.0 \text{ kHz}$)	h_{oe}	3.0	60	-	μmhos
Noise Figure ($V_{CE} = -5.0 \text{ Vdc}$, $I_C = -100 \mu\text{A}\text{dc}$, $R_S = 1.0 \text{ k}\Omega$, $f = 1.0 \text{ kHz}$)	nF	-	4.0	-	dB
SWITCHING CHARACTERISTICS					
Delay Time	($V_{CC} = -3.0 \text{ Vdc}$, $V_{BE} = 0.5 \text{ Vdc}$)	t_d	-	35	ns
Rise Time	($I_C = -10 \text{ mA}\text{dc}$, $I_{B1} = -1.0 \text{ mA}\text{dc}$)	t_r	-	35	
Storage Time	($V_{CC} = -3.0 \text{ Vdc}$, $I_C = -10 \text{ mA}\text{dc}$)	t_s	-	225	ns
Fall Time	($I_{B1} = I_{B2} = -1.0 \text{ mA}\text{dc}$)	t_f	-	75	
Q2 TRANSISTOR: NPN OFF CHARACTERISTICS					
Collector-Base Cutoff Current ($V_{CB} = 50 \text{ V}$, $I_E = 0$)	I_{CBO}	-	-	100	nAdc
Collector-Emitter Cutoff Current ($V_{CB} = 50 \text{ V}$, $I_B = 0$)	I_{CEO}	-	-	500	nAdc
Emitter-Base Cutoff Current ($V_{EB} = 6.0$, $I_C = 5.0 \text{ mA}$)	I_{EBO}	-	-	0.1	mAdc

2. Pulse Test: Pulse Width $\leq 300 \mu\text{s}$; Duty Cycle $\leq 2.0\%$.

NSTB1002DXV5T1G, NSTB1002DXV5T5G

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Characteristic	Symbol	Min	Typ	Max	Unit
ON CHARACTERISTICS					
Collector-Base Breakdown Voltage ($I_C = 10 \mu\text{A}$, $I_E = 0$)	$V_{(\text{BR})\text{CBO}}$	50	—	—	Vdc
Collector-Emitter Breakdown Voltage ($I_C = 2.0 \text{ mA}$, $I_B = 0$)	$V_{(\text{BR})\text{CEO}}$	50	—	—	Vdc
DC Current Gain ($V_{CE} = 10 \text{ V}$, $I_C = 5.0 \text{ mA}$)	h_{FE}	80	140	—	
Collector-Emitter Saturation Voltage ($I_C = 10 \text{ mA}$, $I_B = 0.3 \text{ mA}$)	$V_{CE(\text{SAT})}$	—	—	0.25	Vdc
Output Voltage (on) ($V_{CC} = 5.0 \text{ V}$, $V_B = 2.5 \text{ V}$, $R_L = 1.0 \text{ k}\Omega$)	V_{OL}	—	—	0.2	Vdc
Output Voltage (off) ($V_{CC} = 5.0 \text{ V}$, $V_B = 0.5 \text{ V}$, $R_L = 1.0 \text{ k}\Omega$)	V_{OH}	4.9	—	—	Vdc
Input Resistor	R_1	33	47	61	$\text{k}\Omega$
Resistor Ratio	R_1/R_2	0.8	1.0	1.2	

2. Pulse Test: Pulse Width $\leq 300 \mu\text{s}$; Duty Cycle $\leq 2.0\%$.




Figure 1. Derating Curve

NSTB1002DXV5T1G, NSTB1002DXV5T5G

TYPICAL ELECTRICAL CHARACTERISTICS — PNP TRANSISTOR




Figure 2. DC Current Gain

NSTB1002DXV5T1G, NSTB1002DXV5T5G

TYPICAL ELECTRICAL CHARACTERISTICS — NPN TRANSISTOR




Figure 3. $V_{CE(\text{sat})}$ versus I_C




Figure 4. DC Current Gain




Figure 5. Output Capacitance






Figure 6. Output Current versus Input Voltage



NSTB1002DXV5T1G, NSTB1002DXV5T5G

PACKAGE DIMENSIONS

SOT-553
XV5 SUFFIX
CASE 463B-01
ISSUE B




NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETERS
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.

DIM	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.50	0.55	0.60	0.020	0.022	0.024
b	0.17	0.22	0.27	0.007	0.009	0.011
c	0.08	0.13	0.18	0.003	0.005	0.007
D	1.50	1.60	1.70	0.059	0.063	0.067
E	1.10	1.20	1.30	0.043	0.047	0.051
e	0.50 BSC			0.020 BSC		
L	0.10	0.20	0.30	0.004	0.008	0.012
H _E	1.50	1.60	1.70	0.059	0.063	0.067

SOLDERING FOOTPRINT*



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor

P.O. Box 61312, Phoenix, Arizona 85082-1312 USA

Phone: 480-829-7710 or 800-344-3860 Toll Free USA/Canada

Fax: 480-829-7709 or 800-344-3867 Toll Free USA/Canada

Email: orderfit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051
Phone: 81-3-5773-3850

ON Semiconductor Website: <http://onsemi.com>

Order Literature: <http://www.onsemi.com/litorder>

For additional information, please contact your local Sales Representative.