





NOTES:

ELECTRICAL:

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 50 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:


1. HOUSING MATERIAL : GLASS FILLED NYLON UL94V-0.
2. CONTACT MATERIAL : PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING : GOLD PLATING OVER NICKEL.
4. OPERATING LIFE : 750 CYCLES MIN.
5. PCB RETENTION PRE-SOLDER : 1 LB MIN.
6. PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:

1. STORAGE TEMPERATURE : -40°C TO $+85^{\circ}\text{C}$.
2. OPERATION TEMPERATURE: -40°C TO $+85^{\circ}\text{C}$.
3. WAVE SOLDERING TEMPERATURE: $255\sim 265^{\circ}\text{C}$ (5~10 SECONDS)
4. RoHS COMPLIANT.

MATES WITH MODULAR PLUG CONFORMING TO
FCC PART 68, SUBPART F.

PART NUMBER	TAB	GOLD PLATING
E5908-17A132-L	TABS	6u"
E5908-17A133-L	TABS	15u"
E5908-57A132-L	TOP&SIDE& BOTTOM TABS	6u"



DETACHED LISTS	MM (INCH) TOLERANCES EXCEPT AS NOTED .0 ± 0.2 .00 ± 0.15 .000 ± 0.075 ANGLES ± 0.5		RoHS Compliant TITLE RJ45 STACKED GANGED JACK 2*2 PORTS		 Pulse A TECHNITROL COMPANY	
	 THIRD ANGLE PROJECTION		DFTO Cathy DATE 2006/09/12		DRAWING NO. CE593A93-LA /PART NO. SEE TABLE	
			SIZE A3		REV 0	
			SCALE : 1.5:1		DO NOT SCALE DRAWING	
			SHEET 1		OF 1	