

F

E

D

C

B

A

10

9

8

7

6


5

4

3

2

1


IST CIRCUIT
IDENTIFICATION

NOTES:

1. MATERIAL: GLASS-FILLED POLYESTER UL RATED 94V-0
COLOR: BLACK
2. PART TO BE USED WITH CRIMP TERMINAL
PART NUMBER 50394-8***.
3. APPLICABLE WIRE RANGE: AWG #24 - #30.
4. WIRE INSULATION RANGE: DIAMETER 1.40MM MAXIMUM.
5. 30 CKT SHOWN FOR ILLUSTRATION ONLY.

PLS REFER TO PART
51110-**-60 FOR CENTER
LATCH OPTION.

PART NO.	CKT SIZE	DIM X	DIM Y	DIM Z
51110-0450	4	2.00	4.20	NA
51110-0650	6	4.00	6.20	NA
51110-085*	8	6.00	8.20	NA
51110-105*	10	8.00	10.20	NA
51110-125*	12	10.00	12.20	NA
51110-145*	14	12.00	14.20	8.00
51110-165*	16	14.00	16.20	10.00
51110-185*	18	16.00	18.20	12.00
51110-205*	20	18.00	20.20	14.00
51110-225*	22	20.00	22.20	16.00
51110-245*	24	22.00	24.20	18.00
51110-265*	26	24.00	26.20	20.00
51110-285*	28	26.00	28.20	22.00
51110-305*	30	28.00	30.20	24.00
51110-325*	32	30.00	32.20	26.00
51110-2252	22	20.00	22.20	NA




PART NUMBER LEGEND:

51110-**-5*
CIRCUIT SIZE 0 - WITHOUT CENTER POLARIZATION
KEY AND SIDE LATCH.

1 - WITH CENTER POLARIZATION KEY
AND SIDE LATCH.
(14 TO 32 CIRCUITS ONLY)
WITH CENTER POLARIZATION KEY ONLY.
(8 TO 12 CIRCUITS ONLY)

2 - WITH CENTER POLARIZATION KEY ONLY.
(22 CIRCUITS ONLY)



9

8

7

6

5

4

3

2

1

REVISED	EC NO: S2012-0901	2012/05/31
DRWN:SKANG	2012/06/04	
CHKD:ATSEE		
APPR:MLONG	2012/06/05	
REV	DESCRIPTION	
B6		

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.20	± ---
1 PLACE	± ---	± ---
ANGULAR ± 3 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE MM ONLY	
DRAWN BY	DATE
SKTOH	1993/10/26
CHECKED BY	DATE
EDPOH	1993/10/26
APPROVED BY	DATE
JMCHAN	1993/10/26
MATERIAL NO.	
SIZE	
A3	

SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
TITLE	2MM GRID, WIRE TO BOARD CONNECTOR, CRIMP RECEPT. HOUSING	
MOLEX		MOLEX INCORPORATED
DOCUMENT NO.	SD-51110-**-5*	
SEE TABLE		SHEET NO. 1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		