

Low Power Bipolar Transistors



BC107 / BC108 Series


General Purpose Amplifier / Switches

Features:

- NPN Silicon Planar Epitaxial Transistors





TO-18 Metal Can Package



Dimensions	Minimum	Maximum
A	5.24	5.84
B	4.52	4.97
C	4.31	5.33
D	0.4	0.53
E	-	0.76
F	-	1.27
G	-	2.97
H	0.91	1.17
J	0.71	1.21
K	12.7	-
L	45°	45°

Dimensions : Millimetres



Pin Configuration:

1. Emitter
2. Base
3. Collector

Low Power Bipolar Transistors



BC107 / BC108 Series

Absolute Maximum Ratings

Description	Symbol	BC107	BC108	Unit
Collector-Emitter Voltage	V _{CEO}	45	25	V
Collector-Base Voltage	V _{CBO}	50	30	
Emitter-Base Voltage	V _{EBO}	6	5	
Collector Current Continuous	I _C	0.2		A
Power Dissipation at T _a = 25°C Derate Above 25°C	P _D	0.6 2.28		W mW / °C
Power Dissipation at T _C = 25°C Derate Above 25°C		1 6.67		
Operating and Storage Junction Temperature Range	T _J , T _{stg}	-65 to +200		°C
Thermal Resistance				
Junction to Case	R _{th (j-c)}	175		°C / W

Electrical Characteristics ($T_a = 25^\circ\text{C}$ unless otherwise specified)

Description	Symbol	Test Condition	Minimum	Maximum	Unit
Collector-Emitter Voltage	V_{CEO}	$I_C = 2 \text{ mA}, I_B = 0$ BC107 BC108	45 25	-	V
Collector-Base Voltage	V_{EBO}	$I_E = 10 \mu\text{A}, I_C = 0$ BC107 BC108	6 5	-	
Collector-Cut off Current	I_{CBO}	$V_{CB} = 45 \text{ V}, I_E = 0$ BC107	-	15	nA
		$V_{CB} = 25 \text{ V}, I_E = 0$ BC108		15	
		$T_{amb} = 125^\circ\text{C}$			
		$V_{CB} = 45 \text{ V}, I_E = 0$ BC107 $V_{CB} = 25 \text{ V}, I_E = 0$ BC108		4 4	μA
DC Current	h_{FE}	$I_C = 10 \mu\text{A}, V_{CE} = 5 \text{ V}$ B Group	40	-	-
		C Group	100	-	
		$I_C = 2 \text{ mA}, V_{CE} = 5 \text{ V}$ BC107	110	450	
		BC108	110	800	
		A Group	110	220	
		B Group C Group	200 420	450 800	
Base Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C = 10 \text{ mA}, I_B = 0.5 \text{ mA}$ $I_C = 100 \text{ mA}, I_B = 5 \text{ mA}$	-	0.83 1.05	V
Collector Emitter Saturation Voltage	$V_{CE(sat)}$		-	0.25 0.6	
Base Emitter on Voltage	$V_{BE(on)}$	$I_C = 2 \text{ mA}, V_{CE} = 5 \text{ V}$ $I_C = 10 \text{ mA}, V_{CE} = 5 \text{ V}$	0.55 -	0.7 0.77	

Low Power Bipolar Transistors

BC107 / BC108 Series



Electrical Characteristics ($T_a = 25^\circ\text{C}$ unless otherwise specified)

Description	Symbol	Test Condition	Minimum	Maximum	Unit
Collector Knee Voltage	$V_{CE(K)}$	$I_C = 10\text{ mA}$, $I_B = \text{The Value for Which } I_C = 11\text{ mA at } V_{CE} = 1\text{ V}$	-	0.6	V
Transition Frequency	f_t	$V_{CE} = 5\text{ V}$, $I_C = 10\text{ mA}$ $f = 100\text{ MHz}$	150	-	MHz
Noise Figure	NF	$V_{CE} = 5\text{ V}$, $I_C = 0.2\text{ mA}$ $R_g = 2\text{ k}\Omega$ $F = 1\text{ KHz}$, $B = 200\text{ Hz}$	-	10	dB
Output Capacitance	C_{obo}	$V_{CB} = 10\text{ V}$, $f = 1\text{ MHz}$	-	4.5	pF
Small Signal Current Gain	h_{fe}	All $f = 1\text{ KHz}$ $I_C = 2\text{ mA}$, $V_{CE} = 5\text{ V}$ BC107 BC108 A Group B Group C Group	125 125 125 240 450	500 900 260 500 900	-
Input Impedance	h_{ie}	$I_C = 2\text{ mA}$, $V_{CE} = 5\text{ V}$ A Group B Group C Group	1.6 3.2 6	4.5 8.5 15	$K\Omega$ $K\Omega$
Output Admittance	h_{oe}	$I_C = 2\text{ mA}$, $V_{CE} = 5\text{ V}$ A Group B Group C Group	-	30 60 110	umhos

Specification Table

V_{CEO} (V)	V_{CBO} Maximum (V)	I_C (V)	h_{FE} Minimum at $I_C = 2\text{ mA}$	f_T Minimum (*Typical) (V)	P_{tot} (mW)	Type	Package	Part Number
45	50	0.1	110	150	600	NPN	TO-18	BC107
			200					BC107A
								BC107B
20	30		110		300			BC108
								BC108B
			200		600			BC108C

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.