



General Description



The AON1606 utilize advanced trench MOSFET technology in small DFN 1.0 x 0.6 package. This device is ideal for load switch applications.

Product Summary

V_{DS}	20V
I_D (at $V_{GS}=4.5V$)	0.7A
$R_{DS(ON)}$ (at $V_{GS}=4.5V$)	< 275m Ω
$R_{DS(ON)}$ (at $V_{GS}=2.5V$)	< 335m Ω
$R_{DS(ON)}$ (at $V_{GS}=1.8V$)	< 390m Ω

Typical ESD protection

HBM Class 1C



Absolute Maximum Ratings $T_A=25^\circ\text{C}$ unless otherwise noted

Parameter	Symbol	Maximum	Units
Drain-Source Voltage	V_{DS}	20	V
Gate-Source Voltage	V_{GS}	± 8	V
Continuous Drain Current ^E	I_D	0.7	A
$T_A=25^\circ\text{C}$			
$T_A=70^\circ\text{C}$		0.55	
Pulsed Drain Current ^C	I_{DM}	2.8	A
Power Dissipation ^A	P_D	0.9	W
$T_A=25^\circ\text{C}$			
$T_A=70^\circ\text{C}$		0.55	
Junction and Storage Temperature Range	T_J, T_{STG}	-55 to 150	$^\circ\text{C}$

Thermal Characteristics

Parameter	Symbol	Typ	Max	Units
Maximum Junction-to-Ambient ^A	$R_{\theta JA}$	80	100	$^\circ\text{C/W}$
$t \leq 10s$				
Maximum Junction-to-Ambient ^A	$R_{\theta JA}$	110	140	$^\circ\text{C/W}$
Steady-State				
Maximum Junction-to-Ambient ^B	$R_{\theta JA}$	200	245	$^\circ\text{C/W}$
$t \leq 10s$				
Maximum Junction-to-Ambient ^B	$R_{\theta JA}$	280	340	$^\circ\text{C/W}$
Steady-State				

Electrical Characteristics (T_J=25°C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
STATIC PARAMETERS						
BV _{DSS}	Drain-Source Breakdown Voltage	I _D =250μA, V _{GS} =0V	20			V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =20V, V _{GS} =0V T _J =55°C			1 5	μA
I _{GSS}	Gate-Body leakage current	V _{DS} =0V, V _{GS} =±8V			±10	μA
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250μA	0.3	0.65	1.0	V
I _{D(ON)}	On state drain current	V _{GS} =4.5V, V _{DS} =5V	2.8			A
R _{DS(ON)}	Static Drain-Source On-Resistance	V _{GS} =4.5V, I _D =0.4A T _J =125°C		225 313	275 380	mΩ
		V _{GS} =2.5V, I _D =0.3A		265	335	mΩ
		V _{GS} =1.8V, I _D =0.2A		300	390	mΩ
		V _{GS} =1.5V, I _D =0.1A		355		mΩ
g _{FS}	Forward Transconductance	V _{DS} =5V, I _D =0.4A		2		S
V _{SD}	Diode Forward Voltage	I _S =0.4A, V _{GS} =0V		0.75	1.2	V
I _S	Maximum Body-Diode Continuous Current ^E				-0.7	A
DYNAMIC PARAMETERS						
C _{iss}	Input Capacitance	V _{GS} =0V, V _{DS} =10V, f=1MHz		62.5		pF
C _{oss}	Output Capacitance			12.5		pF
C _{rss}	Reverse Transfer Capacitance			9		pF
R _g	Gate resistance	V _{GS} =0V, V _{DS} =0V, f=1MHz		5.5		Ω
SWITCHING PARAMETERS						
Q _g	Total Gate Charge	V _{GS} =4.5V, V _{DS} =10V, I _D =0.4A		0.85		nC
Q _{gs}	Gate Source Charge			0.1		nC
Q _{gd}	Gate Drain Charge			0.25		nC
t _{D(on)}	Turn-On DelayTime	V _{GS} =4.5V, V _{DS} =10V, R _L =25Ω, R _{GEN} =3Ω		2		ns
t _r	Turn-On Rise Time			4		ns
t _{D(off)}	Turn-Off DelayTime			18		ns
t _f	Turn-Off Fall Time			8		ns

A: The value of R_{θJA} is measured with the device mounted on 1in² FR-4 board with 2oz. Copper, in a still air environment with T_A=25° C. The Power dissipation P_{DSM} is based on R_{θJA} and the maximum allowed junction temperature of 150° C. The value in any given application depends on the user's specific board design, and the maximum temperature of 150° C may be used if the PCB allows it to.

B: The value of R_{θJA} is measured with the device mounted on FR-4 minimum pad board, in a still air environment with T_A=25° C. The Power dissipation P_{DSM} is based on R_{θJA} and the maximum allowed junction temperature of 150° C. The value in any given application depends on the user's specific board design, and the maximum temperature of 150° C may be used if the PCB allows it to.

C: The static characteristics in Figures 1 to 6 are obtained using <300 μs pulses, duty cycle 0.5% max.

D: These tests are performed with the device mounted on 1 in² FR-4 board with 2oz. Copper, in a still air environment with T_A=25° C. The SOA curve provides a single pulse rating.

E: The maximum current limited by package.

THIS PRODUCT HAS BEEN DESIGNED AND QUALIFIED FOR THE CONSUMER MARKET. APPLICATIONS OR USES AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS ARE NOT AUTHORIZED. AOS DOES NOT ASSUME ANY LIABILITY ARISING OUT OF SUCH APPLICATIONS OR USES OF ITS PRODUCTS. AOS RESERVES THE RIGHT TO IMPROVE PRODUCT DESIGN, FUNCTIONS AND RELIABILITY WITHOUT NOTICE.

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




Fig 1: On-Region Characteristics (Note E)




Figure 2: Transfer Characteristics (Note E)




Figure 3: On-Resistance vs. Drain Current and Gate Voltage (Note E)




Figure 4: On-Resistance vs. Junction Temperature (Note E)




Figure 5: On-Resistance vs. Gate-Source Voltage (Note E)











Figure 6: Body-Diode Characteristics (Note E)

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS



Gate Charge Test Circuit & Waveform



Resistive Switching Test Circuit & Waveforms

