

# S60SC6M

## 60V 60A

### FEATURES

- $T_j 150^{\circ}\text{C}$
- $P_{RRSM}$  avalanche guaranteed
- Small  $\theta_{jc}$
- High current capacity


### APPLICATION

- Switching power supply
- DC/DC converter
- Home Appliances, Office Equipment
- Telecommunication

### OUTLINE DIMENSIONS

Case : MTO-3P

Unit : mm



### RATINGS

#### ● Absolute Maximum Ratings (If not specified $T_c=25^{\circ}\text{C}$ )


| Item                                  | Symbol     | Conditions                                                                        | Ratings        | Unit                    |
|---------------------------------------|------------|-----------------------------------------------------------------------------------|----------------|-------------------------|
| Storage Temperature                   | $T_{stg}$  |                                                                                   | $-40 \sim 150$ | $^{\circ}\text{C}$      |
| Operating Junction Temperature        | $T_j$      |                                                                                   | 150            | $^{\circ}\text{C}$      |
| Maximum Reverse Voltage               | $V_{RM}$   |                                                                                   | 60             | V                       |
| Repetitive Peak Surge Reverse Voltage | $V_{RRSM}$ | Pulse width 0.5ms, duty 1/40                                                      | 65             | V                       |
| Average Rectified Forward Current     | $I_o$      | 50Hz sine wave, R-load, Rating for each diode $I_o/2$ , $T_c=118^{\circ}\text{C}$ | 60             | A                       |
| Peak Surge Forward Current            | $I_{FSM}$  | 50Hz sine wave, Non-repetitive 1 cycle peak value, $T_j=125^{\circ}\text{C}$      | 500            | A                       |
| Repetitive Peak Surge Reverse Power   | $P_{RRSM}$ | Pulse width $10 \mu\text{s}$ , Rating of per diode, $T_j=25^{\circ}\text{C}$      | 1000           | W                       |
| Mounting Torque                       | TOR        | (Recommended torque: $0.5\text{N}\cdot\text{m}$ )                                 | 0.8            | $\text{N}\cdot\text{m}$ |

#### ● Electrical Characteristics (If not specified $T_c=25^{\circ}\text{C}$ )


| Item                 | Symbol        | Conditions                                                | Ratings  | Unit                        |
|----------------------|---------------|-----------------------------------------------------------|----------|-----------------------------|
| Forward Voltage      | $V_F$         | $I_F=30\text{A}$ , Pulse measurement, Rating of per diode | Max.0.67 | V                           |
| Reverse Current      | $I_R$         | $V_R=V_{RM}$ , Pulse measurement, Rating of per diode     | Max.20   | mA                          |
| Junction Capacitance | $C_j$         | $f=1\text{MHz}$ , $V_R=10\text{V}$ , Rating of per diode  | Typ.850  | pF                          |
| Thermal Resistance   | $\theta_{jc}$ | junction to case                                          | Max.0.5  | $^{\circ}\text{C}/\text{W}$ |

# S60SC6M

## Forward Voltage




# S60SC6M Junction Capacitance




# S60SC6M

## Reverse Current




## S60SC6M Reverse Power Dissipation



$T_j = 150^\circ\text{C}$



## S60SC6M Forward Power Dissipation




$T_j = 150^\circ\text{C}$



# S60SC6M


## Derating Curve



$V_R = 30V$



## S60SC6M Peak Surge Forward Capability



## SBD Repetitive Surge Reverse Power Derating Curve

