

 Design Support

Technical Documentation

 Design Resources

Design & Development Tools

Evaluation Boards

Conversion Services

Evaluation Board Documents

Custom Foundry Services

Sample Kits

Simulation Models

Product Recommendation Tools

Software

Video

Technical Support

Home > Support > Design Support > Design Resources > Evaluation Boards

NCP3102BUCK1GEVB:NCP3102 DEMO BD 100X110M

Evaluation Board Description

The NCP3102 is a high efficiency, 10 A DC-DC buck converter designed to operate from a 5 V to 12 V supply. The device is capable of producing an output voltage as low as 0.8 V. The NCP3102 can continuously output 10 A through MOSFET switches driven by an internally set 275 kHz oscillator. The 40 -pin device provides an optimal level of integration to reduce size and cost of the power supply. The NCP3102 also incorporates an externally compensated transconductance error amplifier and a capacitor programmable soft -start function. Protection features include programmable short circuit protection and under voltage lockout (UVLO).

Evaluation Board Information

Evaluation Board	Status	Pb - free	Short Description	Parts Used	Action
NCP3102BUCK1GEVB	Active	 Pb - fr	NCP3102 DEMO BD 100X110M	NCP3102MNTXG	Contact Local Sales Office

Technical Documents

Type	Document Title	Document ID/Size	Rev
Eval Board: BOM	NCP3102BUCK1GEVB Bill of Materials ROHS Compliant	NCP3102BUCK1GEVB_BOM_ROHS.PDF - 223.0 KB	1
Eval Board: Gerber	NCP3102BUCK1GEVB Gerber Layout Files (Zip Format)	NCP3102BUCK1GEVB_GERBER.ZIP - 130.0 KB	0
Eval Board: Schematic	NCP3102BUCK1GEVB Schematic	NCP3102BUCK1GEVB_SCHEMATIC.PDF - 120.0 KB	0
Eval Board: Test Procedure	NCP3102BUCK1GEVB Test Procedure	NCP3102BUCK1GEVB_TEST_PROCEDURE.PDF - 369.0 KB	1

Previously Viewed Products

Select Product ...



Clear List

Design Support

- Technical Documentation
- Design Resources
- Technical Support
- Sales Support